




Harnessing > Heat Shrink Components > Heat Shrink Boots



Molded Part Shape: 90°  
Molded Part Shape Code: 222  
Lipped: Yes  
Material Code: 4  
Material Systems Code: 10

Features

Product Type Features

|                   |     |
|-------------------|-----|
| Molded Part Shape | 90° |
|-------------------|-----|

Configuration Features

|        |     |
|--------|-----|
| Lipped | Yes |
|--------|-----|

Body Features

|                       |                              |
|-----------------------|------------------------------|
| Material Code         | 4                            |
| Material Systems Code | 10                           |
| Adhesive Pre-Coat     | Yes                          |
| Material              | Polyolefin Flexible Modified |

Dimensions

|                             |                            |
|-----------------------------|----------------------------|
| Inside Diameter as Supplied | 24 mm[.945 in]             |
| Cable Diameter Range        | 10.4 – 24 mm[.41 – .94 in] |

Usage Conditions

|                             |                            |
|-----------------------------|----------------------------|
| Operating Temperature Range | -55 – 135 °C[-67 – 275 °F] |
|-----------------------------|----------------------------|

Operation/Application

|                       |    |
|-----------------------|----|
| Power Cable Accessory | No |
|-----------------------|----|

Industry Standards

|                      |                       |
|----------------------|-----------------------|
| Approved Standards   | SAE AS81765/1 Type II |
| Government Qualified | No                    |

Other



|                           |                                   |
|---------------------------|-----------------------------------|
| Molded Part Shape Code    | 222                               |
| Fluid/Chemical Resistance | Occasional exposure to fluids     |
| Adhesive Type             | General Purpose Pre-Coat Adhesive |

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                |
|-----------------------------------------------|------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                      |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                      |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                        |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2019 (197)<br>Candidate List Declared Against: JAN 2019 (197) |
| Halogen Content                               | Not Low Halogen - contains Br or Cl > 900 ppm.                                                 |
| Solder Process Capability                     | Not applicable for solder process capability                                                   |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # CJ2087-000  
[HL2010E-KIT-120V](#)



Customers Also Bought

TE Part #322374-1  
DIAMOND GRIP 16-14 HR  
AU R 8

TE Part #  
ZPF000000000033660  
983-0SE 14-12 P8 L

TE Part #1604872-1  
BOOT,SEAL,WIRE,12 POS

TE Part #840471-000  
202F211-51-02/164-0

TE Part #935027-000  
55A1811-8-9-9CS2275

TE Part #115477-000  
55A1821-24-2/6-9CS2275

TE Part #990585-000  
55PC0221-22-2/6

TE Part #  
ZPF000000000033667  
983-0SE 14-12 S7 L

TE Part #  
ZPF000000000098385  
FDBA 50-16-21 PN-K 090  
A499

Documents

Product Drawings

222K121-4/42-0

English

Datasheets & Catalog Pages

1654025\_Sec4\_4

English

Product Specifications

Product Specification

English

Thermofit Adhesive and Sealant Thermofit S-1017

English

Thermofit Adhesive and Sealant

English

Product Environmental Compliance

Safety Datasheet





[Safety Datasheet](#)

English

[Safety Datasheet](#)

French

[Safety Datasheet](#)

German

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

English

[Safety Datasheet](#)

French

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

English

[Safety Datasheet](#)

German

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[222K121-4/42-0](#)