



Connectors > Rectangular Connectors > Connector Contacts



Contact Type: **Socket**  
Contact Mating Area Plating Material: **Gold**  
Contact Termination Area Plating Material: **Gold**  
Operating Voltage: **115 VDC**

Features

Product Type Features

Barrel Type	Crimp
Connector System	Cable-to-Cable
Wire/Cable Type	Strip
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable

Electrical Characteristics

Operating Voltage	115 VDC
-------------------	---------

Body Features

Lattice Contact Mating Area Plating Material	Gold
Material	Copper Alloy

Contact Features

Contact Type	Socket
Contact Mating Area Plating Material	Gold
Contact Termination Area Plating Material	Gold
Contact Size	20
Contact Classification	Signal
Contact Base Material	Copper Alloy
Contact Current Rating (Max)	7.5 A

Termination Features

--	--



Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Contact Retention	With
Contact Retention Type	Spring

Dimensions

Wire Size	24 – 20 AWG
-----------	-------------

Usage Conditions

Operating Temperature Range	-65 – 175 °C[-85 – 347 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal & Data
---------------------	-----------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2019 (197) Candidate List Declared Against: JAN 2019 (197)
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.



Customers Also Bought



TE Part #1577619-1  
TERMINAL RT PIDG PEEK  
STRATO 24-22 AWG



TE Part #1577633-1  
TERMINAL RT PIDG PEEK  
STRATO 18-16 AWG



TE Part #D369-P99-NS0  
369 9 WAY PLUG, NO  
CONTACTS, SKT



TE Part #  
ZPF000000000003592  
724-0001-20



TE Part #D369-R99-NP0  
369 9 WAY REC, NO  
CONTACTS, PIN



TE Part #2226454-1  
PIN INSERT, 16-02 CABLE  
APPLIED



TE Part #  
ZPF000000000003597  
724-0003-16



TE Part #1577621-1  
TERMINAL RT PIDG PEEK  
STRATO 24-22 AWG



TE Part #  
ZPF000000000200230  
724-0001-24

TE Part #  
ZPF000000000020123  
FMJ 11A 00-00 G

Documents

Datasheets & Catalog Pages  
[DEUTSCH Contacts Quick Reference Guide](#)  
English

Product Environmental Compliance  
[REACH Substance Communication Document](#)  
English

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[724-0003-20](#)