


3/8" Square Multi-Turn Fully Sealed Container Cermet Trimmer



FEATURES

- Military and professional grade
- 0.5 W at 70 °C
- Product qualification according to CECC 41101-004 (A, B, C, D, E)
- Tests according to CECC 41000 or IEC 60393-1
- GAM T1
- Fully sealed
- Operating temperature range -55 °C to +155 °C
- Wide ohmic range from 10 Ω to 2.2 MΩ
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912





RoHS
COMPLIANT

DESIGN SUPPORT TOOLS


[click logo to get started](#)
3D
Models
Available

DIMENSIONS in millimeters (± 0.5 mm)





T9XA (PM81A) A







Terminal Spacing on a 2.54 PCB







T9XB (PM81B) C






T9YA (PM82A) B



T9YB (PM82B) D





T9Z (PM83) E



Note

(1) To be measured at base level

ELECTRICAL SPECIFICATIONS	
Resistive element	Cermet
Electrical travel	21 turns \pm 2
Resistance range	10 Ω to 2.2 M Ω
Standard series E3	1 - 2.2 - 4.7 and on request 1 - 2 - 5
Tolerance	Standard 10 %
	On request 5 %
Power rating	Linear 0.5 W at +70 °C 
Circuit diagram	
Temperature coefficient	See Standard Resistance Element table
Limiting element voltage (linear law)	250 V
Contact resistance variation	2 % R _n or 2 Ω
End resistance (typical)	1 Ω
Dielectric strength (RMS)	1000 V
Insulation resistance (500 V _{DC})	10 ⁶ M Ω

MECHANICAL SPECIFICATIONS	
Mechanical travel	23 turns \pm 5
Operating torque (max. Ncm)	1.5
End stop torque	Clutch action
Net weight	Approx. 0.82 g
Wiper (actual travel)	Positioned at approx. 50 %
Terminals	Pure Sn (code e3)

ENVIRONMENTAL SPECIFICATIONS	
Temperature range	-55 °C to +155 °C
Climatic category	55/125/56
Sealing	Fully sealed - IP67

PERFORMANCES					
CECC 41100		REQUIREMENTS		TYPICAL VALUES AND DRIFTS	
TESTS	CONDITIONS	$\Delta R_T/R_T$ (%)	$\Delta R_{1-2}/R_{1-2}$ (%)	$\Delta R_T/R_T$ (%)	$\Delta R_{1-2}/R_{1-2}$ (%)
Climatic sequence	Phase A dry heat 125 °C Phase B damp heat Phase C cold -55 °C Phase D damp heat 5 cycles	± 2 %	± 3 %	± 0.5 %	± 1 %
Long term damp heat	56 days 40 °C, 93 % RH	± 2 % Dielectric strength: 700 V Insulation resistance: > 100 MΩ	± 3 %	± 0.5 % Dielectric strength: 1000 V Insulation resistance: > 10 ⁴ MΩ	± 1 %
Rotational life	200 cycles	± 2 % Contact res. variation: < 3 % R _n	-	± 2 % Contact res. variation: < 1 % R _n	-
Load life	1000 h at rated power 90'/30' - ambient temp. 70 °C	± 2 % Contact res. variation: < 3 % R _n	± 3 %	± 1 % Contact res. variation: < 1 % R _n	± 2 %
Rapid temp. change	5 cycles -55 °C to +125 °C	± 1.5 %	$\Delta V_{1-2}/V_{1-3}$ ± 1 %	± 0.5 %	$\Delta V_{1-2}/V_{1-3}$ < ± 1 %
Shock	50 g at 11 ms 3 successive shocks in 3 directions	± 1 %	± 2 %	± 0.1 %	± 0.2 %
Vibration	10 Hz to 55 Hz 0.75 mm or 10 g during 6 h	± 1 %	$\Delta V_{1-2}/V_{1-3}$ ± 2 %	± 0.1 %	$\Delta V_{1-2}/V_{1-3}$ < ± 0.2 %

Note

- Nothing stated herein shall be construed as a guarantee of quality or durability

STANDARD RESISTANCE ELEMENT DATA				
STANDARD RESISTANCE VALUES	LINEAR LAW			TYPICAL TCR -55 °C TO +125 °C
	MAX. POWER AT 70 °C	MAX. WORKING VOLTAGE	MAX. CUR. THROUGH WIPER	
Ω	W	V	mA	ppm/°C
10	0.5	2.2	224	± 100
22	0.5	3.3	150	
47	0.5	4.8	103	
100	0.5	7	70	
220	0.5	10.5	47	
470	0.5	15.3	32	
1K	0.5	22.4	22	
2.2K	0.5	33.2	15	
4.7K	0.5	48.5	10	
10K	0.5	70.7	7	
22K	0.5	105	4.8	
47K	0.5	153	3.2	
100K	0.5	224	2.2	
220K	0.28	250	1.1	
470K	0.13	250	0.53	
1M	0.06	250	0.25	
2.2M	0.028	250	0.11	

MARKING

- Vishay trademark
- Model
- Style
- Ohmic value (in Ω, kΩ, MΩ)
- Tolerance (in %)
- Manufacturing date
- Marking of terminal 3

PACKAGING

- In tube of 50 pieces code T20 (TU50)



ORDERING INFORMATION (part number)

T	9	X	A	4	7	4	K	T	2	0			
Model	STYLE			OHMIC VALUE			TOLERANCE		PACKAGING		SPECIAL NUMBER		
T9	XA XB YA YB Z			From 10 Ω to 2.2 M Ω 474 = 470 k Ω			K = 10 % on request J = 5 %		T20 = tube 50 pieces		(If applicable) Given by Vishay for custom design		

DESCRIPTION (for information only)

T9	XA	470K	10 %		TU		e3
MODEL	STYLE	VALUE	TOLERANCE	SPECIAL	PACKAGING	SPECIAL	LEAD FINISH

RELATED DOCUMENTS

APPLICATION NOTES

Potentiometers and Trimmers	www.vishay.com/doc?51001
Guidelines for Vishay Sfernice Resistive and Inductive Components	www.vishay.com/doc?52029



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

[T9Z 100 10%](#) [T9XA105KT20](#) [T9XB473KT20](#) [T9Z474KT20](#) [T9YA104KT20](#) [T9XB224KT20](#) [T9XB504KT20](#)
[T9XB223KT20](#) [T9Z101KT20](#) [T9YA221KT20](#) [T9YA501KT20](#) [T9YB103KT20](#) [T9XA474KT20](#) [T9XA223KT20](#)
[T9YB223KT20](#) [T9YA472KT20](#) [T9XA102KT20](#) [T9Z104KT20](#) [T9YB470KT20](#) [T9Z473KT20](#) [T9XA503KT20](#)
[T9Z222KT20](#) [T9YB221KT20](#) [T9YA224KT20](#) [T9XA471KT20](#) [T9YA203KT20](#) [T9YA202KT20](#) [T9Z102KT20](#)
[T9Z471KT20](#) [T9XB103KT20](#) [T9YA104JT20](#) [T9YB222KT20](#) [T9YA470KT20](#) [T9XB472KT20](#) [T9YB104KT20](#)
[T9XA224KT20](#) [T9YA223KT20](#) [T9YA103KT20](#) [T9YB201KT20](#) [T9XA502KT20](#) [T9YA105KT20](#) [T9XB471KT20](#)
[T9YB203KT20](#) [T9XB104KT20](#) [T9YA471KT20](#) [T9XA470KT20](#) [T9YA474KT20](#) [T9XA221KT20](#) [T9YB471KT20](#)
[T9YB474KT20](#) [T9Z472KT20](#) [T9XA101KT20](#) [T9YA100KT20](#) [T9YB102KT20](#) [T9XB222KT20](#) [T9Z103KT20](#)
[T9Z223KT20](#) [T9YA101KT20](#) [T9YB473KT20](#) [T9YB472KT20](#) [T9XA104KT20](#) [T9YB101KT20](#) [T9YA473KT20](#)
[T9YA102KT20](#) [T9XB102KT20](#) [T9YB224KT20](#)