


5693F-A Series PC Board, 3-Up T-1 LEDs

Description and Features



Features

- 3 T-1 LEDs tack mounted in single block saves space and as sembly time.
- High Brite and Super Brite light output.
- Standoffs prevent flux entrapment.
- Black plastic mounting block for high contrast ratio.
- Meets UL 94V-O and Bellcore flammability specifications .
- RoHS Compliant

Available options :

- Low current, 5V and 12V built-in resistors .
- Bi-color and blue LEDs also offered.
- Call factory for ordering information.

Refer to "Mounting Hole Pattern 1.pdf"

Ordering Information: Use chart below to determine model number.

	Red	Amber	Green	Yellow
LED	1	3	5	7

Model No. is as follows: 5693F Pos. 1 Pos. 2 Pos. 3 -A

Example: Position 1 is red, position 2 is yellow, position 3 is green. The part number is 5693F1_7_5-A.

Electro-Optical Characteristics and Ratings

Part Number	Emitted Color	Rated Current (mA)	Typ. Intensity (mcd)	Continuous Forward Current Max. (mA)	Forward Voltage		Reverse Breakdown Voltage Min.(V)	Peak Wavelength (nm)
					Typ. (V)	Max. (V)		
5693F1_1_1-A	Red	10	10.0	30	2.0	3.0	5.0	650
5693F3_3_3-A	Amber	10	7.0	30	2.2	3.0	5.0	603
5693F5_5_5-A	Green	10	16.0	30	2.2	3.0	5.0	562
5693F7_7_7-A	Yellow	10	6.3	30	2.1	3.0	5.0	585

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

VCC:

[5693F7;5;1](#) [5693F5;5;5-A](#) [5693F1;1;1-A](#) [5693F7;7;7-A](#) [5693F3;3;3-A](#) [5693F7;5;3-A](#) [5693F51;51;51A](#) [5693F1;7;1-A](#) [5693F1_7_1-A](#) [5693F7_5_3-A](#)