




NOTES:


- MATERIAL: BODY - THERMOPLASTIC (BLACK), UL 94-V0 RATING
LEVER - THERMOPLASTIC NYLON 6-6 FOR FLEXIBILITY, UL 94-V2 RATING
PINS - PHOSPHOR BRONZE .025" SQUARE TIN PLATE
- SPACING: DUAL ROW, 4 TO 16 CIRCUITS ON .100 x .100 CENTERS
- HEADER: MATES WITH VCC, 450 4XX SERIES, FEMALE LOCKING CONNECTOR



ORDERING CODE: **CNX VXX DRT**

PIN CONFIGURATION	
V =	VERTICAL
XX =	# OF CIRCUITS
04	2x2
06	2x3
08	2x4
10	2x5
12	2x6
14	2x7
16	2x8

STYLE	
DR	DUAL ROW
T	TIN PLATE



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ANGLES DECIMALS 1° X ±.005 XX ±.010 XXX ±.005 FINISH SHOW ALL CORNERS AND SHARP EDGES (SEE NOTE)  THIRD ANGLE PROJECTION PROPRIETARY AND CONFIDENTIAL THIS DOCUMENT IS THE SOLE PROPERTY OF VISUAL COMMUNICATIONS COMPANY, INC. AND REPRODUCTION IN PART OR AS A WHOLE, WITHOUT THE WRITTEN CONSENT OF VISUAL COMMUNICATIONS COMPANY, INC. IS PROHIBITED.		MATERIAL		VISUAL COMMUNICATIONS COMPANY, INC. 190 Bosstick Boulevard, Suite 101 San Marcos, CA 92069 USA Phone (760) 560-1300 Fax (760) 560-1301 Email: vccsales@vccite.com			
SEE NOTES		FINISH		TITLE:			
N/A		CONXRITE DUAL ROW POSITIVE LOCKING HEADER					
APPROVAL		DATE		SIZE	DWG. NO.	REV	
DRAWN K.Howard		9/13/10		B	CNX VXX DRT	001	
CHECKED DPZ		9/20/10					
DO NOT SCALE DRAWING				SCALE: 3:1		SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

VCC:

[CNXV02NTP](#) [CNXV06NTP](#) [CNXV04NTP](#) [CNXV03NTP](#) [CNXV10NTP](#) [CNXV20NTP](#) [CNXV16DRT](#) [CNXV05NTP](#)
[CNXV04DRT](#) [CNXV01NTP](#) [CNXV06DRT](#) [CNXV08DRT](#) [CNXV10DRT](#) [CNXV12DRT](#) [CNXV14DRT](#) [CNXV14NTP](#)
[CNXV08NTP](#) [CNX_V01_NTP](#) [CNX_V04_DRT](#) [CNX_V06_DRT](#) [CNX_V08_DRT](#) [CNX_V10_DRT](#) [CNX_V14_DRT](#)
[CNX_V14_NTP](#)