


NOTES:

1. ROHS COMPLIANT
2. MATERIAL:
 - PANEL CONNECTOR SOCKET - POLYESTER, UL RATING 94-V0
 - HEADER CONNECTOR - POLYESTER, UL RATING 94-V0
 - LENS - POLYCARBONATE, UL RATING 94-V2
 - MOISTURE SEAL - EPDM
 - LOCKWASHER - STEEL, NICKEL PLATE
 - TERMINALS - PHOSPHOR BRONZE, TIN PLATE
 - WIRE - 24 AWG 1007/ 1569
3. MOUNTING: HOLE SIZE - 9/16" (14.288mm) OPENING ON 3/4" (19.05mm) CENTER
4. PANEL THICKNESS: .030" (.762mm) MIN - .188" (4.775mm) MAX
5. LED LEAD LENGTH:
 - FOR BI-LEAD - TRIM TO .300"± 0.010 (7.620mm± 0.254)
 - FOR HI-FLUX - NO TRIM REQUIRED
 - FOR TRI-LEAD - CONTACT FACTORY
6. FOR DRY APPLICATIONS USE HMC 461 OR HMC 463 LENS ; FOR DUST AND WET CONDITIONS USE HMS 462 OR HMS 464 LENS (EXCEEDS NEMA 6P/ IP 67)
7. U.S. & FOREIGN PATENT ISSUED


CABLE ORDERING CODE EXAMPLE:
CNX 460 E02 4 1 12

REVISIONS					
ECN #	REV.	DESCRIPTION	DATE	INITIALS	CHK'D
	001	REVISED PER ECR 111009AZ01	11/26/10	KH	DPZ
431	001	REVISED PER ECR 050112KH01	5/9/12	KH	ED

LEDS
(ORDER SEPARATELY)



10MM BI-LEAD



10MM TRI-LEAD

TERMINATION *	
X =	STRIPPED ENDS
E =	SINGLE ROW LOCKING HEADER
D =	DUAL ROW LOCKING HEADER
02 =	2 WIRES
03 =	3 WIRES
04 =	4 WIRES


WIRE SIZE *	
4	24 AWG

WIRE COLOR *	
1	WHITE - BLACK
2	RED - BLACK
6	WHITE - BLACK - RED
0	WHITE - BLACK - RED - GREEN


WIRE LENGTH *	
04	4 INCHES (101.6mm)
06	6 INCHES (152.4mm)
08	8 INCHES (203.2mm)
12	12 INCHES (304.8mm)
18	18 INCHES (457.2mm)
24	24 INCHES (609.6mm)

* CALL FACTORY
FOR ADDITIONAL
OPTIONS


LENS
(ORDER SEPARATELY)



HMC 461
HMC 463



HMS 462
HMS 464



DIMENSION STYLE: INCHES / MM GENERAL TOLERANCES UNLESS OTHERWISE SPECIFIED: INCHES ±.500 MM ± 12.7	APPROVAL	DATE
	DRAWN KHOWARD	11/26/10
 THIRD ANGLE PROJECTION PROPRIETARY AND CONFIDENTIAL THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF VISUAL COMMUNICATIONS COMPANY, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF VISUAL COMMUNICATIONS COMPANY, INC. IS PROHIBITED.	CHECKED DPZ	11/29/10
	MATERIAL	SEE NOTES
	FINISH	SEE NOTES
	DO NOT SCALE DRAWING	

 12780 DANIELSON CT, SUITE A, POWAY, CA 92064 U.S.A PHONE: (800) 522-5546 EMAIL: vccsales@vccclite.com		
TITLE: CNX 460 CABLE ASSEMBLY		
SIZE B	DWG. NO. CNX 460 ASSY	REV 001
SCALE: 1.75:1		SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

VCC:

[CNX460-X02-4-1-08](#) [CNX460-X02-4-1-24](#) [CNX460-X02-4-1-12](#) [CNX460-X02-4-1-18](#) [CNX460-E02-4-1-12](#) [CNX460-E02-4-1-18](#) [CNX460-E02-4-1-24](#) [CNX460-E02-4-1-08](#) [CNX460E024104](#) [CNX460E024106](#) [CNX460X024104](#) [CNX460X024106](#) [CNX_460_E02_4_1_10](#) [CNX_460_X02_4_1_10](#) [CNX_460_X02_4_1_36](#) [CNX_460_X02_4_2_10](#) [CNX_460_X02_4_2_40](#) [CNX_460_X02_4_2_48](#) [CNX_460_X03_4_6_10](#)