



PMRL200 Series 0.312" (7.93mm) Recessed LED Panel Indicator



LED indicator with reflective bezel, available with single, bi-color or tri-color
Voltage: 2VDC - 120VAC, water-tight option

Key features

- Mounting hole size: 0.312" (7.93mm)
- Maximum panel thickness: .160" (PMRL200), .100" (PMRL200, water-tight)
- Recessed bezel LED
- Reflective chrome-plated body
- Voltage: 2-60 VDC or 120VAC
- Terminals: Bi-pin or wire leads (6" wire leads, 24 AWG)
- Available with a variety of LEDs including AlInGaP and InGaN technology for high brightness applications, single color, bi-color and with integrated resistors
- T-1 3/4 (5mm) LED
- Available in six LED single colors: red, amber, green, orange, blue, and white
- Available in one bi-color: red/green
- Available in two tri-color: red/amber/green or green/amber/red
- Low power consumption - uses up to 90% less energy than an incandescent indicator
- Mounts with hex nut and washer (included)
- Suitable for high vibration applications
- LEDs operate significantly cooler than traditional lamps
- Compliant with RoHS and REACH

- Reflective Chrome-Plated Body - Mounting Hardware Provided - For Detailed LED Data, See Discrete Section, MODEL 125
- Maximum Panel Thickness .160"(PMRL200); .100"(PMRL200, Water-Tight)

1 Model	Wires
PMRL200	W (optional)

TO ORDER, FOLLOW THE EXAMPLE:

Select one **BOLD** component from each numbered category in the tables below.

1 Model	Wire	2 LED	3 Voltage	4 Water Tight
PMRL200	W	-BCA	12H	

→Part Number **PMRL200W-BCA12H**

STANDARD INTENSITY - DIFFUSED ENCAPSULATION					
2 LED	Color	λpk (nm)	Iv ^[1] (mcd)	Viewing Angle	V/C Table ^[2]
-BR	RED	635	14	60	I
-BA	AMB	583	16	60	I
-BG	GRN	565	10	60	I

MEDIUM INTENSITY - TINTED ENCAPSULATION					
LED	Color	λpk (nm)	Iv ^[1] (mcd)	Viewing Angle	V/C Table ^[2]
-BCR	RED	635	120	35	I
-BCA	AMB	583	100	35	I
-BCG	GRN	565	80	24	I

HIGH INTENSITY - WATERCLEAR ENCAPSULATION					
LED	Color	λpk (nm)	Iv ^[1] (mcd)	Viewing Angle	V/C Table ^[2]
-NWR	RED	634	2800	30	I
-NWO	ORG	605	2000	30	I
-NWA	AMB	592	2800	30	I
-NWG	GRN	520	2400	45	II
-NWB	BLU	465	700	45	II
-NWW	CWHT		2500	50	II
-NWL	WWHT		1800	50	II
-NKR	RED	634	3600	15	I
-NKO	ORG	605	8000	15	I
-NKA	AMB	592	3600	15	I
-NKG	GRN	520	10000	15	II
-NKB	BLU	465	3000	15	II
-NKW	CWHT		9200	20	II
-NKL	WWHT		9200	15	II

SPECIALTY LEDs - DIFFUSED ENCAPSULATION						
LED	Color	λpk (nm)	Iv ^[1] (mcd)	Viewing Angle	V/C Table ^[3]	Description
-RLP ^[6]	RED	635	2.3	50	[3]	Low Power
-ALP ^[6]	AMB	583	2.1	50	[3]	Low Power
-GLP ^[6]	GRN	565	2.3	50	[3]	Low Power
-LRG	RED/GRN	660/565	90/40	60	I	Bi-Color, Green Cathode
-RAG ^[7]	RED/AMB/GRN	630/565	6/6/6	60	I	Tri-Color, Common Cathode
-GAR ^[7]	GRN/AMB/RED	635/565	5/5/5	50	I	Tri-Color, Common Anode

[1] Iv = typical luminous intensity @ If = 20mA(Ta = 25°C). For Low Power LEDs, If = 2mA.

[2] See Voltage/Current table for design specifications. Design current for low power LEDs = 2mA.

[3] Ta = 25°C. Voltage "2" indicates external resistor required. Voltages 5H through 60H are VDC. For AC operation, insert D after Voltage (e.g. 24HD). D indicates built-in rectifier, not required for 5H or 120VAC. DC operation not available for 120V. Bi-Color and Tri-Color not available in AC voltages.

[4] Select high intensity LEDs only


[5] Drip-proof (not submersible), supplied with two neoprene gaskets.

[6] Omit H when selecting a voltage (e.g. PMR200-RLP12).

[7] -RAG Wire Leads: green anode/black cathode/red anode. -GAR Wire Leads: green cathode/black anode/red cathode. Tri-Color 5 or 12 volt, omit H from part number.



PMRL200



Standard Wire Leads:

6.0" total length(nominal)/.50" stripped (nominal), red anode/black cathode, 24 AWG TPB UL1061 insulation. Contact factory for other lengths, gauges and colors.

All dimensions are in inches (mm)

Tolerances: .xx"(.x) \pm .025"(.63) / .xxx"(.xx) \pm .010"(.25)
Specifications are subject to change without notice.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

VCC:

[PMRL200-BR28H-WT](#) [PMRL200-BG24H-WT](#) [PMRL200W-BCA24H](#) [PMRL200-BG28H-WT](#) [PMRL200-BA24H-WT](#)
[PMRL200W-ALP28H-WT](#) [PMRL200W-BCG2-WT](#) [PMRL200W12-BG24H-WT](#) [PMRL200W24-RAG2-WT](#)
[PMRL200W36-ALP24](#) [PMRL200W-BA28H](#) [PMRL200W-RAG5H](#) [PMRL200W24-BG2-WT](#) [PMRL200W-BCG12H](#)
[PMRL200W-BR28H-WT](#) [PMRL200W-NWA15H-WT](#) [PMRL200W-NWB48H](#) [PMRL200W-NWB5H](#) [PMRL200W-BR2](#)
[PMRL200W-NWB24H](#) [PMRL200W-NWG120-WT](#) [PMRL200W-NWG28H](#) [PMRL200W-RAG2](#) [PMRL200-G120-WT](#)
[PMRL200W24-BCG24H-WT](#) [PMRL200W24-NWG28H-WT](#) [PMRL200W40-GLP2-WT](#) [PMRL200W-BA2-WT](#)
[PMRL200W-BG12H-WT](#) [PMRL200W-BG2](#) [PMRL200W-NWR28H-WT](#) [PMRL200-BA28H-WT](#) [PMRL200-BR12H-WT](#)
[PMRL200-NWB24H-WT](#) [PMRL200-RAG2-WT](#) [PMRL200W40-RLP2-WT](#) [PMRL200W-BA24H-WT](#) [PMRL200W-](#)
[BCG15H](#) [PMRL200W-BG28H](#) [PMRL200W-NWB28H-WT](#) [PMRL200W-NWB2-WT](#) [PMRL200W-NWG120](#)
[PMRL200W-NWG2-WT](#) [PMRL200W-NWL2-WT](#) [PMRL200W-NWR120](#) [PMRL200-NWB48H-WT](#) [PMRL200W24-BR2-](#)
[WT](#) [PMRL200W-BCR12H-WT](#) [PMRL200W-BCR5H-WT](#) [PMRL200W-BG15H](#) [PMRL200W-BG2-WT](#) [PMRL200W-](#)
[BR24H](#) [PMRL200W-NWA120](#) [PMRL200W-NKA2-WT](#) [PMRL200W-NWA24H-WT](#) [PMRL200W-RAG24H](#) [PMRL200-](#)
[NWB12H-WT](#) [PMRL200W40-ALP2-WT](#) [PMRL200W-BCG24HD-WT](#) [PMRL200W-BCR2-WT](#) [PMRL200W-NKA24H](#)
[PMRL200W-NKR12H-WT](#) [PMRL200W-NWG12H-WT-R-](#) [PMRL200W-NWR120-WT](#) [PMRL200W-RLP28-WT](#)
[PMRL200-NWG120-WT](#) [PMRL200-NWW24H-WT](#) [PMRL200W36-BG2](#) [PMRL200W36-RLP28H](#) [PMRL200W-BCA24H-](#)
[WT](#) [PMRL200W-BCR15H-WT](#) [PMRL200W-NWR15H-WT](#) [PMRL200-BA5H-WT](#) [PMRL200-BG48H-WT](#) [PMRL200-](#)
[BR2-WT](#) [PMRL200-NKA12H-WT](#) [PMRL200-NKG120-WT](#) [PMRL200W-BG120-WT](#) [PMRL200W-BG5H-WT](#)
[PMRL200W-GAR24H](#) [PMRL200W-NKR2-WT](#) [PMRL200W-NWG24H-WT](#) [PMRL200W-NWR12HD-WT](#) [PMRL200W24-](#)
[NWG120](#) [PMRL200W24-NWG120-WT](#) [PMRL200W36H-GLP28H](#) [PMRL200W-BCG24H-WT](#) [PMRL200W-BCG28H](#)
[PMRL200W-BCG28H-WT](#) [PMRL200W-BCA2-WT](#) [PMRL200W-BCG2](#) [PMRL200W-BCG5H](#) [PMRL200W-BG24H](#)
[PMRL200-BR24H-WT](#) [PMRL200W20-RAG2-WT](#) [PMRL200-BA2-WT](#) [PMRL200-BCG28H](#) [PMRL200-BG12H-WT](#)
[PMRL200-BG5H-WT](#) [PMRL200W-BA28H-WT](#)