

## Buffered H-Bridge

### FEATURES

- 1.0-A H-Bridge
- 200-kHz Switching Rate
- Shoot-Through Limited
- TTL Compatible Inputs
- 3.8- to 13.2-V Operating Range
- Surface Mount Packaging

### APPLICATIONS


- VCM Driver
- Brushed Motor Driver
- Stepper Motor Driver
- Power Converter
- Optical Disk Drives
- Power Supplies
- High Performance Servo

### DESCRIPTION


The Si9986 is an integrated, buffered H-bridge with TTL compatible inputs and the capability of delivering a continuous 1.0 A @  $V_{DD} = 12$  V (room temperature) at switching rates up to 200 kHz. Internal logic prevents the upper and lower outputs of either half-bridge from being turned on simultaneously. Unique input codes allow both outputs to be forced low (for braking) or forced to a high impedance level.

The Si9986 is available in both standard and lead (Pb)-free, 8-pin SOIC packages, specified to operate over a voltage range of 3.8 V to 13.2 V, and the commercial temperature range of 0 to 70°C (C suffix) and the industrial temperature range of -40 to 85°C (D suffix).

### FUNCTIONAL BLOCK DIAGRAM, PIN CONFIGURATION AND TRUTH TABLE



| TRUTH TABLE     |                 |                  |                  |
|-----------------|-----------------|------------------|------------------|
| IN <sub>A</sub> | IN <sub>B</sub> | OUT <sub>A</sub> | OUT <sub>B</sub> |
| 1               | 0               | 1                | 0                |
| 0               | 1               | 0                | 1                |
| 0               | 0               | 0                | 0                |
| 1               | 1               | HiZ              | HiZ              |



### ORDERING INFORMATION

| Part Number    | Temperature Range | Package                 |
|----------------|-------------------|-------------------------|
| Si9986CY-T1    | 0 to 70°C         | Tape and Reel           |
| Si9986DY-T1    | -40 to 85°C       |                         |
| Si9986CY-T1—E3 | 0 to 70°C         | Lead Free Tape and Reel |
| Si9986DY-T1—E3 | -40 to 85°C       |                         |
| Si9986CY       | 0 to 70°C         | Bulk (tubes)            |
| Si9986DY       | -40 to 85°C       |                         |

**ABSOLUTE MAXIMUM RATINGS<sup>a</sup>**

|                                           |                            |
|-------------------------------------------|----------------------------|
| Voltage on any pin with respect to ground | −0.3 V to $V_{DD} + 0.3$ V |
| Voltage on pins 5, 8 with respect to GND  | −1 V to $V_{DD} + 1$ V     |
| Voltage on pins 1, 4                      | −0.3 V to GND +1 V         |
| Peak Output Current                       | 1.5 A                      |
| Storage Temperature                       | −65 to 150°C               |
| Maximum Junction Temperature ( $T_J$ )    | 150°C                      |
| Maximum $V_{DD}$                          | 15 V                       |

|                                |             |
|--------------------------------|-------------|
| Power Dissipation <sup>b</sup> | 1 W         |
| $\theta_{JA}$                  | 100°C/W     |
| Operating Temperature Range    |             |
| Si9986CY                       | 0 to 70°C   |
| Si9986DY                       | −40 to 85°C |

**Notes**

- a. Device mounted with all leads soldered or welded to PC board.  
b. Derate 10 mW/°C above 25°C.

**RECOMMENDED OPERATING RANGE**







|                                        |                 |
|----------------------------------------|-----------------|
| $V_{DD}$                               | 3.8 V to 13.2 V |
| Maximum Junction Temperature ( $T_J$ ) | 125°C           |



**SPECIFICATIONS**

| Parameter                             | Symbol            | Test Conditions<br>Unless Otherwise Specified<br><br>V <sub>DD</sub> = 3.8 to 13.2 V<br>S <sub>A</sub> @ GND, S <sub>B</sub> @ GND |                            | Limits<br>C Suffix, 0 to 70°C<br>D Suffix, −40 to 85°C |                      |                  | Unit |
|---------------------------------------|-------------------|------------------------------------------------------------------------------------------------------------------------------------|----------------------------|--------------------------------------------------------|----------------------|------------------|------|
|                                       |                   |                                                                                                                                    |                            | Min <sup>a</sup>                                       | Typ <sup>b</sup>     | Max <sup>a</sup> |      |
| Input                                 |                   |                                                                                                                                    |                            |                                                        |                      |                  |      |
| Input Voltage High                    | V <sub>INH</sub>  |                                                                                                                                    |                            | 2                                                      |                      |                  | V    |
| Input Voltage Low                     | V <sub>INL</sub>  |                                                                                                                                    |                            |                                                        |                      | 1                |      |
| Input Current with Input Voltage High | I <sub>INH</sub>  |                                                                                                                                    | V <sub>IN</sub> = 2 V      |                                                        |                      | 1                | μA   |
| Input Current with Input Voltage Low  | I <sub>INL</sub>  |                                                                                                                                    | V <sub>IN</sub> = 0 V      | −1                                                     |                      |                  |      |
| Output                                |                   |                                                                                                                                    |                            |                                                        |                      |                  |      |
| Output Voltage High                   | V <sub>OUTH</sub> | I <sub>OUT</sub> = −500 mA                                                                                                         | V <sub>DD</sub> = 10.8 V   | 10.5                                                   | 10.7                 |                  | V    |
|                                       |                   |                                                                                                                                    | V <sub>DD</sub> = 4.5 V    | 4.1                                                    | 4.3                  |                  |      |
|                                       |                   | I <sub>OUT</sub> = −300 mA, V <sub>DD</sub> = 3.8 V                                                                                |                            | 3.4                                                    | 3.7                  |                  |      |
| Output Voltage Low                    | V <sub>OUTL</sub> | I <sub>OUT</sub> = 500 mA                                                                                                          | V <sub>DD</sub> = 10.8 V   |                                                        | 0.2                  | 0.3              |      |
|                                       |                   |                                                                                                                                    | V <sub>DD</sub> = 4.5 V    |                                                        | 0.2                  | 0.4              |      |
|                                       |                   | I <sub>OUT</sub> = 300 mA, V <sub>DD</sub> = 3.8 V                                                                                 |                            |                                                        | 0.1                  | 0.4              |      |
| Output Leakage Current High           | I <sub>OLH</sub>  | I <sub>NA</sub> = I <sub>NB</sub> ≥ 2 V, V <sub>OUT</sub> = V <sub>DD</sub> = 13.2 V                                               |                            | −10                                                    | 0                    |                  | μA   |
| Output Leakage Current Low            | I <sub>OLL</sub>  | V <sub>OUT</sub> = 0, V <sub>DD</sub> = 13.2 V                                                                                     |                            |                                                        | 0                    | 10               |      |
| Output V Clamp High                   | V <sub>CLH</sub>  | I <sub>NA</sub> = I <sub>NB</sub> ≥ 2 V                                                                                            | I <sub>OUT</sub> = 100 mA  |                                                        | V <sub>DD</sub> +0.7 |                  | V    |
| Output V Clamp Low                    | V <sub>CLL</sub>  |                                                                                                                                    | I <sub>OUT</sub> = −100 mA |                                                        | −0.7                 |                  |      |
| Supply                                |                   |                                                                                                                                    |                            |                                                        |                      |                  |      |
| V <sub>DD</sub> Supply Current        | I <sub>DD</sub>   | I <sub>N</sub> = 100 kHz, V <sub>DD</sub> = 5 V                                                                                    |                            |                                                        | 2                    |                  | mA   |
|                                       |                   | I <sub>NA</sub> = I <sub>NB</sub> = 4.5 V, V <sub>DD</sub> = 5.5 V                                                                 |                            |                                                        |                      | 300              | μA   |
| Dynamic                               |                   |                                                                                                                                    |                            |                                                        |                      |                  |      |
| Propogation Delay Time                | T <sub>PLH</sub>  | V <sub>DD</sub> = 5 V                                                                                                              |                            |                                                        | 300                  |                  | nS   |
|                                       | T <sub>PHL</sub>  |                                                                                                                                    |                            |                                                        | 100                  |                  |      |

**Notes**

- a. The algebraic convention whereby the most negative value is a minimum and the most positive a maximum, is used in this data sheet.  
b. Typical values are for DESIGN AID ONLY, not guaranteed nor subject to production testing.

**TYPICAL CHARACTERISTICS (25°C UNLESS NOTED)**

**TYPICAL CHARACTERISTICS (25 °C UNLESS NOTED)**



### Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

[SI9986DY](#) [SI9986CY](#) [SI9986CY-T1-E3](#) [SI9986CY-T1](#) [SI9986DY-T1](#) [SI9986DY-T1-E3](#)