

# Metal Film Resistors, Industrial Power, Precision, Flameproof



## FEATURES

- High power rating, small size
- Flameproof, high temperature coating
- Special filming and coating processes
- Excellent high frequency characteristics
- Low noise
- Low voltage coefficient
- Compliant to RoHS directive 2002/95/EC



**RoHS\***  
COMPLIANT

## STANDARD ELECTRICAL SPECIFICATIONS

GLOBAL MODEL	HISTORICAL MODEL	POWER RATING $P_{70^\circ\text{C}}$ W	MAXIMUM WORKING VOLTAGE <sup>(1)</sup> V	RESISTANCE RANGE $\Omega$					
				0.1 % to 1 %	0.1 % to 5 %	0.5 % to 5 %	1 % to 5 %	1 %	2 % to 5 %
CPF1	CPF-1	1	250	5 to 150K	5 to 150K	1 to 150K	0.5 to 150K	0.5 to 150K	0.1 to 150K
CPF2	CPF-2	2	350	5 to 150K	5 to 150K	1 to 150K	0.5 to 150K	0.5 to 150K	0.1 to 150K
CPF3	CPF-3	3	500	8 to 150K	8 to 150K	1 to 150K	1 to 150K	1 to 150K	0.1 to 150K

### Notes

- Marking: Print marked - DALE, model, resistance value, tolerance/temperature coefficient, date code

(1) Continuous working voltage shall be  $\sqrt{P \times R}$  or maximum working voltage, whichever is less.

## TEMPERATURE COEFFICIENT CODES

GLOBAL TC CODE	HISTORICAL TC CODE	TEMPERATURE COEFFICIENT
E	T-9	25 ppm/ $^\circ\text{C}$
H	T-2	50 ppm/ $^\circ\text{C}$
K	T-1	100 ppm/ $^\circ\text{C}$
L	T-0	150 ppm/ $^\circ\text{C}$
N	T-00	200 ppm/ $^\circ\text{C}$

## TECHNICAL SPECIFICATIONS

PARAMETER	UNIT	CPF1	CPF2	CPF3
Rated Dissipation at 70 °C	W	1	2	3
Limiting Element Voltage <sup>(1)</sup>	V $\geq$	250	350	500
Insulation Voltage	V-	900	900	900
Thermal Resistance	K/W	85	60	50
Insulation Resistance	$\Omega$		$10^{10}$	
Category Temperature Range	°C		- 65 °C/+ 230 °C	

### Note

(1) Rated voltage  $\sqrt{P \times R}$

## GLOBAL PART NUMBER INFORMATION


New Global Part Numbering: CPF1562R00FKR36 (preferred part numbering format)

C	P	F	1	5	6	2	R	0	0	F	K	R	3	6		
GLOBAL MODEL	RESISTANCE VALUE	TOLERANCE CODE	TEMPERATURE COEFFICIENT	PACKAGING	SPECIAL											
CPF1	R = $\Omega$ K = $\text{k}\Omega$ R10000 = 0.1 $\Omega$ 10R000 = 10 $\Omega$ 150K00 = 150 $\text{k}\Omega$	B = $\pm 0.1\%$ C = $\pm 0.25\%$ D = $\pm 0.5\%$ F = $\pm 1\%$ G = $\pm 2\%$ J = $\pm 5\%$	E = 25 ppm H = 50 ppm K = 100 ppm L = 150 ppm N = 200 ppm	E14 = Lead (Pb)-free, bulk E36 = Lead(Pb)-free, T/R (full) EE6 = Lead (Pb)-free, T/R (1000 pieces) B14 = Tin/lead, bulk R36 = Tin/lead, T/R (full) RE6 = Tin/lead, T/R (1000 pieces)	Blank = Standard (Dash Number) (Up to 3 digits) From 1 to 999 as applicable											
CPF2																
CPF3																

Historical Part Number example: CPF-1562FT-1 R36 (will continue to be accepted)

CPF-1	5620	F	T-1	R36
HISTORICAL MODEL	RESISTANCE VALUE	TOLERANCE CODE	TEMP. COEFFICIENT	PACKAGING



\* Pb containing terminations are not RoHS compliant, exemptions may apply

**DIMENSIONS**

**Notes**

(1)  $1.08 \pm 0.125$  ( $27.43 \pm 3.18$ ) if tape and reel

- Surface temperatures were taken with an infrared pyrometer in + 25 °C still air. Resistors were supported by their leads in test clips at a point 0.500" (12.70 mm) out from the resistor body ends.

GLOBAL MODEL	DIMENSIONS in inches (millimeters)			
	L	D	L <sub>1</sub> max.	d
CPF1	$0.240 \pm 0.020$ ( $6.10 \pm 0.51$ )	$0.090 \pm 0.008$ ( $2.29 \pm 0.20$ )	0.310 (7.87)	$0.025 \pm 0.002$ ( $0.64 \pm 0.05$ )
CPF2	$0.344 \pm 0.031$ ( $8.74 \pm 0.79$ )	$0.145 \pm 0.015$ ( $3.68 \pm 0.38$ )	0.425 (10.80)	$0.032 \pm 0.002$ ( $0.81 \pm 0.05$ )
CPF3	$0.555 \pm 0.041$ ( $14.10 \pm 1.04$ )	$0.180 \pm 0.015$ ( $4.57 \pm 0.381$ )	0.650 (16.51)	$0.032 \pm 0.002$ ( $0.81 \pm 0.05$ )


**THERMAL RESISTANCE**

**DERATING**

MATERIAL SPECIFICATIONS	
Element	Proprietary nickel-chrome alloy
Core	Cleaned high purity ceramic
Coating	Special high temperature conformal coat
Termination	Standard lead material is solder-coated Solderable and weldable per MIL-STD-1276, Type C

MECHANICAL SPECIFICATIONS	
Terminal Strength	2 pound pull test
Solderability	Continuous satisfactory coverage when tested in accordance with MIL-STD-202, Method 208

PERFORMANCE	
TEST	MAX. $\Delta R$ (Typical Test Lots)
Thermal Shock	± 1.0 %
Short Time Overload	± 0.5 %
Low Temperature Operation	± 0.5 %
Moisture Resistance	± 1.5 %
Resistance To Soldering Heat	± 0.5 %
Shock	± 0.5 %
Vibration	± 0.5 %
Terminal Strength	± 0.5 %
Dielectric Withstanding Voltage	± 0.5 %
Life	± 2.0 %

## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay](#):

[CPF1R51000FLE14](#) [CPF3470R00FKE14](#)