


Wirewound Resistors, Precision Power, Surface Mount



LINKS TO ADDITIONAL RESOURCES



FEATURES

- All welded construction
- Molded encapsulation
- Wraparound terminations
- Excellent stability at different environmental conditions
- High power ratings (up to 3 W)
- Superior surge capability
- Available in non-inductive styles with Ayrton-Perry winding (WSN in lieu of WSC, maximum resistance is one-half WSC range)
- AEC-Q200 qualified ⁽¹⁾
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



Notes

- This datasheet provides information about parts that are RoHS-compliant and / or parts that are non-RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details
- Follow link to Overview of Automotive Grade Products for more details: www.vishay.com/doc?49924
- ⁽¹⁾ Flame retardance test may not be applicable to some resistor technologies

STANDARD ELECTRICAL SPECIFICATIONS

GLOBAL MODEL	HISTORICAL MODEL	SIZE	POWER RATING $P_{70\text{ }^{\circ}\text{C}}$ W	RESISTANCE RANGE Ω	TOLERANCE $\pm \%$	WEIGHT (typical) g/1000 pieces	ENCAPSULATION
WSC01/2	WSC-1/2	2012	0.5	0.1 to 4.99	0.5, 1, 5	90	Epoxy
WSC0001 ⁽²⁾	WSC-1	2515	1	0.1 to 2.77K	0.5, 1, 5	165	Thermoplastic ⁽¹⁾
WSC2515	WSC2515	2515	1	0.1 to 2.5K	0.5, 1, 5	165	Thermoplastic
WSC0002	WSC-2	4527	2	0.1 to 4.92K	0.5, 1, 5	760	Thermoplastic ⁽¹⁾
WSC4527	WSC4527	4527	2	0.1 to 4.92K	0.5, 1, 5	760	Thermoplastic
WSC6927	WSC6927	6927	3	0.1 to 8K	0.5, 1, 5	1675	Thermoplastic

Notes

- Part marking: 1/2 W - DALE, value; 1 W - model, value, tolerance, date code; 2 W and 3 W - DALE, model, value, tolerance, date code
- ⁽¹⁾ As of 1/1/2010, the WSC0001 and WSC0002 are molded with thermoplastic in lieu of epoxy. Reference PCN-DR-002-2009 and PCN-DR-003-2009
- ⁽²⁾ As of February 19, 2016, the WSC0001 was obsolete by PCN-DR-013-2015; the WSC2515 is a drop-in replacement. You may contact your sales representative or submit an inquiry via ww2bresistors@vishay.com for supporting information

TECHNICAL SPECIFICATIONS

PARAMETER	UNIT	WSC01/2	WSC2515	WSC0002	WSC4527, WSC6927
Temperature coefficient measured from -55 °C to +150 °C	ppm/°C	± 50 = 1.0 Ω to 4.99 Ω; ± 90 = 0.1 Ω to 0.99 Ω	± 20 = 26.51 Ω and above; ± 50 = 1.0 Ω to 26.5 Ω; ± 90 = 0.31 Ω to 0.99 Ω; ± 150 = 0.1 Ω to 0.3 Ω	± 20 = 10.0 Ω and above; ± 50 = 1.0 Ω to 9.9 Ω; ± 90 = 0.1 Ω to 0.99 Ω	± 20 = 10 Ω and above; ± 50 = 1.0 Ω to 9.9 Ω; ± 90 = 0.31 Ω to 0.99 Ω; ± 150 = 0.1 Ω to 0.3 Ω
Dielectric withstanding voltage	V _{AC}	> 500			
Insulation resistance	Ω	> 10 ⁹			
Operating temperature range	°C	-65 to +175	-65 to +175		
Maximum working voltage	V	(P x R) ^{1/2}			

GLOBAL PART NUMBER INFORMATION


Global Part Numbering Example: WSC2515R7000FEA (visit www.vishay.net Vishay Dale parts numbering manual for all options)

W	S	C	2	5	1	5	R	7	0	0	0	F	E	A		
GLOBAL MODEL		SIZE		VALUE ⁽¹⁾		TOLERANCE		PACKAGING				SPECIAL				
WSC WSN		01/2 2515 0002 4527 6927		R = decimal K = thousand R7000 = 0.70 Ω 1K500 = 1.5 kΩ		D = ± 0.5 % F = ± 1.0 % G = ± 2.0 % H = ± 3.0 % J = ± 5.0 % K = ± 10 %		EA = lead (Pb)-free, tape / reel EK = lead (Pb)-free, bulk TA = tin / lead, tape / reel (R86) BA = tin / lead, bulk (B43)				(dash number) (up to 2 digits) from 1 to 99 as applicable				

Notes

⁽¹⁾ WSC / WSN marking (www.vishay.com/doc?30327)



- Packaging code: EB (lead (Pb)-free) and TB (tin / lead) are non-standard packaging codes designating 1000 piece reels. These non-standard packaging codes are identical to our standard EA (lead (Pb)-free) and TA (tin / lead), except that they have a package quantity of 1000 pieces


DIMENSIONS in inches (millimeters)


GLOBAL MODEL	DIMENSIONS					SOLDER PAD DIMENSIONS		
	L	H	T	W	W ₁	a	b	L
WSC01/2	0.200 $\pm$ 0.020 (5.08 $\pm$ 0.508)	0.096 $\pm$ 0.015 (2.44 $\pm$ 0.381)	0.040 $\pm$ 0.010 (1.02 $\pm$ 0.254)	0.125 $\pm$ 0.005 (3.18 $\pm$ 0.127)	0.050 $\pm$ 0.010 (1.27 $\pm$ 0.254)	0.085 (2.16)	0.070 (1.78)	0.080 (2.03)
WSC2515	0.250 $\pm$ 0.020 (6.35 $\pm$ 0.508)	0.110 $\pm$ 0.015 (2.79 $\pm$ 0.381)	0.045 $\pm$ 0.010 (1.14 $\pm$ 0.254)	0.150 $\pm$ 0.005 (3.81 $\pm$ 0.127)	0.098 $\pm$ 0.010 (2.49 $\pm$ 0.254)	0.090 (2.29)	0.115 (2.92)	0.120 (3.05)
WSC0002	0.455 $\pm$ 0.020 (11.56 $\pm$ 0.508)	0.167 $\pm$ 0.010 (4.24 $\pm$ 0.254)	0.100 $\pm$ 0.010 (2.54 $\pm$ 0.254)	0.275 $\pm$ 0.005 (6.98 $\pm$ 0.127)	0.215 $\pm$ 0.005 (5.46 $\pm$ 0.127)	0.155 (3.94)	0.230 (5.84)	0.205 (5.21)
WSC4527	0.455 $\pm$ 0.020 (11.56 $\pm$ 0.508)	0.167 $\pm$ 0.010 (4.24 $\pm$ 0.254)	0.100 $\pm$ 0.010 (2.54 $\pm$ 0.254)	0.275 $\pm$ 0.005 (6.98 $\pm$ 0.127)	0.215 $\pm$ 0.005 (5.46 $\pm$ 0.127)	0.155 (3.94)	0.230 (5.84)	0.205 (5.21)
WSC6927	0.690 $\pm$ 0.032 (17.53 $\pm$ 0.813)	0.280 $\pm$ 0.015 (7.11 $\pm$ 0.381)	0.100 $\pm$ 0.010 (2.54 $\pm$ 0.254)	0.275 $\pm$ 0.005 (6.98 $\pm$ 0.127)	0.215 $\pm$ 0.015 (5.46 $\pm$ 0.381)	0.155 (3.94)	0.235 (5.97)	0.470 (11.94)

Notes

- 3D models available: www.vishay.com/doc?30328
- Surface mount solder profile recommendations: www.vishay.com/doc?31052
- Refer to WSC, WSN conversion guide for detailed construction drawings: www.vishay.com/doc?49616
- For WSC2515 0.5 % tolerance parts, W₁ terminal dimension will be 0.090" $\pm$ 0.015"

TEMPERATURE RISE

DERATING


**PULSE CAPABILITY**

www.vishay.com/resistors/SMD-wirewound-pulse-capability-calculator/

Note

- Pulse capability increases based on the amount of wire for the resistance value and construction. The WSC0002 has greater pulse capability than WSC4527 due to differences in internal construction. The non-inductive WSN has greater pulse capability for the same size WSC because the second layer of wire increases the wire mass available to withstand pulse energy without exceeding temperature limits. Follow pulse graphic link for more information regarding capability

PERFORMANCE		
TEST	CONDITIONS OF TEST	TEST LIMITS
Thermal shock	-55 °C to +150 °C, 1000 cycles, 15 min at each extreme	± 0.5 % + 0.05 Ω
Short time overload	5 x rated power for 5 s	± 0.2 % + 0.05 Ω
Low temperature storage	-65 °C for 24 h	± 0.2 % + 0.05 Ω
High temperature exposure	1000 h at +175 °C	± 0.5 % + 0.05 Ω
Bias humidity	+85 °C, 85 % RH, 10 % bias, 1000 h	± 0.2 % + 0.05 Ω
Mechanical shock	100 g's for 6 ms, 5 pulses	± 0.1 % + 0.05 Ω
Vibration	Frequency varied 10 Hz to 500 Hz in 1 min, 3 directions, 9 h	± 0.1 % + 0.05 Ω
Load life	1000 h at rated power, +70 °C, 1.5 h "ON", 0.5 h "OFF"	± 1.0 % + 0.05 Ω
Resistance to solder heat	+260 °C solder, 10 s to 12 s dwell, 25 mm/s emergence	± 0.5 % + 0.05 Ω

PACKAGING				
MODEL	REEL			
	TAPE WIDTH	DIAMETER	PIECES/REEL	CODE
WSC01/2	12 mm / embossed plastic	330 mm / 13"	2000	EA / TA
WSC2515	16 mm / embossed plastic	330 mm / 13"	2000	EA / TA
WSC0002, WSC4527	24 mm / embossed plastic	330 mm / 13"	1200	EA / TA
WSC6927	32 mm / embossed plastic	330 mm / 13"	725	EA / TA

Notes

- Embossed carrier tape per EIA-481
- Additional packaging details at www.vishay.com/doc?20051



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

WSC00024K020FTA	WSC01\22R000FTB	WSC000130R10FBA	WSC000262R00FTA	WSC0002174R0FTA
WSC0002150R0FTA	WSC0002154R0FTA	WSC000227R40FTA	WSC000225R50FTA	WSC01\2R4000FTB
WSC01\21R210FTB	WSC45272K000FEB	WSC0001R2500FTB	WSC2515243R0FTA	WSC00021K500FTA
WSC00022R200FTA	WSC00022R000FTA	WSC00022R700FTA	WSC00022R800FTA	WSC00022R500FTA
WSC00022R430FTA	WSC00022R490FTA	WSC00022R740FTA	WSC0002200R0FTA	WSC000122R00FTB
WSC000115R00FTB	WSC4527400R0FEB	WSC000120R00FTB	WSC000147R00FBA	WSC000113R70FBA
WSC452720R00DBA	WSC45271R000FEB	WSC000249R90FBA	WSC01\21R000FTB	WSC00024K530FTA
WSC25151R000FEB	WSC45275R000FEB	WSC000225R00FTA	WSC000222R00FTA	WSC000224R00FTA
WSC0001180R0FTB	WSC000220R00FTA	WSC00015R110FTB	WSC01\22R700FTB	WSC01\22R300FTB
WSC01\2R1500FTB	WSC00021K000FTA	WSC00022K000FTA	WSC000213R70FTA	WSC00021K740FTA
WSC00023K740FTA	WSC000241R00JTA	WSC000211R00JTA	WSC00021R210FTA	WSC0002R5000FTA
WSC45271K000FEB	WSC000216R20FTA	WSC0002820R0FTA	WSC00028R200FTA	WSC0002866R0FTA
WSC00011K000FTB	WSC00026R800FTA	WSC00026R900FTA	WSC00026R000FTA	WSC0002604R0FTA
WSC0002649R0FTA	WSC0002665R0FTA	WSC000222R10FTA	WSC000210R40FTA	WSC00021K210FTA
WSC00022K340FTA	WSC2515R1000FEB	WSC251510R00FEB	WSC69271K000FEA	WSC00023R010FTA
WSC000240R20FTA	WSC00011K500FTB	WSC000290R90FTA	WSN00014R700FBA	WSC000239R00FTA
WSC000230R00FTA	WSC000275R00FTA	WSC00024R120FTA	WSC01\2R5000FTB	WSC01\2R1000FTB
WSC01\2R2000FTB	WSC01\2R3000FTB	WSC45272R000FEB	WSC01\23R900FTB	WSC000239R20FTA
WSC01\2R3010FTB	WSC01\21R000FEB	WSC452720R00FEB	WSC25151K000FEB	WSC0002820R0JTA
WSC0002R1500FTA	WSC0001R2490FEB	WSC25155R110FEB	WSC251549R90FEB	WSC25152R200FEB