

Low Profile Holder Type Crystal Units



FEATURES

- Low cost
- Industry standard
- Wide frequency range
- Excellent aging
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


RoHS
COMPLIANT

This part is a miniature AT cut strip crystal unit with a low profile package. It is with resistance weld.


STANDARD ELECTRICAL SPECIFICATIONS

PARAMETER	SYMBOL	CONDITION	UNIT	MIN.	TYP.	MAX.
Frequency range	F_O		MHz	3.579545	-	66.000
Frequency tolerance	$\Delta F/F_O$	at 25 °C	ppm	-30	-	+30
Temperature stability	T_C	ref. to 25 °C	ppm	-50	-	+50
Operating temperature range	T_{OPR}		°C	-10	-	+70
Storage temperature range	T_{STG}		°C	-55	-	+125
Shunt capacitance	C_0		pF	-	-	7
Load capacitance	C_L	customer specified	pF	10	-	series
Insulation resistance	I_R	100 V _{DC}	MΩ	500	-	-
Drive level	D_L		μW	-	100	500
Aging (first year)	Fa	at 25 °C, per year	ppm	-5	-	+5

EQUIVALENT SERIES RESISTANCE (ESR) AND MODE OF VIBRATION (MODE)

FREQUENCY RANGE (MHz)	MAX. ESR (Ω)	MODE	FREQUENCY RANGE (MHz)	MAX. ESR (Ω)	MODE
3.579 to 3.999	200	fundamental/AT	10.000 to 13.999	80	fundamental/AT
4.000 to 4.999	150	fundamental/AT	14.000 to 39.999	50	fundamental/AT
5.000 to 5.999	120	fundamental/AT	40.000 to 66.000	80	3 rd overtone
6.000 to 9.999	100	fundamental/AT			

DIMENSIONS in inches [millimeters]



**ORDERING INFORMATION****XT49S****R****-20****SP****12M****e2**

MODEL

OTR

LOAD

OPTIONS

FREQUENCY/MHz

JEDEC® LEAD (Pb)-FREE
STANDARDblank = standard
R = -40 °C to +85 °Cblank = series
-16 = 16 pF
-20 = 20 pF standard
-30 = 30 pF
-32 = 32 pFblank = standard
SP = spacer
SL = sleeve**GLOBAL PART NUMBER**

X

T

9

S

MODEL

2

0

LOAD

A

PACKAGE
CODE

N

A

OPTION

1

2

M

FREQUENCY

GLOBAL PART NUMBERING

X

T

9

S

MODEL NUMBERXT9S = XT49S
XT9M = XT49M
XTU1 = XTUM1

2

0

**LOAD
CAPACITANCE**18 = 18 pF
20 = 20 pF
NL = series
to be specified by
customer

A

**PACKAGE
CODE****Tape and reel**
H = RF7 (XT9M)**Bulk**
A = B04
(all models)

N

A

OPTIONSNA = no additional
options
RR = extended
temperature
of -40 °C to +85 °C
Contact factory for
all other options

4

0

M

FREQUENCY4M = 4 MHz
40M = 40 MHz
100M = 100 MHz
12M288 = 12.288 MHz
M is used as
decimal place
holder in frequency

Example: XT49S-20 40M

X

T

3

6

MODEL NUMBERXT46 = XT46C
XT36 = XT36C

2

0

LOAD CAPACITANCE18 = 18 pF
20 = 20 pF
NL = series
to be specified by
customer

A

**PACKAGE
CODE****Tape and reel**
H = RF7**Bulk**
A = B04
(all models)

1

2

M

FREQUENCY4M = 4 MHz
40M = 40 MHz
100M = 100 MHz
12M288 = 12.288 MHz
M is used as
decimal place
holder in frequency

Example: XT36C-20 12M



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

[XT9S20ANA12M288](#) [XT9S20ANA3M6864](#) [XT9S20ANA3M579545](#) [XT9SNLANA12M](#) [XT9S20ANA8M](#)
[XT9SNLANA12M288](#) [XT9S20ANA20M](#) [XT9S20ANA10M](#) [XT9SNLANA3M579545](#) [XT9S20ANA4M](#) [XT9S20ANA16M](#)
[XT9SNLANA4M](#) [XT9SNLANA10M](#) [XT9S20ANA12M](#)