


Order information

Ripac Vario-Module 4 U, 6 U

Rail type	Ripac Vario-Module	Packs of	4 U (3 + 1)			6 U			Page
	Installation width (HP)		84	84	84	84	84	84	
	Depth (mm)		250.4	310.4	370.4	310.4	370.4	430.4	
	Enclosure Model No. VM with vent holes	1	3981.110	3981.120	3981.130	3981.140	3981.150	3981.160	
	e		22	28	34	28	34	40	
	B1		449.0	449.0	449.0	449.0	449.0	449.0	
	B2		465.1	465.1	465.1	465.1	465.1	465.1	
Expansion accessories/Individual parts									
	Top cover, non vented	1	3981.900	3981.910	3981.920	3981.910	3981.920	3981.930	
	Top cover, vented	1	3981.940	3981.950	3981.960	3981.950	3981.960	3981.970	
	Bottom cover, non vented	1	3981.700	3981.710	3981.720	3981.710	3981.720	3981.730	
	Bottom cover, vented	1	3981.740	3981.750	3981.760	3981.750	3981.760	3981.770	
	Corner trim pieces for assembly as instrument case	2	3981.320	3981.320	3981.320	3981.330	3981.330	3981.330	226
	Mounting flanges for assembly as rack-mounted unit – without handle holes – with handle holes	2 2	3981.220 3981.270	3981.220 3981.270	3981.220 3981.270	3981.230 3981.280	3981.230 3981.280	3981.230 3981.280	226 226
A	Front horizontal rails (not suitable for depth-adjustable installation)	1	3684.562	3684.562	3684.562	3684.562	3684.562	3684.562	148
B	Front horizontal rails with 10 mm extension for injector/extractor handles (not suitable for depth-adjustable installation)	1	3684.567	3684.567	3684.567	3684.567	3684.567	3684.567	148
C1	Rear horizontal rails	1	3684.572	3684.572	3684.572	3684.572	3684.572	3684.572	149
D1	Rear horizontal rails, centre	1	–	–	–	3684.582	3684.582	3684.582	150
E	Rear adaptor rail, centre	1	–	–	–	3684.591	3684.591	3684.591	151
F	Z rail DIN 41 612	1	3684.602	3684.602	3684.602	3684.602	3684.602	3684.602	152
G	Insulating strips (21 HP)	1	3684.611	3684.611	3684.611	3684.611	3684.611	3684.611	153
H	Conductive strips (84 HP)	1	3684.612	3684.612	3684.612	3684.612	3684.612	3684.612	153
I	Threaded inserts	1	3684.610	3684.610	3684.610	3684.610	3684.610	3684.610	152
EMC expansion									
K	EMC gaskets, horizontal – for upper/lower horizontal rail	1	3684.808	3684.808	3684.808	3684.808	3684.808	3684.808	152
	– between covers and horizontal rails	10	3684.245	3684.245	3684.245	3684.245	3684.245	3684.245	166
	EMC gaskets, vertical	1	3686.976	3686.976	3686.976	3686.977	3686.977	3686.977	146
	Front/rear panel, EMC		see page 182 – 195						
Other accessories									
	Front/rear panels		see page 182 – 195						
	Carrying handles	2	3981.350	3981.360	3981.370	3981.360	3981.370	3981.380	227
	Front handles*	2	3636.010	3636.010	3636.010	3666.010	3666.010	3666.010	226
	Acrylic front door	1	3981.450	3981.450	3981.450	3981.460	3981.460	3981.460	227
	Rear adjustable feet	4	3901.000	3901.000	3901.000	3901.000	3901.000	3901.000	227


* Only in conjunction with mounting flanges with handle holes

4 U
(3 + 1)



T = Depth
HE = U
TE = HP

6 U





Technical specifications:

May be used as a rack mounted unit or instrument case.
External dimensions to DIN 41 494, part 1 for installation in enclosures, 482.6 mm (19"); Installation dimensions for board type plug-in units to DIN 41 494, part 5 and IEC 60 297-3 and IEEE 1101.1/1101.10.

Protection category:

IP 40 for solid version

Material/Surface finish:

Side panels: Extruded aluminium section, spray finished in RAL 7035

Horizontal rails: Extruded aluminium section, spray finished in RAL 7035

Corner trim: Die-cast zinc, spray finished in RAL 7035

Covers: Sheet steel, spray finished in RAL 7035

Side trim: Extruded aluminium section, spray finished in RAL 7035

Contact points: Conductive

Supply includes:


- 2 side panels
- 1 top cover with/without vent holes
- 1 bottom cover with/without vent holes
- 4 horizontal rails
- 4 threaded inserts
- 2 rear corner trim pieces for EMC gaskets
- 2 side trim pieces, centre
- Assembly parts

Ripac Vario-Module accessories

see page 226/227

Horizontal rails

from page 148




1) Equipped as an instrument case:

Front corner trim must be ordered separately.

2) Equipped as a rack-mounted unit:


Mounting flanges must be ordered separately.

Horizontal rail configuration



■ Included in the supply

■ To be ordered separately, depending on application



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wakefield Thermal:](#)

[3684562](#) [3684567](#) [3684572](#) [3684582](#)