




TECHNICAL CHARACTERISTICS

MATERIAL

INSULATOR: LCP
FLAMMABILITY RATING: UL94-V0
COLOR: BLACK
CONTACT MATERIAL: COPPER ALLOY
CONTACT TYPE: STAMPED
CONTACT PLATING: TIN
QUALITY CLASS: 25 MATING CYCLES
PITCH: 3.00MM

ENVIRONMENTAL

OPERATING TEMPERATURE: -40 UP TO 105°C
COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL

CURRENT RATING: 5A
WORKING VOLTAGE: 250V AC
INSULATOR RESISTANCE: >1000 MOHM
DIELECTRIC WITHSTANDING VOLTAGE: 1500V AC/MN
CONTACT RESISTANCE: 10 mOHM MAX

STANDARD

 CERTIFIED: E323964

SOLDERING

JEDEC LEAD FREE REFLOW SOLDERING PROCESS


PACKAGING

TRAY

DIMENSION

A = 3.00 x (NB. PIN / 2 - 1)
B = 3.00 x (NB. PIN / 2 + 1) + 0.70

RoHS Compliant				PROJECTION: 	GENERAL TOLERANCE .X = +/- 0.2 .XX = +/- 0.15	 WÜRTH ELEKTRONIK		
K	04-NOV-16	PCN	AK	APPROVAL: BBu	UNIT: MM	DESCRIPTION: 3.00MM MALE DUAL ROW SMT RIGHT ANGLE HEADER SMT SOLDER TAB		SIZE A4
J	07-MAR-16	COPLANARITY	AK		SCALE:			
I	02-JUL-15	PINNING	AK		SHEET: 1/3	WERI PART NO: 662 0xx 231 722		
H	20-JAN-2015	PROJECTION	QP		DRAW: PEARL			
REV	DATE	FILE	BY					



Note:
1.Dimension
Tray Size:260(L)x190(W)x12.0(H) (mm)
Carton Size:400X280X280(mm)
2.Quantity:
XX Pcs/Tray
48 Trays/Carton

Pin.	Pcs/Tray	Pcs/Carton	Pin.	Pcs/Tray	Pcs/Carton
4	96	4608	16	56	2688
6	80	3840	18	48	2304
8	72	3456	20	40	1920
10	64	3072	22	40	1920
12	64	3072	24	40	1920
14	56	2688			

RoHS Compliant				PROJECTION:	GENERAL TOLERANCE	 WÜRTH ELEKTRONIK DESCRIPTION: 3.00MM MALE DUAL ROW SMT RIGHT ANGLE HEADER SMT SOLDER TAB WERI PART NO: 662 0xx 231 722_TPK SIZE A4	
G					.X = +/- 0.2		
F					.XX = +/- 0.15		
E							
D							
C				APPROVAL: BBu	UNIT: MM		
B					SCALE:		
A					SHEET: 2/3		
REV	DATE	FILE	BY		DRAW: PEARL		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wurth Elektronik:](#)

[662012231722](#)