





Dual Common Cathode Schottky Rectifier

ITO-220AB


MBRF15xxCT

D²PAK (TO-263AB)

MBRB15xxCT


DESIGN SUPPORT TOOLS


[click logo to get started](#)

RoHS
COMPLIANT

FEATURES

- Power pack
- Guardring for overvoltage protection
- Low power loss, high efficiency
- Low forward voltage drop
- High forward surge capability
- High frequency operation
- Meets MSL level 1, per J-STD-020, LF maximum peak of 245 °C (for D²PAK (TO-263AB)) package
- Solder bath temperature 275 °C maximum, 10 s, per JESD 22-B106 (for ITO-220AB package)
- AEC-Q101 qualified
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

TYPICAL APPLICATIONS

For use in high frequency rectifier of switching mode power supplies, freewheeling diodes, DC/DC converters, or polarity protection application.

MECHANICAL DATA

Case: ITO-220AB, D²PAK (TO-263AB)

Molding compound meets UL 94 V-0 flammability rating
Base P/N-E3 - RoHS-compliant, commercial grade
Base P/NHE3_X - RoHS-compliant, AEC-Q101 qualified ("X" denotes revision code, e.g. A, B,...)

Terminals: matte tin plated leads, solderable per J-STD-002 and JESD 22-B102
E3 suffix meets JESD 201 class 1A whisker test, HE3 suffix meets JESD 201 class 2 whisker test

Polarity: as marked

Mounting Torque: 10 in-lbs maximum

PRIMARY CHARACTERISTICS	
I _{F(AV)}	2 x 7.5 A
V _{RRM}	45 V, 60 V
I _{FSM}	150 A
V _F	0.57 V, 0.65 V
T _J max.	150 °C
Package	ITO-220AB, D ² PAK (TO-263AB)
Circuit configuration	Common cathode

MAXIMUM RATINGS (T _C = 25 °C unless otherwise noted)				
PARAMETER	SYMBOL	MBRB1545CT	MBRB1560CT	UNIT
Maximum repetitive peak reverse voltage	V _{RRM}	45	60	V
Working peak reverse voltage	V _{RWM}	45	60	
Maximum DC blocking voltage	V _{DC}	45	60	
Maximum average forward rectified current at T _C = 105 °C	I _{F(AV)} per diode	15		A
Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load per diode		7.5		
Peak repetitive reverse surge current per diode at t _p = 2.0 µs, 1 kHz	I _{RRM}	1.0	0.5	
Voltage rate of change (rated V _R)	dV/dt	10 000		
Operating junction temperature range	T _J	-65 to +150		°C
Storage temperature range	T _{STG}	-65 to +175		
Isolation voltage (ITO-220AB only) from terminal to heatsink t = 1 min	V _{AC}	1500		V

ELECTRICAL CHARACTERISTICS ($T_C = 25^\circ\text{C}$ unless otherwise noted)						
PARAMETER	SYMBOL	TEST CONDITIONS	MBRB1545CT	MBRB1560CT	UNIT	
Maximum instantaneous forward voltage per diode	V_F ⁽¹⁾	$I_F = 7.5 \text{ A}$ $T_C = 25^\circ\text{C}$	-	0.75	V	
		$I_F = 7.5 \text{ A}$ $T_C = 125^\circ\text{C}$	0.57	0.65		
		$I_F = 15 \text{ A}$ $T_C = 25^\circ\text{C}$	0.84	-		
		$I_F = 15 \text{ A}$ $T_C = 125^\circ\text{C}$	0.72	-		
Maximum instantaneous reverse current at DC blocking voltage per diode	I_R ⁽²⁾	Rated V_R	$T_C = 25^\circ\text{C}$	0.1	1.0	mA
			$T_C = 125^\circ\text{C}$	15	50	

Notes

(1) Pulse test: 300 μs pulse width, 1 % duty cycle







(2) Pulse test: pulse width $\leq 40 \text{ ms}$

THERMAL CHARACTERISTICS ($T_C = 25^\circ\text{C}$ unless otherwise noted)					
PARAMETER	SYMBOL	MBRF	MBRB	UNIT	
Maximum thermal resistance per diode	$R_{\theta JA}$	-	60	$^\circ\text{C/W}$	
	$R_{\theta JC}$	5.0	3.0		

ORDERING INFORMATION (Example)					
PACKAGE	PREFERRED P/N	UNIT WEIGHT (g)	PACKAGE CODE	BASE QUANTITY	DELIVERY MODE
ITO-220AB	MBRF1545CT-E3/45	1.99	45	50/tube	Tube
TO-263AB	MBRB1545CT-E3/45	1.35	45	50/tube	Tube
TO-263AB	MBRB1545CT-E3/81	1.35	81	800/reel	Tape and reel
ITO-220AB	MBRF1545CTHE3_A/P ⁽¹⁾	1.99	P	50/tube	Tube
TO-263AB	MBRB1545CTHE3_B/P ⁽¹⁾	1.35	P	50/tube	Tube
TO-263AB	MBRB1545CTHE3_B/I ⁽¹⁾	1.35	I	800/reel	Tape and reel


Note

(1) AEC-Q101 qualified


RATINGS AND CHARACTERISTICS CURVES ($T_C = 25^\circ\text{C}$ unless otherwise noted)

Fig. 1 - Forward Current Derating Curve

Fig. 4 - Typical Reverse Characteristics Per Diode

Fig. 2 - Maximum Non-Repetitive Peak Forward Surge Current Per Diode

Fig. 5 - Typical Junction Capacitance Per Diode

Fig. 3 - Typical Instantaneous Forward Characteristics Per Diode

Fig. 6 - Typical Transient Thermal Impedance Per Diode

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)


ITO-220AB



D²PAK (TO-263AB)



Mounting Pad Layout



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay](#):

[MBRB1545CT-E3/45](#) [MBRB1545CT-E3/81](#) [MBRB1560CT-E3/45](#) [MBRB1560CT-E3/81](#) [MBRF1545CT-E3/45](#)
[MBRF1560CT-E3/45](#) [MBRF1545CTHE3_A/P](#) [MBRF1560CTHE3_A/P](#)