

1	2	3	4	5
---	---	---	---	---

RECOMMENDED PCB LAYOUT

TECHNICAL CHARACTERISTICS

MATERIAL

INSULATOR: PA66

FLAMMABILITY RATING: UL94-V0

COLOR: GREEN

CONTACT PIN: BRASS (CuZn)

SOLDER TAIL PLATING: TIN

ENVIRONMENTAL

OPERATING TEMPERATURE: -40 UP TO 105°C

COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL

	cULus	VDE
CURRENT RATING:	10 A	10.5 A
WORKING VOLTAGE:	300 VAC	300 VAC
WITHSTANDING VOLTAGE:	1.6 KV	2.5 KV
CONTACT RESISTANCE:	20 mOhm MAX	

STANDARD

CERTIFIED E315414

CERTIFIED 40023195

MECHANICAL

PITCH: 3.81 MM

SOLDERING

JEDEC LEAD FREE WAVE SOLDERING PROCESS


PACKAGING

BOX

DIMENSION

A = (NB. PINS -1) x PITCH

B = ((NB. PINS -1) x PITCH) +5

RoHS Compliant				PROJECTION: 	GENERAL TOLERANCE .X = $\pm$ 0.2 .XX = $\pm$ 0.15		
G							
F							
E							
D	11-APR-16	DRAWING	AK	APPROVAL: FBr	UNIT: MM	DESCRIPTION: SERIE 322 - 3.81MM HORIZONTAL PCB HEADER WR-TBL	SIZE
C	12-OCT-09	STANDARD	JP		SCALE:		
B	29-OCT-08	CHARACTERISTICS	JP		SHEET: 1/2	WERI PART NO: 691 322 310 0xx	A4
A	31-OCT-07	PDF	EC		DRAW: MARVIN		
REV	DATE	FILE	BY				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wurth Elektronik:](#)

[691322310012](#)