




TECHNICAL CHARACTERISTICS

MATERIAL

INSULATOR: PA 66

FLAMABILITY RATING: UL94-V0

COLOR: GREEN

METAL HOUSING: BRASS (CuZn)

TERMINAL SCREW: STEEL ZINC PLATING "-" SLOT TYPE

WIRE GUARD: PhBz TIN PLATED

ENVIRONMENTAL

OPERATING TEMPERATURE: -40 UP TO 105°C

COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL

CURRENT RATING: 15A cULus 17A VDE

WORKING VOLTAGE: 300VAC 300VAC

WITHSTANDING VOLTAGE: 1.6KV 2.5KV

CONTACT RESISTANCE: 20 mOhm MAX

STANDARD

CERTIFIED: E315414

CERTIFIED: 40023402

MECHANICAL

SOLID WIRE: 24-12 AWG / 0.205-3.31 MM²

STRANDED WIRE: 24-12 AWG / 0.205-3.31 MM²

TORQUE: 3.5 Lb.In - 0.4 Nm

WIRE STRIPE LENGTH: 6-7 MM

SCREW: M3

PITCH: 5.08 MM

PACKAGING

BOX

RoHS Compliant				PROJECTION: 	GENERAL TOLERANCE .X = +/- 0.2 .XX = +/- 0.15	 WÜRTH ELEKTRONIK	DESCRIPTION: SERIE 3445 - 5.08MM HORIZONTAL CABLE ENTRY PLUG WITH HOOK ON BACK SIDE - WR-TBL	SIZE A4	D
G									
F									
E									
D									
C				APPROVAL: RJ	UNIT: MM	WERI PART NO: 691 344 510 0xx			
B	24-JUL-14	DRAWINGS	AS		SCALE:				
A	04-NOV-08	PDF	JP		SHEET: 1/2				
REV	DATE	FILE	BY		DRAW: MARVIN				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wurth Elektronik:](#)

[691344510003](#)