




TECHNICAL CHARACTERISTICS

MATERIAL

INSULATOR: PA 66
FLAMMABILITY RATING: UL94-V0
COLOR: GREEN
METAL HOUSING: BRASS (CuZn)
TERMINAL SCREW: STEEL ZINC PLATING "-" SLOT TYPE
WIRE GUARD: PhBz TIN PLATED

ENVIRONMENTAL

OPERATING TEMPERATURE: -40 UP TO 105°C
COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL

	cULus	VDE
CURRENT RATING:	20 A	20 A
WORKING VOLTAGE:	300 VAC	300 VAC
WITHSTANDING VOLTAGE:	1.6 KV	2.5 KV
CONTACT RESISTANCE:	20 mOhm MAX	

STANDARD

ULus CERTIFIED E315414
CE CERTIFIED 40023195

MECHANICAL

SOLID WIRE:	24-12 AWG / 0.205-3.31 MM²
STRANDED WIRE:	24-12 AWG / 0.205-3.31 MM²
TORQUE:	5 Lb.In / 0.5 Nm

WIRE STRIPE LENGTH: 7-8 MM

SCREW: M3

PITCH: 5.08 MM

PACKAGING

BOX

DIMENSION

A = (NB. PINS -1) x PITCH

B = NB. PINS x PITCH

C = (NB. PINS x PITCH) +0,1

RoHS Compliant

G				PROJECTION: 	GENERAL TOLERANCE .X = ± 0.2 .XX = ± 0.15		DESCRIPTION: SERIE 351 - 5.08MM VERTICAL CABLE ENTRY PLUG - WR-TBL	SIZE A4
F	22-APR-16	DRAWING	AK					
E	16-OCT-15	CURRENT cULus	AK					
D	05-NOV-12	V-UL	GG					
C	13-OCT-09	STANDARD	JP	APPROVAL: FBr	UNIT: MM	WERI PART NO: 691 351 500 0xx		
B	29-OCT-08	CHARACTERISTICS	JP		SCALE:			
A	31-OCT-07	PDF	EC		SHEET: 1/2			
REV	DATE	FILE	BY		DRAW: MARVIN			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wurth Elektronik:](#)

[691351500008](#)