Vishay General Semiconductor

Surface Mount PAR[®] Transient Voltage Suppressors

High Temperature Stability and High Reliability Conditions



 Junction passivation optimized design passivated anisotropic rectifier technology

· Available in uni-directional polarity only

 T_J = 175 °C capability suitable for high reliability and automotive requirement

RoHS

COMPLIANT

- Low leakage current
- Low forward voltage drop
- High surge capability
- Meets ISO7637-2 surge specification (varied by test condition)
- Meets MSL level 1, per J-STD-020, LF maximum peak of 245 °C
- AEC-Q101 qualified
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

TYPICAL APPLICATIONS

Use in sensitive electronics protection against voltage transients induced by inductive load switching and lighting, especially for automotive load dump protection application.

MECHANICAL DATA

Case: DO-218AB

Molding compound meets UL 94 V-0 flammability rating Base P/NHE3_X - RoHS-compliant and AEC-Q101 qualified ("X" denotes revision code e.g. A, B, ...)

Terminals: matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

HE3 suffix meets JESD 201 class 2 whisker test

Polarity: heatsink is anode

MAXIMUM RATINGS (T _C = 25 °C unless otherwise noted)						
PARAMETER		SYMBOL	VALUE	UNIT		
Peak pulse power dissipation	with 10/1000 µs waveform	D	6600	W		
	with 10/10 000 µs waveform	P _{PPM}	5200			
Power dissipation on infinite hea	tsink at $T_C = 25 \ ^{\circ}C$ (fig. 1)	PD	8.0	W		
Peak pulse current with 10/1000	µs waveform	I _{PPM} ⁽¹⁾	See next table	А		
Peak forward surge current 8.3 r	ns single half sine-wave	I _{FSM}	700	А		
Operating junction and storage t	emperature range	T _J , T _{STG}	-55 to +175	°C		

Note

 $^{(1)}\,$ Non-repetitive current pulse derated above T_A = 25 $^\circ C$

Revision: 06-Dec-2018

1

Document Number: 88387

For technical questions within your region: <u>DiodesAmericas@vishay.com</u>, <u>DiodesAsia@vishay.com</u>, <u>DiodesEurope@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>



PRIMARY CHARACTERISTICS					
V _{BR}	11.1 V to 52.8 V				
V _{WM}	10 V to 43 V				
P _{PPM} (10 x 1000 μs)	6600 W				
P _{PPM} (10 x 10 000 μs)	5200 W				
P _D	8 W				
I _{FSM}	700 A				
T _J max.	175 °C				
Polarity	Uni-directional				
Package	DO-218AB				



SM8S10A thru SM8S43A



www.vishay.com

Vishay General Semiconductor

ELECTRICAL CHARACTERISTICS ($T_C = 25 \text{ °C}$ unless otherwise noted)										
DEVICE TYPE	BREAKDOWN VOLTAGE V _{BR} (V)		TEST CURRENT հ	STAND-OFF VOLTAGE V _{WM}	MAXIMUM REVERSE LEAKAGE	MAXIMUM REVERSE LEAKAGE AT V _{WM}	MAX. PEAK PULSE CURRENT AT 10/1000 µs	MAXIMUM CLAMPING VOLTAGE	TYPICAL TEMP. COEFFICIENT OF V _{BR} ⁽¹⁾	
	MIN.	NOM.	MAX.	(mA)	(V)	ΑΤ V _{WM} I _D (μΑ)	T _J = 175 °C I _D (μΑ)	WAVEFORM (A)	AT I _{PPM} V _C (V)	αT (%/°C)
SM8S10A	11.1	11.7	12.3	5.0	10.0	15	250	388	17.0	0.069
SM8S11A	12.2	12.9	13.5	5.0	11.0	10	150	363	18.2	0.072
SM8S12A	13.3	14.0	14.7	5.0	12.0	10	150	332	19.9	0.074
SM8S13A	14.4	15.2	15.9	5.0	13.0	10	150	307	21.5	0.076
SM8S14A	15.6	16.4	17.2	5.0	14.0	10	150	284	23.2	0.078
SM8S15A	16.7	17.6	18.5	5.0	15.0	10	150	270	24.4	0.080
SM8S16A	17.8	18.8	19.7	5.0	16.0	10	150	254	26.0	0.081
SM8S17A	18.9	19.9	20.9	5.0	17.0	10	150	239	27.6	0.082
SM8S18A	20.0	21.1	22.1	5.0	18.0	10	150	226	29.2	0.083
SM8S20A	22.2	23.4	24.5	5.0	20.0	10	150	204	32.4	0.085
SM8S22A	24.4	25.7	26.9	5.0	22.0	10	150	186	35.5	0.086
SM8S24A	26.7	28.1	29.5	5.0	24.0	10	150	170	38.9	0.087
SM8S26A	28.9	30.4	31.9	5.0	26.0	10	150	157	42.1	0.088
SM8S28A	31.1	32.8	34.4	5.0	28.0	10	150	145	45.4	0.089
SM8S30A	33.3	35.1	36.8	5.0	30.0	10	150	136	48.4	0.090
SM8S33A	36.7	38.7	40.6	5.0	33.0	10	150	124	53.3	0.091
SM8S36A	40.0	42.1	44.2	5.0	36.0	10	150	114	58.1	0.091
SM8S40A	44.4	46.8	49.1	5.0	40.0	10	150	102	64.5	0.092
SM8S43A	47.8	50.3	52.8	5.0	43.0	10	150	95.1	69.4	0.093

Notes

For all types maximum V_F = 1.8 V at I_F = 100 A measured on 8.3 ms single half sine-wave or equivalent square wave, duty cycle = 4 pulses per minute maximum

⁽¹⁾ To calculate V_{BR} vs. junction temperature, use the following formula: V_{BR} at T_J = V_{BR} at 25 °C x (1 + α T x (T_J - 25))

THERMAL CHARACTERISTICS ($T_c = 25 \text{ °C}$ unless otherwise noted)						
PARAMETER	VALUE	UNIT				
Typical thermal resistance, junction to case	$R_{ ext{ heta}JC}$	0.90	°C/W			

ORDERING INFORMATION (Example)						
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE		
SM8S10AHE3_A/I (1)	2.605	Ι	750	13" diameter plastic tape and reel, anode towards the sprocket hole		

Note

⁽¹⁾ AEC-Q101 qualified



Vishay General Semiconductor

RATINGS AND CHARACTERISTICS CURVES ($T_A = 25$ °C unless otherwise noted)




Fig. 1 - Power Derating Curve




Fig. 2 - Load Dump Power Characteristics (10 ms Exponential Waveform)





Fig. 3 - Pulse Waveform








Fig. 5 - Typical Transient Thermal Impedance




Fig. 6 - Typical Junction Capacitance

Revision: 06-Dec-2018

3

For technical questions within your region: <u>DiodesAmericas@vishay.com</u>, <u>DiodesAsia@vishay.com</u>, <u>DiodesEurope@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>



Vishay General Semiconductor


0.091 (2.3)

0.067 (1.7)

0.116 (3.0)

0.093 (2.4)

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)





Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

SM8S40AHE3_A/I	SM8S14AHE3_A/I	SM8S26AHE3_A/I	SM8S11AHE3_A/I	SM8S22AHE3_A/I	SM8S10AHE3_A/I
SM8S13AHE3_A/I	SM8S24AHE3_A/I	SM8S43AHE3_A/I	SM8S17AHE3_A/I	SM8S36AHE3_A/I	SM8S33AHE3_A/I
SM8S15AHE3_A/I	SM8S12AHE3_A/I	SM8S28AHE3_A/I	SM8S20AHE3_A/I	SM8S30AHE3_A/I	SM8S16AHE3_A/I
SM8S18AHE3_A/I					