


CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect



#### ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	4-3 @20°C	2.90 ohms ±20%
D.C. RESISTANCE	5-1 @20°C	0.815 ohms ±20%
D.C. RESISTANCE	6-10 @20°C	0.240 ohms ±20%
INDUCTANCE	4-3 65kHz, 100mVAC, L <sub>s</sub>	1.20mH ±10%
SATURATION CURRENT	20% rolloff from initial	540mA
LEAKAGE INDUCTANCE	4-3 tie(1+5, 6+10), 100kHz, 100mVAC, L <sub>s</sub>	15uH max.
DIELECTRIC	4-6 tie(3+5), 1875VAC, 1 second	1500VAC, 1 minute
URNS RATIO	(4-3):(5-1)	4:1, ±2%
URNS RATIO	(4-3):(6-10)	2.97:1, ±2%
URNS RATIO	(4-2):(2-3)	1:1, ±2%

#### GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Designed to comply with requirements as defined by UL1310.

Wire insulation & RoHS status not affected by wire color.  
Wire insulation color may vary depending on availability.

DETAILS SUBJECT TO CHANGE

REV.	DATE	Packaging Specifications	CONVENTION PLACEMENT	Tolerances unless otherwise specified:	DRAWING TITLE	PART NO.
		Method: Tray		Angles: ±1°	TRANSFORMER	750311992
		PKG-0887		Decimals: ±.005 [.13]		
		www.we-online.com/midcom		Fractions: ±1/64		
6B	11/12			Footprint: ±.001 [.03]		
6A	12/10	SEE REVISION SHEET FOR REVISION LEVEL		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750311992	SPECIFICATION SHEET 1 OF 1



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wurth Elektronik:](#)

[750311992](#)