





| | | |
|-------------------|------|---------------|
| CUSTOMER TERMINAL | RoHS | LEAD(Pb)-FREE |
| Sn96%, Ag4% | Yes | Yes |



TERM. NO.'s FOR REF. ONLY



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

| PARAMETER | TEST CONDITIONS | VALUE |
|-----------------------|---------------------------------------|------------------------|
| 6C 6B D.C. RESISTANCE | 2-3 @20°C | 0.225 ohms ±10% |
| 6B D.C. RESISTANCE | 5-6 @20°C | 0.260 ohms ±10% |
| 6C 6B D.C. RESISTANCE | 7-8 @20°C | 0.175 ohms ±10% |
| INDUCTANCE | 2-3 10kHz, 100mVAC, Ls | 26.0uH ±10% |
| SATURATION CURRENT | 20% rolloff from initial | 550mA |
| LEAKAGE INDUCTANCE | 2-3 tie(5+6+7+8), 100kHz, 100mVAC, Ls | 0.5uH typ., 1.0uH max. |
| DIELECTRIC | 2-8 tie(6+7), 1875VAC, 1 second | 1500VAC, 1 minute |
| URNS RATIO | (2-3):(6-5) | 1:1, ±1% |
| URNS RATIO | (2-3):(8-7) | 2:1, ±2% |

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Safety Standard Undefined.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

| | | | | | | |
|------|-------|---|--|--|-------------------------------------|------------------------------|
| REV. | DATE | Packaging Specifications Method: Tape & Reel 6B PKG-0951 www.we-online.com/midcom | | Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.005 [.13] | DRAWING TITLE TRANSFORMER | PART NO. 750312924 |
| 6C | 10/19 | | | | | |
| 6B | 1/14 | | | | | |
| 6A | 6/13 | SEE REVISION SHEET FOR REVISION LEVEL | | This drawing is dual dimensioned. Dimensions in brackets are in millimeters. | eiSos p/n: 750312924 | SPECIFICATION SHEET 1 OF 1 |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wurth Elektronik:](#)

[750312924](#)