


CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect



* DIMENSION MAY BE EXCEEDED WITH SOLDER ONLY



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-2 @20°C	0.438 ohms ±10%
D.C. RESISTANCE	3-4 @20°C	0.305 ohms ±10%
D.C. RESISTANCE	5-7 @20°C	0.040 ohms ±20%
D.C. RESISTANCE	6-8 @20°C	0.040 ohms ±20%
INDUCTANCE	3-4 10kHz, 100mVAC, Ls	44uH ±10%
SATURATION CURRENT	20% rolloff from initial	1.8A
LEAKAGE INDUCTANCE	3-4 tie(1+2, 5+6+7+8), 100kHz, 100mVAC, Ls	0.8uH typ., 1.5uH max.
DIELECTRIC	1-8 tie(2+3, 5+6), 3000VDC, 1 second	2400VDC, 1 minute
DIELECTRIC	1-4 625VAC, 1 second	500VAC, 1 minute
TURNS RATIO	(4-3):(2-1)	1.6:1, ±1%
TURNS RATIO	(4-3):(5-7)	4:1, ±1%
TURNS RATIO	(4-3):(6-8)	4:1, ±1%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Safety Standard Undefined.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tape & Reel PKG-0410 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [0.13] Footprint: ±.005 [0.13]	DRAWING TITLE TRANSFORMER	PART NO. 750313109
6A	7/14	SEE REVISION SHEET FOR REVISION LEVEL	CONVENTION PLACEMENT	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750313109	SPECIFICATION SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wurth Elektronik:](#)

[750313109](#)