

Standard Recovery Diodes, (Stud Version), 380 A



DO-9 (DO-205AB)

FEATURES

- Wide current range
- High voltage ratings up to 3200 V
- High surge current capabilities
- Stud cathode and stud anode version
- Standard JEDEC® types
- Compression bonded encapsulations
- Designed and qualified for industrial level
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


RoHS
COMPLIANT

TYPICAL APPLICATIONS

- Converters
- Power supplies
- Machine tool controls
- High power drives
- Medium traction applications

PRIMARY CHARACTERISTICS

$I_{F(AV)}$	380 A
Package	DO-9 (DO-205AB)
Circuit configuration	Single

MAJOR RATINGS AND CHARACTERISTICS

PARAMETER	TEST CONDITIONS	VS-SD300N/R		UNITS
		16 to 20	25 to 32	
$I_{F(AV)}$		380	380	A
	T_C	100	70	°C
$I_{F(RMS)}$		595	425	A
I_{FSM}	50 Hz	6050	6050	
	60 Hz	6335	6335	
I^2t	50 Hz	183	183	kA ² s
	60 Hz	167	167	
V_{RRM}	Range	1600 to 2000	2500 to 3200	V
T_J		-40 to +180	-40 to +150	°C

ELECTRICAL SPECIFICATIONS

VOLTAGE RATINGS

TYPE NUMBER	VOLTAGE CODE	V_{RRM} , MAXIMUM REPETITIVE PEAK REVERSE VOLTAGE V	V_{RSM} , MAXIMUM NON-REPETITIVE PEAK REVERSE VOLTAGE V	I_{RRM} MAXIMUM AT $T_J = T_J$ MAXIMUM mA
VS-SD300N/R	16	1600	1700	15
	20	2000	2100	
	25	2500	2600	
	28	2800	2900	
	32	3200	3300	

**FORWARD CONDUCTION**

PARAMETER	SYMBOL	TEST CONDITIONS			SD300N/R		UNITS
					16 to 20	25 to 32	
Maximum average forward current at case temperature	I _{F(AV)}	180° conduction, half sine wave			380	270	A
					100	100	°C
					300	380	A
					125	70	°C
Maximum RMS forward current	I _{F(RMS)}	DC at T _C = 88 °C (02 to 24), T _C = 91 °C (25 to 32)			595	425	
Maximum peak, one-cycle forward, non-repetitive surge current	I _{FSM}	t = 10 ms	No voltage reapplied	Sinusoidal half wave, initial T _J = T _J maximum	6050		A
		t = 8.3 ms			6335		
		t = 10 ms	100 % V _{RRM} reapplied		5090		
		t = 8.3 ms			5330		
Maximum I ² t for fusing	I ² t	t = 10 ms	No voltage reapplied		183		kA ² s
		t = 8.3 ms			167		
		t = 10 ms	100 % V _{RRM} reapplied		129		
		t = 8.3 ms			118		
Maximum I ² √t for fusing	I ² √t	t = 0.1 to 10 ms, no voltage reapplied			1830		kA ² √s
Low level value of threshold voltage	V _{F(TO)1}	(16.7 % × π × I _{F(AV)}) < I < π × I _{F(AV)} , T _J = T _J maximum			0.95		V
High level value of threshold voltage	V _{F(TO)2}	(I > π × I _{F(AV)}), T _J = T _J maximum			1.05		
Low level value of forward slope resistance	r _{f1}	(16.7 % × π × I _{F(AV)}) < I < π × I _{F(AV)} , T _J = T _J maximum			0.75		mΩ
High level value of forward slope resistance	r _{f2}	(I > π × I _{F(AV)}), T _J = T _J maximum			0.66		
Maximum forward voltage drop	V _{FM}	I _{pk} = 1180 A, T _J = T _J maximum, t _p = 10 ms sinusoidal wave			1.83	1.83	V

THERMAL AND MECHANICAL SPECIFICATIONS

PARAMETER	SYMBOL	TEST CONDITIONS	SD300N/R		UNITS
			16 to 20	25 to 32	
Maximum junction operating temperature range	T _J		-40 to 180	-40 to 150	°C
Maximum storage temperature range	T _{Stg}		-55 to 200		
Maximum thermal resistance, junction to case	R _{thJC}	DC operation	0.11		K/W
Maximum thermal resistance, case to heatsink	R _{thCS}	Mounting surface, smooth, flat, and greased	0.04		
Maximum allowed mounting torque ± 10 %		Not-lubricated threads	27		Nm
Approximate weight			250		g
Case style		See dimensions (link at the end of datasheet)	DO-9 (DO-205AB)		

 ΔR_{thJC} CONDUCTION

CONDUCTION ANGLE	SINUSOIDAL CONDUCTION	RECTANGULAR CONDUCTION	TEST CONDITIONS	UNITS
180°	0.019	0.013	$T_J = T_J$ maximum	K/W
120°	0.023	0.023		
90°	0.028	0.030		
60°	0.042	0.044		
30°	0.073	0.074		

Note

- The table above shows the increment of thermal resistance R_{thJC} when devices operate at different conduction angles than DC




Fig. 1 - Current Ratings Characteristics




Fig. 3 - Current Ratings Characteristics




Fig. 2 - Current Ratings Characteristics




Fig. 4 - Current Ratings Characteristics




Fig. 5 - Forward Power Loss Characteristics




Fig. 6 - Forward Power Loss Characteristics




Fig. 7 - Forward Power Loss Characteristics




Fig. 8 - Forward Power Loss Characteristics




Fig. 9 - Maximum Non-Repetitive Surge Current




Fig. 10 - Maximum Non-Repetitive Surge Current





Fig. 11 - Forward Voltage Drop Characteristics


Fig. 12 - Thermal Impedance Z_{thJC} Characteristics



ORDERING INFORMATION TABLE


Device code	VS-	SD	30	0	N	32	P	C
	1	2	3	4	5	6	7	8

- | | |
|----------|--|
| 1 | - Vishay semiconductors product |
| 2 | - Diode |
| 3 | - Essential part number |
| 4 | - 0 = standard recovery |
| 5 | - <ul style="list-style-type: none">• N = stud normal polarity (cathode to stud)• R = stud reverse polarity (anode to stud) |
| 6 | - Voltage code x 100 = V_{RRM} (see Voltage Ratings table) |
| 7 | - P = stud base DO-9 (DO-205AB) 3/4" 16UNF-2A |
| 8 | - C = ceramic housing |

LINKS TO RELATED DOCUMENTS	
Dimensions	www.vishay.com/doc?95301

DO-205AB (DO-9)

DIMENSIONS in millimeters (inches)





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

[VS-SD300N16PC](#) [VS-SD300R32PC](#) [VS-SD300R28PC](#) [VS-SD300N20PC](#) [VS-SD300N28PC](#) [VS-SD300R20PC](#)
[VS-SD300N25PC](#) [VS-SD300N32PC](#) [VS-SD300R25PC](#) [VS-SD300R16PC](#)