



CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-3 @20°C	0.146 ohms ±10%
D.C. RESISTANCE	6-4 @20°C	0.151 ohms ±10%
INDUCTANCE	1-3 100kHz, 10mVAC, Ls	388uH ±30%
DIELECTRIC	1-6 3438VAC, 1 second	2750VAC, 1 minute
TURNS RATIO	(6-4):(1-3)	1.1:1, ±1%



GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C.

Designed to comply with the following requirements as defined by IEC60950-1, EN60950-1, UL60950-1/CSA60950-1 and AS/NZS60950.1:
- Functional insulation.

CURRENT RATING: 200mA

VOLTAGE - TIME: 9.44Vus (1-2)

DETAILS SUBJECT TO CHANGE

REV.	DATE	Packaging Specifications		Tolerances unless otherwise specified:	DRAWING TITLE	PART NO.
6E	12/20	Method: Tape & Reel		Angles: ±1°	Decimals: ±.005 [0.13]	TRANSFORMER
6D	7/17	PKG-0895	Fractions: ±1/64	Footprint: ±.005 [0.13]	eiSos p/n: 750315225	
6C	7/16	www.we-online.com/midcom	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.			
6B	8/15	SEE REVISION SHEET FOR REVISION LEVEL				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wurth Elektronik:](#)

[750315225](#)