




CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
6B D.C. RESISTANCE	1-2 @20°C	0.410 ohms ±10%
6B D.C. RESISTANCE	2-3 @20°C	0.275 ohms ±10%
6B D.C. RESISTANCE	3-4 @20°C	0.800 ohms ±10%
6B D.C. RESISTANCE	6-7 @20°C	1.08 ohms ±10%
6B D.C. RESISTANCE	5-8 @20°C	1.85 ohms ±10%
INDUCTANCE	5-8 10kHz, 100mVAC, Ls	300uH ±20%
SATURATION CURRENT	20% rolloff from initial	150mA
LEAKAGE INDUCTANCE	5-8 tie(6+7, 1+2+3+4), 100kHz, 100mVAC, Ls	1.0uH typ., 2.0uH max.
DIELECTRIC	1-8 tie(5+6), 3750VDC, 1 second	3000VDC, 1 minute
URNS RATIO	(5-8):(6-7)	2:1, ±1%
URNS RATIO	(5-8):(1-2)	4.57:1, ±1%
URNS RATIO	(5-8):(2-3)	3.56:1, ±1%
URNS RATIO	(5-8):(3-4)	2.46:1, ±1%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tape & Reel PKG-1042 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.005 [.13]	DRAWING TITLE TRANSFORMER	PART NO. 750315319
6B	5/20			This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750315319	SPECIFICATION SHEET 1 OF 1
6A	8/15	SEE REVISION SHEET FOR REVISION LEVEL				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wurth Elektronik:](#)

[750315319](#)