

CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes


more than you expect



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-5 tie(1+2, 4+5), @20°C	0.012 ohms max.
D.C. RESISTANCE	6-10 tie(6+7, 9+10), @20°C	0.016 ohms ±20%
INDUCTANCE	tie(6+7, 9+10), 10kHz, 100mVAC, Ls	98uH min.
LEAKAGE INDUCTANCE	tie(1+2+4+5, 6+7, 9+10), 100kHz, 10mVAC, Ls	400nH typ., 800nH max.
DIELECTRIC	tie(4+5, 6+7), 1250VAC, 1 second	-
URNS RATIO	(10-6):(1-5), tie(1+2, 4+5, 6+7, 9+10)	2.2:1, ±2%

GENERAL SPECIFICATIONS:
OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.
Designed for functional insulation only.



Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications	CONVENTION PLACEMENT	Tolerances unless otherwise specified:	DRAWING TITLE	PART NO.
		Method: Tape & Reel PKG-0499 www.we-online.com/midcom		Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.005 [.13]	TRANSFORMER	750315945
6A	4/16	SEE REVISION SHEET FOR	REVISION LEVEL	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750315945	SPECIFICATION SHEET 1 OF 1



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wurth Elektronik:](#)

[750315945](#)