

CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	2-4 @20°C	0.133 ohms max.
D.C. RESISTANCE	9-7 @20°C	0.103 ohms max.
D.C. RESISTANCE	10-6 @20°C	0.380 ohms max.
INDUCTANCE	2-4 10kHz, 10mVAC, Ls	60uH min.
LEAKAGE INDUCTANCE	2-4 tie(6+7+8+9+10), 100kHz, 10mVAC, Ls	160nH typ., 240nH max.
DIELECTRIC	2-10 3125VAC, 1 second	2500VAC, 1 minute
URNS RATIO	(2-4):(9-7)	1.17:1, ±1%
URNS RATIO	(10-6):(2-4)	2.57:1, ±1%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Designed to comply with the following requirements as defined by IEC60950-1, EN60950-1, UL60950-1/CSA60950-1 and AS/NZS60950.1:



- Functional insulation for a primary circuit at a working voltage of 265Vrms, 400Vpeak, Overvoltage Category II.

Voltage-Time: 8.9Vus

COPLANARITY: All 10 terminals must lie on a plane within .004 [.10] of Surface A after lead tinning.

See design 750316669 for mounting through printed circuit board for lower height applications.

©Patent Protected by US10,575,419.



Wire insulation & RoHS status not affected by wire color.  
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications	CONVENTION PLACEMENT
6D	7/20	Method: Tape & Reel	
6C	5/20	PKG-1098	
6B	4/19	www.we-online.com/midcom	
6A	7/17	SEE REVISION SHEET FOR REVISION LEVEL	

Tolerances unless otherwise specified:  
Angles: ±1° Decimals: ±.005 [.13]  
Fractions: ±1/64 Footprint: ±.005 [.13]

This drawing is dual dimensioned. Dimensions in brackets are in millimeters.

DRAWING TITLE  
**TRANSFORMER**

eiSos p/n: 750316017

PART NO.  
**750316017**

SPECIFICATION SHEET 1 OF 1



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wurth Elektronik:](#)

[750316017](#)