

1		2		3		4		5																																																																																																									
						TECHNICAL CHARACTERISTICS MATERIAL INSULATOR: PA 66 FLAMMABILITY RATING: UL94-V0 COLOR: GREEN CONTACT PIN: BRASS (CuZn) SURFACE OF SOLDER TAIL PLATING: TIN ENVIRONMENTAL OPERATING TEMPERATURE: -40 UP TO 105°C COMPLIANCE: LEAD FREE AND ROHS ELECTRICAL CURRENT RATING: 10A WORKING VOLTAGE: 300VAC WITHSTANDING VOLTAGE: 1.6KV CONTACT RESISTANCE: 20 mOhm MAX STANDARD UL CERTIFIED E315414 MECHANICAL PITCH: 5.08mm SOLDERING JEDEC LEAD FREE WAVE SOLDERING PROCESS PACKAGING BOX																																																																																																											
						<table><tr><th>Poles</th><th>04</th><th>06</th><th>08</th><th>10</th><th>12</th><th>14</th><th>16</th><th>18</th><th>20</th><th>22</th><th>24</th><th>26</th></tr><tr><td>Dim L</td><td>10.16</td><td>15.24</td><td>20.32</td><td>25.40</td><td>30.48</td><td>35.56</td><td>40.64</td><td>45.72</td><td>50.80</td><td>55.88</td><td>60.96</td><td>66.04</td></tr><tr><td>Dim B</td><td>5.08</td><td>10.16</td><td>15.24</td><td>20.32</td><td>25.40</td><td>30.48</td><td>35.56</td><td>40.64</td><td>45.72</td><td>50.80</td><td>55.88</td><td>60.96</td></tr><tr><td>TOL</td><td colspan="4">±0.15</td><td colspan="4">±0.20</td><td colspan="4">±0.25</td></tr><tr><th>Poles</th><th>28</th><th>30</th><th>32</th><th>34</th><th>36</th><th>38</th><th>40</th><th>42</th><th>44</th><th>46</th><th>48</th><th></th></tr><tr><td>Dim L</td><td>71.12</td><td>76.20</td><td>81.28</td><td>86.36</td><td>91.44</td><td>96.52</td><td>101.60</td><td>106.68</td><td>111.76</td><td>116.84</td><td>121.92</td><td></td></tr><tr><td>Dim B</td><td>66.04</td><td>71.12</td><td>76.20</td><td>81.28</td><td>86.36</td><td>91.44</td><td>96.52</td><td>101.60</td><td>106.68</td><td>111.76</td><td>116.84</td><td></td></tr><tr><td>TOL</td><td colspan="2">±0.25</td><td colspan="4">±0.30</td><td colspan="4">±0.35</td><td colspan="2"></td></tr></table>				Poles	04	06	08	10	12	14	16	18	20	22	24	26	Dim L	10.16	15.24	20.32	25.40	30.48	35.56	40.64	45.72	50.80	55.88	60.96	66.04	Dim B	5.08	10.16	15.24	20.32	25.40	30.48	35.56	40.64	45.72	50.80	55.88	60.96	TOL	±0.15				±0.20				±0.25				Poles	28	30	32	34	36	38	40	42	44	46	48		Dim L	71.12	76.20	81.28	86.36	91.44	96.52	101.60	106.68	111.76	116.84	121.92		Dim B	66.04	71.12	76.20	81.28	86.36	91.44	96.52	101.60	106.68	111.76	116.84		TOL	±0.25		±0.30				±0.35					
Poles	04	06	08	10	12	14	16	18	20	22	24	26																																																																																																					
Dim L	10.16	15.24	20.32	25.40	30.48	35.56	40.64	45.72	50.80	55.88	60.96	66.04																																																																																																					
Dim B	5.08	10.16	15.24	20.32	25.40	30.48	35.56	40.64	45.72	50.80	55.88	60.96																																																																																																					
TOL	±0.15				±0.20				±0.25																																																																																																								
Poles	28	30	32	34	36	38	40	42	44	46	48																																																																																																						
Dim L	71.12	76.20	81.28	86.36	91.44	96.52	101.60	106.68	111.76	116.84	121.92																																																																																																						
Dim B	66.04	71.12	76.20	81.28	86.36	91.44	96.52	101.60	106.68	111.76	116.84																																																																																																						
TOL	±0.25		±0.30				±0.35																																																																																																										
RoHS Compliant				PROJECTION: 		GENERAL TOLERANCE .X = +/- 0.2 .XX = +/- 0.15																																																																																																											
G				APPROVAL: FBr		UNIT: MM		DESCRIPTION: SERIE 3355 - 5.08MM DOUBLE LEVEL HORIZONTAL MALE		SIZE																																																																																																							
F						SCALE:		PCB HEADER TYPE WR-TBL		A4																																																																																																							
E						SHEET: 1/2		WERI PART NO: 691 335 510 0xx																																																																																																									
D						DRAW: MARVIN																																																																																																											
C																																																																																																																	
B	07-JUL-15	UPDATE	AK																																																																																																														
A	18-JUN-10	PDF	JP																																																																																																														
REV	DATE	FILE	BY																																																																																																														

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Würth Elektronik:](#)

[691335510004](#) [691335510006](#) [691335510008](#) [691335510010](#) [691335510012](#) [691335510016](#)