



CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn98%, Cu2%	Yes	Yes

more than you expect



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-3 @20°C	700 mOhms max.
D.C. RESISTANCE	6-5 @20°C	450 mOhms max.
D.C. RESISTANCE	5-4 @20°C	450 mOhms max.
INDUCTANCE	1-3 10kHz, 100mVAC, Ls	700uH min.
LEAKAGE INDUCTANCE	1-3 tie(6+5+4), 100kHz, 100mVAC, Ls	600nH max.
DIELECTRIC	1-6 2500VDC, 2 seconds	-
URNS RATIO	(1-3):(6-5):(5-4)	2:1:1, ±2%

GENERAL SPECIFICATIONS:

COPLANARITY: All 5 terminals must lie on a plane within .004 [.10] of Surface A after lead tinning.

ET RATING: 12Vus

Designed to meet UL Recognized Insulation System M1-130(B), E106391.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

DETAILS SUBJECT TO CHANGE

REV.	DATE	Packaging Specifications Method: Tape & Reel PKG-0468 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.005 [.13]	DRAWING TITLE TRANSFORMER	PART NO. 750313723
6B	7/15			This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750313723	SPECIFICATION SHEET 1 OF 1
6A	2/15	SEE REVISION SHEET FOR REVISION LEVEL				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wurth Elektronik:](#)

[750313723](#)