




Dual High-Voltage Trench MOS Barrier Schottky Rectifier

Ultra Low $V_F = 0.54 \text{ V}$ at $I_F = 5 \text{ A}$



FEATURES

- Trench MOS Schottky technology
- Low forward voltage drop, low power losses
- High efficiency operation
- Solder bath temperature 275 °C maximum, 10 s, per JESD 22-B106
- Compliant to RoHS directive 2002/95/EC and in accordance to WEEE 2002/96/EC



RoHS
COMPLIANT

TYPICAL APPLICATIONS

For use in high frequency converters, switching power supplies, freewheeling diodes, OR-ing diode, dc-to-dc converters and reverse battery protection.

PRIMARY CHARACTERISTICS

$I_{F(AV)}$	2 x 10 A
V_{RRM}	100 V
I_{FSM}	120 A
V_F at $I_F = 10 \text{ A}$	0.65 V
$T_J \text{ max.}$	150 °C

MECHANICAL DATA

Case: TO-220AB and ITO-220AB

Molding compound meets UL 94 V-0 flammability rating

Base P/N-E3 - RoHS compliant, commercial grade

Terminals: Matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

E3 suffix meets JESD 201 class 1A whisker test

Polarity: As marked

Mounting Torque: 10 in-lbs maximum

MAXIMUM RATINGS ($T_A = 25 \text{ °C}$ unless otherwise noted)

PARAMETER	SYMBOL	V20100R	VF20100R	UNIT
Maximum repetitive peak reverse voltage	V_{RRM}	100		V
Maximum average forward rectified current per device per diode (fig. 1)	$I_{F(AV)}$	20 10		A
Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load per diode	I_{FSM}	120		A
Non-repetitive avalanche energy at $T_J = 25 \text{ °C}$, $L = 60 \text{ mH}$ per diode	E_{AS}	80		mJ
Peak repetitive reverse current at $t_p = 2 \text{ } \mu\text{s}$, 1 kHz, $T_J = 38 \text{ °C} \pm 2 \text{ °C}$ per diode	I_{RRM}	0.5		A
Voltage rate of change (rated V_R)	dV/dt	10 000		V/ μs
Isolation voltage (ITO-220AB only) from terminal to heatsink $t = 1 \text{ min}$	V_{AC}	1500		V
Operating junction and storage temperature range	T_J, T_{STG}	- 40 to + 150		°C

V20100R & VF20100R

Vishay General Semiconductor



ELECTRICAL CHARACTERISTICS ($T_A = 25\text{ }^{\circ}\text{C}$ unless otherwise noted)						
PARAMETER	TEST CONDITIONS		SYMBOL	TYP.	MAX.	UNIT
Breakdown voltage	$I_R = 1.0\text{ mA}$	$T_A = 25\text{ }^{\circ}\text{C}$	V_{BR}	100 (minimum)	-	V
Instantaneous forward voltage per diode ⁽¹⁾	$I_F = 5\text{ A}$	$T_A = 25\text{ }^{\circ}\text{C}$	V_F	0.62	-	V
	$I_F = 10\text{ A}$	$T_A = 25\text{ }^{\circ}\text{C}$		0.81	0.90	
	$I_F = 5\text{ A}$	$T_A = 125\text{ }^{\circ}\text{C}$		0.54	-	
	$I_F = 10\text{ A}$	$T_A = 125\text{ }^{\circ}\text{C}$		0.65	0.72	
Reverse current per diode ⁽²⁾	$V_R = 70\text{ V}$	$T_A = 25\text{ }^{\circ}\text{C}$	I_R	4	-	μA
		$T_A = 125\text{ }^{\circ}\text{C}$		4	-	mA
	$V_R = 100\text{ V}$	$T_A = 25\text{ }^{\circ}\text{C}$		-	150	μA
		$T_A = 125\text{ }^{\circ}\text{C}$		5.6	15	mA

Notes

⁽¹⁾ Pulse test: 300 μs pulse width, 1 % duty cycle⁽²⁾ Pulse test: Pulse width $\leq 40\text{ ms}$

THERMAL CHARACTERISTICS ($T_A = 25\text{ }^{\circ}\text{C}$ unless otherwise noted)				
PARAMETER	SYMBOL	V20100R	VF20100R	UNIT
Typical thermal resistance per diode	$R_{\theta JC}$	2.8	5.0	$^{\circ}\text{C/W}$

ORDERING INFORMATION (Example)					
PACKAGE	PREFERRED P/N	UNIT WEIGHT (g)	PACKAGE CODE	BASE QUANTITY	DELIVERY MODE
TO-220AB	V20100R-E3/4W	1.88	4W	50/tube	Tube
ITO-220AB	VF20100R-E3/4W	1.75	4W	50/tube	Tube

RATINGS AND CHARACTERISTICS CURVES


 $(T_A = 25\text{ }^{\circ}\text{C}$ unless otherwise noted)

Figure 1. Maximum Forward Current Derating Curve




Figure 2. Forward Power Loss Characteristics Per Diode




Figure 3. Typical Instantaneous Forward Characteristics Per Diode




Figure 6. Typical Transient Thermal Impedance Per Diode




Figure 4. Typical Reverse Characteristics Per Diode




Figure 7. Typical Transient Thermal Impedance Per Diode






Figure 5. Typical Junction Capacitance Per Diode

V20100R & VF20100R

Vishay General Semiconductor

**PACKAGE OUTLINE DIMENSIONS** in inches (millimeters)**TO-220AB****ITO-220AB**



Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

[VF20100R-E3/4W](#)