



E2467NL

NOTICE: THE INFORMATION AND
DESIGN CONTAINED HEREIN IS THE
PROPERTY OF PULSE WHO
RESERVES ALL RIGHTS THERETO.

FINAL OUTLINE NOTES:

CHECK DIMENSIONS PER PACKAGE SPECIFICATION ITEM 10.



SCHEMATIC

Electrical @ 25°C

PARAMETER	SPECIFICATIONS
Turns Ratio	(1-3) : (14-16) = 1CT:1CT ±2% (6-8) : (9-11) = 1CT:2CT ±2%
CAPACITANCE WINDING TO WINDING	(1-3) 8 pF MAX (AT 100 KHz 20 mVRMS) (6-8) 12 pF MAX
DC RESISTANCE	0.3 OHMS MAX
LEAKAGE INDUCTANCE	0.3 uH MAX
INPUT - OUTPUT ISOLATION	1500 VRMS MIN @ 60 SECONDS

UNLESS OTHERWISE SPECIFIED, ALL
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:

DECIMALS ANGLES
.XX ±.01 ± 1°
.XXX ±.005

DO NOT SCALE DRAWING

SIZE CAGE CODE
B01961

DWG. NO.

E2467NL

REV.

P1

SCALE NONE

CADD FILE

E2467NL-1





SHEET

1 OF 2

12CT2004

E2467NL

NOTICE: THE INFORMATION AND
DESIGN CONTAINED HEREIN IS THE
PROPERTY OF PULSE WHO
RESERVES ALL RIGHTS THERETO.



UNLESS OTHERWISE SPECIFIED, ALL
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:

DECIMALS ANGLES
.XX ±.01 ± 1°
.XXX ±.005

DO NOT SCALE DRAWING

SIZE
B01961

CAGE CODE

SCALE NONE

DWG. NO.

E2467NL

CADD FILE E2467NL-2

SHEET 2 OF 2

REV.

P1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pulse:

[E2467NLT](#) [E2467NL](#)