



## General Purpose Plastic Rectifier



DO-201AD

### FEATURES

- Low forward voltage drop
- Low leakage current,  $I_R$  less than 0.1  $\mu$ A
- High forward surge capability
- Solder dip 275 °C max. 10 s, per JESD 22-B106
- Material categorization: For definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)



RoHS COMPLIANT

### TYPICAL APPLICATIONS

For use in general purpose rectification of power supplies, inverters, converters, and freewheeling diodes application.

#### Note

- These devices are not AEC-Q101 qualified.

### MECHANICAL DATA

**Case:** DO-201AD, molded epoxy body

Molding compound meets UL 94 V-0 flammability rating

Base P/N-E3 - RoHS-compliant, commercial grade

**Terminals:** Matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

E3 suffix meets JESD 201 class 1A whisker test

**Polarity:** Color band denotes cathode end

PRIMARY CHARACTERISTICS	
$I_{F(AV)}$	3.0 A
$V_{RRM}$	200 V, 400 V, 600 V, 800 V, 1300 V
$I_{FSM}$	150 A
$I_R$	5.0 $\mu$ A
$V_F$	1.1 V
$T_J$ max.	150 °C
Package	DO-201AD
Diode variations	Single die

MAXIMUM RATINGS ( $T_A = 25$ °C unless otherwise noted)							
PARAMETER	SYMBOL	BY251P	BY252P	BY253P	BY254P	BY255P	UNIT
Maximum repetitive peak reverse voltage	$V_{RRM}$	200	400	600	800	1300	V
Maximum RMS voltage	$V_{RMS}$	140	280	420	560	910	V
Maximum DC blocking voltage	$V_{DC}$	200	400	600	800	1300	V
Maximum average forward rectified current 10 mm lead length	$I_{F(AV)}$	3.0					A
Peak forward surge current 10 ms single half sine-wave superimposed on rated load	$I_{FSM}$	150					A
Maximum full load reverse current, full cycle average 10 mm lead length	$I_{R(AV)}$	100					$\mu$ A
Operating junction and storage temperature range	$T_J, T_{STG}$	- 55 to + 150					°C

ELECTRICAL CHARACTERISTICS ( $T_A = 25$ °C unless otherwise noted)								
PARAMETER	TEST CONDITIONS	SYMBOL	BY251P	BY252P	BY253P	BY254P	BY255P	UNIT
Maximum instantaneous forward voltage	3.0 A	$V_F$	1.1					V
Maximum reverse current at rated DC blocking voltage	$T_A = 25$ °C	$I_R$	5.0					$\mu$ A
Maximum reverse recovery time	$I_F = 0.5$ A, $I_R = 1.0$ V, $I_{rr} = 0.25$ A	$t_{rr}$	3.0					$\mu$ s
Typical junction capacitance	4.0 V, 1 MHz	$C_J$	40					pF



<b>THERMAL CHARACTERISTICS</b> ( $T_A = 25\text{ }^\circ\text{C}$ unless otherwise noted)							
PARAMETER	SYMBOL	BY251P	BY252P	BY253P	BY254P	BY255P	UNIT
Typical thermal resistance	$R_{\theta JA}$ <sup>(1)</sup>	20					$^\circ\text{C/W}$
	$R_{\theta JL}$ <sup>(1)</sup>	10					

**Note**

(1) Thermal resistance from junction to ambient and from junction to lead at 0.375" (9.5 mm) lead length, PCB mounted

<b>ORDERING INFORMATION</b> (Example)				
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE
BY253P-E3/54	1.1	54	1400	13" diameter paper tape and reel
BY253P-E3/73	1.1	73	1000	Ammo pack packaging

**RATINGS AND CHARACTERISTICS CURVES** ( $T_A = 25\text{ }^\circ\text{C}$  unless otherwise noted)




Fig. 1 - Forward Current Derating Curve




Fig. 3 - Maximum Non-repetitive Peak Forward Surge Current




Fig. 2 - Maximum Non-repetitive Peak Forward Surge Current




Fig. 4 - Typical Instantaneous Forward Characteristics





Fig. 5 - Typical Junction Capacitance

**PACKAGE OUTLINE DIMENSIONS** in inches (millimeters)





## **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

[BY251GP/23](#) [BY251GP/4](#) [BY251GP/54](#) [BY251GP-E3/23](#) [BY251GP-E3/4](#) [BY251GP-E3/54](#) [BY251GP-E3/73](#)  
[BY251GPHE3/54](#) [BY251GPHE3/73](#) [BY252GP-E3/51](#) [BY252GP-E3/54](#) [BY252GPHE3/54](#) [BY253GP/4](#) [BY253GP/54](#)  
[BY253GP-E3/4](#) [BY253GP-E3/54](#) [BY253GPHE3/54](#) [BY254GP/4](#) [BY254GP/54](#) [BY254GP-E3/4](#) [BY254GP-E3/54](#)  
[BY254GPHE3/54](#) [BY255GP/23](#) [BY255GP/4](#) [BY255GP/54](#) [BY255GP-E3/23](#) [BY255GP-E3/4](#) [BY255GP-E3/51](#)  
[BY255GP-E3/54](#) [BY255GP-E3/73](#) [BY255GPHE3/54](#) [BY255GPHE3/73](#) [BY255P-E3/51](#) [BY252GP-E3/1](#) [BY255GP/1](#)  
[BY255GP-E3/1](#)