



www.vishay.com

Vishay

Lead (Pb)-free Thick Film, Rectangular Commodity Chip Resistors



FEATURES





- Stability ($\Delta R/R \le 1$ % for 1000 h at 70 °C)
- Lead (Pb)-free solder contacts on Ni barrier layer
- COMPLIANT HALOGEN FREE

- · Metal glaze on ceramic
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

STANDARD E	STANDARD ELECTRICAL SPECIFICATIONS									
MODEL	CASE SIZE INCH	CASE SIZE METRIC	POWER RATING P _{70 °C} W	LIMITING ELEMENT VOLTAGE MAX. V ≅	TEMPERATURE COEFFICIENT ppm/K	TOLERANCE %	RESISTANCE RANGE Ω	E-SERIES		
		RR 1005M	0.000	50	± 100	± 1	1R0 to 10M	E24; E96		
CRCW0402C	0402		0.063	30	± 200	± 5	1R0 to 10M	E24		
			Zero-Ohm-Resistor: $R_{\text{max.}}$ = 20 m Ω , $I_{\text{max.}}$ at 70 °C = 1.5 A							
	0603	RR 1608M	0.10	75	± 100	± 1	1R0 to 10M	E24; E96		
CRCW0603C				75	± 200	± 5	1R0 to 10M	E24		
			Zero-Ohm-Resistor: $R_{\text{max.}}$ = 20 m Ω , $I_{\text{max.}}$ at 70 °C = 2.0 A							
			0.125	150	± 100	± 1	1R0 to 10M	E24; E96		
CRCW0805C	0805	RR 2012M		150	± 200	± 5	1R0 to 10M	E24		
Zero-Ohm-Resistor: $R_{\text{max.}} = 20 \text{ m}\Omega$, $I_{\text{max.}}$ at 70 °C = 2.5 A										
CRCW1206C	1206	RR 3216M	0.25	200	± 100	± 1	1R0 to 10M	E24; E96		
					± 200	± 5	1R0 to 10M	E24		
			Zero-Ohm-Resistor: $R_{\text{max.}} = 20 \text{ m}\Omega$, $I_{\text{max.}}$ at 70 °C = 3.5 A							

Notes


- These resistors do not feature a limited lifetime when operated within the permissible limits. However, resistance value drift increasing over
 operating time may result in exceeding a limit acceptable to the specific application, thereby establishing a functional lifetime
- · Power rating depends on the max. temperature at the solder point, the component placement density and the substrate material

TECHNICAL SPECIFICATIONS							
PARAMETER	UNIT	CRCW0402C	CRCW0603C	CRCW0805C	CRCW1206C		
Rated dissipation at 70°C (1)	W	0.063	0.10	0.125	0.25		
Limiting element voltage U _{max.} AC/DC	V	50	75	150	200		
Insulation voltage $U_{\text{ins.}}$ (1 min)	V	> 75	> 100	> 200	> 300		
Insulation resistance	Ω		> `	10 ⁹			
Category temperature range	°C		- 55 to	+ 155			
Failure rate	h ⁻¹		0.1 x	: 10 ⁻⁹			
Weight/1000 pieces	g	0.65	2	5.5	10		

Note


⁽¹⁾ The power dissipation on the resistor generates a temperature rise against the local ambient, depending on the heat flow support of the printed-circuit board (thermal resistance). The rated dissipation applies only if the permitted film temperature of 155 °C is not exceeded






PACKAGING							
TYPE / SIZE	CODE	QUANTITY	PACKAGING STYLE	WIDTH	PITCH	PACKAGING DIMENSIONS	
CRCW0402C	ED = ET7	10 000		8 mm	2 mm	Ø 180 mm/7"	
ChCW0402C	EE = EF4	50 000				Ø 330 mm/13"	
	EA = ET1	5000	Paper tape acc. to IEC 60286-3, Type 1a		4 mm	Ø 180 mm/7"	
CRCW0603C	EB = ET5	10 000				Ø 254 mm/10"	
	EC = ET6	20 000				Ø 330 mm/13"	
	EA = ET1	5000			4 mm	Ø 180 mm/7"	
CRCW0805C	EB = ET5	10 000				Ø 254 mm/10"	
	EC = ET6	20 000				Ø 330 mm/13"	
CRCW1206C	EA = ET1	5000			4 mm	Ø 180 mm/7"	
	EB = ET5	10 000				Ø 254 mm/10"	
	EC = ET6	20 000				Ø 330 mm/13"	

DIMENSIONS






CITE DIMENSIONS (in millimatora)					SOLDER PAD DIMENSIONS (1) (in millimeters)							
	SIZE DIMENSIONS (in millimeters)				REFLOW SOLDERING WAVE SOLD				SOLDE	ERING		
INCH	METRIC	L	W	Н	T1	T2	а	b	I	а	b	I
0402	1005	1.0 ± 0.10	0.5 ± 0.05	0.30 ± 0.05	0.25 ± 0.10	0.2 ± 0.1	0.4	0.6	0.5			
0603	1608	1.60 ± 0.10	0.80 ± 0.10	0.45 ± 0.10	0.3 ± 0.2	0.3 ± 0.2	0.5	0.9	1.0	0.9	0.9	1.0
0805	2012	2.0 ± 0.10	1.25 ± 0.15	0.50 ± 0.10	0.35 ± 0.15	0.35 ± 0.2	0.7	1.3	1.2	0.9	1.3	1.3
1206	3216	3.05 ± 0.10	1.55 ± 0.10	0.55 + 0.10 - 0.05	0.35 ± 0.15	0.45 ± 0.2	0.9	1.7	2.0	1.1	1.7	2.3

Note

⁽¹⁾ The rated dissipation applies only if the permitted film temperature is not exceeded. Furthermore, a high level of ambient temperature or of power dissipation may raise the temperature of the solder joint, hence special solder alloys or board materials maybe required to maintain the reliability of the assembly. Specified power rating above 125 °C requires dedicated heat-sink pads, which depend on board materials. The given solder pad dimensions reflect the considerations for board design and assembly as outlined e.g. in standards IEC 61188-5-x, or in publication IPC-7351. They do not guarantee any supposed thermal properties, particularly as these are also strongly influenced by many other parameters. Still the given solder pad dimensions will be found adequate for most general applications



FUNCTIONAL PERFORMANCE



TEST PR	OCEDURES	S AND REQUIF	REMENTS				
EN 60115-1	IEC 60068-2				REQUIREMENTS PERMISSIBLE CHANGE ($\triangle R$)		
CLAUSE	THE TEST DESCRIPTION		STABILITY CLASS 1 OR BETTER	STABILITY CLASS 2 OR BETTER			
			Stability for prod	luct types:			
				CRCWC e3	1 Ω to 10 MΩ	1 Ω to 10 MΩ	
4.5	-	Resistance		-	± 1 %	± 5 %	
4.8.4.2	-	Temperature coefficient		5/20) °C and 125/20) °C	± 100 ppm/K	± 200 ppm/K	
4.13	-	Short time overload	$U = 2.5 \times \sqrt{P_{70}}$	$\overline{x R} \le 2 \times U_{\text{max.}}$ 5 s	± (2 % R	+ 0.1 Ω)	
4.17.5	58 (Td)	Solderability	Pre-aging 4 h at 155 °C, dryheat	Solder bath method; Sn60Pb40 non activated flux; (235 ± 5) °C (2 ± 0.2) s	Good tinning (≥ 95 % covered) no visible damage		
				Solder bath method; Sn96.5Ag3Cu0.5 non activated flux; (245 ± 5) °C (3 ± 0.3) s	Good tinning (≥ 95 % covered) no visible damage		
4.18.2	58 (Td)	Resistance to soldering heat	Solder bath method (260 ± 5) °C; (10 ± 1) s		± (1% R + 0.05 Ω)		
4.19	14 (Na)	Rapid change of temperature	30 min. at - 55 °C; 30 min. at 125 °C; 5 cycles		± (0.25 % R + 0.05 Ω)	$\pm (0.5 \% R + 0.05 \Omega)$	
4.24	78 (Cab)	Damp heat, steady state	(40 ± 2) °C; 56 days; (93 ± 3) % RH		± (1 % R + 0.05 Ω)	± (2 % R + 0.1 Ω)	
4.36	-	Operation at low temperature	-55 °C, 1 h		± (1 % R	+ 0.05 Ω)	
4.25.1		Endurance	$U = \sqrt{P_{70} \times R} \le U_{\text{max.};}$ 1.5 h on; 0.5 h off;				
	-	at 70 °C	70 °C; 1000 h		± (1 % R + 0.05 Ω)	± (2 % R + 0.1 Ω)	
			70 °	C; 8000 h	± (2 % R + 0.1 Ω)	± (4 % R + 0.1 Ω)	
4.25.3	-	Endurance at upper category temperature	155 °C, 1000 h		± (1 % R + 0.05 Ω)	± (2 % R + 0.1 Ω)	



Vishay

APPLICABLE SPECIFICATIONS

EN 60115-1 Generic specification
 EN 140400 Sectional specification
 EN 140401-802 Detail specification

• IEC 60068-2-X Variety of environmental test procedures

• IEC 60286-3 Packaging of SMD components



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

CRCW12061M15FKEA0	CRCW04021R20JNED0	CRCW12063R60JNEAC	CRCW12063R65FKEAC
CRCW06031R43FKEAC	CRCW12062M61FKEAC	CRCW040215R8FKEDC	CRCW0603360RJNEAC
CRCW060340R2FKEBC	CRCW060311K0JNEBC	CRCW1206215KFKEBC	CRCW06031M13FKEBC
CRCW1206182KFKEBC	CRCW04023M74FKEDC	CRCW1206820KFKEBC	CRCW080560K4FKEBC
CRCW06033M90JNEBC	CRCW080513R3FKEBC	CRCW06034M12FKEBC	CRCW080515R4FKEAC
CRCW080566R5FKEBC	CRCW060312R0FKEBC	CRCW120612R4FKEBC	CRCW06031M27FKEBC
CRCW080595R3FKEBC	CRCW08056K80FKEBC	CRCW06038K45FKEBC	CRCW0805287KFKEBC
CRCW1206374RFKEBC	CRCW0805105RFKEAC	CRCW1206475KFKEBC	CRCW1206182RFKEBC
CRCW080526R7FKEBC	CRCW060329R4FKEBC	CRCW0805200KJNEBC	CRCW080591R0FKEAC
CRCW120664R9FKEAC	CRCW120618R2FKEBC	CRCW12061K20FKEBC	CRCW0603158RFKEBC
CRCW120618R7FKEAC	CRCW1206232RFKEAC	CRCW0805422RFKEAC	CRCW0805620KFKEAC
CRCW12062R70JNEAC	CRCW120620R0JNEAC	CRCW0603487RFKEAC	CRCW06031M69FKEAC
CRCW060328K0FKEBC	CRCW1206316KFKEBC	CRCW12064K12FKEBC	CRCW1206102KFKEBC
CRCW08055M23FKEAC	CRCW12065K49FKEBC	CRCW080527K0JNEBC	CRCW06039K53FKEBC
CRCW060336K0JNEBC	CRCW0805274RFKEBC	CRCW08051M65FKEBC	CRCW12064K53FKEBC
CRCW0805180KJNEBC	CRCW0805820RFKEBC	CRCW06031R20JNEAC	CRCW04024M87FKEDC
CRCW08054M42FKEBC	CRCW08054K12FKEBC	CRCW060357K6FKEBC	CRCW12062M37FKEAC
CRCW040210R7FKEDC	CRCW12063M60FKEBC	CRCW080539R2FKEBC	CRCW12062K37FKEBC
CRCW1206453KFKEBC	CRCW080530K0JNEBC	CRCW080530K1FKEBC	CRCW060388R7FKEBC
CRCW0603953RFKEBC	CRCW12063M30FKEBC	CRCW12063M16FKEAC	CRCW08052M26FKEAC
CRCW06036M81FKEBC	CRCW06032M05FKEBC	CRCW1206160RJNEBC	CRCW120669K8FKEBC
CRCW1206806KFKEBC	CRCW12065K10JNEBC	CRCW08051K58FKEBC	CRCW0805442KFKEBC
CRCW08052M61FKEAC	CRCW0603143RFKEBC	CRCW06032M21FKEBC	CRCW080551R0FKEBC
CRCW080511R3FKEBC	CRCW1206158KFKEBC	CRCW060356R0FKEBC	CRCW06032M61FKEAC
CRCW0805665RFKEBC	CRCW12062K49FKEBC	CRCW120690K9FKEBC	CRCW060395K3FKEBC