


Thick Film Chip Resistors, High Voltage



FEATURES

- AEC-Q200 qualified
- Voltages up to 3000 V
- Automatic placement capability
- Termination style: 3-sided wraparound termination
- Tape and reel packaging available
- Internationally standardized sizes, custom sizes available
- Termination material: solder-coated nickel barrier or solder coated non-magnetic terminations standard
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE

LINKS TO ADDITIONAL RESOURCES



3D Models

STANDARD ELECTRICAL SPECIFICATIONS

GLOBAL MODEL	CASE SIZE	POWER RATING $P_{70\text{ }^{\circ}\text{C}}$ W	MAX. WORKING VOLTAGE ⁽²⁾ V	RESISTANCE RANGE ⁽¹⁾ Ω	TOLERANCE \pm %	TEMPERATURE COEFFICIENT ⁽³⁾ \pm ppm/ $^{\circ}\text{C}$
CRMA1206	1206	0.30	1000	150 to 15M	0.5, 1, 2, 5, 10	100
CRMA1210	1210	0.35	1250	300 to 20M	0.5, 1, 2, 5, 10	100
CRMA2010	2010	0.50	2000	500 to 40M	0.5, 1, 2, 5, 10	100
CRMA2510	2510	0.80	2500	1K to 60M	0.5, 1, 2, 5, 10	100
CRMA2512	2512	1.0	3000	1K to 75M	0.5, 1, 2, 5, 10	100

Notes

- For non-standard sizes, lower values or higher power rating requirement, contact factory
- ⁽¹⁾ Resistance values calibrated at 10 V_{DC}. Calibration at other voltages available upon request
- ⁽²⁾ Continuous working voltage shall be $\sqrt{P \times R}$ or maximum working voltage, whichever is less
- ⁽³⁾ Reference only: not for all values specified. Consult factory for your size and value

TECHNICAL SPECIFICATIONS

PARAMETER	UNIT	CRMA1206	CRMA1210	CRMA2010	CRMA2510	CRMA2512
Rated dissipation at 70 $^{\circ}\text{C}$	W	0.30	0.35	0.50	0.80	1.0
Limiting element voltage	V _≡	1000	1250	2000	2500	3000
Insulation resistance	Ω	$\geq 10^{11}$	$\geq 10^{11}$	$\geq 10^{11}$	$\geq 10^{11}$	$\geq 10^{11}$
Category temperature range	$^{\circ}\text{C}$	-55 to +155	-55 to +155	-55 to +155	-55 to +155	-55 to +155
Weight/1000 (typical)	g	12.2	19.6	32.2	39.8	49.7
VCR (typical)	ppm/V	< 2	< 2	< 2	< 2	< 2

GLOBAL PART NUMBER INFORMATION

Global Part Numbering: CRMA1210AF1K00FLET (preferred part number format)


GLOBAL MODEL	SIZE	TERMINAL STYLE	TERMINAL MATERIAL	RESISTANCE VALUE	TOLERANCE	TCR	SOLDER TERMINATION	PACKAGING
CRMA	1206 1210 2010 2510 2512	A = 3-sided	F = nickel barrier G = non-magnetic	R = Ω K = k Ω M = M Ω 110R = 110 Ω 49K9 = 49.9 k Ω 10M0 = 10 M Ω	D = $\pm 0.5\%$ F = $\pm 1\%$ G = $\pm 2\%$ J = $\pm 5\%$ K = $\pm 10\%$	K = 100 ppm	E = Sn100	B = bulk (250 pcs max.) F = T / R (full reel) 1 = T / R (1000 pcs) 5 = T / R (500 pcs) T = T / R (250 pcs min.) W = waffle tray

Note

- For additional information on packaging, refer to the Surface Mount Resistor Packaging document (www.vishay.com/doc?31543)


DIMENSIONS in inches (millimeters)

TERMINATION STYLE A (3-SIDED WRAPAROUND)	MODEL	LENGTH (L)	WIDTH (W)	THICKNESS (T)
	CRMA1206	0.125 \pm 0.006 (3.18 \pm 0.15)	0.063 \pm 0.006 (1.60 \pm 0.15)	0.025 \pm 0.004 (0.64 \pm 0.10)
	CRMA1210	0.125 \pm 0.006 (3.18 \pm 0.15)	0.100 \pm 0.006 (2.54 \pm 0.15)	0.025 \pm 0.004 (0.64 \pm 0.10)
	CRMA2010	0.200 \pm 0.006 (5.08 \pm 0.15)	0.100 \pm 0.006 (2.54 \pm 0.15)	0.025 \pm 0.004 (0.64 \pm 0.10)
	CRMA2510	0.250 \pm 0.006 (6.35 \pm 0.15)	0.100 \pm 0.006 (2.54 \pm 0.15)	0.025 \pm 0.004 (0.64 \pm 0.10)
	CRMA2512	0.250 \pm 0.006 (6.35 \pm 0.15)	0.126 \pm 0.006 (3.20 \pm 0.15)	0.025 \pm 0.004 (0.64 \pm 0.10)



TYPE	TERMINATION MATERIAL	TERMINATION STYLE	TERMINATION STYLE / MATERIAL CODE	SOLDER TERMINATION CODE
Solderable	Nickel barrier	3-sided (wraparound)	AF	E
Solderable	Non-magnetic	3-sided (wraparound)	AG	E

DERATING CURVE



MATERIAL SPECIFICATIONS

Resistive element	Ruthenium oxide
Encapsulation	Epoxy
Substrate	96 % alumina
Termination	Solder-coated nickel barrier
Solder finish	Pure tin standard



PERFORMANCE		
TEST	CONDITIONS OF TEST	TEST RESULTS (TYPICAL TEST LOTS)
Thermal shock	-55 °C to +150 °C, 1000 cycles, 15 min at each extreme	$\pm (1.0 \% + 0.05 \Omega)$
High temperature exposure	1000 h at +170 °C	$\pm (1.0 \% + 0.05 \Omega)$
Bias humidity	+85 °C, 85 % RH, 10 % bias, 1000 h	$\pm (1.0 \% + 0.0005 \Omega)$
Mechanical shock	100 g's for 6 ms, 5 pulses	$\pm (0.5 \% + 0.0005 \Omega)$
Vibration	Frequency varied 10 Hz to 2000 Hz in 1 min, 3 directions, 12 h	$\pm (0.5 \% + 0.0005 \Omega)$
Load life	1000 h at rated power, +70 °C, 1.5 h "ON", 0.5 h "OFF"	$\pm (1.0 \% + 0.0005 \Omega)$
Resistance to solder heat	+260 °C solder, 10 s to 12 s dwell, 25 mm/s emergence	$\pm (1.0 \% + 0.0005 \Omega)$
Moisture resistance	MIL-STD-202, method 106, 0 % power, 7a and 7b not required	$\pm (1.0 \% + 0.0005 \Omega)$



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

CRMA1206AF11K0FKEF	CRMA2512AF33M0FKEF	CRMA2510AF10M0FKEF	CRMA1206AF1M00FKEF
CRMA2010AF10M0FKEF	CRMA2010AF550KFKEF	CRMA2010AF20M0FKEF	CRMA2512AF15M0FKEF
CRMA2512AF75M0FKEF	CRMA2010AF3M32FKEF	CRMA1210AF10M0FKEF	CRMA1210AF4K70FKEF
CRMA2512AF2M00FKEF	CRMA1206AF500KFKEF	CRMA2010AF1K00FKEF	CRMA1206AF10M0DKEF
CRMA1206AF10K0FKEF	CRMA1206AF10M0FKEF	CRMA1206AF14M0DKEF	CRMA1210AF20M0FKEF
CRMA2010AF100KFKEF	CRMA2010AF1M00FKEF	CRMA2512AF10M0FKEF	CRMA2512AF1M00FKEF
CRMA2512AF50M0FKEF	CRMA1206AF100DFKEF	CRMA1206AF100KFKEF	CRMA1206AF10K0DKEF
CRMA1206AF14M0FKEF	CRMA1206AF15M0DKEF	CRMA1206AF15M0FKEF	CRMA1206AF180KDKEF
CRMA1206AF180KFKEF	CRMA1206AF220KDKEF	CRMA1206AF220KFKEF	CRMA1206AF2M15DKEF
CRMA1206AF2M15FKEF	CRMA1206AF300KDKEF	CRMA1206AF300KFKEF	CRMA1206AF3M30DKEF
CRMA1206AF3M30FKEF	CRMA1206AF47K0DKEF	CRMA1206AF47K0FKEF	CRMA1206AF4M70DKEF
CRMA1206AF4M70FKEF	CRMA1206AF510KDKEF	CRMA1206AF510KFKEF	CRMA1206AF6M00DKEF
CRMA1206AF6M00FKEF	CRMA1206AF750KDKEF	CRMA1206AF750KFKEF	CRMA1210AF10K0DKEF
CRMA1210AF10K0FKEF	CRMA1210AF120KDKEF	CRMA1210AF120KFKEF	CRMA1210AF15M0DKEF
CRMA1210AF15M0FKEF	CRMA1210AF1M00DKEF	CRMA1210AF1M00FKEF	CRMA1210AF20M0DKEF
CRMA1210AF2M10DKEF	CRMA1210AF2M10FKEF	CRMA1210AF3M00DKEF	CRMA1210AF3M00FKEF
CRMA1210AF4M99DKEF	CRMA1210AF4M99FKEF	CRMA1210AF549KDKEF	CRMA1210AF549KFKEF
CRMA1210AF62K0DKEF	CRMA1210AF62K0FKEF	CRMA1210AF681KDKEF	CRMA1210AF681KFKEF
CRMA2010AF100KDKEF	CRMA2010AF1M00DKEF	CRMA2010AF2M70DKEF	CRMA2010AF2M70FKEF
CRMA2010AF33M0DKEF	CRMA2010AF33M0FKEF	CRMA2010AF40M0DKEF	CRMA2010AF40M0FKEF
CRMA2010AF47K0DKEF	CRMA2010AF47K0FKEF	CRMA2010AF499KDKEF	CRMA2010AF499KFKEF
CRMA2512AF10M0DKEF	CRMA2512AF1M00DKEF	CRMA2512AF20M0DKEF	CRMA2512AF20M0FKEF
CRMA2512AF2M20DKEF	CRMA2512AF2M20FKEF	CRMA2512AF40M0DKEF	CRMA2512AF40M0FKEF
CRMA2512AF499KDKEF	CRMA2512AF499KFKEF	CRMA2512AF50M0DKEF	CRMA1206AF100KDKEF
CRMA1206AF3M00FKEF	CRMA1206AF5M00FKEF	CRMA2510AF1K96FKE1	CRMA2512AF10K0FKEF