

www.vishay.com

Vishay Dale

# Wirewound Resistors, High Energy, Silicone Coated, Axial Lead



#### **FEATURES**

- High continuous energy handling up to 106.5 J
- · High temperature silicone coating
- Complete welded construction
- Excellent stability in operation
- High power to size ratio
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912





ROHS COMPLIANT HALOGEN


FKEE
Available
00000
<u>GREEN</u>
(5-2008)
Available

STANDARD ELECTRICAL SPECIFICATIONS							
GLOBAL MODEL	POWER RATING <sup>(1)</sup> P <sub>25°C</sub> W  CHARACTERISTIC U  +250 °C	POWER RATING <sup>(1)</sup> P <sub>25°C</sub> W CHARACTERISTIC V +350°C	RESISTANCE RANGE Ω	MAXIMUM SHORT TERM PULSE ENERGY J	TOLERANCE ± %	WEIGHT (max.) g	
CW02BHE	3.0	3.75	1.5 to 87.5	10.4	5, 10	0.7	
CW005HE	5.0	6.5	5.5 to 343.6	39.1	5, 10	4.2	
CW010HE	10.0	13.0	15.0 to 938.0	106.5	5, 10	9.0	

#### Note

<sup>(1)</sup> Vishay Dale CW...HE models have two power ratings, depending on operating temperature and stability requirements.


TECHNICAL SPECIFICATIONS				
PARAMETER	UNIT	CWHE RESISTOR CHARACTERISTICS		
Temperature Coefficient	ppm/°C	$\pm$ 30 for 10 $\Omega$ and above, $\pm$ 50 for 1.0 $\Omega$ to 9.9 $\Omega$		
Short Time Overload	-	5x rated power for 5 s for CW02BHE 10x rated power for 5 s for CW005HE and CW010HE		
Terminal Strength	lb	10 minimum		
Maximum Working Voltage	V	$(P \times R)^{1/2}$		
Operating Temperature Range	°C	Characteristic U = -65 to +250, characteristic V = -65 to +350		
Power Rating	-	Characteristic U = +250 °C max. hot spot temperature, $\pm$ 0.5 % max. $\Delta R$ in 2000 h load life Characteristic V = +350 °C max. hot spot temperature, $\pm$ 3.0 % max. $\Delta R$ in 2000 h load life		







### STANDARD ENERGY PERFORMANCE CHARACTERISTICS

GLOBAL MODEL	RESISTANCE RANGE Ω	MAX. PULSE ENERGY J/Ω	FUSING ENERGY J/Ω	CURRENT TO FUSE $^{(1)}$ A/ $\Omega$	POWER TO FUSE <sup>(1)</sup> W/Ω
	1.5 to 2.0	5.200	21.150	7.2700	211.3000
CW02BHE	2.1 to 2.8	3.286	13.393	4.1357	134.0286
	2.9 to 4.0	2.000	8.200	2.2650	82.0925
	4.1 to 5.6	1.268	5.196	1.2857	51.8839
	5.7 to 7.6	0.842	3.408	0.7684	34.1000
	7.7 to 10.8	0.519	2.111	0.4250	21.1056
GWUZBFE	10.9 to 15.4	0.325	1.312	0.2351	13.0870
	15.5 to 21.8	0.202	0.817	0.1312	8.1839
	21.9 to 30.5	0.121	0.521	0.0748	5.1980
	30.6 to 41.7	0.084	0.341	0.0444	3.4101
	41.8 to 59.1	0.052	0.213	0.0247	2.1289
	59.2 to 87.5	0.031	0.125	0.0128	1.2442
	5.5 to 7.6	5.145	20.921	1.9026	209.2105
	7.7 to 10.5	3.324	13.552	1.1086	135.4800
	10.6 to 15.1	2.040	8.311	0.6040	83.1311
	15.2 to 21.4	1.280	5.206	0.3369	52.0425
	21.5 to 29.3	0.836	3.410	0.1993	34.1003
C/MO0E LIE	29.4 to 41.8	0.519	2.110	0.1098	21.1053
CW005HE	41.9 to 59.6	0.322	1.309	0.0607	13.0871
	59.7 to 84.6	0.201	0.818	0.0338	8.1840
	84.7 to 118.6	0.120	0.519	0.0192	5.1980
	118.7 to 162.3	0.084	0.341	0.0114	3.4100
	162.4 to 230.6	0.052	0.213	0.0063	2.1290
	230.7 to 343.6	0.031	0.125	0.0033	1.2442
	15.0 to 20.7	5.145	20.923	0.6986	209.2101
	20.8 to 28.6	3.329	13.549	0.4070	135.4773
	28.7 to 41.0	2.037	8.312	0.2224	83.1395
	41.1 to 58.0	1.281	5.217	0.1243	52.1643
CW010HE	58.1 to 79.7	0.836	3.410	0.0733	34.1003
	79.8 to 113.6	0.518	2.111	0.0404	21.1054
	113.7 to 162.3	0.322	1.309	0.0223	13.0871
	162.4 to 230.5	0.201	0.818	0.0124	8.1841
	230.6 to 323.2	0.120	0.520	0.0071	5.1980
	323.3 to 442.7	0.084	0.341	0.0042	3.4100
	442.8 to 629.3	0.052	0.213	0.0023	2.1290
	629.4 to 938.0	0.031	0.124	0.0012	1.2442








#### Note

(1) Time to fuse is 0.1 s.

www.vishay.com

Vishay Dale

#### **DIMENSIONS** in inches (millimeters)



MODEL	DIMENSIONS in inches [millimeters]				
MODEL	Α	B [MAXIMUM] (2)	С	D	
CW02BHE	0.562 ± 0.062 [14.27 ± 1.57]	0.622 [15.80]	$0.188 \pm 0.032  [4.78 \pm 0.813]$	0.032 ± 0.002 [0.813 ± 0.051]	
CW005HE	0.875 ± 0.062 [22.22 ± 1.57]	1.0 [25.40]	$0.312 \pm 0.032  [7.92 \pm 0.813]$	0.040 ± 0.002 [1.02 ± 0.051]	
CW010HE	1.781 ± 0.062 [45.24 ± 1.57]	1.875 [47.62]	$0.375 \pm 0.032 \ [9.52 \pm 0.813]$	$0.040 \pm 0.002 [1.02 \pm 0.051]$	

#### **Notes**

(1) On some standard reel pack methods, the leads may be trimmed to a shorter length than shown.

#### **MATERIAL SPECIFICATIONS**

**Element:** Nickel-chrome alloy **Core:** Ceramic: Steatite

Coating: Special high temperature silicone

Standard Terminals: Tinned Copperweld®
End Caps: Stainless steel


Part Marking: DALE, model, wattage (3), value, tolerance,

date code

Note

(3) Wattage marked on resistor will be "V" characteristic.

#### **DERATING**



PERFORMANCE						
TEST	CONDITIONS OF TEST					
Thermal Shock	Rated power applied until thermally stable, then a minimum of 15 min at -55 °C	± (2.0 % + 0.05 Ω) ΔR				
Short Time Overload	5x rated power for 5 s for CW02BHE 10x rated power for 5 s for CW005HE and CW010HE	± (2.0 % + 0.05 Ω) ΔR				
High Temperature Exposure	250 h at +350 °C	$\pm$ (4.0 % + 0.05 $\Omega$ ) $\Delta R$				
Load Life	2000 h at rated power, +25 °C, 1.5 h "ON", 0.5 h "OFF"	$\pm$ (3.0 % + 0.05 Ω) ΔR				

#### Note

<sup>(2)</sup> B (maximum) dimension is clean lead to clean lead.

<sup>(4)</sup> All ΔR figures shown are maximum, based upon testing requirements per MIL-PRF-26 at a maximum operating temperature of +350 °C.
ΔR maximum figures are considerably lower when tested at a maximum operating temperature of +250 °C.



### **Legal Disclaimer Notice**

Vishay

### **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

# **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

# Vishay:

CW00510R00JE73HE	CW02B7R500JE12HE	CW02B15R00JE12H	E CW02B47R00JE12H	E CW02B50R00JE12HE
CW00510R00JE12HE	CW01010R00JE12HE	CW005150R0JE73HE	CW010499R0JE12HE	CW005330R0JE12HE
CW010390R0JE12HE	CW02B10R00JE12HE	CW00533R00JE73HE	CW010270R0JE12HE	CW010680R0JE73HE
CW02B68R00JE70HE	CW02B47R00JE70HE	CW01022R00JE12HE	CW010200R0JE73HE	CW010470R0JE73HE
CW01068R00JE12HE	CW010820R0JE12HE	CW02B20R00JE70HE	CW00568R00JE12HE	CW005100R0JE73HE
CW010390R0JE73HE	CW01056R00JE12HE	CW01022R00JE73HE	CW01027R00JE73HE	CW010100R0JE73HE
CW010330R0JE73HE	CW010220R0JE73HE	CW0054R700JE12HE	CW00530R00JE12HE	CW00556R00JE12HE
CW00591R00JE12HE	CW010250R0JE73HE	CW00539R00JE12HE	CW00539R00JE73HE	CW01012R00JE73HE
CW01039R00JE12HE	CW005220R0JE73HE	CW010220R0JE12HE	CW01030R00JE73HE	CW01056R00JE73HE
CW010110R0JE73HE	CW02B4R000JE12HE	CW02B22R00JE70HE	CW00522R00JE12HE	CW00527R00JE12HE
CW00556R00JE73HE	CW02B10R00JE70HE	CW00520R00JE12HE	CW00533R00JE12HE	CW005250R0JE73HE
CW010620R0JE12HE	CW01020R00JE12HE	CW010200R0JE12HE	CW00512R00JE12HE	CW005270R0JE12HE
CW010150R0JE73HE	CW01010R00JE73HE	CW02B20R00JE12HE	CW01012R00JE12HE	CW01030R00JE12HE
CW01050R00JE12HE	CW005180R0JE73HE	CW01050R00JE73HE	CW010470R0JE12HE	CW010499R0JE73HE
CW02B15R00JE70HE	CW02B68R00JE12HE	CW00550R00JE73HE	CW00591R00JE73HE	CW01015R00JE12HE
CW01047R00JE12HE	CW010120R0JE12HE	CW010680R0JE12HE	CW01091R00JE12HE	CW010180R0JE73HE
CW010270R0JE73HE	CW02B50R00JE70HE	CW010150R0JE12HE	CW02B4R000JE70HE	CW02B22R00JE12HE
CW01091R00JE73HE	CW010100R0JE12HE	CW00547R00JE73HE	CW005180R0JE12HE	CW005250R0JE12HE
CW010120R0JE73HE	CW01020R00JE73HE	CW01033R00JE73HE	CW010110R0JE12HE	CW010250R0JE12HE
CW00522R00JE73HE	CW005150R0JE12HE	CW005100R0JE12HE	CW010620R0JE73HE	CW010820R0JE73HE