

## Audio Jack Detector with Send / End Detect

## DESCRIPTION

The DG2592 is an audio jack detector and pop noise control switch IC. It integrates the circuits necessary to detect the presence of a stereo headset with a microphone and send / end control button.

When there is no ear phone detected, the DG2592 connects the microphone bias line to ground through the MIC pin. The DG2592 also gives a logic high signal to the baseband controller through the DET pin.

The DG2592 senses the DC levels at both L\_Detect and GND\_Detect. When an ear phone is plugged in, the voltage at both pins will go low. The DG2592 will indicate the presence of the ear phone by pulling DET low and the MIC switch will turn off.

The DG2592 is available in small miniQFN10 of 1.4 mm x 1.8 mm x 0.55 mm and ultra thin UTMQFN10 of 0.35 mm thickness.

## FEATURES


- Wide operating voltage range: 1.6 V to 5.5 V
- Low quiescent current of 10  $\mu$ A, max. at  $V_{DD} = 1.8$  V
- Integrated sense comparator for audio L of 1.4 V  $\pm$  5 % threshold
- 1.2  $\Omega$ /max. MIC bias switch provides quick discharge and clamping
- ESD Protected
  - Human body model > 8 kV
  - Charged device model > 2 kV
  - IEC 61000-4-2 air discharge > 15 kV
  - IEC 61000-4-2 contact discharge > 8 kV
- Ultra thin and compact miniQFN10 and UTDFN10
- Material categorization: for definitions of compliance please see [www.vishay.com/doc/99912](http://www.vishay.com/doc/99912)



**RoHS**  
COMPLIANT  
HALOGEN  
**FREE**

## APPLICATIONS

- Cellular phones
- Tablet devices
- Portable media players
- Digital cameras



### Fig. 1 - Typical Application Circuit

## PACKAGE OUTLINE





Fig. 2 - Device Pin Out miniQFN10 Top View, Pin 1 Dot Marking is on Top of the Device


| PIN DESCRIPTION |                  |        |                                                                                                                                        |
|-----------------|------------------|--------|----------------------------------------------------------------------------------------------------------------------------------------|
| PIN#            | NAME             | TYPE   | FUNCTION                                                                                                                               |
| 1               | GND              | Power  | Ground                                                                                                                                 |
| 2               | MIC              | Output | Microphone bias switch input                                                                                                           |
| 3               | V <sub>DD</sub>  | Power  | Power supply for ear jack plug in detection circuit. A bypass capacitor of 0.1 $\mu$ F is recommended as close as possible to this pin |
| 4               | L_DET            | Input  | Connected to L_DET pin at audio jack                                                                                                   |
| 5               | GND_DET          | Input  | Connect to GND_DET pin at audio jack                                                                                                   |
| 6               | DET              | Output | Detect logic output connected to baseband controller                                                                                   |
| 7               | S/E              | Output | S/E detect comparator output                                                                                                           |
| 8               | S/E_DET          | Input  | Non-inverting input of S/E press detection comparator                                                                                  |
| 9               | S/E_REF          | Input  | Inverting input of S/E press detection comparator. External voltage is provided as press detection reference threshold                 |
| 10              | V <sub>DD2</sub> | Power  | Power supply pin for the S/E detection circuit. A bypass capacitor of 0.1 $\mu$ F is recommended as close as possible to this pin      |

| ORDERING INFORMATION |                                     |                   |            |                           |               |
|----------------------|-------------------------------------|-------------------|------------|---------------------------|---------------|
| PART NUMBER          | FUNCTION                            | TEMPERATURE RANGE | PACKAGE    | SIZE                      | REEL QUANTITY |
| DG2592DN-T1-GE4      | Audio jack detector with S/E detect | -40 °C to 85 °C   | miniQFN-10 | 1.4 mm x 1.8 mm x 0.55 mm | 3000          |
| DG2592DN1-T1-GE4     |                                     |                   | UTMQFN-10  | 1.4 mm x 1.8 mm x 0.35 mm | 3000          |

## DEVICE MARKING



7 = DG2592 Marking Code, W = Date / Lot Traceability Code


**Fig. 3 - Functional Block Diagram**
**TRUTH TABLE**

| INPUTS |         | OUTPUTS |      | AUDIO JACK   |
|--------|---------|---------|------|--------------|
| L_DET  | GND_DET | DET     | MIC  |              |
| 0      | 0       | Low     | High | Detected     |
| 1      | 0       | High    | Low  | Not detected |
| 0      | 1       | High    | Low  | Not detected |
| 1      | 1       | High    | Low  | Not detected |

**ABSOLUTE MAXIMUM RATINGS**

| PINS OR PARAMETERS                 |                                                           | CONDITIONS                                              | LIMITS                     | UNIT  |
|------------------------------------|-----------------------------------------------------------|---------------------------------------------------------|----------------------------|-------|
| V <sub>DD</sub> , V <sub>DD2</sub> |                                                           | Reference to GND                                        | -0.3 to 6                  | V     |
| L_Detect, GND_Detect, DET          |                                                           | Reference to GND                                        | -0.3 V to V <sub>DD</sub>  |       |
| S/E_DET, S/E_REF, S/E              |                                                           | Reference to GND                                        | -0.3 V to V <sub>DD2</sub> |       |
| MIC                                |                                                           |                                                         | -0.3 to 6                  |       |
| Storage Temperature                |                                                           |                                                         | -65 to +150                | °C    |
| MSL                                |                                                           | Moisture sensitivity level (JEDEC® J-STD-020)           | 1                          | Level |
| I <sub>MIC</sub>                   |                                                           | Switch DC current                                       | 200                        | mA    |
| I <sub>MICPEAK</sub>               |                                                           | Switch peak current (pulsed at 1 ms, < 10 % duty cycle) | 500                        |       |
| Latch Up Current                   |                                                           | JESD78                                                  | ± 600                      |       |
| ESD                                | Human body model; ANSI / ESDA / JEDEC JS-001              |                                                         | > 8000                     | V     |
|                                    | Charged device model; JESD22-C101                         |                                                         | > 2000                     |       |
|                                    | Machine model; JESD22-A115                                |                                                         | > 400                      |       |
|                                    | IEC61000-2-4, level 4<br>L_DET, GND_DET, MIC and GND pins | Contact                                                 | > 8000                     |       |
|                                    |                                                           | Air                                                     | > 15 000                   |       |

**RECOMMENDED OPERATING CONDITION**

|                                    |  |                       |    |
|------------------------------------|--|-----------------------|----|
| V <sub>DD</sub> , V <sub>DD2</sub> |  | 1.6 to 5.5            | V  |
| Ear Jack Detection Input Pins      |  | 0 to V <sub>DD</sub>  | V  |
| S/E Press Detection Input Pins     |  | 0 to V <sub>DD2</sub> | V  |
| MIC Bias Voltage                   |  | 0 to 5.5              | V  |
| Operating Junction Temperature     |  | -40 to +125           | °C |

**Note**

- The control logic pins should not float and should be set to either high or low logic levels.


Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

**ELECTRICAL CHARACTERISTICS**


| PARAMETER                        | SYMBOL          | TEST CONDITION                                                                                                                                                                                                  | LIMITS |      |      | UNIT          |
|----------------------------------|-----------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------|------|------|---------------|
|                                  |                 | UNLESS OTHERWISE SPECIFIED,<br>$V_{DD} = 1.8\text{ V}$ , $V_{DD2} = 2.1\text{ V}$ , $T_A = -40\text{ }^{\circ}\text{C}$ to $85\text{ }^{\circ}\text{C}$ ,<br>TYPICAL VALUES are at $25\text{ }^{\circ}\text{C}$ | MIN.   | TYP. | MAX. |               |
| Quiescent Current                | $I_Q$           | L_DETECT, GND_DETECT are open                                                                                                                                                                                   | -      | 6    | 10   | $\mu\text{A}$ |
| Ear Jack In Current              | $I_{DD}$        | L_DETECT, GND_DETECT are connected with $10\text{ k}\Omega$ to GND                                                                                                                                              | -      | 3    | 6    |               |
| S/E Detection Current            | $I_{DD2}$       | S/E_DET = $0\text{ V}$ , S/E_REF = $1.05\text{ V}$                                                                                                                                                              | -      | 2    | 3.5  |               |
| L_DETECT Reference Voltage       | $V_{TH\_L}$     | L_DET switching low to high                                                                                                                                                                                     | 1.33   | 1.4  | 1.5  | V             |
| Propagation Delay to DET         | $t_{PLH}$       | $C_{OUT} = 15\text{ pF}$ , GND_DET = $0\text{ V}$ ,<br>L_DET = $1.52\text{ V}$ to DET = $0.9\text{ V}$                                                                                                          | 80     | 149  | 300  | ns            |
| Propagation Delay to DET         | $t_{PHL}$       | $C_{OUT} = 15\text{ pF}$ , GND_DET = $0\text{ V}$ ,<br>L_DET = $1.31\text{ V}$ to DET = $0.9\text{ V}$                                                                                                          | 130    | 325  | 550  |               |
| Low Voltage L_DET Leakage        | $I_{L\_DET}$    | L_DET = $0\text{ V}$                                                                                                                                                                                            | -      | 0.84 | 2    | $\mu\text{A}$ |
| High Voltage L_DET Leakage       | $I_{H\_DET}$    | L_DET = $1.8\text{ V}$                                                                                                                                                                                          | -      | 30   | -    | pA            |
| L_DET Input Capacitance          | $C_{L\_DET}$    |                                                                                                                                                                                                                 | -      | 4    | -    | pF            |
| GND_DETECT Logic Low Voltage     | $V_{IL\_GND}$   |                                                                                                                                                                                                                 | 0.63   | 0.86 | -    | V             |
| GND_DETECT Logic High Voltage    | $V_{IH\_GND}$   |                                                                                                                                                                                                                 | -      | 0.89 | 1.17 |               |
| GND_DET Propagation Delay to DET | $t_{PGND\_DET}$ | $C_{OUT} = 15\text{ pF}$ , $R_L = 1\text{ M}\Omega$ , L_DET = $0\text{ V}$ ,<br>GND_DET switches between $0\text{ V}$ and $1.8\text{ V}$                                                                        | -      | 10   | -    | ns            |
| Low Voltage GND_DET Leakage      | $I_{IL}$        | GND_DET = $0\text{ V}$                                                                                                                                                                                          | -      | 0.93 | 2    | $\mu\text{A}$ |
| High Voltage GND_DET Leakage     | $I_{IH}$        | GND_DET = $1.8\text{ V}$                                                                                                                                                                                        | -      | 80   | -    | pA            |
| GND_DET Input Capacitance        | $C_{G\_DET}$    | $f = 1\text{ MHz}$                                                                                                                                                                                              | -      | 3.5  | -    | pF            |
| MIC Pull Down Resistance         | $R_{MIC}$       | $I_{MIC} = 1\text{ mA}$ L_DETECT, GND_DETECT = open                                                                                                                                                             | -      | -    | 1.25 | $\Omega$      |
| MIC Leakage                      |                 | $V_{MIC} = 2.4\text{ V}$                                                                                                                                                                                        | -1     | -    | 1    | $\mu\text{A}$ |
| DET Pull Up Resistance           | $R_{OUTH}$      | L_DETECT, GND_DETECT = open                                                                                                                                                                                     | -      | 135  | 200  | $\Omega$      |
| DET Pull Down Resistance         | $R_{OUTL}$      | L_DETECT, GND_DETECT are connected with $10\text{ k}\Omega$ to GND                                                                                                                                              | -      | 120  | 200  |               |
| DET High Logic Voltage           | $V_{OUTH}$      | $I_{DET} = 0.1\text{ mA}$ , L_DETECT, GND_DETECT = open                                                                                                                                                         | 1.6    | -    | -    | V             |
| DET Low Logic Voltage            | $V_{OUTL}$      | $I_{DET} = 0.1\text{ mA}$ , L_DETECT, GND_DETECT are connected with<br>$10\text{ k}\Omega$ to GND                                                                                                               | -      | -    | 0.3  |               |
| DET Rise Time                    | $t_{DET\_R}$    | $C_{OUT} = 15\text{ pF}$ , $R_L = 1\text{ M}\Omega$ , DET = $10\%$ to $90\%$                                                                                                                                    | -      | 14   | -    | ns            |
| DET Fall Time                    | $t_{DET\_F}$    | $C_{OUT} = 15\text{ pF}$ , $R_L = 1\text{ M}\Omega$ , DET = $90\%$ to $10\%$                                                                                                                                    | -      | 4.4  | -    |               |
| Propagation Delay to S/E         | $t_{PS/E}$      | $C_{OUT} = 15\text{ pF}$ , $R_L = 1\text{ M}\Omega$ , $V_{CM} = \text{mid-supply}$ ,<br>$100\text{ mV}$ overdrive                                                                                               | 50     | 170  | 500  |               |
| Input Leakage                    | $I_{SE\_IN}$    | $V_{CM} = 0.9\text{ V}$                                                                                                                                                                                         | -      | 4    | -    | pA            |
| Input Capacitance                | $C_{SE\_IN}$    | $f = 1\text{ MHz}$                                                                                                                                                                                              | -      | 3.5  | -    | pF            |
| Voltage Output Low               | $V_{OL}$        | $I_{OL} = 0.1\text{ mA}$                                                                                                                                                                                        | -      | -    | 0.2  | V             |
| Voltage Output High              | $V_{OH}$        | $I_{OH} = 0.1\text{ mA}$                                                                                                                                                                                        | 1.9    | -    | -    |               |
| Rise Time                        | $t_{S/E\_R}$    | $C_{OUT} = 15\text{ pF}$ , $R_L = 1\text{ M}\Omega$ , S/E = $10\%$ to $90\%$                                                                                                                                    | -      | 16   | -    | ns            |
| Fall Time                        | $t_{S/E\_F}$    | $C_{OUT} = 15\text{ pF}$ , $R_L = 1\text{ M}\Omega$ , S/E = $90\%$ to $10\%$                                                                                                                                    | -      | 12.1 | -    |               |




**TYPICAL CHARACTERISTICS** ( $T_A = 25^\circ\text{C}$ , unless otherwise noted)




Quiescent Current vs.  $V_{DD}$




Ear Jack In Current vs. Temperature




Quiescent Current vs. Temperature









S/E Detection Current vs.  $V_{DD2}$



Ear Jack In Current vs.  $V_{DD}$




S/E Detection Current vs. Temperature


**TYPICAL CHARACTERISTICS** ( $T_A = 25\text{ }^{\circ}\text{C}$ , unless otherwise noted)

**MIC On Resistance vs.  $V_{DD}$** 

**MIC Leakage Current vs. Temperature**

**MIC On Resistance vs. Temperature**

**DET Pulldown Resistance vs.  $I_{OUT}$** 

**MIC Leakage Current vs.  $V_{MIC}$** 

**DET Pulldown Resistance vs. Temperature**




**TYPICAL CHARACTERISTICS** ( $T_A = 25^\circ\text{C}$ , unless otherwise noted)




**DET Pullup Resistance vs.  $I_{OUT}$**




**SE Pulldown Resistance vs. Temperature**




**DET Pullup Resistance vs. Temperature**









**SE Pullup Resistance vs.  $I_{OUT}$**






**SE Pulldown Resistance vs.  $I_{OUT}$**




**SE Pullup Resistance vs. Temperature**

**TYPICAL CHARACTERISTICS** ( $T_A = 25\text{ }^{\circ}\text{C}$ , unless otherwise noted)

**L\_Detect Threshold Voltage vs. Temperature**

**L\_Detect to DET Propagation Delay vs. Temperature**

**GND\_Detect Threshold Voltage vs. Temperature**

**GND\_Detect to DET Propagation Delay vs. Temperature**

**S/E\_Detect Threshold Voltage vs. Temperature**

**S/E\_Detect to S/E Propagation Delay vs. Temperature**


**TYPICAL CHARACTERISTICS** ( $T_A = 25\text{ }^{\circ}\text{C}$ , unless otherwise noted)

**L\_Detect to MIC Propagation Delay vs. Temperature**

**DET Rise / Fall Time vs. Temperature**

**S/E\_Detect to Rise / Fall Time vs. Temperature**

## TEST CIRCUIT



**Fig. 4 - Test Circuit**

## TIMING DIAGRAM




**Fig. 5 - Timing Diagram**

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see [www.vishay.com/ppg?62970](http://www.vishay.com/ppg?62970).



## RECOMMENDED MINIMUM PADS FOR MINI QFN 10L



Mounting Footprint  
Dimensions in mm (inch)



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

[DG2592DN-T1-GE4](#) [DG2592DN1-T1-GE4](#)