

## Precision CMOS Analog Switches

### DESCRIPTION

The DG417, DG418, DG419 monolithic CMOS analog switches were designed to provide high performance switching of analog signals. Combining low power, low leakages, high speed, low on-resistance and small physical size, the DG417 series is ideally suited for portable and battery powered industrial and military applications requiring high performance and efficient use of board space.

To achieve high-voltage ratings and superior switching performance, the DG417 series is built on Vishay Siliconix's high voltage silicon gate (HVSG) process. Break-before-make is guaranteed for the DG419, which is an SPDT configuration. An epitaxial layer prevents latchup.

Each switch conducts equally well in both directions when on, and blocks up to the power supply level when off.

The DG417 and DG418 respond to opposite control logic levels as shown in the Truth Table.

### FEATURES

- $\pm 15$  V analog signal range
- On-resistance -  $R_{DS(on)}$ : 20  $\Omega$
- Fast switching action -  $t_{ON}$ : 100 ns
- Ultra low power requirements -  $P_D$ : 35 nW
- TTL and CMOS compatible
- MiniDIP and SOIC packaging
- 44 V supply max. rating
- 44 V supply max. rating
- Compliant to RoHS directive 2002/95/EC



Available  
**RoHS\***  
COMPLIANT



### BENEFITS

- Wide dynamic range
- Low signal errors and distortion
- Break-before-make switching action
- Simple interfacing
- Reduced board space
- Improved reliability

### APPLICATIONS

- Precision test equipment
- Precision instrumentation
- Battery powered systems
- Sample-and-hold circuits
- Military radios
- Guidance and control systems
- Hard disk drives

### FUNCTIONAL BLOCK DIAGRAM AND PIN CONFIGURATION



#### TRUTH TABLE

| Logic | DG417 | DG418 |
|-------|-------|-------|
| 0     | ON    | OFF   |
| 1     | OFF   | ON    |

Logic "0"  $\leq 0.8$  V

Logic "1"  $\geq 2.4$  V

#### TRUTH TABLE DG419

| Logic | SW <sub>1</sub> | SW <sub>2</sub> |
|-------|-----------------|-----------------|
| 0     | ON              | OFF             |
| 1     | OFF             | ON              |

Logic "0"  $\leq 0.8$  V

Logic "1"  $\geq 2.4$  V

\* Pb containing terminations are not RoHS compliant, exemptions may apply

| ORDERING INFORMATION |                       |                                                      |
|----------------------|-----------------------|------------------------------------------------------|
| Temp. Range          | Package               | Part Number                                          |
| DG417, DG418         |                       |                                                      |
| - 40 °C to 85 °C     | 8-Pin Plastic MiniDIP | DG417DJ<br>DG417DJ-E3                                |
|                      |                       | DG418DJ<br>DG418DJ-E3                                |
|                      | 8-Pin Narrow SOIC     | DG417DY<br>DG417DY-E3<br>DG417DY-T1<br>DG417DY-T1-E3 |
|                      |                       | DG418DY<br>DG418DY-E3<br>DG418DY-T1<br>DG418DY-T1-E3 |
| DG419                |                       |                                                      |
| - 40 °C to 85 °C     | 8-Pin Plastic MiniDIP | DG419DJ<br>DG419DJ-E3                                |
|                      | 8-Pin Narrow SOIC     | DG419DY<br>DG419DY-E3<br>DG419DY-T1<br>DG419DY-T1-E3 |

| ABSOLUTE MAXIMUM RATINGS                                      |                                    |                                                          |      |
|---------------------------------------------------------------|------------------------------------|----------------------------------------------------------|------|
| Parameter (Voltages referenced to V-)                         |                                    | Limit                                                    | Unit |
| V+                                                            |                                    | 44                                                       | V    |
| GND                                                           |                                    | 25                                                       |      |
| V <sub>L</sub>                                                |                                    | (GND - 0.3) to (V+) + 0.3                                |      |
| Digital Inputs <sup>a</sup> , V <sub>S</sub> , V <sub>D</sub> |                                    | (V-) - 2 to (V+) + 2<br>or 30 mA, whichever occurs first |      |
| Current , (Any Terminal) Continuous                           |                                    | 30                                                       | mA   |
| Current, S or D (Pulsed at 1 ms, 10 % Duty Cycle)             |                                    | 100                                                      |      |
| Storage Temperature                                           | (AK Suffix)                        | - 65 to 150                                              | °C   |
|                                                               | (DJ, DY Suffix)                    | - 65 to 125                                              |      |
| Power Dissipation (Package) <sup>b</sup>                      | 8-Pin Plastic MiniDIP <sup>c</sup> | 400                                                      | mW   |
|                                                               | 8-Pin Narrow SOIC <sup>d</sup>     | 400                                                      |      |
|                                                               | 8-Pin CerDIP <sup>e</sup>          | 600                                                      |      |

Notes:

a. Signals on S<sub>X</sub>, D<sub>X</sub>, or IN<sub>X</sub> exceeding V+ or V- will be clamped by internal diodes. Limit forward diode current to maximum current ratings.

b. All leads welded or soldered to PC board.

c. Derate 6 mW/°C above 75 °C.

d. Derate 6.5 mW/°C above 75 °C.

e. Derate 12 mW/°C above 75 °C.


**SCHEMATIC DIAGRAM** Typical Channel


Figure 1.

| SPECIFICATIONS <sup>a</sup>          |                     |                                                                                                                                                                      |                |                    |                   |                               |                   |                              |                   |      |
|--------------------------------------|---------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------|--------------------|-------------------|-------------------------------|-------------------|------------------------------|-------------------|------|
| Parameter                            | Symbol              | Test Conditions<br>Unless Otherwise Specified<br>V <sub>+</sub> = 15 V, V <sub>-</sub> = - 15 V<br>V <sub>L</sub> = 5 V, V <sub>IN</sub> = 2.4 V, 0.8 V <sup>f</sup> |                | Temp. <sup>b</sup> | Typ. <sup>c</sup> | A Suffix<br>- 55 °C to 125 °C |                   | D Suffix<br>- 40 °C to 85 °C |                   | Unit |
|                                      |                     |                                                                                                                                                                      |                |                    |                   | Min. <sup>d</sup>             | Max. <sup>d</sup> | Min. <sup>d</sup>            | Max. <sup>d</sup> |      |
| Analog Switch                        |                     |                                                                                                                                                                      |                |                    |                   |                               |                   |                              |                   |      |
| Analog Signal Range <sup>e</sup>     | V <sub>ANALOG</sub> |                                                                                                                                                                      |                | Full               |                   | - 15                          | 15                | - 15                         | 15                | V    |
| Drain-Source On-Resistance           | R <sub>DS(on)</sub> | I <sub>S</sub> = - 10 mA, V <sub>D</sub> = ± 12.5 V<br>V <sub>+</sub> = 13.5 V, V <sub>-</sub> = - 13.5 V                                                            |                | Room Full          | 20                |                               | 35<br>45          |                              | 35<br>45          | Ω    |
| Switch Off Leakage Current           | I <sub>S(off)</sub> | V <sub>+</sub> = 16.5, V <sub>-</sub> = - 16.5 V<br>V <sub>D</sub> = ± 15.5 V<br>V <sub>S</sub> = ± 15.5 V                                                           | DG417          | Room Full          | - 0.1             | - 0.25<br>- 20                | 0.25<br>20        | - 0.25<br>- 5                | 0.25<br>5         | nA   |
|                                      | DG418               |                                                                                                                                                                      | Room Full      | - 0.1              | - 0.25<br>- 20    | 0.25<br>20                    | - 0.25<br>- 5     | 0.25<br>5                    |                   |      |
|                                      | DG419               |                                                                                                                                                                      | Room Full      | - 0.1              | - 0.75<br>- 60    | 0.75<br>60                    | - 0.75<br>- 12    | 0.75<br>12                   |                   |      |
| Channel Off Leakage Current          | I <sub>D(on)</sub>  | V <sub>+</sub> = 16.5 V, V <sub>-</sub> = - 16.5 V<br>V <sub>S</sub> = V <sub>D</sub> = ± 15.5 V                                                                     | DG417          | Room Full          | - 0.4             | - 0.4<br>- 40                 | 0.4<br>40         | - 0.4<br>- 10                | 0.4<br>10         |      |
|                                      |                     |                                                                                                                                                                      | DG418          | Room Full          | - 0.4             | - 0.4<br>- 40                 | 0.4<br>40         | - 0.4<br>- 10                | 0.4<br>10         |      |
|                                      |                     |                                                                                                                                                                      | DG419          | Room Full          | - 0.4             | - 0.75<br>- 60                | 0.75<br>60        | - 0.75<br>- 12               | 0.75<br>12        |      |
| Digital Control                      |                     |                                                                                                                                                                      |                |                    |                   |                               |                   |                              |                   |      |
| Input Current V <sub>IN</sub> Low    | I <sub>IL</sub>     |                                                                                                                                                                      |                | Full               | 0.005             | - 0.5                         | 0.5               | - 0.5                        | 0.5               | μA   |
| Input Current V <sub>IN</sub> High   | I <sub>IH</sub>     |                                                                                                                                                                      |                | Full               | 0.005             | - 0.5                         | 0.5               | - 0.5                        | 0.5               |      |
| Dynamic Characteristics              |                     |                                                                                                                                                                      |                |                    |                   |                               |                   |                              |                   |      |
| Turn-On Time                         | t <sub>ON</sub>     | R <sub>L</sub> = 300 Ω, C <sub>L</sub> = 35 pF<br>V <sub>S</sub> = ± 10 V                                                                                            | DG417<br>DG418 | Room Full          | 100               |                               | 175<br>250        |                              | 175<br>250        | ns   |
| Turn-Off Time                        | t <sub>OFF</sub>    | See Switching Time<br>Test Circuit                                                                                                                                   | DG417<br>DG418 | Room Full          | 60                |                               | 145<br>210        |                              | 145<br>210        |      |
| Transition Time                      | t <sub>TRANS</sub>  | R <sub>L</sub> = 300 Ω, C <sub>L</sub> = 35 pF<br>V <sub>S1</sub> = ± 10 V, V <sub>S2</sub> = ± 10 V                                                                 | DG419          | Room Full          |                   |                               | 175<br>250        |                              | 175<br>250        |      |
| Break-Before-Make Time Delay (DG403) | t <sub>D</sub>      | R <sub>L</sub> = 300 Ω, C <sub>L</sub> = 35 pF<br>V <sub>S1</sub> = V <sub>S2</sub> = ± 10 V                                                                         | DG419          | Room               | 13                | 5                             |                   | 5                            |                   |      |
| Charge Injection                     | Q                   | C <sub>L</sub> = 10 nF, V <sub>gen</sub> = 0 V, R <sub>gen</sub> = 0 Ω                                                                                               |                | Room               | 60                |                               |                   |                              |                   | pC   |

| SPECIFICATIONS <sup>a</sup> |                     |                                                                                                                                                                      |  |                    |                   |                               |                   |                              |                   |      |
|-----------------------------|---------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--------------------|-------------------|-------------------------------|-------------------|------------------------------|-------------------|------|
| Parameter                   | Symbol              | Test Conditions<br>Unless Otherwise Specified<br>V <sub>+</sub> = 15 V, V <sub>-</sub> = - 15 V<br>V <sub>L</sub> = 5 V, V <sub>IN</sub> = 2.4 V, 0.8 V <sup>f</sup> |  | Temp. <sup>b</sup> | Typ. <sup>c</sup> | A Suffix<br>- 55 °C to 125 °C |                   | D Suffix<br>- 40 °C to 85 °C |                   | Unit |
|                             |                     |                                                                                                                                                                      |  |                    |                   | Min. <sup>d</sup>             | Max. <sup>d</sup> | Min. <sup>d</sup>            | Max. <sup>d</sup> |      |
| Dynamic Characteristics     |                     |                                                                                                                                                                      |  |                    |                   |                               |                   |                              |                   |      |
| Source Off Capacitance      | C <sub>S(off)</sub> | f = 1 MHz, V <sub>S</sub> = 0 V                                                                                                                                      |  | Room               | 8                 |                               |                   |                              |                   | pF   |
| Drain Off Capacitance       | C <sub>D(off)</sub> |                                                                                                                                                                      |  | DG417<br>DG418     | Room              | 8                             |                   |                              |                   |      |
| Channel On Capacitance      | C <sub>D(on)</sub>  | f = 1 MHz, V <sub>S</sub> = 0 V                                                                                                                                      |  | DG417<br>DG418     | Room              | 30                            |                   |                              |                   |      |
|                             |                     |                                                                                                                                                                      |  | DG419              | Room              | 35                            |                   |                              |                   |      |
| Power Supplies              |                     |                                                                                                                                                                      |  |                    |                   |                               |                   |                              |                   |      |
| Positive Supply Current     | I <sub>+</sub>      | V <sub>+</sub> = 16.5 V, V <sub>-</sub> = - 16.5 V<br>V <sub>IN</sub> = 0 or 5 V                                                                                     |  | Room<br>Full       | 0.001             |                               | 1<br>5            |                              | 1<br>5            | μA   |
| Negative Supply Current     | I <sub>-</sub>      |                                                                                                                                                                      |  | Room<br>Full       | - 0.001           | - 1<br>- 5                    |                   | - 1<br>- 5                   |                   |      |
| Logic Supply Current        | I <sub>L</sub>      |                                                                                                                                                                      |  | Room<br>Full       | 0.001             |                               | 1<br>5            |                              | 1<br>5            |      |
| Ground Current              | I <sub>GND</sub>    |                                                                                                                                                                      |  | Room<br>Full       | - 0.0001          | - 1<br>- 5                    |                   | - 1<br>- 5                   |                   |      |


| SPECIFICATIONS <sup>a</sup> for Unipolar Supplies |                     |                                                                                                                                                                   |                    |                   |                               |                   |                              |                   |      |
|---------------------------------------------------|---------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------|-------------------|-------------------------------|-------------------|------------------------------|-------------------|------|
| Parameter                                         | Symbol              | Test Conditions<br>Unless Otherwise Specified<br>V <sub>+</sub> = 12 V, V <sub>-</sub> = 0 V<br>V <sub>L</sub> = 5 V, V <sub>IN</sub> = 2.4 V, 0.8 V <sup>f</sup> | Temp. <sup>b</sup> | Typ. <sup>c</sup> | A Suffix<br>- 55 °C to 125 °C |                   | D Suffix<br>- 40 °C to 85 °C |                   | Unit |
|                                                   |                     |                                                                                                                                                                   |                    |                   | Min. <sup>d</sup>             | Max. <sup>d</sup> | Min. <sup>d</sup>            | Max. <sup>d</sup> |      |
| Analog Switch                                     |                     |                                                                                                                                                                   |                    |                   |                               |                   |                              |                   |      |
| Analog Signal Range <sup>e</sup>                  | V <sub>ANALOG</sub> |                                                                                                                                                                   | Full               |                   | 0                             | 12                | 0                            | 12                | V    |
| Drain-Source On-Resistance                        | R <sub>DS(on)</sub> | I <sub>S</sub> = - 10 mA, V <sub>D</sub> = 3.8 V<br>V <sub>+</sub> = 10.8 V                                                                                       | Room               | 40                |                               |                   |                              |                   | Ω    |
| Dynamic Characteristics                           |                     |                                                                                                                                                                   |                    |                   |                               |                   |                              |                   |      |
| Turn-On Time                                      | t <sub>ON</sub>     | R <sub>L</sub> = 300 Ω, C <sub>L</sub> = 35 pF, V <sub>S</sub> = 8 V<br>See Switching Time Test Circuit                                                           | Room               | 110               |                               |                   |                              |                   | ns   |
| Turn-Off Time                                     | t <sub>OFF</sub>    |                                                                                                                                                                   | Room               | 40                |                               |                   |                              |                   |      |
| Break-Before-Make Time Delay                      | t <sub>D</sub>      | DG419 Only<br>R <sub>L</sub> = 300 Ω, C <sub>L</sub> = 35 pF                                                                                                      | Room               | 60                |                               |                   |                              |                   |      |
| Charge Injection                                  | Q                   | C <sub>L</sub> = 10 nF, V <sub>gen</sub> = 0 V, R <sub>gen</sub> = 0 Ω                                                                                            | Room               | 5                 |                               |                   |                              |                   | pC   |
| Power Supplies                                    |                     |                                                                                                                                                                   |                    |                   |                               |                   |                              |                   |      |
| Positive Supply Current                           | I <sub>+</sub>      | V <sub>+</sub> = 13.2 V, V <sub>L</sub> = 5.25 V<br>V <sub>IN</sub> = 0 or 5 V                                                                                    | Room               | 0.001             |                               |                   |                              |                   | μA   |
| Negative Supply Current                           | I <sub>-</sub>      |                                                                                                                                                                   | Room               | - 0.001           |                               |                   |                              |                   |      |
| Logic Supply Current                              | I <sub>L</sub>      |                                                                                                                                                                   | Room               | 0.001             |                               |                   |                              |                   |      |
| Ground Current                                    | I <sub>GND</sub>    |                                                                                                                                                                   | Room               | - 0.001           |                               |                   |                              |                   |      |



Notes:

- Refer to Process Option Flowchart.
- Room = 25 °C, Full = as determined by the operating temperature suffix.
- Typical values are for DESIGN AID ONLY, not guaranteed nor subject to production testing.
- The algebraic convention whereby the most negative value is a minimum and the most positive a maximum, is used in this data sheet.
- Guaranteed by design, not subject to production test.
- $V_{IN}$  = input voltage to perform proper function.


Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

**TYPICAL CHARACTERISTICS** 25 °C, unless otherwise noted


 **$R_{DS(on)}$  vs.  $V_D$  and Supply Voltage**

 **$R_{DS(on)}$  vs. Temperature**

**Leakage Currents vs. Analog Voltage**

**Drain Charge Injection**

**Input Switching Threshold vs. Supply Voltages**


## TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted




Switching Time vs. Temperature



Crosstalk and Off Isolation vs. Frequency




Switching Time vs. Supply Voltages



Switching Time vs.  $V_+$



Power Supply Currents vs. Switching Frequency



Supply Current vs. Temperature


## TEST CIRCUITS

$V_O$  is the steady state output with the switch on.



$C_L$  (includes fixture and stray capacitance)

$$V_O = V_S \frac{R_L}{R_L + r_{DS(on)}}$$



Note: Logic input waveform is inverted for switches that have the opposite logic sense.

Figure 2. Switching Time (DG417, DG418)



$C_L$  (includes fixture and stray capacitance)



Figure 3. Break-Before-Make (DG419)



$C_L$  (includes fixture and stray capacitance)

$$V_O = V_S \frac{R_L}{R_L + r_{DS(on)}}$$



Figure 4. Transition Time (DG419)

## TEST CIRCUITS




Figure 5. Charge Injection





Figure 6. Crosstalk (DG419)




Figure 7. Off Isolation




Figure 8. Insertion Loss

## TEST CIRCUITS




Figure 9. Source/Drain Capacitances

## APPLICATIONS

### Switched Signal Powers Analog Switch

The analog switch in Figure 10 derives power from its input signal, provided the input signal amplitude exceeds 4 V and its frequency exceeds 1 kHz.

This circuit is useful when signals have to be routed to either of two remote loads. Only three conductors are required: one for the signal to be switched, one for the control signal and a common return.

A positive input pulse turns on the clamping diode  $D_1$  and charges  $C_1$ . The charge stored on  $C_1$  is used to power the chip; operation is satisfactory because the switch requires less than  $1 \mu\text{A}$  of stand-by supply current. Loading of the signal source is imperceptible. The DG419's on-resistance is a low  $100 \Omega$  for a 5 V input signal.




Figure 10. Switched Signal Powers Remote SPDT Analog Switch

## APPLICATIONS

### Micropower UPS Transfer Switch

When  $V_{CC}$  drops to 3.3 V, the DG417 changes states, closing  $SW_1$  and connecting the backup cell, as shown in Figure 10.  $D_1$  prevents current from leaking back towards the rest of the circuit. Current consumption by the CMOS analog switch is around 100 pA; this ensures that most of the power available is applied to the memory, where it is really needed. In the stand-by mode, hundreds of A are sufficient to retain memory data.

When the 5 V supply comes back up, the resistor divider senses the presence of at least 3.5 V, and causes a new change of state in the analog switch, restoring normal operation.




Figure 11. Micropower UPS Circuit

### Programmable Gain Amplifier

The DG419, as shown in figure 11, allows accurate gain selection in a small package. Switching into virtual ground reduces distortion caused by  $R_{DS(on)}$  variation as a function of analog signal amplitude.

### GaAs FET Driver

The DG419, as shown in figure 12 may be used as a GaAs FET driver. It translates a TTL control signal into - 8 V, 0 V level outputs to drive the gate.




Figure 12. Programmable Gain Amplifier




Figure 13. GaAs FET Driver

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see [www.vishay.com/ppg?70051](http://www.vishay.com/ppg?70051).

## SOIC (NARROW): 8-LEAD




JEDEC Part Number: MS-012



| DIM                            | MILLIMETERS |      | INCHES    |       |
|--------------------------------|-------------|------|-----------|-------|
|                                | Min         | Max  | Min       | Max   |
| A                              | 1.35        | 1.75 | 0.053     | 0.069 |
| A <sub>1</sub>                 | 0.10        | 0.20 | 0.004     | 0.008 |
| B                              | 0.35        | 0.51 | 0.014     | 0.020 |
| C                              | 0.19        | 0.25 | 0.0075    | 0.010 |
| D                              | 4.80        | 5.00 | 0.189     | 0.196 |
| E                              | 3.80        | 4.00 | 0.150     | 0.157 |
| e                              | 1.27 BSC    |      | 0.050 BSC |       |
| H                              | 5.80        | 6.20 | 0.228     | 0.244 |
| h                              | 0.25        | 0.50 | 0.010     | 0.020 |
| L                              | 0.50        | 0.93 | 0.020     | 0.037 |
| q                              | 0°          | 8°   | 0°        | 8°    |
| S                              | 0.44        | 0.64 | 0.018     | 0.026 |
| ECN: C-06527-Rev. I, 11-Sep-06 |             |      |           |       |
| DWG: 5498                      |             |      |           |       |



### PDIP: 8-LEAD



| Dim                  | MILLIMETERS |       | INCHES |       |
|----------------------|-------------|-------|--------|-------|
|                      | Min         | Max   | Min    | Max   |
| <b>A</b>             | 3.81        | 5.08  | 0.150  | 0.200 |
| <b>A<sub>1</sub></b> | 0.38        | 1.27  | 0.015  | 0.050 |
| <b>B</b>             | 0.38        | 0.51  | 0.015  | 0.020 |
| <b>B<sub>1</sub></b> | 0.89        | 1.65  | 0.035  | 0.065 |
| <b>C</b>             | 0.20        | 0.30  | 0.008  | 0.012 |
| <b>D</b>             | 9.02        | 10.92 | 0.355  | 0.430 |
| <b>E</b>             | 7.62        | 8.26  | 0.300  | 0.325 |
| <b>E<sub>1</sub></b> | 5.59        | 7.11  | 0.220  | 0.280 |
| <b>e<sub>1</sub></b> | 2.29        | 2.79  | 0.090  | 0.110 |
| <b>e<sub>A</sub></b> | 7.37        | 7.87  | 0.290  | 0.310 |
| <b>L</b>             | 2.79        | 3.81  | 0.110  | 0.150 |
| <b>Q<sub>1</sub></b> | 1.27        | 2.03  | 0.050  | 0.080 |
| <b>S</b>             | 0.76        | 1.65  | 0.030  | 0.065 |

ECN: S-03946—Rev. E, 09-Jul-01  
DWG: 5478

NOTE: End leads may be half leads.

## RECOMMENDED MINIMUM PADS FOR SO-8



Recommended Minimum Pads  
Dimensions in Inches/(mm)

[Return to Index](#)



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

[DG418AK](#) [DG419AK](#) [DG418DY-E3](#) [DG418DJ-E3](#) [DG417DY-E3](#) [DG419DJ-E3](#) [DG418DJ](#) [DG418DY](#) [DG419DY](#)  
[DG419DJ](#) [DG417AK](#) [DG417DJ](#) [DG417DY](#) [DG417DY-T1](#) [DG419DY-T1](#) [DG419DY-E3](#) [DG417DJ-E3](#) [DG417DY-T1-](#)  
[E3](#) [DG418DY-T1-E3](#) [DG419DY-T1-E3](#) [DG418DY-T1](#) [DG419AK-E3](#) [DG417AK-E3](#) [DG418AK-E3](#)