

Overview

The C4C capacitor is a polypropylene metallized film and polyester double-metallized foil capacitor with a polyester tape wrapping filled with resin, and uses tinned copper wires.

Applications

Typical applications include snubber, clamping, resonance, coupling/decoupling, pulse, and blocking.

Benefits


- Self-healing
- Low loss
- High ripple current
- High contact reliability
- Suitable for high frequency applications
- PP metallized and PET double-sided metallized foil



Part Number System

C4	C	A	M	U	B	3100	AA	0	J
Series	Type	Fire Protection	Rated Voltage (VDC)	Insulation	Lead Diameter (mm)	Capacitance Code (pF)	Packaging	Capacitor Length (mm)	Tolerance
C4 = MKP Capacitors	C = Round body, snubber application	A = No fire retardant S = Fire retardant (on request)	M = 850 P = 1,200 W = 2,000 Y = 3,000	U = Polyester tape and resin protection 0 = Uninsulated (upon request, but not in combination with Fire Protection "S")	B = 0.8 C = 1.0 D = 1.2	Digits two – four indicate the first three digits of the capacitance value. First digit indicates the number of zeros to be added.	AA = Bulk (Bag) – straight leads see "Dimensions Table"	0 = 33 1 = 44 3 = 58	J = 5% K = 10%

Dimensions – Millimeters



D	L	d	LL
Maximum	Maximum	Nominal	±5
10 – 14	33	0.8	40
14.5 – 21.5	33	1	40
19 – 23	44	1	40
23.5 – 33.5	44	1.2	40
28.5 – 32	58	1.2	40

Qualification

Reference Standards	VDE 0560, IEC 61071, EN 61071
Application Class (DIN 40040)	GPE/LS
Vibration Strength	DIN 40040, Table 6, Class V

Performance Characteristics

Temperature Range	-40°C to +85°C
Maximum Permissible Ambient Temperature	+70°C
IEC Climatic Category	40/85/56 according to IEC 68-1
Peak Non-Repetitive Maximum Current	$I_{PKR} \times 1.5$
Test Voltage Terminal to Terminal (VTT)	2 V_n for 10 seconds
Test Voltage Terminal to Case (VTC)	3 k VDC 50 Hz for 60 seconds
Insulation Resistance Test Conditions	Temperature: +25°C ±5% Voltage charge time: 1 minute Test voltage: 100 VDC Typical value ($R_{is} \times C$): 3,000 seconds
Dissipation Factor (DF)	$\leq 5 \times 10^{-4}$ at 1 kHz and 20°C
Capacitance Deviation in Operating Temperature Range of -40°C to +85°C	±1.5% maximum on capacitance value measured at +20°C
Life Expectancy	$\geq 30,000$ hours at V_{RMS} $\geq 100,000$ hours at V_n
Failure Quota	300/10 ⁹ components per hour
Change of Capacitance vs. Operating Time	-3% after 30,000 hours at V_{RMS} or after 100,000 hours at V_n
Protection	Polyester wrapping with epoxy resin fill
Flame Retardant (IEC 384-1)	Standard execution: non-flame retardant On request: flame retardant execution Category C
Leads	Tinned copper
Installation	Any position
Damp Heat Test	Test Conditions
	Relative humidity: 93% ±2%
	Temperature: +40°C
	Test duration: 56 days
	Capacitance change: $\leq \pm 5\%$
	DF change: $\leq 50\%$ of nominal value at 1 kHz
	Insulation resistance: $\geq 50\%$ of limit value

Table 1 – Ratings & Part Number Reference

Cap Value (µF)	VDC	VAC	Peak VDC	Maximum Dimensions (mm)		Ripple Current 100 kHz 70°C (A)	Peak Current (A)	ESR (Max) 100 kHz (mΩ)	dV/dt (V/µs)	Packaging Quantity	Part Number
				D	L						
0.1	850	450	1,200	10.5	33	5	45	16.6	450	300	C4C(1)M(2)B3100AA0(3)
0.15	850	450	1,200	12.5	33	7	68	11.5	450	300	C4C(1)M(2)B3150AA0(3)
0.22	850	450	1,200	15.5	33	9	99	8.1	450	200	C4C(1)M(2)C3220AA0(3)
0.33	850	450	1,200	18.5	33	9	149	5.8	450	150	C4C(1)M(2)C3330AA0(3)
0.47	850	450	1,200	21.5	33	9	212	4.6	450	100	C4C(1)M(2)C3470AA0(3)
0.68	850	450	1,200	21	44	9	204	5.1	300	100	C4C(1)M(2)C3680AA1(3)
1	850	450	1,200	25	44	12	300	3.8	300	50	C4C(1)M(2)D4100AA1(3)
1.5	850	450	1,200	30.5	44	12	450	3.1	300	50	C4C(1)M(2)D4150AA1(3)
2	850	450	1,200	28.5	58	12	400	3.8	200	30	C4C(1)M(2)D4200AA3(3)
2.2	850	450	1,200	29.5	58	12	440	3.7	200	30	C4C(1)M(2)D4220AA3(3)
2.5	850	450	1,200	31.5	58	12	500	3.5	200	30	C4C(1)M(2)D4250AA3(3)
0.047	1,200	500	1,600	10	33	4	33	27.1	700	400	C4C(1)P(2)B2470AA0(3)
0.068	1,200	500	1,600	12	33	5	48	19.1	700	300	C4C(1)P(2)B2680AA0(3)
0.1	1,200	500	1,600	14	33	7	70	13.4	700	250	C4C(1)P(2)B3100AA0(3)
0.15	1,200	500	1,600	17.5	33	9	105	9.2	700	150	C4C(1)P(2)C3150AA0(3)
0.22	1,200	500	1,600	20.5	33	9	154	6.8	700	100	C4C(1)P(2)C3220AA0(3)
0.33	1,200	500	1,600	20	44	9	149	7.2	450	100	C4C(1)P(2)C3330AA1(3)
0.47	1,200	500	1,600	23	44	9	212	5.6	450	70	C4C(1)P(2)C3470AA1(3)
0.68	1,200	500	1,600	27.5	44	12	306	4.2	450	50	C4C(1)P(2)D3680AA1(3)
1	1,200	500	1,600	33	44	12	450	3.5	450	50	C4C(1)P(2)D4100AA1(3)
1.2	1,200	500	1,600	29	58	12	330	4.5	275	30	C4C(1)P(2)D4120AA3(3)
1.5	1,200	500	1,600	32	58	12	413	4	275	30	C4C(1)P(2)D4150AA3(3)
0.022	2,000	630	2,400	10.5	33	3	25	48.2	1,150	400	C4C(1)W(2)B2220AA0(3)
0.033	2,000	630	2,400	12.5	33	4	38	32.5	1,150	300	C4C(1)W(2)B2330AA0(3)
0.047	2,000	630	2,400	15	33	6	54	23	1,150	200	C4C(1)W(2)C2470AA0(3)
0.068	2,000	630	2,400	17.5	33	7	78	16.3	1,150	150	C4C(1)W(2)C2680AA0(3)
0.1	2,000	630	2,400	20.5	33	9	115	11.6	1,150	100	C4C(1)W(2)C3100AA0(3)
0.15	2,000	630	2,400	19.5	44	9	105	11.3	700	100	C4C(1)W(2)C3150AA1(3)
0.22	2,000	630	2,400	23.5	44	12	154	8	700	70	C4C(1)W(2)D3220AA1(3)
0.33	2,000	630	2,400	28.5	44	12	231	5.9	700	50	C4C(1)W(2)D3330AA1(3)
0.47	2,000	630	2,400	33.5	44	12	329	4.8	700	50	C4C(1)W(2)D3470AA1(3)
0.56	2,000	630	2,400	29	58	12	224	6.1	400	30	C4C(1)W(2)D3560AA3(3)
0.68	2,000	630	2,400	32	58	12	272	5.4	400	30	C4C(1)W(2)D3680AA3(3)
0.0068	3,000	750	3,500	10	33	2	14.5	132	2,100	400	C4C(1)Y(2)B1680AA0(3)
0.01	3,000	750	3,500	12	33	3	21	90.3	2,100	300	C4C(1)Y(2)B2100AA0(3)
0.015	3,000	750	3,500	14.5	33	4	32	60.5	2,100	200	C4C(1)Y(2)C2150AA0(3)
0.022	3,000	750	3,500	17	33	5	46	41.6	2,100	150	C4C(1)Y(2)C2220AA0(3)
0.033	3,000	750	3,500	20.5	33	6	69	28.3	2,100	100	C4C(1)Y(2)C2330AA0(3)
0.047	3,000	750	3,500	19	44	7	59	25.7	1,250	100	C4C(1)Y(2)C2470AA1(3)
0.068	3,000	750	3,500	22.5	44	9	85	18.3	1,250	70	C4C(1)Y(2)C2680AA1(3)
0.1	3,000	750	3,500	27	44	12	125	12.8	1,250	50	C4C(1)Y(2)D3100AA1(3)
0.15	3,000	750	3,500	32	44	12	188	9.2	1,250	50	C4C(1)Y(2)D3150AA1(3)
0.22	3,000	750	3,500	31	58	12	165	9.5	750	30	C4C(1)Y(2)D3220AA3(3)
Capacitance Value (µF)	VDC	VAC	Peak VDC	D (mm)	L (mm)	Ripple Current	Peak Current	ESR	dV/dt (V/µs)	Packaging Quantity	Part Number

(1) A = No fire retardant; S = fire retardant (on request)

(2) U = Tape and resin protection; 0 = unprotected (upon request, but not in combination with Fire retardant code "S")

(3) K = ±10%, J = ±5%

Environmental Compliance

As a leading global supplier of electronic components and an environmentally conscious company, KEMET continually aspires to improve the environmental effects of our manufacturing processes and our finished electronic components.

In Europe (RoHS Directive) and in some other geographical areas such as China (China RoHS), legislation has been enacted to prevent or otherwise limit the use of certain hazardous materials, including lead (Pb), in electronic equipment. KEMET monitors legislation globally to ensure compliance and endeavors to adjust our manufacturing processes and/or electronic components as may be required by applicable law.

For military, medical, automotive, and some commercial applications, the use of lead (Pb) in the termination is necessary and/or required by design. KEMET is committed to communicating RoHS compliance to our customers. Information related to RoHS compliance will be provided in data sheets and using specific identifiers on the packaging labels.

All KEMET power film capacitors are RoHS compliant.

Materials & Environment

The selection of raw materials that KEMET uses for the production of its electronic components is the result of extensive experience. KEMET directs specific attention toward environmental protection. KEMET selects its suppliers according to ISO 9001 standards and performs statistical analyses on raw materials before acceptance for use in manufacturing our electronic components. All materials are, to the best of KEMET's knowledge, non-toxic and free from cadmium; mercury; chrome and compounds; polychlorine triphenyl (PCB); bromide and chlorinedioxins bromurate clorurate; CFC and HCFC; and asbestos.

Dissipation Factor

Dissipation factor is a complex function involved with capacitor inefficiency. The $\tan \delta$ may vary up and down with increased temperature. For more information, refer to Performance Characteristics.

Sealing

Hermetically Sealed Capacitors


As the temperature increases, the pressure inside the capacitor increases. If the internal pressure is high enough, it can cause a breach in the capacitor. Such a breach can result in leakage, impregnation, filling fluid, or moisture susceptibility.

Barometric Pressure


The altitude at which hermetically sealed capacitors are operated controls the capacitor's voltage rating. As the barometric pressure decreases, the susceptibility to terminal arc-over increases. Non-hermetic capacitors can be affected by internal stresses due to pressure changes. These effects can be in the form of capacitance changes, dielectric arc-over, and/or low insulation resistance. Altitude can also affect heat transfer. Heat that is generated in an operation cannot be dissipated properly, and high RI^2 losses and eventual failure can result.

Soldering Process


The implementation of the RoHS Directive has required the selection SnAgCu (SAC) alloys or SnCu alloys as primary solder. This has increased the liquidus temperature from that of 183°C for SnPb eutectic alloy to 217 – 221°C for the new alloys. As a result, the heat stress to components, even in wave soldering, has increased considerably due to higher pre-heat and wave temperatures. Polypropylene capacitors are especially sensitive to heat (melting point of polypropylene is 160 – 170°C). Wave soldering can be destructive especially for mechanically small polypropylene capacitors (lead spacings 5 – 10 mm) and great care must be taken during soldering. The solder profiles from KEMET are highly recommended. You may also refer to the wave soldering curve from IEC Publication 61760-1 Edition 2. Please consult KEMET with any questions.




Construction



Winding Scheme



Marking



Slight change in the layout can be possible but this does not affect the content of the information of the current marking.

This change will be achieved without impact to product form, fit or function, as the products are equivalent with respect to physical, mechanical, quality and reliability characteristics.

KEMET Electronics Corporation Sales Offices

For a complete list of our global sales offices, please visit www.kemet.com/sales.

Disclaimer

YAGEO Corporation and its affiliates do not recommend the use of commercial or automotive grade products for high reliability applications or manned space flight.

All product specifications, statements, information and data (collectively, the "Information") in this datasheet are subject to change. The customer is responsible for checking and verifying the extent to which the Information contained in this publication is applicable to an order at the time the order is placed. All Information given herein is believed to be accurate and reliable, but it is presented without guarantee, warranty, or responsibility of any kind, expressed or implied.

Statements of suitability for certain applications are based on KEMET Electronics Corporation's ("KEMET") knowledge of typical operating conditions for such applications, but are not intended to constitute – and KEMET specifically disclaims – any warranty concerning suitability for a specific customer application or use. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by KEMET with reference to the use of KEMET's products is given gratis, and KEMET assumes no obligation or liability for the advice given or results obtained.

Although KEMET designs and manufactures its products to the most stringent quality and safety standards, given the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage.

Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicated or that other measures may not be required.

Additional information about production site flexibility can be found <[here](#)>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[KEMET:](#)

C4CAMUC3470AA0J	C4CAMUC3680AA1J	C4CAPUB3100AA0J	C4CAYUC2470AA1J	C4CAYUC2680AA1J
C4CAMUC3680ZR0J	C4CAWUD3560AA3J	C4CAWUD3470AA1J	C4CAWUD3220ZR1J	C4CAMUD4150AA1J
C4CAWUB2330AA0J	C4CAWUD3330ZR1J	C4CAYUD3220AA3J	C4CAMUC3750ZA0J	C4CAPUC4100ZA3J
C4CAMUC3470ZR0J	C4CAWUC3100AA0J	C4CAWUC3220AA1J	C4CSMUD3680ZF1J	C4CAWUD3330AA1J
C4CAWUD3220AA1J	C4CAYUC2150AA0J	C4CAYUC2330AA0J	C4CAPUC3220AA0J	C4CAPUC3330AA1J
C4CAPUD4100AA1J	C4CAYUB2100AA0J	C4CAPUB3100AA1J	C4CAPUC3470AA1J	C4CAYUC2220AA0J
C4CAMUD4100AA1J	C4CAYUD3150AA1J	C4CAPUC3220AA1J	C4CAWUC3150AA1J	C4CAPUC3150AA0J
C4CAYUD3100AA1J	C4CAMUD4220AA3J	C4CAMUB3100AA0J		