


Optocoupler, Phototransistor Output, Dual Channel



1179073_7

DESCRIPTION

The ILD610 series is a dual channel optocoupler series for high density applications. Each channel consists of an optically coupled pair with a gallium arsenide infrared LED and silicon NPN phototransistor. Signal information, including a DC level, can be transmitted by the device while maintaining a high degree of electrical isolation between input and output. The ILD610 series is the dual version of SFH610 series and uses a repetitive pin-out configuration instead of the more common alternating pin-out used in most dual couplers.

FEATURES



- Dual version of SFH610 series
- Isolation test voltage, 5300 V_{RMS}
- V_{CEsat} 0.25 (≤ 0.4) V at I_F = 10 mA, I_C = 2.5 mA
- V_{CEO} = 70 V
- Compliant to RoHS Directive 2002/95/EC and in accordance to WEEE 2002/96/EC


RoHS
COMPLIANT

AGENCY APPROVALS

- UL1577, file no. E52744 system code H or J, double protection
- DIN EN 60747-5-5 (VDE 0884)/DIN EN 60747-5-5 pending
- CSA 93751
- BSI IEC 60950; IEC 60065

ORDERING INFORMATION



AGENCY CERTIFIED/PACKAGE	CTR (%)			
	40 to 80	63 to 125	100 to 200	160 to 320
UL, CSA, BSI				
DIP-8	ILD610-1	-	ILD610-3	-
DIP-8, 400 mil, option 6	-	-	ILD610-3X006	-
SMD-8, option 7	-	ILD610-2X007T	-	-
SMD-8, option 9	-	-	ILD610-3X009	ILD610-4X009

Note

- Additional options may be possible, please contact sales office.

ABSOLUTE MAXIMUM RATINGS ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)				
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT
INPUT				
Reverse voltage		V_R	6.0	V
Surge forward current	$t \leq 1.0\text{ ms}$	I_{FSM}	1.5	A
Power dissipation		P_{diss}	100	mW
Derate linearly from $25\text{ }^{\circ}\text{C}$			1.3	mW/ $^{\circ}\text{C}$
Forward continuous current		I_F	60	mA
OUTPUT				
Collector emitter voltage		V_{CE}	70	V
Collector current		I_C	50	mA
	$t \leq 1.0\text{ ms}$	I_C	100	mA
Power dissipation		P_{diss}	150	mW
Derate linearly from $25\text{ }^{\circ}\text{C}$			2.0	mW/ $^{\circ}\text{C}$
COUPLER				
Isolation test voltage	$t = 1.0\text{ s}$	V_{ISO}	5300	V_{RMS}
Isolation resistance	$V_{IO} = 500\text{ V}$, $T_{amb} = 25\text{ }^{\circ}\text{C}$	R_{IO}	$\geq 10^{12}$	Ω
	$V_{IO} = 500\text{ V}$, $T_{amb} = 100\text{ }^{\circ}\text{C}$	R_{IO}	$\geq 10^{11}$	Ω
Storage temperature		T_{stg}	- 55 to + 150	$^{\circ}\text{C}$
Operating temperature		T_{amb}	- 55 to + 100	$^{\circ}\text{C}$
Junction temperature		T_j	100	$^{\circ}\text{C}$
Lead soldering time at $260\text{ }^{\circ}\text{C}$			10	s

Note

- Stresses in excess of the absolute maximum ratings can cause permanent damage to the device. Functional operation of the device is not implied at these or any other conditions in excess of those given in the operational sections of this document. Exposure to absolute maximum ratings for extended periods of the time can adversely affect reliability.

ELECTRICAL CHARACTERISTICS (T _{amb} = 25 °C, unless otherwise specified)							
PARAMETER	TEST CONDITION	PART	SYMBOL	MIN.	TYP.	MAX.	UNIT
INPUT							
Forward voltage	I _F = 60 mA		V _F		1.25	1.65	V
Reverse current	V _R = 6.0 V		I _R		0.01	10	μA
Capacitance	V _R = 0 V, f = 1.0 MHz		C _O		25		pF
OUTPUT							
Collector emitter breakdown voltage	I _C = 10 mA, I _E = 10 μA		BV _{CEO}	70	90		V
			BV _{CEO}	6.0	7.0		V
Collector emitter dark current	V _{CE} = 10 V		I _{CEO}		2.0	50	nA
Collector emitter capacitance	V _{CE} = 5.0 V, f = 1.0 MHz		C _{CE}		7.0		pF
Collector emitter leakage current	V _{CE} = 10 V	ILD610-1	I _{CEO}		2.0	50	nA
		ILD610-2	I _{CEO}		2.0	50	nA
		ILD610-3	I _{CEO}		5.0	100	nA
		ILD610-4	I _{CEO}		5.0	100	nA
COUPLER							
Collector emitter saturation voltage	I _F = 10 mA, I _C = 2.5 mA		V _{CEsat}		0.25	0.40	V
Coupling capacitance			C _C		0.35		pF

Note

- Minimum and maximum values are testing requirements. Typical values are characteristics of the device and are the result of engineering evaluation. Typical values are for information only and are not part of the testing requirements.




Optocoupler, Phototransistor Output, Dual Channel Vishay Semiconductors

CURRENT TRANSFER RATIO ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)							
PARAMETER	TEST CONDITION	PART	SYMBOL	MIN.	TYP.	MAX.	UNIT
CTR ⁽¹⁾	$I_F = 10\text{ mA}$, $V_{CE} = 5.0\text{ V}$	ILD610-1	CTR	40		80	%
		ILD610-2	CTR	63		125	%
		ILD610-3	CTR	100		200	%
		ILD610-4	CTR	160		320	%
	$I_F = 1.0\text{ mA}$, $V_{CE} = 5.0\text{ V}$	ILD610-1	CTR	13			%
		ILD610-2	CTR	22			%
		ILD610-3	CTR	34			%
		ILD610-4	CTR	56			%


Note⁽¹⁾ CTR will match within a ratio of 1.7:1

SWITCHING CHARACTERISTICS (T _{amb} = 25 °C, unless otherwise specified)							
PARAMETER	TEST CONDITION	PART	SYMBOL	MIN.	TYP.	MAX.	UNIT
NON-SATURATED							
Rise time	V _{CC} = 5.0 V, R _L = 75 Ω, I _F = 10 mA	ILD610-1	t _r		2.0		μs
		ILD610-2			2.5		
		ILD610-3			2.9		
		ILD610-4			3.3		
Fall time	V _{CC} = 5.0 V, R _L = 75 Ω, I _F = 10 mA	ILD610-1	t _f		2.0		μs
		ILD610-2			2.6		
		ILD610-3			3.1		
		ILD610-4			3.5		
Turn-on time	V _{CC} = 5.0 V, R _L = 75 Ω, I _F = 10 mA	ILD610-1	t _{on}		3.0		μs
		ILD610-2			3.2		
		ILD610-3			3.6		
		ILD610-4			4.1		
Turn-off time	V _{CC} = 5.0 V, R _L = 75 Ω, I _F = 10 mA	ILD610-1	t _{off}		2.9		μs
		ILD610-2			3.4		
		ILD610-3			3.7		
		ILD610-4			4.1		
SATURATED							
Rise time	V _{CC} = 5.0 V, R _L = 1.0 kΩ, I _F = 20 mA	ILD610-1	t _r		2.0		μs
	V _{CC} = 5.0 V, R _L = 1.0 kΩ, I _F = 10 mA	ILD610-2			2.8		
	V _{CC} = 5.0 V, R _L = 1.0 kΩ, I _F = 10 mA	ILD610-3			2.8		
	V _{CC} = 5.0 V, R _L = 1.0 kΩ, I _F = 5 mA	ILD610-4			4.6		
Fall time	V _{CC} = 5.0 V, R _L = 1.0 kΩ, I _F = 20 mA	ILD610-1	t _f		11		μs
	V _{CC} = 5.0 V, R _L = 1.0 kΩ, I _F = 10 mA	ILD610-2			14		
	V _{CC} = 5.0 V, R _L = 1.0 kΩ, I _F = 10 mA	ILD610-3			14		
	V _{CC} = 5.0 V, R _L = 1.0 kΩ, I _F = 5 mA	ILD610-4			15		
Turn-on time	V _{CC} = 5.0 V, R _L = 1.0 kΩ, I _F = 20 mA	ILD610-1	t _{on}		3.0		μs
	V _{CC} = 5.0 V, R _L = 1.0 kΩ, I _F = 10 mA	ILD610-2			4.3		
	V _{CC} = 5.0 V, R _L = 1.0 kΩ, I _F = 10 mA	ILD610-3			4.3		
	V _{CC} = 5.0 V, R _L = 1.0 kΩ, I _F = 5 mA	ILD610-4			6.0		
Turn-off time	V _{CC} = 5.0 V, R _L = 1.0 kΩ, I _F = 20 mA	ILD610-1	t _{off}		18		μs
	V _{CC} = 5.0 V, R _L = 1.0 kΩ, I _F = 10 mA	ILD610-2			25		
	V _{CC} = 5.0 V, R _L = 1.0 kΩ, I _F = 10 mA	ILD610-3			25		
	V _{CC} = 5.0 V, R _L = 1.0 kΩ, I _F = 5 mA	ILD610-4			25		

TYPICAL CHARACTERISTICS ($T_{amb} = 25^\circ\text{C}$, unless otherwise specified)


iilct6_01

Fig. 1 - Forward Voltage vs. Forward Current




iilct6_04

Fig. 4 - Normalized Non-Saturated and Saturated CTR vs. LED Current




iilct6_02

Fig. 2 - Normalized Non-Saturated and Saturated CTR vs. LED Current




iilct6_05

Fig. 5 - Normalized Non-Saturated and Saturated CTR vs. LED Current




iilct6_03

Fig. 3 - Normalized Non-Saturated and Saturated CTR vs. LED Current




iilct6_06


Fig. 6 - Collector Emitter Current vs. Temperature and LED Current




iilct6_07

Fig. 7 - Collector Emitter Leakage Current vs. Temperature



iild610_10

Fig. 10 - Non-Saturated Switching Schematic


iilct6_08

Fig. 8 - Propagation Delay vs. Collector Load Resistor


iild610_11

Fig. 11 - Saturated Switching Time Test Waveform


iild610_09


Fig. 9 - Switching Timing

ILD610

Vishay Semiconductors Optocoupler, Phototransistor Output, Dual Channel



PACKAGE DIMENSIONS in millimeters



PACKAGE MARKING



Notes

- Only option 1 and 7 reflected in the package marking
- Tape and reel suffix (T) is not part of the package marking



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

[ILD610-2X007T](#) [ILD610-3X001](#) [ILD610-4](#)