

# DATA SHEET

## ANTI-SULFURATED CHIP RESISTORS AUTOMOTIVE GRADE

AA series

$\pm 5\%$ ,  $\pm 1\%$ ,  $\pm 0.5\%$

sizes 0201/0402/0603/0805/1206/

1210/1218/2010/2512

RoHS compliant & Halogen free



**SCOPE**

This specification describes AA0201 to AA2512 chip resistors with lead-free terminations made by thick film process.

**APPLICATIONS**

- Car electronics
- Engine control unit
- Body control system
- Safety devices

**FEATURES**

- Superior resistance against sulfur containing atmosphere
- AEC-Q200 qualified
- Moisture sensitivity level: MSL1
- AA series soldering is compliant with J-STD-020D
- Halogen free epoxy
- RoHS compliant
- Reduce environmentally hazardous waste
- High component and equipment reliability
- The resistors are 100% performed by automatic optical inspection

**ORDERING INFORMATION - GLOBAL PART NUMBER**

Part number is identified by the series name, size, tolerance, packaging type, temperature coefficient, taping reel and resistance value.

**GLOBAL PART NUMBER**

AA XXXX X X X XX XXXX L  
(1) (2) (3) (4) (5) (6) (7)

**(1) SIZE**

0201 / 0402 / 0603 / 0805 / 1206 / 1210 / 1218 / 2010 / 2512

**(2) TOLERANCE**

D = ±0.5%

F = ±1%

J = ±5% (for Jumper ordering, use code of J)

**(3) PACKAGING TYPE**

R = Paper/PE taping reel

K = Embossed taping reel

**(4) TEMPERATURE COEFFICIENT OF RESISTANCE**

– = Base on spec

**(5) TAPING REEL**

07 = 7 inch dia. Reel

13 = 13 inch dia. Reel

**(6) RESISTANCE VALUE**

1Ω to 10 MΩ

There are 2~4 digits indicated the resistance value. Letter R/K/M is decimal point, no need to mention the last zero after R/K/M, e.g. 1K2, not 1K20.

**(7) DEFAULT CODE**

Letter L is the system default code for ordering only. (Note)

Resistance rule of global part number		
Resistance coding rule		Example
XXXX		1R = 1 Ω
(1 to 9.76 Ω)		1R5 = 1.5 Ω
		9R76 = 9.76 Ω
XXRX		10R = 10 Ω
(10 to 97.6 Ω)		97R6 = 97.6 Ω
XXXR		100R = 100 Ω
(100 to 976 Ω)		976R = 976 Ω
KXXX		1K = 1,000 Ω
(1 to 9.76 KΩ)		9K76 = 9760 Ω
XMXX		1M = 1,000,000 Ω
(1 to 9.76 MΩ)		9M76 = 9,760,000 Ω
XXMX		10M = 10,000,000 Ω
(10 MΩ)		

**ORDERING EXAMPLE**


The ordering code for an AA0402 chip resistor, value 100 KΩ with ±1% tolerance, supplied in 7-inch tape reel is: AA0402FR-07100KL

**NOTE**

1. All our R-Chip products are RoHS compliant and Halogen free. "LFP" of the internal 2D reel label states "Lead-Free Process".
2. On customized label, "LFP" or specific symbol can be printed.


**MARKING**

AA0201 / AA0402



No marking


AA0603 / AA0805 / AA1206 / AA1210 / AA2010 / AA2512




E-24 series: 3 digits,  $\pm 5\%$   
First two digits for significant figure and 3rd digit for number of zeros

Fig. 2 Value = 10 K $\Omega$ 

AA0603




E-24 series: 3 digits,  $\pm 1\%$   
One short bar under marking letter

Fig. 3 Value = 24  $\Omega$ 

E-96 series: 3 digits,  $\pm 1\%$   
First two digits for E-96 marking rule and 3rd letter for number of zeros

Fig. 4 Value = 12.4 K $\Omega$ 


AA0805 / AA1206 / AA1210 / AA2010 / AA2512




Both E-24 and E-96 series: 4 digits,  $\pm 1\%$   
First three digits for significant figure and 4th digit for number of zeros

Fig. 5 Value = 10 K $\Omega$ 

AA1218



E-24 series: 3 digits,  $\pm 5\%$   
First two digits for significant figure and 3rd digit for number of zeros

Fig. 6 Value = 10 K $\Omega$ 

Both E-24 and E-96 series: 4 digits,  $\pm 1\%$   
First three digits for significant figure and 4th digit for number of zeros


Fig. 7 Value = 10 K $\Omega$ **NOTE**

For further marking information, please refer to data sheet "Chip resistors marking". Marking of AA series is the same as RC series.

## CONSTRUCTION

The resistors are constructed on top of an automotive grade ceramic body. Internal metal electrodes are added at each end and connected by a resistive glaze. The resistive glaze is covered by a lead-free glass. The composition of the glaze is adjusted to give the approximately required resistance value and laser trimming of this resistive glaze achieves the value within tolerance. The whole element is covered by a protective overcoat. Size 0603 and bigger is marked with the resistance value on top. Finally, the two external terminations (Ni / matte tin) are added, as shown in Fig.8.


## OUTLINES



## DIMENSIONS

Table I For outlines, please refer to Fig. 9

TYPE	L (mm)	W (mm)	H (mm)	$l_1$ (mm)	$l_2$ (mm)
AA0201	$0.60 \pm 0.03$	$0.30 \pm 0.03$	$0.23 \pm 0.03$	$0.12 \pm 0.05$	$0.15 \pm 0.05$
AA0402	$1.00 \pm 0.05$	$0.50 \pm 0.05$	$0.35 \pm 0.05$	$0.20 \pm 0.10$	$0.25 \pm 0.10$
AA0603	$1.60 \pm 0.10$	$0.80 \pm 0.10$	$0.45 \pm 0.10$	$0.25 \pm 0.15$	$0.25 \pm 0.15$
AA0805	$2.00 \pm 0.10$	$1.25 \pm 0.10$	$0.50 \pm 0.10$	$0.35 \pm 0.20$	$0.35 \pm 0.20$
AA1206	$3.10 \pm 0.10$	$1.60 \pm 0.10$	$0.55 \pm 0.10$	$0.45 \pm 0.20$	$0.50 \pm 0.20$
AA1210	$3.10 \pm 0.10$	$2.60 \pm 0.15$	$0.57 \pm 0.10$	$0.45 \pm 0.20$	$0.50 \pm 0.20$
AA1218	$3.10 \pm 0.10$	$4.60 \pm 0.10$	$0.57 \pm 0.10$	$0.45 \pm 0.20$	$0.50 \pm 0.20$
AA2010	$5.00 \pm 0.10$	$2.50 \pm 0.15$	$0.57 \pm 0.10$	$0.55 \pm 0.20$	$0.55 \pm 0.20$
AA2512	$6.35 \pm 0.10$	$3.20 \pm 0.15$	$0.57 \pm 0.10$	$0.60 \pm 0.20$	$0.60 \pm 0.20$



**ELECTRICAL CHARACTERISTICS**

Table 2

TYPE	RESISTANCE RANGE	CHARACTERISTICS					Jumper Criteria
		Operating Temperature Range	Max. Working Voltage	Max. Overload Voltage	Dielectric Withstanding Voltage	Temperature Coefficient of Resistance	
AA0201	5% (E24) $1\Omega \leq R \leq 22M\Omega$ (0201: Max. $10M\Omega$ . 1218: Max. $1M\Omega$ ) 0.5%, 1% (E24/E96) $1\Omega \leq R \leq 10M\Omega$ (1218: Max. $1M\Omega$ ) Jumper < $50m\Omega$	-55 °C to +155 °C	25V	50V	50V	$1\Omega \leq R \leq 10\Omega$ , -100/+400 ppm/°C $10\Omega < R \leq 10M\Omega$ , $\pm 300$ ppm/°C	Rated Current 0.5A Max. Current 1.0A
AA0402			50 V	100 V	100 V		Rated Current 1A Max. Current 2A
AA0603			75V	150 V	150 V		Rated Current 1A Max. Current 2A
AA0805			150 V	300 V	300 V		Rated Current 2A Max. Current 5A
AA1206			200 V	400 V	500 V	$1\Omega \leq R \leq 10\Omega$ , $\pm 200$ ppm/°C	Rated Current 2A Max. Current 10A
AA1210			200 V	500 V	500 V	$10\Omega < R \leq 10M\Omega$ , $\pm 150$ ppm/°C $10M\Omega < R \leq 22M\Omega$ , $\pm 200$ ppm/°C	Rated Current 2A Max. Current 10A
AA1218			200 V	500 V	500 V		Rated Current 6A Max. Current 10A
AA2010			200 V	500 V	500 V		Rated Current 2A Max. Current 10A
AA2512			200 V	500 V	500 V		Rated Current 2A Max. Current 10A

## FOOTPRINT AND SOLDERING PROFILES

Recommended footprint and soldering profiles. Please refer to data sheet “Chip resistors mounting”.

## PACKING STYLE AND PACKAGING QUANTITY

Table 3 Packing style and packaging quantity

PACKING STYLE	REEL DIMENSION	AA0201	AA0402	AA0603	AA0805	AA1206	AA1210	AA1218	AA2010	AA2512
Paper/PE taping reel (R)	7" (178 mm)	10,000	10,000	5,000	5,000	5,000	5,000	---	---	---
	13" (330 mm)	50,000	50,000	20,000	20,000	20,000	20,000	---	---	---
Embossed taping reel (K)	7" (178 mm)	---	---	---	---	---	---	4,000	4,000	4,000

### NOTE

I. For paper/PE/embossed tape and reel specifications/dimensions, please refer to data sheet “Chip resistors packing”.

## FUNCTIONAL DESCRIPTION

### OPERATING TEMPERATURE RANGE

Range: -55°C to +155°C

### POWER RATING

Each type rated power at 70°C:

AA0201=1/20W (0.05W)

AA0402=1/16 W (0.0625W)

AA0603=1/10 W (0.1W)

AA0805=1/8 W (0.125W)

AA1206=1/4 W (0.25W)

AA1210=1/2 W (0.5W)

AA1218=1 W

AA2010=3/4 W (0.75W)

AA2512=1 W

### RATED VOLTAGE

The DC or AA (rms) continuous working voltage corresponding to the rated power is determined by the following formula:

$$V = \sqrt{P \times R}$$


Or Maximum working voltage whichever is less

Where

V = Continuous rated DC or AA (rms) working voltage (V)

P = Rated power (W)

R = Resistance value ( $\Omega$ )



**TESTS AND REQUIREMENTS**

Table 4 Test condition, procedure and requirements

TEST	TEST METHOD	PROCEDURE	REQUIREMENTS
High Temperature Exposure	AEC-Q200 Test 3 MIL-STD-202 Method 108	1,000 hours at $T_A = 155\text{ }^{\circ}\text{C}$ , unpowered	$\pm(1.0\%+0.05\Omega)$ <50 m $\Omega$ for Jumper
Moisture Resistance	MIL-STD-202 Method 106	Each temperature / humidity cycle is defined at 8 hours, 3 cycles / 24 hours for 10d. with $25\text{ }^{\circ}\text{C}$ / $65\text{ }^{\circ}\text{C}$ 95% R.H, without steps 7a & 7b, unpowered  Parts mounted on test-boards, without condensation on parts	$\pm(0.5\%+0.05\Omega)$ for D/F tol. $\pm(2.0\%+0.05\Omega)$ for J tol. <100 m $\Omega$ for Jumper
Biased Humidity	AEC-Q200 Test 7 MIL-STD-202 Method 103	1,000 hours; $85\text{ }^{\circ}\text{C}$ / 85% RH 10% of operating power  Measurement at $24\pm 4$ hours after test conclusion.	$\pm(3.0\%+0.05\Omega)$ <100 m $\Omega$ for Jumper
Operational Life	AEC-Q200 Test 8 MIL-STD-202 Method 108	1,000 hours at $125\text{ }^{\circ}\text{C}$ , derated voltage applied for 1.5 hours on, 0.5 hour off, still-air required	$\pm(1.0\%+0.05\Omega)$ <100 m $\Omega$ for Jumper
Resistance to Soldering Heat	AEC-Q200 Test 15 MIL-STD-202 Method 210	Condition B, no pre-heat of samples Lead-free solder, $260\pm 5\text{ }^{\circ}\text{C}$ , $10\pm 1$ seconds immersion time  Procedure 2 for SMD: devices fluxed and cleaned with isopropanol	$\pm(0.5\%+0.05\Omega)$ for D/F tol. $\pm(1.0\%+0.05\Omega)$ for J tol. <50 m $\Omega$ for Jumper No visible damage
Thermal Shock	MIL-STD-202 Method 107	$-55/+125\text{ }^{\circ}\text{C}$  Number of cycles is 300. Devices mounted  Maximum transfer time is 20 seconds. Dwell time is 15 minutes. Air – Air	$\pm(1.0\%+0.05\Omega)$ <50 m $\Omega$ for Jumper
ESD	AEC-Q200 Test 17 AEC-Q200-002	1 pos. + 1 neg. discharges  0201: 500V 0402/0603: 1KV 0805 and above: 2KV	$\pm(3.0\%+0.05\Omega)$ <50 m $\Omega$ for Jumper

TEST	TEST METHOD	PROCEDURE	REQUIREMENTS
Solderability - Wetting	AEC-Q200 Test I8 J-STD-002	Electrical Test not required Magnification 50X SMD conditions: (a) Method B, aging 4 hours at 155 °C dry heat, dipping at 235±3 °C for 5±0.5 seconds. (b) Method B, steam aging 8 hours, dipping at 215±3 °C for 5±0.5 seconds. (c) Method D, steam aging 8 hours, dipping at 260±3 °C for 30±0.5 seconds.	Well tinned (≥95% covered) No visible damage
Board Flex	AEC-Q200 Test 21 AEC-Q200-005	Chips mounted on a 100mm x 40mm glass epoxy resin PCB (FR4) Bending for 0201/0402: 5 mm 0603/0805: 3 mm 1206 and above: 2 mm Holding time: minimum 60 seconds	±(1.0%+0.05Ω) <50 mΩ for Jumper
Temperature Coefficient of Resistance (T.C.R.)	IEC 60115-1 4.8 MIL-STD-202 Method 304	At +25/-55 °C and +25/+125 °C  <b>Formula:</b> $T.C.R = \frac{R_2 - R_1}{R_1(t_2 - t_1)} \times 10^6 \text{ (ppm/°C)}$ Where t <sub>1</sub> =+25 °C or specified room temperature t <sub>2</sub> =-55 °C or +125 °C test temperature R <sub>1</sub> =resistance at reference temperature in ohms R <sub>2</sub> =resistance at test temperature in ohms	Refer to table 2
Short Time Overload	IEC60115-1 8.1	2.5 times of rated voltage or maximum overload voltage whichever is less for 5 sec at room temperature	±(1.0%+0.05Ω) <50 mΩ for Jumper
FOS	ASTM-B-809-95	- Sulfur (saturated vapor) 1000 hours, 90±2 °C unpowered	±(1.0%+0.05Ω)
	ASTM-B-809-95* *Modified	- Sulfur 750 hours, 105 °C. unpowered	±(4.0%+0.05Ω)



**REVISION HISTORY**

REVISION	DATE	CHANGE NOTIFICATION	DESCRIPTION
Version 3	Dec. 08, 2015	-	- Update Dielectric Withstanding Voltage
Version 2	Apr. 09, 2015	-	- Modified FOS test procedure
Version 1	Jan. 27, 2015	-	- Dimensions update
Version 0	Feb. 27, 2014	-	- First issue of this specification

## **LEGAL DISCLAIMER**

YAGEO, its distributors and agents (collectively, "YAGEO"), hereby disclaims any and all liabilities for any errors, inaccuracies or incompleteness contained in any product related information, including but not limited to product specifications, datasheets, pictures and/or graphics. YAGEO may make changes, modifications and/or improvements to product related information at any time and without notice.

YAGEO makes no representation, warranty, and/or guarantee about the fitness of its products for any particular purpose or the continuing production of any of its products. To the maximum extent permitted by law, YAGEO disclaims (i) any and all liability arising out of the application or use of any YAGEO product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for a particular purpose, non -infringement and merchantability.

YAGEO products are designed for general purpose applications under normal operation and usage conditions. Please contact YAGEO for the applications listed below which require especially high reliability for the prevention of defects which might directly cause damage to the third party's life, body or property: Aerospace equipment (artificial satellite, rocket, etc.), Atomic energy-related equipment, Aviation equipment, Disaster prevention equipment, crime prevention equipment, Electric heating apparatus, burning equipment, Highly public information network equipment, data-processing equipment, Medical devices, Military equipment, Power generation control equipment, Safety equipment, Traffic signal equipment, Transportation equipment and Undersea equipment, or for any other application or use in which the failure of YAGEO products could result in personal injury or death, or serious property damage. Particularly **YAGEO Corporation and its affiliates do not recommend the use of commercial or automotive grade products for high reliability applications or manned space flight.**

Information provided here is intended to indicate product specifications only. YAGEO reserves all the rights for revising this content without further notification, as long as products are unchanged. Any product change will be announced by PCN.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[YAGEO:](#)

[AA0402FR-0718KL](#) [AA0402FR-07100KL](#) [AA0603FR-0710KL](#) [AA1218FK-071KL](#) [AA1206JR-070RL](#) [AA0603FR-071KL](#) [AA0402FR-0720KL](#) [AA0402FR-0710KL](#) [AA0603JR-070RL](#) [AA0402JR-070RL](#) [AA0402FR-07249KL](#) [AA0402JR-071KL](#) [AA0603FR-0724K9L](#) [AA0402FR-071KL](#) [AA0402FR-07100RL](#) [AA0402FR-071ML](#) [AA0603FR-0724KL](#) [AA0603FR-076K34L](#) [AA0402FR-072M8L](#) [AA1206FR-0718K2L](#) [AA0402JR-0768KL](#) [AA0603FR-075K1L](#) [AA0402JR-07220RL](#) [AA2010FK-07120RL](#) [AA1218FK-0710RL](#) [AA2512JK-07120KL](#) [AA0603JR-073KL](#) [AA0402FR-0722RL](#) [AA0603FR-0715KL](#) [AA0402FR-073K3L](#) [AA0402JR-0715KL](#) [AA0603FR-07374KL](#) [AA1210JR-07100RL](#) [AA1210FR-0751KL](#) [AA0603FR-0768KL](#) [AA0402JR-07100KL](#) [AA0603FR-0782KL](#) [AA2512JK-072R4L](#) [AA0603FR-0778K7L](#) [AA0603FR-0756KL](#) [AA1210FR-0710RL](#) [AA2512FK-0762RL](#) [AA0603FR-071ML](#) [AA0603FR-0714K7L](#) [AA0805FR-072K61L](#) [AA1206JR-07130KL](#) [AA0805FR-07100RL](#) [AA1206FR-0747RL](#) [AA0402FR-07750KL](#) [AA0603FR-0748K7L](#) [AA0603JR-07680RL](#) [AA0201FR-07100KL](#) [AA0805FR-0710RL](#) [AA0402FR-07113RL](#) [AA0402FR-0761K9L](#) [AA0402JR-072K2L](#) [AA0402FR-07715RL](#) [AA0603JR-07100RL](#) [AA0402JR-07100RL](#) [AA1206JR-073K3L](#) [AA0402JR-074K7L](#) [AA0402JR-071M2L](#) [AA0805FR-072R2L](#) [AA0805JR-071RL](#) [AA0603FR-07392KL](#) [AA1210FR-079R1L](#) [AA0603FR-07390KL](#) [AA2512FK-077K5L](#) [AA0402FR-072M15L](#) [AA0603FR-0710ML](#) [AA0805JR-0710KL](#) [AA1206JR-0710KL](#) [AA0805JR-070RL](#) [AA0402FR-074K64L](#) [AA0402JR-07470RL](#) [AA1206FR-07100RL](#) [AA0402FR-0710ML](#) [AA1206FR-072M32L](#) [AA0603JR-0710KL](#) [AA1210JR-070RL](#) [AA0603JR-0710ML](#) [AA0402FR-0726K1L](#) [AA0402FR-078K2L](#) [AA0603FR-072K49L](#) [AA0603FR-071K4L](#) [AA2010JK-070RL](#) [AA1206FR-072K74L](#) [AA0402JR-0722KL](#) [AA1210FR-07110KL](#) [AA0201FR-07100RL](#) [AA0603FR-074K7L](#) [AA0603JR-073ML](#) [AA0402JR-074M3L](#) [AA1206JR-07130RL](#) [AA2512JK-07330RL](#) [AA0805FR-079K76L](#) [AA0402FR-071R21L](#) [AA0402JR-071ML](#) [AA0402JR-071K8L](#) [AA1210FR-0791KL](#)