

## Thin Film MELF Resistors With Established Reliability



### FEATURES

- IECQ-CECC approved to EN 140401-803, version E
- Established reliability, failure rate level E6
- Advanced metal film technology
- Single Lot Date Code
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)



### APPLICATIONS

- Medical
- Military
- Aerospace

MMU 0102 VG03, MMA 0204 VG03, and MMB 0207 VG03 thin film MELF resistors with established reliability are the perfect choice for all high-reliability applications typically found in military, aircraft and spacecraft electronics. These versions supplement the families of professional and precision MELF resistors MMU 0102, MMA 0204, and MMB 0207.

TECHNICAL SPECIFICATIONS			
DESCRIPTION	MMU 0102 VG03	MMA 0204 VG03	MMB 0207 VG03
DIN size	0102	0204	0207
Metric size code (EN/CECC style)	RC2211M	RC3715M	RC6123M
Resistance range	100 $\Omega$ to 2.21 M $\Omega$ ; 0 $\Omega$	1 $\Omega$ to 5.11 M $\Omega$ ; 0 $\Omega$	1 $\Omega$ to 10 M $\Omega$ ; 0 $\Omega$
Resistance tolerance	$\pm 1\%$ ; $\pm 0.1\%$		
Temperature coefficient	$\pm 50$ ppm/K; $\pm 15$ ppm/K		
Rated dissipation, $P_{70}$	0.2 W	0.25 W	0.4 W
Operating voltage, $U_{max}$ , AC <sub>RMS</sub> or DC	150 V	200 V	350 V <sup>(1)</sup>
Permissible film temperature, $\vartheta_{F max}$	125 °C		
Operating temperature range	-55 °C to 125 °C		
Max. resistance change at $P_{70}$ for resistance, $ \Delta R/R $ after:	100 $\Omega$ to 221 k $\Omega$	1 $\Omega$ to 332 k $\Omega$	1 $\Omega$ to 1 M $\Omega$
1000 h	$\leq 0.15\%$ <sup>(1)</sup>		
8000 h	$\leq 0.3\%$ <sup>(1)</sup>		
225 000 h	$\leq 1\%$		
Permissible voltage against ambient (insulation):			
1 min; $U_{ins}$	200 V	300 V	500 V
Assessed failure rate level	E6 = $10^{-6}$ /h		
Quality factor, $\pi_Q$	0.3		
Failure rate: FIT <sub>observed</sub>	$< 0.05 \times 10^{-9}$ /h		

### Notes

- These resistors do not feature a limited lifetime when operated within the permissible limits. However, resistance value drift increasing over operating time may result in exceeding a limit acceptable to the specific application, thereby establishing a functional lifetime
- The failure rate level E6 ( $10^{-6}$ /h,  $\pi_Q = 0.3$ ), corresponding to MIL level P, is superior to level E5 ( $10^{-5}$ /h,  $\pi_Q = 1$ ) and thus may be used as a replacement

<sup>(1)</sup> These data provide a user advantage over the requirements of EN 140401-803



TEMPERATURE COEFFICIENT AND RESISTANCE RANGE <sup>(1)</sup>				
TYPE / SIZE	TCR	TOLERANCE	RESISTANCE	E-SERIES
MMU 0102 VG03	± 50 ppm/K	± 1 %	100 Ω to 2.21 MΩ	E96
	± 15 ppm/K	± 0.1 %	100 Ω to 100 kΩ	E192
	Jumper <sup>(2)</sup> ; $I_{max.} = 2\text{ A}$	≤ 10 mΩ	0 Ω	-
MMA 0204 VG03	± 50 ppm/K	± 1 %	1 Ω to 5.11 MΩ	E96
	± 15 ppm/K	± 0.1 %	75 Ω to 100 kΩ	E192
	Jumper <sup>(2)</sup> ; $I_{max.} = 3\text{ A}$	≤ 10 mΩ	0 Ω	-
MMB 0207 VG03	± 50 ppm/K	± 1 %	1 Ω to 10 MΩ	E96
	± 15 ppm/K	± 0.1 %	75 Ω to 499 kΩ	E192
	Jumper <sup>(2)</sup> ; $I_{max.} = 5\text{ A}$	≤ 10 mΩ	0 Ω	-

## Notes

- Other TCR or tolerances, or combinations thereof, or resistance values from other E-series than given are not permitted in EN 140401-803 for version E products
- <sup>(1)</sup> For the approved IECQ-CECC resistance range, please refer to [www.vishay.com/doc?28945](http://www.vishay.com/doc?28945)
- <sup>(2)</sup> The temperature coefficient of resistance (TCR) is not specified for 0 Ω jumpers

PACKAGING						
TYPE / SIZE	CODE	QUANTITY	PACKAGING STYLE	WIDTH	PITCH	PACKAGING DIMENSIONS
MMU 0102 VG03	B1	1000	Antistatic blister tape acc. IEC 60286-3, Type 2a, on reel	8 mm	4 mm	Ø 180 mm / 7"
	B3 = BL	3000				Ø 330 mm / 13"
	B0	10 000				
MMA 0204 VG03	B1	1000	Antistatic blister tape acc. IEC 60286-3, Type 2a, on reel	8 mm	4 mm	Ø 180 mm / 7"
	B3 = BL	3000				Ø 330 mm / 13"
	B0	10 000				
MMB 0207 VG03	B1	1000	Antistatic blister tape acc. IEC 60286-3, Type 2a, on reel	12 mm	4 mm	Ø 180 mm / 7"
	B2	2000				Ø 330 mm / 13"
	B7	7000				



## PART NUMBER AND PRODUCT DESCRIPTION

Part Number: MMA0204WC4999FB300

Part Number: MMA0204WZ0000ZB300

M	M	A	0	2	0	4	W	C	4	9	9	9	F	B	3	0	0
M	M	A	0	2	0	4	W	Z	0	0	0	0	Z	B	3	0	0

TYPE / SIZE	VERSION	TCR	RESISTANCE	TOLERANCE	PACKAGING
MMU 0102 MMA 0204 MMB 0207	W = EN 140401-803, "Version E"; failure rate level E6	C = $\pm 50$ ppm/K E = $\pm 15$ ppm/K Z = jumper	3 digit value 1 digit multiplier  MULTIPLIER 8 = $\cdot 10^{-2}$ 9 = $\cdot 10^{-1}$ 0 = $\cdot 10^0$ 1 = $\cdot 10^1$ 2 = $\cdot 10^2$ 3 = $\cdot 10^3$ 4 = $\cdot 10^4$ 5 = $\cdot 10^5$ 0000 = jumper	F = $\pm 1$ % B = $\pm 0.1$ % Z = jumper	B1 B3 B0 B2 B7

Product Description: MMA 0204-50 1 % VG03 BL 49R9

Product Description: MMA 0204 VG03 BL 0R0

MMA 0204	-50	1 %	VG03	BL	49R9
MMA 0204	-	-	VG03	BL	0R0
TYPE / SIZE	TCR	TOLERANCE	VERSION	PACKAGING	RESISTANCE
MMU 0102 MMA 0204 MMB 0207	$\pm 50$ ppm/K $\pm 15$ ppm/K	$\pm 1$ % $\pm 0.1$ %	VG03 = EN 140401-803, "Version E"; failure rate level E6	B1 BL B0 B2 B7	49R9 = 49.9 $\Omega$ 4K64 = 4.64 k $\Omega$ 0R0 = jumper

## Notes

- The products can be ordered using either the PART NUMBER or the PRODUCT DESCRIPTION
- Products within a packaging unit are Single Lot Date Code

## EN 140401-803 ORDERING INFORMATION

Example of the ordering information for a resistor: MMA 0204-50 1 % VG03 49R9

EN140401-803EZRC3715MR49R9FE6

Example of the ordering information for a zero ohm jumper: MMA 0204 VG03 0R0

EN140401-803EZRC3715M-0R00-E6

The elements used in the component number have the following meaning:

EN140401-803	EN detail specification number
EZ	Assessment level for the zero-defect approach
RC3715M	Style (size)
R	Temperature coefficient, according to EN 60062 R = $\pm 50$ ppm/K; P = $\pm 15$ ppm/K
49R9	Resistance, according to EN 60062, 4 characters
F	Tolerance on rated resistance, according to EN 60062 F = $\pm 1$ %; B = $\pm 0.1$ %
E6	Failure rate level according to EN 60115-1, annex ZR

## Notes

- The ordering information according to EN 140401-803:2017 shown above succeeds and replaces the ordering information according to earlier versions of the detail specification EN 140401-803 or its predecessor CECC 40401-803, for example:  
CECC 40401-803 EZ RC3715M C 49R9 F E6  
CECC 40401-803 S RC3715 C 49R9 F E6  
with EZ: S Assessment level, where EZ is successor to and superior replacement for S  
RC3715M; RC3715 Style, with added suffix M for "metric"  
C Temperature coefficient, according to the detail specification  
C =  $\pm 50$  ppm/K; E =  $\pm 15$  ppm/K.
- EN 140401-803 succeeds the prior specifications CECC 40401-803, CECC 40401-001 (now "Version E") and CECC 40401-005 (now "Version A")



## DESCRIPTION

Production is strictly controlled and follows an extensive set of instructions established for reproducibility. A homogeneous film of metal alloy is deposited on a high grade ceramic body ( $\text{Al}_2\text{O}_3$ ) and conditioned to achieve the desired temperature coefficient. Nickel plated steel termination caps are firmly pressed on the metallized rods. A special laser is used to achieve the target value by smoothly cutting a helical groove in the resistive layer without damaging the ceramics. The resistor elements are covered by a protective coating designed for electrical, mechanical and climatic protection. The terminations receive a final pure matte tin on nickel plating. Five color code rings designate the resistance value and tolerance in accordance with **IEC 60062** <sup>(1)</sup>.

The result of the determined production is verified by an extensive testing procedure performed on 100 % of the individual resistors. This includes pulse load screening (for  $R \geq 10 \Omega$ ) and additional non-linearity screening (for  $R \geq 30 \Omega$ ) for the elimination of products with a potential risk of early life failures according to EN 140401-803, 2.1.2.2. Only accepted products are laid directly into the blister tape in accordance with **IEC 60286-3** <sup>(1)</sup>, **Type 2a**. Products within a package unit are from the same production lot and carry the same date code.

## ASSEMBLY

The resistors are suitable for processing on automatic SMD assembly systems. They are suitable for automatic soldering using wave, reflow or vapor phase as shown in **IEC 61760-1** <sup>(1)</sup>. Solderability is specified for 2 years after production or requalification, however, excellent solderability is proven after extended storage in excess of 10 years. The permitted storage time is 20 years. The immunity of the plating against tin whisker growth has been proven under extensive testing.

The resistors are completely lead (Pb)-free, the pure tin plating provides compatibility with lead (Pb)-free soldering processes.

The encapsulation is resistant to all cleaning solvents commonly used in the electronics industry, including alcohols, esters and aqueous solutions. The suitability of conformal coatings, potting compounds, and their processes, if applied, shall be qualified by appropriate means to ensure the long-term stability of the whole system.

## Notes

- (1) The quoted IEC standards are also released as EN standards with the same number and identical contents
- (2) The IEC 62474 list of declarable substances is maintained in a dedicated database, which is available at <http://std.iec.ch/iec62474>
- (3) The Global Automotive Declarable Substance List (GADSL) is maintained by the American Chemistry Council, and available at [www.gadsl.org](http://www.gadsl.org)
- (4) The SVHC list is maintained by the European Chemical Agency (ECHA) and available at <http://echa.europa.eu/candidate-list-table>

## MATERIALS

Vishay acknowledges the following systems for the regulation of hazardous substances.

- IEC 62474, Material Declaration for Products of and for the Electrotechnical Industry, with the list of declarable substances given therein <sup>(2)</sup>
- The Global Automotive Declarable Substance List (GADSL) <sup>(3)</sup>
- The REACH regulation (1907/2006/EC) and the related list of substances with very high concern (SVHC) <sup>(4)</sup> for its supply chain

The products do not contain any of the banned substances as per IEC 62474, GADSL, or the SVHC list, see [www.vishay.com/how/leadfree](http://www.vishay.com/how/leadfree).


Hence the products fully comply with the following directives:

- 2000/53/EC End-of-Life Vehicle Directive (ELV) and Annex II (ELV II)
- 2011/65/EU Restriction of the Use of Hazardous Substances Directive (RoHS) with amendment 2015/863/EU
- 2012/19/EU Waste Electrical and Electronic Equipment Directive (WEEE)

Vishay pursues the elimination of conflict minerals from its supply chain, see the Conflict Minerals Policy at [www.vishay.com/doc?49037](http://www.vishay.com/doc?49037).

## APPROVALS

Where applicable, the resistors are approved within the IECQ-CECC Quality Assessment System for Electronic Components to the detail specification **EN 140401-803** which refers to **EN 60115-1**, **EN 60115-8** and the variety of environmental test procedures of the **IEC 60068** <sup>(1)</sup> series.

Conformity is attested by the use of the **CECC** logo () as the mark of conformity on the package label.

Vishay Beyschlag has achieved “**Approval of Manufacturer**” in accordance with **IECQ 03-1**. The release certificate for “**Technology Approval Schedule**” in accordance with **CECC 240001** and based on **IECQ 03-3-1** is granted for the Vishay Beyschlag manufacturing process. The Vishay Beyschlag production facility is registered with the CAGE code D9539.


## RELATED PRODUCTS

A wider range of TCR, tolerance, and resistance values, plus the option of values from a different E series is available with products approved to **EN 140401-803**, Version A, without established reliability, nominal failure rate level E0 (quality factor  $\pi_Q = 3$ ). See the datasheets:


- “Professional Thin Film MELF Resistors”  
[www.vishay.com/doc?28713](http://www.vishay.com/doc?28713)
- “Precision Thin Film MELF Resistors”  
[www.vishay.com/doc?28714](http://www.vishay.com/doc?28714)
- “Ultra Precision Thin Film MELF Resistors”  
[www.vishay.com/doc?28715](http://www.vishay.com/doc?28715)




## FUNCTIONAL PERFORMANCE



### Derating



### Current Noise Voltage Ratio



### Non-Linearity - Third Harmonic Ratio $A_3$

Further information on the performance of these products is given in the following datasheets:

- “Professional Thin Film MELF Resistors” ([www.vishay.com/doc?28713](http://www.vishay.com/doc?28713)) for products  $\pm 50$  ppm/K;  $\pm 1$  % and 0  $\Omega$  jumper
- “Precision Thin Film MELF Resistors” ([www.vishay.com/doc?28714](http://www.vishay.com/doc?28714)) for products  $\pm 15$  ppm/K;  $\pm 0.1$  %

## TESTS AND REQUIREMENTS

All tests are carried out in accordance with the following specifications:

EN 60115-1, generic specification


EN 60115-8 (successor of EN 140400), sectional specification

EN 140401-803, detail specification

For further information on the tests and requirements of these products please refer to the specifications mentioned above, and to the following datasheets:

- “Professional Thin Film MELF Resistors” ([www.vishay.com/doc?28713](http://www.vishay.com/doc?28713)) for products  $\pm 50$  ppm/K;  $\pm 1$  % and 0  $\Omega$  jumper
- “Precision Thin Film MELF Resistors” ([www.vishay.com/doc?28714](http://www.vishay.com/doc?28714)) for products  $\pm 15$  ppm/K;  $\pm 0.1$  %

## DIMENSIONS




DIMENSIONS AND MASS						
TYPE	L (mm)	D (mm)	L <sub>1</sub> min. (mm)	D <sub>1</sub> (mm)	K (mm)	MASS (mg)
MMU 0102 VG03	2.2 + 0/- 0.1	1.1 + 0/- 0.1	1.2	D + 0/- 0.1	0.4 + 0.1/- 0.05	8
MMA 0204 VG03	3.6 + 0/- 0.2	1.4 + 0/- 0.1	1.8	D + 0/- 0.15	0.75 $\pm$ 0.1	22
MMB 0207 VG03	5.8 + 0/- 0.15	2.2 + 0/- 0.2	3.2	D + 0/- 0.2	1.15 $\pm$ 0.1	80

### Note

- Color code marking is applied according to IEC 60062 <sup>(1)</sup> in five bands. Each color band appears as a single solid line, voids are permissible if at least  $\frac{2}{3}$  of the band is visible from each radial angle of view. The last color band for tolerance is approximately 50 % wider than the other bands. An interrupted blue band between the 1<sup>st</sup> and 2<sup>nd</sup> full band indicates the failure rate level E6. An interrupted orange band between the 4<sup>th</sup> and 5<sup>th</sup> full band indicates the temperature coefficient of 15 ppm/K

## SOLDER PAD DIMENSIONS



RECOMMENDED SOLDER PAD DIMENSIONS								
TYPE	WAVE SOLDERING				REFLOW SOLDERING			
	G (mm)	Y (mm)	X (mm)	Z (mm)	G (mm)	Y (mm)	X (mm)	Z (mm)
MMU 0102 VG03	0.7	1.2	1.5	3.1	1.1	0.8	1.3	2.7
MMA 0204 VG03	1.5	1.5	1.8	4.5	1.7	1.2	1.6	4.1
MMB 0207 VG03	2.8	2.1	2.6	7.0	3.2	1.7	2.4	6.6

### Notes

- The given solder pad dimensions reflect the considerations for board design and assembly as outlined e.g. in standards IEC 61188-5-x <sup>(1)</sup>, or in publication IPC 7351. They do not guarantee any supposed thermal properties, however, they will be found adequate for most general applications

<sup>(1)</sup> The quoted IEC standards are also released as EN standards with the same number and identical contents

**HISTORICAL 12NC INFORMATION**

- The resistors had a 12-digit numeric code starting with 2312
- The subsequent 4 digits indicated the resistor type, specification and packaging; see the 12NC table
- The remaining 4 digits indicated the resistance value:
  - The first 3 digits indicate the resistance value
  - The last digit indicated the resistance decade in accordance with the resistance decade table

RESISTANCE DECADE	LAST DIGIT
1 $\Omega$ to 9.99 $\Omega$	8
10 $\Omega$ to 99.9 $\Omega$	9
100 $\Omega$ to 999 $\Omega$	1
1 k $\Omega$ to 9.99 k $\Omega$	2
10 k $\Omega$ to 99.9 k $\Omega$	3
100 k $\Omega$ to 999 k $\Omega$	4
1 M $\Omega$ to 9.99 M $\Omega$	5
10 M $\Omega$	6

**Historical 12NC Example**

The 12NC of a MMU 0102 VG03 resistor, value 287K and TCR 50 with  $\pm 1$  % tolerance, supplied in blister tape of 3000 units per reel was: 2312 165 02874.

**HISTORICAL 12NC - RESISTOR TYPE AND PACKAGING**

DESCRIPTION			2312 ... ..			
			BLISTER TAPE ON REEL			BULK CASE
TYPE	TCR	TOL.	B1 1000 PIECES	BL 3000 PIECES	B0 10 000 PIECES	M8 8000 PIECES
MMU 0102 VG03	$\pm 50$ ppm/K	$\pm 1$ %	170 0....	165 0....	175 0....	060 0....
	$\pm 15$ ppm/K	$\pm 0.1$ %	172 0....	167 0....	177 0....	062 0....
	Jumper		172 90001	167 90001	177 90001	062 90001
TYPE	TCR	TOL.	B1 1000 PIECES	BL 3000 PIECES	B0 10 000 PIECES	M3 3000 PIECES
MMA 0204 VG03	$\pm 50$ ppm/K	$\pm 1$ %	140 0....	155 0....	145 0....	040 0....
	$\pm 15$ ppm/K	$\pm 0.1$ %	142 0....	157 0....	147 0....	042 0....
	Jumper		142 90001	157 90001	147 90001	042 90001
TYPE	TCR	TOL.	B1 1000 PIECES	B2 2000 PIECES	B7 7000 PIECES	-
MMB 0207 VG03	$\pm 50$ ppm/K	$\pm 1$ %	180 0....	195 0....	185 0....	
	$\pm 15$ ppm/K	$\pm 0.1$ %	182 0....	197 0....	187 0....	
	Jumper		182 90001	197 90001	187 90001	





## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

<a href="#">MMA0204WC1652FB100</a>	<a href="#">MMA0204WC9532FB100</a>	<a href="#">MMA0204WC1402FB100</a>	<a href="#">MMA0204WC1302FB100</a>
<a href="#">MMA0204WC4122FB100</a>	<a href="#">MMA0204WC1133FB100</a>	<a href="#">MMA0204WC3921FB100</a>	<a href="#">MMU0102WZ0000ZB300</a>
<a href="#">MMA0204WC2741FB100</a>	<a href="#">MMU0102WC1000FB300</a>	<a href="#">MMA0204WC1002FB100</a>	<a href="#">MMA0204WC1003FB100</a>
<a href="#">MMA0204WC2002FB100</a>	<a href="#">MMA0204WC1000FB100</a>	<a href="#">MMB0207WC4993FB100</a>	<a href="#">MMA0204WC1303FB100</a>
<a href="#">MMA0204WC2211FB100</a>	<a href="#">MMU0102WE2001BB100</a>	<a href="#">MMU0102WE5111BB100</a>	<a href="#">MMU0102WC1822FB300</a>
<a href="#">MMU0102WC3010FB300</a>	<a href="#">MMU0102WC2432FB300</a>	<a href="#">MMU0102WC2211FB300</a>	<a href="#">MMA0204WC4323FB300</a>
<a href="#">MMU0102WE3921BB100</a>	<a href="#">MMA0204WC1008FB300</a>	<a href="#">MMA0204WC7681FB100</a>	<a href="#">MMA0204WC2212FB100</a>
<a href="#">MMA0204WC3324FB100</a>	<a href="#">MMA0204WC5628FB100</a>	<a href="#">MMA0204WZ0000ZB100</a>	<a href="#">MMA0204WE7501BB100</a>
<a href="#">MMU0102WC6190FB100</a>	<a href="#">MMA0204WE5622BB100</a>	<a href="#">MMA0204WC4021FB300</a>	<a href="#">MMU0102WC2002FB300</a>
<a href="#">MMA0204WE6812BB100</a>	<a href="#">MMA0204WE3441BB100</a>	<a href="#">MMU0102WC1002FB100</a>	<a href="#">MMA0204WE8251BB100</a>
<a href="#">MMA0204WC1009FB100</a>	<a href="#">MMU0102WE1003BB100</a>	<a href="#">MMA0204WE3321BB100</a>	<a href="#">MMA0204WE1003BB100</a>
<a href="#">MMA0204WE5231BB100</a>	<a href="#">MMA0204WC1211FB300</a>	<a href="#">MMU0102WC1500FB300</a>	<a href="#">MMU0102WC3322FB300</a>
<a href="#">MMA0204WE2001BB300</a>	<a href="#">MMA0204WC4999FB100</a>	<a href="#">MMA0204WC1004FB300</a>	<a href="#">MMA0204WC3402FB100</a>
<a href="#">MMB0207WC6811FB100</a>	<a href="#">MMA0204WC5621FB100</a>	<a href="#">MMA0204WC5623FB300</a>	<a href="#">MMA0204WC2009FB100</a>
<a href="#">MMA0204WC5490FB100</a>	<a href="#">MMU0102WE6810BB100</a>	<a href="#">MMA0204WC7501FB300</a>	<a href="#">MMA0204WC3928FB100</a>
<a href="#">MMA0204WC3013FB100</a>	<a href="#">MMA0204WC2321FB100</a>	<a href="#">MMA0204WC2372FB100</a>	<a href="#">MMA0204WE1691BB100</a>
<a href="#">MMA0204WE4321BB100</a>	<a href="#">MMA0204WC2213FB100</a>	<a href="#">MMA0204WE4642BB100</a>	<a href="#">MMA0204WC1300FB100</a>
<a href="#">MMA0204WE2182BB100</a>	<a href="#">MMA0204WE2292BB100</a>	<a href="#">MMU0102WE1211BB100</a>	<a href="#">MMU0102WE3322BB100</a>
<a href="#">MMA0204WC3922FB100</a>	<a href="#">MMA0204WC6811FB100</a>	<a href="#">MMA0204WC4751FB100</a>	<a href="#">MMA0204WC1501FB100</a>
<a href="#">MMU0102WC2214FB300</a>	<a href="#">MMA0204WE1022BB100</a>	<a href="#">MMA0204WE3742BB100</a>	<a href="#">MMA0204WE1101BB100</a>
<a href="#">MMA0204WE1472BB100</a>	<a href="#">MMU0102WC1302FB300</a>	<a href="#">MMA0204WE6982BB100</a>	<a href="#">MMA0204WE6191BB100</a>
<a href="#">MMA0204WC2740FB300</a>	<a href="#">MMA0204WC5622FB100</a>	<a href="#">MMA0204WC2003FB100</a>	<a href="#">MMA0204WC4992FB100</a>
<a href="#">MMU0102WC3921FB300</a>	<a href="#">MMU0102WE4752BB100</a>	<a href="#">MMU0102WC6810FB300</a>	<a href="#">MMA0204WE1211BB100</a>
<a href="#">MMA0204WE1821BB100</a>	<a href="#">MMA0204WE9092BB100</a>	<a href="#">MMU0102WC9090FB300</a>	<a href="#">MMA0204WE1912BB100</a>
<a href="#">MMA0204WC9761FB100</a>	<a href="#">MMA0204WE2002BB100</a>	<a href="#">MMA0204WC5110FB300</a>	<a href="#">MMA0204WC9531FB100</a>