



- ▼ 100% R_g & UIS Test
- ▼ Simple Drive Requirement
- ▼ Low On-resistance
- ▼ RoHS Compliant & Halogen-Free



BV_{DSS}	40V
$R_{DS(ON)}$	1.5m Ω



SPPAK 5x6

Description

XP4NA1R5HC series are innovated design and silicon process technology to achieve the lowest possible on-resistance and fast switching performance. It provides the designer with an extreme efficient device for use in a wide range of power applications.

The SPPAK 5x6 package is special for DC-DC converters application and the foot print is compatible with SO-8 with backside heat sink and lower profile.

Absolute Maximum Ratings@ $T_j=25^\circ\text{C}$ (unless otherwise specified)

Symbol	Parameter	Rating	Units
V_{DS}	Drain-Source Voltage	40	V
V_{GS}	Gate-Source Voltage	± 20	V
$I_D@T_C=25^\circ\text{C}$	Drain Current, V_{GS} @ 10V ⁶ (Silicon Limited)	225	A
$I_D@T_C=25^\circ\text{C}$	Drain Current, V_{GS} @ 10V ⁶ (Package Limited)	100	A
$I_D@T_C=100^\circ\text{C}$	Drain Current, V_{GS} @ 10V ⁶ (Package Limited)	100	A
$I_D@T_A=25^\circ\text{C}$	Drain Current, V_{GS} @ 10V ³	45	A
$I_D@T_A=70^\circ\text{C}$	Drain Current, V_{GS} @ 10V ³	36	A
I_{DM}	Pulsed Drain Current ¹	720	A
$P_D@T_C=25^\circ\text{C}$	Total Power Dissipation	125	W
$P_D@T_A=25^\circ\text{C}$	Total Power Dissipation ³	5	W
E_{AS}	Single Pulse Avalanche Energy ⁴	125	mJ
T_{STG}	Storage Temperature Range	-55 to 150	$^\circ\text{C}$
T_J	Operating Junction Temperature Range	-55 to 150	$^\circ\text{C}$

Thermal Data

Symbol	Parameter	Value	Unit
R_{thj-c}	Maximum Thermal Resistance, Junction-case	1	$^\circ\text{C}/\text{W}$
R_{thj-a}	Maximum Thermal Resistance, Junction-ambient ³	25	$^\circ\text{C}/\text{W}$

Electrical Characteristics@T_j=25°C(unless otherwise specified)

Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Units
BV _{DSS}	Drain-Source Breakdown Voltage	V _{GS} =0V, I _D =250uA	40	-	-	V
R _{DS(ON)}	Static Drain-Source On-Resistance ²	V _{GS} =10V, I _D =40A	-	-	1.5	mΩ
V _{GS(th)}	Gate Threshold Voltage	V _{DS} =V _{GS} , I _D =250uA	2.4	-	3.6	V
g _{fs}	Forward Transconductance	V _{DS} =5V, I _D =40A	-	150	-	S
I _{DSS}	Drain-Source Leakage Current	V _{DS} =32V, V _{GS} =0V	-	-	10	uA
I _{GSS}	Gate-Source Leakage	V _{GS} =±20V, V _{DS} =0V	-	-	±0.1	uA
Q _g	Total Gate Charge ⁵	I _D =40A	-	88	140.8	nC
Q _{gs}	Gate-Source Charge ⁵	V _{DS} =20V	-	21	-	nC
Q _{gd}	Gate-Drain ("Miller") Charge ⁵	V _{GS} =10V	-	26	-	nC
t _{d(on)}	Turn-on Delay Time ⁵	V _{DS} =20V	-	16	-	ns
t _r	Rise Time ⁵	I _D =40A	-	70	-	ns
t _{d(off)}	Turn-off Delay Time ⁵	R _G =1Ω	-	38	-	ns
t _f	Fall Time ⁵	V _{GS} =10V	-	11	-	ns
C _{iss}	Input Capacitance ⁵	V _{GS} =0V	-	4460	7136	pF
C _{oss}	Output Capacitance ⁵	V _{DS} =30V	-	960	-	pF
C _{rss}	Reverse Transfer Capacitance ⁵	f=1.0MHz	-	90	-	pF
R _g	Gate Resistance	f=1.0MHz	-	1	2	Ω

Source-Drain Diode

Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Units
V _{SD}	Forward On Voltage ²	I _S =40A, V _{GS} =0V	-	-	1.2	V
t _{rr}	Reverse Recovery Time ⁵	I _S =40A, V _{GS} =0V,	-	47	-	ns
Q _{rr}	Reverse Recovery Charge ⁵	dI/dt=100A/μs	-	45	-	nC

Notes:

- 1.Pulse width limited by Max. junction temperature.
- 2.Pulse test
- 3.Surface mounted on 1 in² copper pad of FR4 board, t ≤10sec ; 60°C/W at steady state.
- 4.Starting T_j=25°C , V_{DD}=30V , L=0.1mH , R_G=25Ω ,V_{GS}=10V
- 5.Guaranteed by design.
- 6.Package limitation current is 100A .
- 7.These curves are based on the junction-to-case thermal impedance which is measured with the device mounted to a large heatsink, assuming a maximum junction temperature of T_{J(MAX)}=150°C.

THIS PRODUCT IS SENSITIVE TO ELECTROSTATIC DISCHARGE, PLEASE HANDLE WITH CAUTION.

USE OF THIS PRODUCT AS A CRITICAL COMPONENT IN LIFE SUPPORT, AUTOMOTIVE OR OTHER SIMILAR SYSTEMS IS NOT AUTHORIZED.

XSEMI DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

XSEMI RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN.




Fig 1. Typical Output Characteristics




Fig 2. Typical Output Characteristics







Fig 3. On-Resistance v.s. Gate Voltage



**Fig 4. Normalized On-Resistance
v.s. Junction Temperature**



**Fig 5. Forward Characteristic of
Reverse Diode**



**Fig 6. Gate Threshold Voltage v.s.
Junction Temperature**




Fig 7. Gate Charge Characteristics




Fig 8. Typical Capacitance Characteristics




Fig 9. Maximum Safe Operating Area⁷




Fig 10. Effective Transient Thermal Impedance




Fig 11. Drain Current v.s. Case Temperature




Fig 12. Transfer Characteristics




Fig 13. Normalized BV_{DSS} v.s. Junction Temperature




Fig 14. Total Power Dissipation






Fig 15. Typ. Drain-Source on State Resistance


MARKING INFORMATION

Package Outline : SPPAK 5X6




SYMBOLS	Millimeters		
	MIN	NOM	MAX
A	1.00	-	1.30
A1	0	0.075	0.15
A2	0.98	1.05	1.12
b	0.35	0.42	0.50
b2	4.02	4.23	4.41
c	0.19	0.22	0.25
c1	0.24	0.27	0.30
D	4.45	-	4.70
D1	-	-	4.45
E	4.95	-	5.30
E1	3.50	-	3.70
e	1.27 BSC		
H	5.95	-	6.25
L	0.40	-	0.85
L1	0.27	-	0.57
L2	0.80	-	1.30

- 1.All Dimensions Are in Millimeters.
- 2.Dimension Does Not Include Mold Protrusions.



SPPAK 5X6 FOOTPRINT :



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[YAGEO:](#)

[XP4NA1R5HCST](#)