

# DATA SHEET

## METAL FILM RESISTORS

High Power, Flameproof  
FMP Series

$\pm 1\%$ ,  $\pm 5\%$

1/2W to 3W

RoHS compliant & Halogen Free



**YAGEO**

Product specification – May 14, 2024 V.6





## APPLICATIONS

- All general purpose applications
- Power applications

## FEATURES

- Ultra miniature size
- Wide resistance range
- High power rating
- High stability
- PPAP ready (FMP-50)
- Flameproof coating equivalent to UL94V-0
- RoHS compliant & halogen-free

## ORDERING INFORMATION

Part number of the high power, flameproof metal film resistor are identified by the series, power rating, tolerance, packing, temperature coefficient, forming and resistance value.

## PART NUMBER

| <u>FMP</u><br>(1) | <u>200</u><br>(2) | <u>F</u><br>(3) | <u>I</u><br>(4) | <u>F</u><br>(5) | <u>52-</u><br>(6) | <u>100R</u><br>(7) |
|-------------------|-------------------|-----------------|-----------------|-----------------|-------------------|--------------------|
|-------------------|-------------------|-----------------|-----------------|-----------------|-------------------|--------------------|

### (1) SERIES

FMP Series

### (2) POWER RATING

-50 = 1/2W

100 = 1W

200 = 2W

3WS = 3W

300 = 3W

### (3) TOLERANCE

F =  $\pm 1\%$

J =  $\pm 5\%$

### (4) PACKAGING

R = Reel Pack

T = Box Pack

B = Bulk

### (5) TEMPERATURE COEFFICIENT OF RESISTANCE

E =  $\pm 50\text{ppm}/^\circ\text{C}$

F =  $\pm 100\text{ppm}/^\circ\text{C}$

- = Based on spec.

### (6) FORMING

26- = 26mm

52- = 52.4mm

73- = 73mm

52E = 52.4mm,  $\Phi d = 0.70 \pm 0.05\text{mm}$

52J = 52.4mm,  $\Phi d = 0.8 \pm 0.05\text{mm}$

52G = 52.4mm,  $\Phi d \geq 0.6\text{mm}$

M = M Type Forming

F = F Type Forming

FK = FK Type Forming

FFK = FFK Type Forming

FKK = FKK Type Forming

FT = FT Type Forming

MT = MTsert

PN = PANAsert

AV = AVIsert

Note: 26mm, 52.4mm and 73mm represent dimension A of the axial type, please refer to the category of AXIAL/REEL TAPE SPECIFICATION for the detail.

### (7) RESISTANCE VALUE


E24 & E96 Series

Example:


100R = 100 $\Omega$ , 10K = 10,000 $\Omega$ , 1M = 1,000,000 $\Omega$

DIMENSIONS

Unit: mm

|                                                                                   | Ultra Miniature | L          | ψD        | H        | ψd         |
|-----------------------------------------------------------------------------------|-----------------|------------|-----------|----------|------------|
|  | FMP-50          | 3.4 ± 0.3  | 1.9 ± 0.2 | 28 ± 2.0 | 0.45 ±0.05 |
|                                                                                   | FMP100          | 6.3 ± 0.5  | 2.4 ± 0.2 | 28 ± 2.0 | 0.55 ±0.05 |
|                                                                                   | FMP200          | 9.0 ± 0.5  | 3.9 ± 0.3 | 26 ± 2.0 | 0.55 ±0.05 |
|                                                                                   | FMP3WS          | 11.5 ± 1.0 | 4.5 ± 0.5 | 35 ± 2.0 | 0.8±0.05   |
|                                                                                   | FMP300          | 15.5± 1.0  | 5.0 ± 0.5 | 33 ± 2.0 | 0.8±0.05   |

DERATING CURVE



ELECTRICAL CHARACTERISTICS

| CHARACTERISTICS             | FMP-50                                                  | FMP100 | FMP200 | FMP3WS | FMP300 |
|-----------------------------|---------------------------------------------------------|--------|--------|--------|--------|
| Power Rating at 70 °C       | 1/2W                                                    | 1W     | 2W     | 3W     | 3W     |
| Maximum Working Voltage     | 200V                                                    | 350V   | 500V   | 500V   | 750V   |
| Maximum Overload Voltage    | 400V                                                    | 600V   | 700V   | 700V   | 1000V  |
| Voltage Proof on Insulation | 300V                                                    | 500V   | 500V   | 500V   | 500V   |
| Resistance Range            | 1Ω ~ 4M7Ω for E24 & E96 series value                    |        |        |        |        |
| Operating Temp. Range       | - 55°C to +155°C                                        |        |        |        |        |
| Temperature Coefficient     | ±100ppm/°C , ±50ppm/°C(FMP-50 & FMP100 types, R ≥ 10RΩ) |        |        |        |        |

Note: For resistance value out of above range is by request.

**TEST AND REQUIREMENTS**

| TEST                          | TEST METHOD      | PROCEDURE                                                                                | APPRAISE                                  |
|-------------------------------|------------------|------------------------------------------------------------------------------------------|-------------------------------------------|
| Short Time Overload           | IEC 60115-1 4.13 | 2.5 times RCWV for 5 sec.(Not more than maximum overload voltage)                        | $\pm 1.0\% + 0.05\Omega$                  |
| Voltage Proof on Insulation   | IEC 60115-1 4.7  | In V-Block for 60 sec. test voltage as above table                                       | No Breakdown                              |
| Temperature Coefficient       | IEC 60115-1 4.8  | Between -55°C to +155°C                                                                  | By Type                                   |
| Insulation Resistance         | IEC 60115-1 4.6  | In V-Block for 60 sec.                                                                   | >1,000M $\Omega$                          |
| Solderability                 | IEC 60115-1 4.17 | 245 $\pm$ 5°C for 3 $\pm$ 0.5 Sec.                                                       | 95% Min. coverage                         |
| Solvent Resistance of Marking | IEC 60115-1 4.30 | IPA for 5 $\pm$ 0.5 Min. with ultrasonic                                                 | No deterioration of coatings and markings |
| Robustness of Terminations    | IEC 60115-1 4.16 | Direct load for 10 Sec. in the direction of the terminal leads                           | $\geq 2.5\text{Kg}(24.5\text{N})$         |
| Periodic-pulse Overload       | IEC 60115-1 4.39 | 4 times RCWV(or Umax., whichever less) 10,000 cycles (1 Sec. on, 25 Sec.off)             | $\pm 1.0\% + 0.05\Omega$                  |
| Damp Heat Steady State        | IEC 60115-1 4.24 | 40 $\pm$ 2°C,90-95% RH for 56 days, loaded with 0.1 times RCWV(or Umax., whichever less) | $\pm 2.0\% + 0.05\Omega$                  |
| Endurance at 70°C             | IEC 60115-1 4.25 | 70 $\pm$ 2°C at RCWV(or Umax., whichever less) for 1,000 Hr.(1.5 Hr.on,0.5 Hr. off)      | $\pm 2.0\% + 0.05\Omega$                  |
| Temperature Cycling           | IEC 60115-1 4.19 | -55°C → Room Temp. → +155°C → Room Temp.(5 cycles)                                       | $\pm 1.0\% + 0.05\Omega$                  |
| Resistance to Soldering Heat  | IEC 60115-1 4.18 | 260 $\pm$ 3°C for 10 $\pm$ 1 Sec., immersed to a point 3 $\pm$ 0.5mm from the body       | $\pm 0.25\% + 0.05\Omega$                 |
| Accidental Overload Test      | IEC 60115-1 4.26 | 4 times RCWV(or Umax., whichever less) for 1 Min.                                        | No evidence of flaming or arcing          |

Note:

**RCWV (Rated Continuous Working Voltage ):**

The DC or AC (rms) continuous working voltage corresponding to the rated power is determined by the following formula:

$$V = \sqrt{P \times R}$$

or max. working voltage whichever is less


Where

V=Continuous rated DC or


AC (rms) working voltage (V)

P=Rated power (W)


R=Resistance value ( $\Omega$ )

**PULSE DIAGRAMS**

FMP100 Series:  $P_{max}$ : Maximum permissible peak pulse power  
 $t_i$ : Pulse duration  
 $t_p$ : Pulse repetition time




FMP200 Series:  $P_{max}$ : Maximum permissible peak pulse power  
 $t_i$ : Pulse duration  
 $t_p$ : Pulse repetition time



FMP300 Series:  $P_{max}$ : Maximum permissible peak pulse power  
 $t_i$ : Pulse duration  
 $t_p$ : Pulse repetition time




AXIAL / REEL TAPE SPECIFICATION



Unit: mm

| Ultra Miniature  | a       | A          | B1-B2 (Max.) | S (spacing) | T (max. deviation of spacing)               |
|------------------|---------|------------|--------------|-------------|---------------------------------------------|
| FMP-50           | 6 ± 0.5 | 52.4 ± 1.5 | 1.2          | 5           | 0.5 mm per 5 spacing<br>1 mm per 10 spacing |
|                  |         | 26.0 ± 1.5 | 1            |             |                                             |
| FMP100<br>FMP200 | 6 ± 0.5 | 52.4 ± 1.5 | 1.2          | 5           |                                             |
| FMP3WS           | 6 ± 0.5 | 73.0 ± 1.5 | 1.5          | 5           |                                             |
|                  |         | 52.4 ± 1.5 | 1.2          |             |                                             |
| FMP300           | 6 ± 0.5 | 73.0 ± 1.5 | 1.5          | 10          |                                             |

TAPE ON REEL PACKING




TYPE Unit: mm/piece

| Ultra Miniature | Across Flange(A) | B    | Quantity Per Reel |
|-----------------|------------------|------|-------------------|
| FMP-50          | 66.5             | 75.5 | 5,000             |
| FMP100          | 66.5             | 75.5 | 5,000             |
| FMP200          | 66.5             | 75.5 | 2,500             |
| FMP3WS          | 87               | 96   | 2,000             |
| FMP300          | 87               | 96   | 1,000             |



TAPE ON BOX PACKING




| TYPE            | DIMENSIONS |     |     | Unit: mm/piece   |
|-----------------|------------|-----|-----|------------------|
| Ultra Miniature | A          | B   | C   | Quantity Per Box |
| FMP-50          | 81         | 70  | 260 | 5,000            |
| FMP100          | 81         | 104 | 260 | 5,000            |
| FMP200          | 73         | 45  | 258 | 1,000            |
| FMP3WS          | 103        | 78  | 260 | 1,000            |
| FMP300          | 103        | 78  | 260 | 1,000            |

BULK PACKING

| Ultra Miniature | Piece/Per Inner Box | Bag/Per Inner Box | Piece Per Bag |
|-----------------|---------------------|-------------------|---------------|
| FMP-50          | 10,000              | 10                | 1,000         |
| FMP100          | 10,000              | 10                | 1,000         |
| FMP200          | 5,000               | 5                 | 1,000         |
| FMP3WS          | 2,000               | 4                 | 500           |
| FMP300          | 1,000               | 2                 | 500           |


FORMING

M TYPE




| TYPE            | DIMENSIONS     |               |                 |              |              | Unit: mm |
|-----------------|----------------|---------------|-----------------|--------------|--------------|----------|
| Ultra Miniature | L              | $\psi D$      | $\psi d$        | P            | H            |          |
| FMP-50          | $3.4 \pm 0.3$  | $1.9 \pm 0.2$ | $0.45 \pm 0.05$ | $6.0 \pm 1$  | $10.0 \pm 1$ |          |
| FMP100          | $6.3 \pm 0.5$  | $2.4 \pm 0.2$ | $0.55 \pm 0.05$ | $10.0 \pm 1$ | $10.0 \pm 1$ |          |
| FMP300          | $15.5 \pm 1.0$ | $5.0 \pm 0.5$ | $0.8 \pm 0.05$  | $20.0 \pm 1$ | $15.0 \pm 1$ |          |

MHA TYPE




| TYPE      | DIMENSIONS |          |           |          |          |         |          |          | Unit: mm |
|-----------|------------|----------|-----------|----------|----------|---------|----------|----------|----------|
| Miniature | L          | ψD       | ψd        | B        | H0       | H1      | P        | P0       |          |
|           | 9.0±0.5    | 3.9±0.3  | 0.55±0.05 | 17.5Max  | 19.0±1.0 | 4.0±1.0 | 30.0±1.0 | 15.0±0.3 |          |
| FMP200    | P1         | P2       | F         | W        | W0       | W1      | ψD0      |          |          |
|           | 7.5±1.0    | 3.75±0.5 | 7.5±0.5   | 18.0±0.5 | 5.0Min   | 9.0±0.5 | 4.0±0.2  |          |          |

MHB TYPE




| TYPE      | DIMENSIONS |          |          |          |         |          |           |         |         | Unit: mm |
|-----------|------------|----------|----------|----------|---------|----------|-----------|---------|---------|----------|
| Miniature | L          | ψD       | ψd       | B        | H       | H0       | H1        | H2      | H3      |          |
|           | 15.5±1.0   | 5.0±0.5  | 0.8±0.05 | 21.0Max. | 30Max.  | 18.0±1.0 | 5.5(Ref.) | 8.0±1.5 | 16Max.  |          |
| FMP300    | P          | P0       | P1       | P2       | F       | W        | W0        | W1      | ψD0     |          |
|           | 30.0±1.0   | 15.0±0.3 | 7.5±1.0  | 3.75±0.8 | 7.5±0.5 | 18.0±0.5 | 5.0Min.   | 9.0±0.5 | 4.0±0.3 |          |

MHC TYPE




| TYPE      | DIMENSIONS |          |          |          |          |          |          |          | Unit: mm |
|-----------|------------|----------|----------|----------|----------|----------|----------|----------|----------|
| Miniature | L          | ψD       | ψd       | B        | H        | HI       | P        | P0       |          |
|           | 15.5±1.0   | 5.0±0.5  | 0.8±0.05 | 21.0Max. | 19.0±1.0 | 5.25±1.0 | 30.0±1.0 | 15.0±0.3 |          |
| FMP300    | F          | W        | W0       | W1       | ψD0      |          |          |          |          |
|           | 10.0±0.5   | 18.0±0.5 | 5.0Min.  | 9.0±0.5  | 4.0±0.2  |          |          |          |          |


F TYPE




FK TYPE



FFK TYPE




FKK TYPE



| TYPE            | DIMENSIONS |         |           |     |     |        |      |         |        |       | Unit: mm |
|-----------------|------------|---------|-----------|-----|-----|--------|------|---------|--------|-------|----------|
| Ultra Miniature | L          | ψD      | ψd        | P   | h   | H Max. | hl   | HI Max. | E Max. | e     |          |
| FMP200          | 9.0±0.5    | 3.9±0.3 | 0.55±0.05 | 6±1 | -   | -      | 5± 1 | 18.5    | 3.5    | -     |          |
| FMP300          | 15.5±1     | 5.0±0.5 | 0.8±0.05  | 8±1 | 8±1 | 28     | 5± 1 | 25      | 3.5    | 3.5±1 |          |


## FT TYPE (Taping Pack)



| TYPE            | DIMENSIONS |         |         | Unit: mm |
|-----------------|------------|---------|---------|----------|
| Ultra Miniature | H1 Max.    | H2 Max. | H3 Max. |          |
| FMP100          | 10         | 18.5    | 8.5     |          |
| FMP200          | 13         | 21.5    | 8.5     |          |
| FMP3WS          | 16         | 24.5    | 8.5     |          |


## MT TYPE (Taping Pack)

Rated Watts : 0.5W




## AV TYPE (Taping Pack)

## PN TYPE (Taping Pack)




| TYPE            | DIMENSIONS |         |         | Unit: mm |
|-----------------|------------|---------|---------|----------|
| Ultra Miniature | H1 Max.    | H2 Max. | H3 Max. |          |
| FMP100          | 13         | 21.5    | 8.5     |          |
| FMP200          | 17         | 25.5    | 8.5     |          |
| FMP3WS          | 19         | 27.5    | 8.5     |          |



| TYPE            | DIMENSIONS |         |         | Unit: mm |
|-----------------|------------|---------|---------|----------|
| Ultra Miniature | H1 Max.    | H2 Max. | H3 Max. |          |
| FMP100          | 11.5       | 20      | 8.5     |          |
| FMP200          | 14.5       | 23      | 8.5     |          |
| FMP3WS          | 17.5       | 26      | 8.5     |          |

MARKING



**REVISION HISTORY**

| REVISION  | DATE         | CHANGE NOTIFICATION | DESCRIPTION                                          |
|-----------|--------------|---------------------|------------------------------------------------------|
| Version 6 | May.14, 2024 |                     | - Added 52G type                                     |
| Version 5 | Apr.2, 2024  |                     | - Added forming code description for part number     |
| Version 4 | Aug.31, 2023 |                     | - Update legal disclaimer and footer version numbers |
| Version 3 | May.25, 2023 |                     | - Updated the tape specification of FMP300           |
| Version 2 | Oct.25, 2021 |                     | - Add F type for FMP200 series                       |
| Version 1 | Oct.12, 2021 | -                   | - Updated the tape specification of FMP200           |
| Version 0 | Aug.2, 2021  | -                   | - First issue of this specification                  |

*“ Yageo reserves all the rights for revising the content of this datasheet without further notification, as long as the products itse lf are unchanged. Any product change will be announced by PCN.”*



## LEGAL DISCLAIMER

YAGEO, its distributors and agents (collectively, "YAGEO"), hereby disclaims any and all liabilities for any errors, inaccuracies or incompleteness contained in any product related information, including but not limited to product specifications, datasheets, pictures and/or graphics. YAGEO may make changes, modifications and/or improvements to product related information at any time and without notice.

YAGEO makes no representation, warranty, and/or guarantee about the fitness of its products for any particular purpose or the continuing production of any of its products. To the maximum extent permitted by law, YAGEO disclaims (i) any and all liability arising out of the application or use of any YAGEO product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for a particular purpose, non-infringement and merchantability.

YAGEO products are designed for general purpose applications under normal operation and usage conditions. Please contact YAGEO for the applications listed below which require especially high reliability for the prevention of defects which might directly cause damage to the third party's life, body or property: Aerospace equipment (artificial satellite, rocket, etc.), Atomic energy-related equipment, Aviation equipment, Disaster prevention equipment, crime prevention equipment, Electric heating apparatus, burning equipment, Highly public information network equipment, data-processing equipment, Medical devices, Military equipment, Power generation control equipment, Safety equipment, Traffic signal equipment, Transportation equipment and Undersea equipment, or for any other application or use in which the failure of YAGEO products could result in personal injury or death, or serious property damage. Particularly **YAGEO Corporation and its affiliates do not recommend the use of commercial or automotive grade products for high reliability applications or manned space flight.**

Information provided here is intended to indicate product specifications only. YAGEO reserves all the rights for revising this content without further notification, as long as products are unchanged. Any product change will be announced by PCN.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[YAGEO:](#)

[FMP100JR-52-220R](#) [FMP200FRF52-220R](#) [FMP200JR-52-1M](#) [FMP200JR-52-200K](#) [FMP200JR-52-220K](#)  
[FMP200JR-52-390R](#) [FMP200JR-52-470R](#) [FMP100JR-52-27K](#) [FMP300FRF73-100K](#) [FMP100JR-52-1K](#) [FMP100JR-52-22K](#) [FMP100JR-52-22R](#) [FMP100JR-52-270R](#) [FMP100JR-52-2K2](#) [FMP100JR-52-4K7](#) [FMP200JR-52-39K](#)  
[FMP100JR-52-100K](#) [FMP200JR-52-22R](#) [FMP200JR-52-100K](#) [FMP200JR-52-4K7](#) [FMP200JR-52-33R](#) [FMP200JR-52-10K](#) [FMP200JR-52-1K5](#) [FMP100JR-52-1M](#) [FMP100JR-52-560R](#) [FMP200JR-52-47K](#) [FMP100JR-52-10R](#)  
[FMP200JR-52-47R](#) [FMP100JR-52-1K5](#) [FMP200JR-52-18K](#) [FMP200FRF52-100R](#) [FMP100JR-52-1K2](#) [FMP100JR-52-18K](#) [FMP200JR-52-120R](#) [FMP200JR-52-22K](#) [FMP100JR-52-100R](#) [FMP100JR-52-150K](#) [FMP200JR-52-27K](#)  
[FMP200JR-52-56R](#) [FMP200JR-52-2K2](#) [FMP200JR-52-220R](#) [FMP100JR-52-680R](#) [FMP200JR-52-12R](#) [FMP100JR-52-120R](#) [FMP200JR-52-510R](#) [FMP200JR-52-82R](#) [FMP100JR-52-110R](#) [FMP100JR-52-33R](#) [FMP100JR-52-470R](#)  
[FMP100JR-52-150R](#) [FMP200JR-52-100R](#) [FMP200JR-52-1K](#) [FMP200JR-52-10R](#) [FMP200JR-52-3K3](#) [FMP200JR-52-5K6](#) [FMP200JR-52-680R](#) [FMP100JR-52-1R](#) [FMP200FRF52-10K](#) [FMP200JR-52-1R](#) [FMP300JT-73-10K](#)  
[FMP300FTF73-220K](#) [FMP300FTF73-10K](#) [FMP300JT-73-220K](#) [FMP200JR-52-3R3](#) [FMP200JR-52-1R5](#) [FMP200JR-52-8R2](#) [FMP100JR-52-0R51](#) [FMP200JR-52-0R82](#) [FMP100JT-52-1K](#) [FMP300JT-73-10R](#) [FMP300FRF73-120R](#)  
[FMP300FRF73-150K](#) [FMP200JT-52-470R](#) [FMP200JT-52-22R](#) [FMP100JR-52-0R39](#) [FMP300JT-73-12R](#) [FMP100JT-52-470R](#) [FMP300JT-73-18K](#) [FMP200JR-52-6R8](#) [FMP300FRF73-180K](#) [FMP200JT-52-120K](#) [FMP100JT-52-47R](#)  
[FMP100JT-52-2K2](#) [FMP200FTF52-330R](#) [FMP200FTF52-90K](#) [FMP300JTF73-1R2](#) [FMP200FTF52-1R](#)  
[FMP200JTF52-1R](#)