COMPLIANT



Fixed Wirewound High Power Vitreous Resistors with Terminal Collars or Bands



The RW wirewound power resistors are extremely well suited to professional applications, where high power and excellent endurance are required. They meet all requirements of NF C 93-214 specifications and five sizes cover the power range from 10 W to 80 W. Non inductive types are available, by using the special RWNI winding. For higher power or extremely severe conditions of use, see the RWST series.


NF F 16101, 10/1988 and 16102, 04/1992: Not applicable (our parts are made of metallic and refractory materials). NF C 93-214. Performances according to NF C 93-214.

RW

20 x 117

FEATURES

- 10 W to 80 W at 25 °C
- NF C 93-214
- RB 13 x 70 RB 20 x 117
- High power up to 80 W at 25 °C
- High long term stability drift < 2.5 % after 5000 h
- · Great mechanical strength
- Fire proof
- Environmental performance
- Thermal shock strength 0.5 % (100 % h at -25 °C)
- Material categorization: for definitions of compliance please see www.vishav.com/doc?99912



 21 ± 0.7

33

 21 ± 0.7

 42 ± 1.5

 28 ± 0.7

 24 ± 0.7



DIMEN	DIMENSIONS in millimeters												
SERIES	CONNECTIONS			L + 0.5	L + 0.5 + 0 M ± 1.5	N + 2	P ± 1	± 1 Q ± 0.5	D + 2	S ± 2	т	øυ	
SEMILS	COLLAR	COLLAR	COLLAR	BAND	+ 0	IVI ± 1.5	14 ± 2		Q ± 0.5		JIZ		20
RW 8 x 34	AN	-	-	-	5	1	27	-	-	-	-	-	3.2
RW 10 x 50	AN	CR	ı	В	6.35	1.5	40	19.5	19.5	72	62	12	4.2
RW 13 x 70	AN	CR	CS	В	0.6	3.5	56	22.5	20.5	91	81	15	4.2
RW 16 x 94	AN	ı	ı	В	0.6	4	78	ı	ı	-	ı	-	4.2
RW 20 x 117	AN	-	-	В	0.8	6	98	-	-	-	-	-	4.2

STANDARD ELECTRICAL SPECIFICATIONS							
MODEL	SIZE	RESISTANCE RANGE Ω	RATED POWER P _{25 °C} W	TOLERANCE ± %			
RW 8 x 34	0834	1 to 10K	10	5			
RW 10 x 50	1050	1 to 27K	17	5			
RW 13 x 70	1370	2.2 to 56K	28	5			
RW 16 x 94	1694	2.2 to 56K	44	5			
RW 20 x 117	20117	2.7 to 68K	72	5			

MECHANICAL SPECIFICATIONS						
Mechanical Protection	Enamel					
Resistive Element	Ni-Cr wire					
Connections	B band AN - CR - CS collars					
Average Unit Weight	10 g to 100 g					

ENVIRONMENTAL SPECIFICATIONS							
Temperature Range	-55 °C, +450 °C						
Climatic Category	-55 °C / +200 °C / 56 days						

TECHNICAL SPECIFICATIONS						
Resistance Range	1 Ω to 68 k Ω (E12 preferred series value)					
Power Rating	10 W to 80 W at 25 °C					
Temperature Coefficient	75 ppm/°C (typical)					
Dielectric Strength	1000 V _{RMS} (AN collars)					
Insulation Resistance	100 M Ω (500 V _{DC}) AN collars					
Shelf Life	0.1 % year (typical)					

PERFORMANCE					
TESTS	CONDITIONS	REQUIREMENTS	TYPICAL VALUES AND DRIFTS		
Short Time Overload	10 P _r during 5 s voltage limited at < 5000 V current limited at 5 A	2 % or 0.05 Ω	0.5 %		
Climatic Sequence	-55 °C, +200 °C 5 cycles	3 % or 0.05 Ω Insulation resistance > 100 M Ω	0.5 %		
Humidity (Steady State)	56 days 95 % relative humidity	2 % or 0.05 Ω Insulation resistance > 100 M Ω	0.5 %		
Thermal Shock	Load at 100 % P_r followed by cold temp. exposure at -55 °C	2 % or 0.05 Ω	0.5 %		
Shock	Severity 50, 9 shocks/each side	1 % or 0.05 Ω	0.25 %		
Vibration	Severity 55B	1 % or 0.05 Ω	0.25 %		
Terminal Strength	Collar AN traction 40 N band B torque 60 Ncm	1 % or 0.05 Ω	0.5 %		
Load Life	90' / 30' cycle	5 %	1000 h	1.5 %	
Loau Lile	1000 h at P _r 25 °C	J 70	5000 h	2.5 %	

SPECIAL FEATURES							
RW STYLE	8 x 34	10 x 50	13 x 70	16 x 94	20 x 117		
Designation NF C 93-214	-	-	RB 13 x 70	-	RB 20 x 117		
Maximum Power Rating at 25 °C	13 W	20 W	32 W	50 W	80 W		
Ohmic Range (E12, E24 series)	1 Ω to10 k Ω	1 Ω to27 kΩ	$2.2~\Omega$ to $56~\text{k}\Omega$	$2.2~\Omega$ to $56~\text{k}\Omega$	$2.7~\Omega$ to $68~\text{k}\Omega$		
Limiting Element Voltage	300 V	450 V	650 V	900 V	1100 V		
Critical Resistance	6.9 kΩ	10 kΩ	13.2 kΩ	16 kΩ	15.1 kΩ		


Revision: 04-Apr-2019 2 Document Number: 50016




NON INDUCTIVE WINDING

For high frequencies, low self induction resistors are available with special windings. RWNI designation.

MODEL	RWNI	RWNI	RWNI	RWNI	RWNI
AND STYLE	8 x 34	10 x 50	13 x 70	16 x 94	20 x 117
Ohmic Range	4.7 Ω 100 Ω	$4.7~\Omega$ 220 Ω	$4.7~\Omega$ 620 Ω	10 Ω 1.2 kΩ	10 Ω 2.2 kΩ




TEMPERATURE RISE



MARKING

Vishay Sfernice trademark, model, style, NF style (if applicable) nominal resistance (in Ω), tolerance (in %), manufacturing date.

ORDE	ORDERING INFORMATION								
RW	20 × 117	NI		AN	68 Ω	± 5 %	B020	е	
MODEL	STYLE	NON-INDUCTIVE WINDING Optional	SPECIAL DESIGN Optional	CONNECTIONS	OHMIC VALUE Custom items are subject to extra-charge and min. order. Please see price list.	TOLERANCE	PACKAGING	LEAD (Pb)-FREE	



RELATED DOCUMENTS						
APPLICATION NOTES						
Potentiometers and Trimmers	www.vishay.com/doc?51001					
Guidelines for Vishay Sfernice Resistive and Inductive Components	www.vishay.com/doc?52029					



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

<u>RW13X70D561JBA25</u> <u>RW16X94A821JB00</u> <u>RW13X70B183JB00</u> <u>RW13X70B8R2JB00</u> <u>RW13X70A821JB00</u> RW13x70D151JB00