

Chip Bead

ABGK Series ISO9001 | ISO14001 | IATF16949



- Noise
Suppression
- Shield
- Multilayer
- Ferrite
- Medium
Current


Part Numbering

A	BGK	00	160808	121	Y	00
Grade	Series Name	Control Code	Dimensions Code (mm)	Impedance (Ω)	Tolerance	Internal Code
			160808 1.6x0.8x0.8	600 60	Y ±25%	
			201209 2.0x1.25x0.9	121 120		
				102 1000		

This specification applies to Multilayer Chip ferrite Bead for Automotive Electronics based on AEC-Q200 except for Power train and Safety.


ABGK00160808 Type

■ Dimensions



unit:mm

■ Recommended Land Pattern



unit:mm

■ Electrical Characteristics












Part No.	Impedance (Ω)	Test Freq.	RDC (Ω)Max.	Rated Current (mA)Max.
ABGK00160808100Y00	10	100 MHz, 200 mV	0.03	1000
ABGK00160808300Y00	30	100 MHz, 200 mV	0.06	800
ABGK00160808600Y00	60	100 MHz, 200 mV	0.06	700
ABGK00160808800Y00	80	100 MHz, 200 mV	0.10	600
ABGK00160808121Y00	120	100 MHz, 200 mV	0.15	600
ABGK00160808201Y00	200	100 MHz, 200 mV	0.18	400
ABGK00160808221Y00	220	100 MHz, 200 mV	0.18	550
ABGK00160808301Y00	300	100 MHz, 200 mV	0.25	500
ABGK00160808471Y00	470	100 MHz, 200 mV	0.30	400
ABGK00160808601Y00	600	100 MHz, 200 mV	0.30	400
ABGK00160808102Y00	1000	100 MHz, 200 mV	0.45	300

Note: When ordering, please specify tolerance code. Tolerance: Y=±25%

1. Operating temperature range - 55°C ~ 125°C
2. Rate Current : Applied the current to coils, the temperature rise shall not be more than 30°C
3. Measure Equipment:
Z: HP4291A
RDC: HP4338B or CHEN HWA 502


ABGK00160808 Type

Characteristics Graph




ABGK00201209 Type

■ Dimensions



unit:mm

■ Recommended Land Pattern



unit:mm

■ Electrical Characteristics








Part No.	Impedance (Ω)	Test Freq.	RDC (Ω)Max.	Rated Current (mA)Max.
ABGK00201209600Y00	60	100 MHz,200 mV	0.10	900
ABGK00201209800Y00	80	100 MHz,200 mV	0.10	800
ABGK00201209121Y00	120	100 MHz,200 mV	0.15	800
ABGK00201209221Y00	220	100 MHz,200 mV	0.18	750
ABGK00201209301Y00	300	100 MHz,200 mV	0.18	700
ABGK00201209601Y00	600	100 MHz,200 mV	0.25	500
ABGK00201209102Y00	1000	100 MHz,200 mV	0.30	400

Note: When ordering, please specify tolerance code. Tolerance: Y=±25%

- Operating temperature range - 55°C ~ 125°C
- Rate Current : Applied the current to coils, the temperature rise shall not be more than 30°C
- Measure Equipment:
Z: HP4291A
RDC: HP4338B or CHEN HWA 502


ABGK00201209 Type

Characteristics Graph




■ Packaging

Tape Dimensions




Tape Material

Carrier Tape: Polycarbonate (Tape A)
Carrier Tape: Paper (Tape B)
Cover Tape: Polystyrene



Reel Dimensions



Dimensions in mm

TYPE	Tape Dimensions								Reel Dimensions				Quantity PCS / Reel
	A	B	T	W	P	F	K	Tape	A	B	C	D	
ABGK00160808	1.05	1.85	0.95	8	4	3.5	-	B	178	60	12	2	4000
ABGK00201209	1.5	2.30	0.97	8	4	3.5	-	B	178	60	12	2	4000

For More Information:

Americas - prodinfo_power_americas@yageo.com | Europe - prodinfo_power_emea@yageo.com | Asia - prodinfo_power_asia@yageo.com

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2022. Pulse Electronics, Inc. All rights reserved.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pulse:

<u>ABGK00160808100Y00</u>	<u>ABGK00160808102Y00</u>	<u>ABGK00160808121Y00</u>	<u>ABGK00160808201Y00</u>
<u>ABGK00160808221Y00</u>	<u>ABGK00160808300Y00</u>	<u>ABGK00160808301Y00</u>	<u>ABGK00160808471Y00</u>
<u>ABGK00160808600Y00</u>	<u>ABGK00160808601Y00</u>	<u>ABGK00160808800Y00</u>	<u>ABGK00201209102Y00</u>
<u>ABGK00201209121Y00</u>	<u>ABGK00201209221Y00</u>	<u>ABGK00201209301Y00</u>	<u>ABGK00201209600Y00</u>
<u>ABGK00201209601Y00</u>	<u>ABGK00201209800Y00</u>		