


# SMD Multi-layer Ferrite Chip Beads

BBFJ Series




Chilisin offers a wide range of multi-layered ferrite chip beads with various sizes, frequency characteristics, and impedance values for EMI solutions. These ferrite formulas are used to compose seven types of EMI suppression chip beads: BBSY, BBBK, BBSJ, BBGK, BBPY, BBUP, BBNQ, BBFY, BBFJ and BBHV series.

## Product Identification



## Shape and Dimensions




Dimensions in mm

| TYPE    | A        | B         | C        | D         |
|---------|----------|-----------|----------|-----------|
| ①060303 | 0.6±0.03 | 0.30±0.03 | 0.3±0.03 | 0.15±0.05 |
| ②100505 | 1.0±0.10 | 0.50±0.10 | 0.5±0.10 | 0.25±0.10 |
| ③160805 | 1.6±0.15 | 0.80±0.15 | 0.5±0.15 | 0.3±0.2   |
| ④160808 | 1.6±0.15 | 0.80±0.15 | 0.8±0.15 | 0.3±0.2   |
| ⑤201209 | 2.0±0.20 | 1.25±0.20 | 0.9±0.20 | 0.5±0.3   |
| ⑥321611 | 3.2±0.20 | 1.60±0.20 | 1.1±0.20 | 0.5±0.3   |
| ⑦453215 | 4.5±0.25 | 3.20±0.20 | 1.5±0.20 | 0.5±0.3   |

- ① : BBSY / BBSJ / BBNQ / BBPY  
② : BBSY / BBSJ / BBNQ / BBPY / BBUP / BBFY / BBFJ  
③ : BBUP ④ : BBBK / BBSJ / BBGK / BBPY / BBNQ / BBUP / BBHV  
⑤ : BBBK / BBGK / BBPY / BBUP ⑥ : BBSY / BBBK / BBPY / BBUP  
⑦ : BBPY / BBUP

## Recommended Pattern



Dimensions in mm

| TYPE    | A         | B           | C         |
|---------|-----------|-------------|-----------|
| ①060303 | 0.2 ~ 0.3 | 0.75 ~ 1.05 | 0.3       |
| ②100505 | 0.4       | 1.2 ~ 1.4   | 0.5       |
| ③160805 | 0.7 ~ 0.8 | 1.8 ~ 2.0   | 0.6 ~ 0.8 |
| ④160808 | 0.7 ~ 0.8 | 1.8 ~ 2.0   | 0.6 ~ 0.8 |
| ⑤201209 | 1.0 ~ 1.2 | 2.6 ~ 4.0   | 1.0 ~ 1.4 |
| ⑥321611 | 2.0 ~ 2.4 | 4.2 ~ 5.2   | 1.3 ~ 1.9 |
| ⑦453215 | 3.0       | 5.5 ~ 6.5   | 2.4       |

\* Don't apply narrower pattern than listed above to BBPY and BBUP  
Narrow pattern might cause excessive heat or open circuit.

## Dimension Conversion

| Code   | Dimension in mm<br>(AxBxC) | EIA  |
|--------|----------------------------|------|
| 060303 | 0.6X0.3X0.3                | 0201 |
| 100505 | 1.0X0.5X0.5                | 0402 |
| 160805 | 1.6x0.8x0.5                | 0603 |
| 160808 | 1.6x0.8x0.8                | 0603 |
| 201209 | 2.0x1.2x0.9                | 0805 |
| 321611 | 3.2x1.6x1.1                | 1206 |
| 453215 | 4.5x3.2x1.5                | 1812 |





## Electrical Characteristics

| Part Number        | Impedance<br>( $\Omega \pm 25\%$ ) | Test Frequency<br>(MHz) | Impedance<br>( $\Omega \pm 40\%$ ) | Test Frequency<br>(MHz) | RDC<br>( $\Omega$ ) Max | Rated current<br>(mA) Max |
|--------------------|------------------------------------|-------------------------|------------------------------------|-------------------------|-------------------------|---------------------------|
| BBFJ00100505601Y00 | 600                                | 100                     | 1400                               | 1000                    | 0.85                    | 300                       |
| BBFJ00100505102Y00 | 1000                               | 100                     | 2000                               | 1000                    | 1.25                    | 250                       |
| BBFJ00100505152Y00 | 1500                               | 100                     | 2400                               | 1000                    | 1.80                    | 230                       |
| BBFJ00100505182Y00 | 1800                               | 100                     | 2700                               | 1000                    | 2.20                    | 200                       |

**Note:** When ordering, please specify tolerance code. Tolerance : Y=±25%


- Operating temperature range - 55°C ~ 125°C(Including self - temperature rise)
- Rate Current : Applied the current to coils, the temperature rise shall not be more than 30°C
- Measure Equipment :  
Z : HP4291A  
RDC : HP4338B or CHEN HWA 502

**Test Instruments :** Agilent E4991A Impedance / Material Analyzer




## Packaging Specifications

## Tape Dimensions




### Tape Material



- ① : BBSY/BBSJ/BBNQ/BBPY    ③ : BBUP  
② : BBSY/BBSJ/BBNQ/BBPY/BBUP/BBFY/BBFJ  
④ : BBBK/BBSJ/BBGK/BBPY/BBNQ/BBUP/BBHV  
⑤ : BBBK/BBGK/BBPY/BBUP  
⑥ : BBSY/BBBK/BBPY/BBUP  
⑦ : BBPY/BBUP

## Reel Dimensions



### Dimensions in mm

| TYPE    | Tape Dimensions |      |      |     |     |     |      |      | Reel Dimensions |    |    |   | Quantity   |
|---------|-----------------|------|------|-----|-----|-----|------|------|-----------------|----|----|---|------------|
|         | A               | B    | T    | W   | P   | F   | K    | Tape | A               | B  | C  | D | PCS / REEL |
| ①060303 | 0.37            | 0.67 | 0.42 | 8.0 | 2.0 | 3.5 | -    | B    | 178             | 60 | 10 | 2 | 15000      |
| ②100505 | 0.62            | 1.12 | 0.60 | 8.0 | 2.0 | 3.5 | -    | B    | 178             | 60 | 12 | 2 | 10000      |
| ③160805 | 1.05            | 1.85 | 0.60 | 8.0 | 2.0 | 3.5 | -    | B    | 178             | 60 | 12 | 2 | 10000      |
| ④160808 | 1.05            | 1.85 | 0.95 | 8.0 | 4.0 | 3.5 | -    | B    | 178             | 60 | 12 | 2 | 4000       |
| ⑤201209 | 1.50            | 2.30 | 0.97 | 8.0 | 4.0 | 3.5 | -    | B    | 178             | 60 | 12 | 2 | 4000       |
| ⑥321611 | 1.88            | 3.50 | 0.22 | 8.0 | 4.0 | 3.5 | 1.27 | A    | 178             | 60 | 12 | 2 | 3000       |
| ⑦453215 | 3.66            | 4.95 | 0.24 | 12  | 8.0 | 5.5 | 1.85 | A    | 178             | 60 | 14 | 2 | 1000       |

### For More Information:

Americas - [prodinfo\\_power\\_americas@yageo.com](mailto:prodinfo_power_americas@yageo.com) | Europe - [prodinfo\\_power\\_emea@yageo.com](mailto:prodinfo_power_emea@yageo.com) | Asia - [prodinfo\\_power\\_asia@yageo.com](mailto:prodinfo_power_asia@yageo.com)

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2022, Pulse Electronics, Inc. All rights reserved.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pulse:

[BBFJ00100505102Y00](#) [BBFJ00100505601Y00](#)