**Vishay Siliconix** 

RoHS


HALOGEN

FREE



## Power MOSFET

PRODUCT SUMMARY					
V <sub>DS</sub> (V)	-60				
R <sub>DS(on)</sub> (Ω)	V <sub>GS</sub> = -10 V	0.14			
Q <sub>g</sub> max. (nC)	34				
Q <sub>gs</sub> (nC)	9.9				
Q <sub>gd</sub> (nC)	16				
Configuration	Single				



#### **FEATURES**

- Advanced process technology
- Surface mount (IRF9Z34S, SiHF9Z34S)
- 175 °C operating temperature
- Fast switching
- P-channel
- · Fully avalanche rated
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

#### Note

This datasheet provides information about parts that are RoHS-compliant and / or parts that are non-RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details.

#### DESCRIPTION

Third generation power MOSFETs from Vishay utilize advanced processing techniques to achieve extremely low on-resistance per silicon area. This benefit, combined with the fast switching speed and ruggedized device design that power MOSFETs are well known for, provides the designer with an extremely efficient and reliable device for use in a wide variety of applications.

The D<sup>2</sup>PAK is a surface mount power package capable of accommodating die sizes up to HEX-4. It provides the highest power capability and the lowest possible on-resistance in any existing surface mount package. The D<sup>2</sup>PAK is suitable for high current applications because of its low internal connection resistance and can dissipate up to 2.0 W in a typical surface mount application.

ORDERING INFORMATION							
Package	D <sup>2</sup> PAK (TO-263)	D <sup>2</sup> PAK (TO-263)	D <sup>2</sup> PAK (TO-263)				
Lead (Pb)-free and Halogen-free	SiHF9Z34S-GE3	SiHF9Z34STRL-GE3 a	SiHF9Z34STRR-GE3 <sup>a</sup>				
Lead (Pb)-free	IRF9Z34SPbF	IRF9Z34STRLPbF <sup>a</sup>	IRF9Z34STRRPbF <sup>a</sup>				
Note							

a. See device orientation.

ABSOLUTE MAXIMUM RATINGS (T <sub>C</sub> :	= 25 °C, unl	ess otherwis	se noted)			
PARAMETER	SYMBOL	LIMIT	UNIT			
Drain-Source Voltage	V <sub>DS</sub>	-60	v			
Gate-Source Voltage	V <sub>GS</sub>	± 20	v			
Continuous Drain Current	V <sub>GS</sub> at -10 V	T <sub>C</sub> = 25 °C T <sub>C</sub> = 100 °C	I	-18		
Continuous Drain Current	V <sub>GS</sub> at -10 V	T <sub>C</sub> = 100 °C	ID	-13	А	
Pulsed Drain Current <sup>a, e</sup>	I <sub>DM</sub>	-72				
Linear Derating Factor		0.59	W/°C			
Single Pulse Avalanche Energy <sup>b, e</sup>	E <sub>AS</sub>	370	mJ			
Avalanche Current <sup>a</sup>	I <sub>AR</sub>	-18	А			
Repetitive Avalanche Energy <sup>a</sup>		E <sub>AR</sub>	8.8	mJ		
Maximum Dawar Disaination	T <sub>C</sub> = 25 °C		D	88	- w	
Maximum Power Dissipation	T <sub>A</sub> = 25 °C		PD	3.7		
Peak Diode Recovery dV/dt <sup>c, e</sup>		dV/dt	-4.5	V/ns		
Operating Junction and Storage Temperature Range	е		T <sub>J</sub> , T <sub>stg</sub>	-55 to +175	°C	
Soldering Recommendations (Peak temperature) <sup>d</sup>	for 10 s			300		

#### Notes

a. Repetitive rating; pulse width limited by maximum junction temperature (see fig. 11).

b.  $V_{DD}$  = - 25 V, starting  $T_J$  = 25 °C, L = 1.3 mH,  $R_g$  = 25  $\Omega$ ,  $I_{AS}$  = - 18 A (see fig. 12). c.  $I_{SD} \le$  - 18 A, dl/dt  $\le$  170 A/µs,  $V_{DD} \le V_{DS}$ ,  $T_J \le$  175 °C. d. 1.6 mm from case.

e. Uses IRF9Z34, SiHF9Z34 data and test conditions.

S16-0754-Rev. E, 02-May-16

1



Vishay Siliconix

THERMAL RESISTANCE RATINGS							
PARAMETER	SYMBOL	TYP.	MAX.	UNIT			
Maximum Junction-to-Ambient (PCB mounted, steady-state) <sup>a</sup>	R <sub>thJA</sub>	-	40	°C/W			
Maximum Junction-to-Case (Drain)	R <sub>thJC</sub>	-	1.7				

Note

a. When mounted on 1" square PCB (FR-4 or G-10 material).

PARAMETER	AMETER SYMBOL			MIN.	TYP.	MAX.	UNIT
Static		-					
Drain-Source Breakdown Voltage	V <sub>DS</sub>	V <sub>GS</sub> =	= 0 V, I <sub>D</sub> = -250 μA	-60	-	-	V
V <sub>DS</sub> Temperature Coefficient	$\Delta V_{DS}/T_{J}$	Reference to 25 °C, $I_D$ = -1 mA °		-	-0.06	-	V/°C
Gate-Source Threshold Voltage	V <sub>GS(th)</sub>	$V_{DS} = V_{GS}, I_D = -250 \ \mu A$		-2.0	-	-4.0	V
Gate-Source Leakage	I <sub>GSS</sub>		$V_{GS} = \pm 20 V$	-	-	± 100	nA
	I <sub>DSS</sub>	V <sub>DS</sub> =	$V_{DS} = -60 \text{ V}, \text{ V}_{GS} = 0 \text{ V}$		-	-100	
Zero Gate Voltage Drain Current		V <sub>DS</sub> = -48 V	′, V <sub>GS</sub> = 0 V, T <sub>J</sub> = 150 °C	-	-	-500	μA
Drain-Source On-State Resistance	R <sub>DS(on)</sub>	$V_{GS} = -10 V$	I <sub>D</sub> = -11 A <sup>b</sup>	-	-	0.14	Ω
Forward Transconductance	g <sub>fs</sub>	V <sub>DS</sub> =	-25 V, I <sub>D</sub> = -11 A <sup>c</sup>	5.9	-	-	S
Dynamic						•	
Input Capacitance	C <sub>iss</sub>		$V_{GS} = 0 V_{V}$	-	1100	-	
Output Capacitance	C <sub>oss</sub>		$V_{DS} = -25 V,$	-	620	-	pF
Reverse Transfer Capacitance	C <sub>rss</sub>	f = 1.	0 MHz, see fig. 5 <sup>c</sup>	-	100	-	
Total Gate Charge	Qg			-	-	34	
Gate-Source Charge	Q <sub>gs</sub>	V <sub>GS</sub> = -10 V	I <sub>D</sub> = -18 A, V <sub>DS</sub> = -48 V, see fig. 6 and 13 <sup>b, c</sup>	-	-	9.9	nC
Gate-Drain Charge	Q <sub>gd</sub>		see lig. o and to	-	-	16	
Turn-On Delay Time	t <sub>d(on)</sub>				18	-	
Rise Time	t <sub>r</sub>	V <sub>DD</sub> =	-30 V, I <sub>D</sub> = -18 A,	-	120	-	-
Turn-Off Delay Time	t <sub>d(off)</sub>	$R_g = 12 \Omega$ , $R_D = 1.5 \Omega$ , see fig. 10 <sup>b, c</sup>		-	20	-	ns
Fall Time	t <sub>f</sub>			-	58	-	
Gate Input Resistance	Rg	f = 1	MHz, open drain	0.7	-	3.9	Ω
Drain-Source Body Diode Characteristic	s	<u>.</u>					
Continuous Source-Drain Diode Current	I <sub>S</sub>	MOSFET sym showing the		-	-	-18	^
Pulsed Diode Forward Current <sup>a</sup>	I <sub>SM</sub>	0	integral reverse p -n junction diode		-	-72	A
Body Diode Voltage	V <sub>SD</sub>	T <sub>J</sub> = 25 °C	, I <sub>S</sub> = -18 A, V <sub>GS</sub> = 0 V <sup>b</sup>	-	-	-6.3	V
Body Diode Reverse Recovery Time	t <sub>rr</sub>			-	100	200	ns
Body Diode Reverse Recovery Charge	Q <sub>rr</sub>	$-1_{J} = 25 \text{°C}, I_{F} =$	-18 A, dl/dt = 100 A/μs <sup>b, c</sup>	-	280	520	nC
Forward Turn-On Time	t <sub>on</sub>	Intrinsic turn-on time is negligible (turn-on is dominated by $L_S$ and $L_F$					

Notes

b. Repetitive rating; pulse width limited by maximum junction temperature (see fig. 11).

c. Pulse width  $\leq$  300 µs; duty cycle  $\leq$  2 %.

d. Uses IRF9Z34, SiHF9Z34 data and test conditions.



**Vishay Siliconix** 

## TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Fig. 1 - Typical Output Characteristics





Fig. 2 - Typical Output Characteristics








Fig. 4 - Normalized On-Resistance vs. Temperature




Fig. 5 - Typical Capacitance vs. Drain-to-Source Voltage




Fig. 6 - Typical Gate Charge vs. Gate-to-Source Voltage

S16-0754-Rev. E, 02-May-16

3

Document Number: 91093

For technical questions, contact: <u>hvm@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>






Fig. 7 - Typical Source-Drain Diode Forward Voltage





Fig. 8 - Maximum Safe Operating Area



0 25 50 75 100 125 150 175 91093\_09 T<sub>C</sub>, Case Temperature (°C)

Fig. 9 - Maximum Drain Current vs. Case Temperature




Fig. 10a - Switching Time Test Circuit




Fig. 10b - Switching Time Waveforms




Fig. 11 - Maximum Effective Transient Thermal Impedance, Junction-to-Case

S16-0754-Rev. E, 02-May-16

4 questions contact: but Document Number: 91093

For technical questions, contact: <u>hvm@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>

## IRF9Z34S, SiHF9Z34S

**Vishay Siliconix** 







Fig. 12a - Unclamped Inductive Test Circuit



Vishay Siliconix

Fig. 12b - Unclamped Inductive Waveforms




Fig. 12c - Maximum Avalanche Energy vs. Drain Current




Fig. 13 - Maximum Avalanche Energy vs. Drain Current





Fig. 13b - Gate Charge Test Circuit

5

For technical questions, contact: <u>hvm@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>



**Vishay Siliconix** 



Peak Diode Recovery dV/dt Test Circuit

Fig. 14 - For P-Channel

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data see www.vishay.com/ppg?91093.

H

A1

B

Gauge plane

L3

Detail "A" Rotated 90° CW scale 8:1

0° to 8° **Vishay Siliconix** 

Seating plane

## **TO-263AB (HIGH VOLTAGE)**

∕3 ⁄4 A

н

∕₅∖

Detail A

(Datum A)

D

 $\underline{4}$ 11

	2	-	Y 2 x b2 2 x b ⊕ 0.010 @ A(	■ ating 5 b1, b b1, b b1, b c) c) c) c) c) c) c) c) c) c)	$\begin{array}{c} c_{1} \\ c_{1} \\ c_{2} \\ c_{3} \\ c_{4} \\ c_{5} \\ c_{7} \\$	<b>a</b> - 1		Ū.	1 <u>4</u>	
	MILLIN	IETERS	INCHES				MILLIMETERS		INCHES	
DIM.	MIN.	MAX.	MIN.	MAX.		DIM.	MIN.	MAX.	MIN.	MAX.
А	4.06	4.83	0.160	0.190		D1	6.86	-	0.270	-
				0.010		-		10.07	0.000	0.420
A1	0.00	0.25	0.000	0.010		E	9.65	10.67	0.380	0.120
A1 b	0.00 0.51	0.25 0.99	0.000	0.010		E1	9.65 6.22	- 10.67	0.380	-
							6.22	- 10.67 - BSC	0.245	- BSC
b	0.51	0.99	0.020	0.039		E1	6.22	-	0.245	-
b b1	0.51 0.51	0.99 0.89	0.020 0.020	0.039 0.035		E1 e	6.22 2.54	- BSC	0.245	- ) BSC
b b1 b2	0.51 0.51 1.14	0.99 0.89 1.78	0.020 0.020 0.045	0.039 0.035 0.070		E1 e H	6.22 2.54 14.61	- BSC 15.88	0.245 0.100 0.575	- ) BSC 0.625
b b1 b2 b3	0.51 0.51 1.14 1.14	0.99 0.89 1.78 1.73	0.020 0.020 0.045 0.045	0.039 0.035 0.070 0.068		E1 e H L	6.22 2.54 14.61 1.78	- BSC 15.88 2.79	0.245 0.100 0.575 0.070	- 0 BSC 0.625 0.110
b b1 b2 b3 c	0.51 0.51 1.14 1.14 0.38	0.99 0.89 1.78 1.73 0.74	0.020 0.020 0.045 0.045 0.015	0.039 0.035 0.070 0.068 0.029		E1 e H L L1	6.22 2.54 14.61 1.78 - -	- BSC 15.88 2.79 1.65	0.245 0.100 0.575 0.070 - -	- 0 BSC 0.625 0.110 0.066
b b1 b2 b3 c c1	0.51 0.51 1.14 1.14 0.38 0.38	0.99 0.89 1.78 1.73 0.74 0.58	0.020 0.020 0.045 0.045 0.015 0.015	0.039 0.035 0.070 0.068 0.029 0.023		E1 e H L L1 L2	6.22 2.54 14.61 1.78 - -	- BSC 15.88 2.79 1.65 1.78	0.245 0.100 0.575 0.070 - -	- 0 BSC 0.625 0.110 0.066 0.070

Α

Notes

1. Dimensioning and tolerancing per ASME Y14.5M-1994.

2. Dimensions are shown in millimeters (inches).

3. Dimension D and E do not include mold flash. Mold flash shall not exceed 0.127 mm (0.005") per side. These dimensions are measured at the outmost extremes of the plastic body at datum A.

4. Thermal PAD contour optional within dimension E, L1, D1 and E1.

5. Dimension b1 and c1 apply to base metal only.

6. Datum A and B to be determined at datum plane H.

7. Outline conforms to JEDEC outline to TO-263AB.



www.vishay.com

1



## **RECOMMENDED MINIMUM PADS FOR D<sup>2</sup>PAK: 3-Lead**



Recommended Minimum Pads Dimensions in Inches/(mm)

Return to Index



Vishay

## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

IRF9Z34STRLPBF IRF9Z34SPBF IRF9Z34STRRPBF IRF9Z34S IRF9Z34STRL IRF9Z34STRR IRF9Z30PBF