

- ⊕ **Current Rating:** Over 30A_{pk}
- ⊕ **Inductance Range:** 330nH to 470nH
- ⊕ **Height:** 10.0mm Max
- ⊕ **Footprint:** 10.0mm x 7.0mm Max

Electrical Specifications @ 25°C — Operating Temperature - 40°C to +130°C⁷





Part Number	Inductance ¹ @ 0A _{DC} (nH +/- 15%)	Inductance ² @ I _{rated} (nH TYP)	I _{rated} ³ (ADC)	DCR ⁴ (mΩ nominal)	Saturation Current ⁵ (A TYP)		Heating Current ⁶ (A TYP)
					25°C	100°C	
PA5034.331HLT	330	231	40	0.4 +/- 10%	40	32	47
PA5034.471HLT	470	329	30		30	22	

NOTES:

- Inductance measured at 100kHz, 100mVrms.
- Inductance at I_{rated} is the value of the inductance at 25°C at the listed rated current.
- The rated current as listed is either the saturation current (25°C or 100°C) or the heating current depending on which value is lower.
- The nominal DCR is measured at point $\triangle 2$, as shown below on the mechanical drawing.
- The saturation current is the typical current which causes the inductance to drop by 20% at the stated ambient temperatures (25°C, 100°C). This current is determined by placing the component in the specified ambient environment and applying a short duration pulse current (to eliminate self-heating effects) to the component.
- The heating current is the DC current which causes the part temperature to increase by approximately 40°C when used in a typical application.
- In high volt*time applications, additional heating in the component can occur due to core losses in the inductor which may necessitate derating the current in order to limit the temperature rise of the component. To determine the approximate total losses (or temperature rise) for a given application, the coreloss and temperature rise curves can be used.
- Parts with the HLT suffix are sold in tape and reel packaging. Pulse complies to industry standard tape and reel specification EIA-481. The tape and reel for this product has a width (W=24mm), pitch (Po=16mm) and depth (Ko=10.5mm). Samples of these parts can be ordered by removing the HLT suffix and replacing with HL.
- The temperature of the component (ambient plus temperature rise) must be within the stated operating temperature range.


Mechanical

PA5034.XXXHLT



SUGGESTED PAD LAYOUT
TOLERANCES ±0.05 mm

Schematic




Weight: 2.74grms

Tape & Reel: 300/ Reel

Dimensions:


Unless otherwise specified,
all tolerances are ± 0.25

TAPE & REEL INFO




SURFACE MOUNTING TYPE, REEL/TAPE LIST								
TYPE	REEL SIZE (mm)			TAPE SIZE (mm)			QTY	
	W ± 0.30	A0 ± 0.1	B0 ± 0.1	K0 ± 0.1	K1 ± 0.1	P1 ± 0.1	F ± 0.1	PCS/REEL
PA5034.XXXHLT	24.0	6.9	10.2	10.5	9.65	16.0	11.5	300

PA5034.331HLT, L vs I, Curve




PA5034.471HLT, L vs I, Curve




SMT Power Inductors

Power Beads - PA5034.XXXHLT Series

PA5034.XXXHLT CoreLoss (W)



PA5034.XXXHLT Temp Rise vs Power Dissipation



Total Power Dissipation (W) = CopperLoss + CoreLoss
CopperLoss = $I_{rms}^2 * R_{dc}(mOhms) / 1000$
CoreLoss = (from table)

For More Information:

Americas - proinfo_power_america@yageo.com | Europe - proinfo_power_emea@yageo.com | Asia - proinfo_power_asia@yageo.com

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2021. Pulse Electronics, Inc. All rights reserved.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pulse:

[PA5034.331HLT](#) [PA5034.471HLT](#)