



Sample Kit Surface Mount Thermistors NTCS, TFPT, NTHS, PTS



FEATURES

- NTC and PTC thermistors
- AEC-Q200 qualified and UL certified products available
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE

The commercial-off-the-shelf thermistors are now conveniently taped in strips, individually labeled and packaged in new engineering design kits.

SPECIFICATIONS				
Engineering kit	SMD Thermistors-Sample Kit			
Thermistor series	NTCS, NTCS...SMT	NTHS	PTS	TFPT
Case size	0402, 0603, 0805	0603, 0805, 1206	0603, 0805, 1206	0603, 0805, 1206
Resistance range	2 kΩ to 680 kΩ	22 kΩ to 330 kΩ	100 Ω to 1 kΩ	100 Ω to 10 kΩ
Tolerance	± 1 %, ± 3 %, ± 5 %	± 5 %	± 0.3 K	± 1 %
B _{25/85} /TCR	3420 K to 4125 K	3715 K to 4073 K	3850 ppm/°C	4110 ppm/°C
Number of SAP materials	67	15	5	22
Thermistors per value / case size	100 pieces / 0402 50 pieces / 0603 and 0805	50 pieces / case size	25 pieces / case size	25 pieces / case size

Note

- For further information please refer to product datasheet:
NTCS0402: www.vishay.com/doc?29003; NTCS0603: www.vishay.com/doc?29056; NTCS0805: www.vishay.com/doc?29044;
NTCS...SMT: www.vishay.com/doc?29151; NTHS: www.vishay.com/doc?33008; PTS: www.vishay.com/doc?28762;
TFPT: www.vishay.com/doc?33017.

PART NUMBER AND PRODUCT DESCRIPTION																			
PART NUMBER: NTCSTFPTNTHSPTSLAB																			
<table border="1" style="width: 100%; text-align: center;"> <tr> <td>N</td><td>T</td><td>C</td><td>S</td><td>T</td><td>F</td><td>P</td><td>T</td><td>N</td><td>T</td><td>H</td><td>S</td><td>P</td><td>T</td><td>S</td><td>L</td><td>A</td><td>B</td> </tr> </table>		N	T	C	S	T	F	P	T	N	T	H	S	P	T	S	L	A	B
N	T	C	S	T	F	P	T	N	T	H	S	P	T	S	L	A	B		
<table border="1" style="margin: auto;"> <tr><td>KIT</td></tr> <tr><td>NTCSTFPTNTHSPTSLAB</td></tr> </table>		KIT	NTCSTFPTNTHSPTSLAB																
KIT																			
NTCSTFPTNTHSPTSLAB																			
PRODUCT DESCRIPTION: SMD THERMISTORS LAB e3																			
<table border="1" style="margin: auto;"> <tr><td>SMD THERMISTORS LAB</td></tr> <tr><td>KIT</td></tr> <tr><td>Laboratory kit, SMD thermistors</td></tr> </table>	SMD THERMISTORS LAB	KIT	Laboratory kit, SMD thermistors	<table border="1" style="margin: auto;"> <tr><td>e3</td></tr> <tr><td>LEAD (Pb)-FREE</td></tr> <tr><td>e3 = pure tin termination finish</td></tr> </table>	e3	LEAD (Pb)-FREE	e3 = pure tin termination finish												
SMD THERMISTORS LAB																			
KIT																			
Laboratory kit, SMD thermistors																			
e3																			
LEAD (Pb)-FREE																			
e3 = pure tin termination finish																			



ELECTRICAL DATA AND ORDERING INFORMATION

NTCS AND NTHS SERIES					
SAP MATERIAL	R₂₅-VALUE (kΩ)	TOL. ON R₂₅ (%)	B_{25/85} (K)	TOL. ON B_{25/85} (%)	CURVE
NTCS0402E3472HMT	4.7	± 3	3595	± 3	-
NTCS0402E3472JMT	4.7	± 5	3595	± 3	-
NTCS0402E3103FLT	10	± 1	3490	± 3	-
NTCS0402E3103HLT	10	± 3	3490	± 3	-
NTCS0402E3103HHT	10	± 3	3950	± 3	-
NTCS0402E3103JHT	10	± 5	3950	± 3	-
NTCS0402E3153HHT	15	± 3	3965	± 3	-
NTCS0402E3153JHT	15	± 5	3965	± 3	-
NTCS0402E3223HMT	22	± 3	3590	± 3	-
NTCS0402E3223JMT	22	± 5	3590	± 3	-
NTCS0402E3333HMT	33	± 3	3670	± 3	-
NTCS0402E3333JMT	33	± 5	3670	± 3	-
NTCS0402E3473FXT	47	± 1	4075	± 3	-
NTCS0402E3473HXT	47	± 3	4075	± 3	-
NTCS0402E3683HHT	68	± 3	3910	± 3	-
NTCS0402E3683JHT	68	± 5	3910	± 3	-
NTCS0402E3104FHT	100	± 1	3950	± 3	-
NTCS0402E3104HHT	100	± 3	3950	± 3	-
NTCS0402E3214SMT	210	± 1	3590	± 1	-
NTCS0603E3202JLT	2	± 5	3420	± 1	-
NTCS0603E3222FMT	2.2	± 1	3520	± 1	-
NTCS0603E3272FMT	2.7	± 1	3600	± 1	-
NTCS0603E3472FHT	4.7	± 1	3830	± 1	-
NTCS0603E3472HHT	4.7	± 3	3830	± 1	-
NTCS0603E3103FLT	10	± 1	3435	± 1	-
NTCS0603E3103HLT	10	± 3	3435	± 1	-
NTCS0603E3103FMT	10	± 1	3610	± 1	-
NTCS0603E3103HMT	10	± 3	3610	± 1	-
NTCS0603E3103FHT	10	± 1	3960	± 1	-
NTCS0603E3103HHT	10	± 3	3960	± 1	-
NTCS0603E3153FMT	15	± 1	3600	± 1	-
NTCS0603E3153HMT	15	± 3	3600	± 1	-
NTCS0603E3223FMT	22	± 1	3730	± 1	-
NTCS0603E3223HMT	22	± 3	3730	± 1	-
NTCS0603E3333FHT	33	± 1	3860	± 1	-
NTCS0603E3333HHT	33	± 3	3860	± 1	-
NTCS0603E3473FHT	47	± 1	3960	± 1	-
NTCS0603E3473HHT	47	± 3	3960	± 1	-
NTCS0603E3683FHT	68	± 1	3985	± 1	-
NTCS0603E3683HHT	68	± 3	3985	± 1	-
NTCS0603E3104FXT	100	± 1	4100	± 1	-
NTCS0603E3104HXT	100	± 3	4100	± 1	-
NTCS0603E3124SMT	122	± 1	3590	± 1	-
NTCS0805E3222FMT	2.2	± 1	3600	± 1	-
NTCS0805E3472FMT	4.7	± 1	3500	± 1	-
NTCS0805E3103FLT	10	± 1	3430	± 3	-
NTCS0805E3103HLT	10	± 3	3430	± 3	-
NTCS0805E3103FMT	10	± 1	3570	± 3	-
NTCS0805E3103HMT	10	± 3	3570	± 3	-
NTCS0805E3103FHT	10	± 1	3940	± 1	-
NTCS0805E3103HHT	10	± 3	3940	± 1	-
NTCS0805E3153FMT	15	± 1	3700	± 1	-
NTCS0805E3223FHT	22	± 1	3800	± 1	-
NTCS0805E3333FHT	33	± 1	3920	± 1	-
NTCS0805E3473FHT	47	± 1	3960	± 1	-
NTCS0805E3683FXT	68	± 1	4100	± 1	-
NTCS0805E3683HXT	68	± 3	4100	± 1	-



ELECTRICAL DATA AND ORDERING INFORMATION

Table with 6 columns: SAP MATERIAL, R25-VALUE (kΩ), TOL. ON R25 (%), B25/85 (K), TOL. ON B25/85 (%), CURVE. Rows include NTCS and NTHS series.

ELECTRICAL DATA AND ORDERING INFORMATION

Table with 7 columns: SAP MATERIAL, R0-VALUE (Ω), TOL. ON R0 (%), R25-VALUE (Ω), TOL. ON R25 (%), TCR (ppm/°C), TOL. ON TCR (ppm/°C)/TOL. CLASS. Rows include PTS and TFPT series.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

[NTCSTFPTNTHSPTSLAB](#)