

Directional DAS Series

2xMiMo 4G/5G Antenna + 1350-1550MHz

PD698-3800M2NF



Features & Applications:

- 4G / 5G-FR1 698-3800MHz
- Including 1350-1550MHz band
- 2-Port MiMo
- In-building wall mount
- Directional radiation pattern
- Low PIM and SAR compliant
- Connector N-Female as standard
- For 4.3-10 Female version use P/N: PD698-3800M243

ELECTRICAL SPECIFICATIONS

PD698-3800M2NF						
Frequency range	MHz		698-960	1350-1550	1710-2700	3300-3800
Gain	dBi		6.0±1	8.0±1	9.0±1	9.0±1
Polarization			±90deg V+H			
Beam width	Horizontal	deg	90	75	70	70
	Vertical		75	60	55	55
VSWR			≤2.0	≤1.7	≤1.7	≤1.7
Front-to-back ratio	dB		>15	>15	>15	>15
PIM,3rd order,2x20W	dBc		≤-150			N/A
Max. input power	W		50			
Impedance	Ohm		50			
SAR compliance			Compliant based on whole-body SAR limit RF Exposure calculation (CEI EN 50383)			

MECHANICAL SPECIFICATIONS

PD698-3800M2NF						
Dimension (W x L x H)		Housing Material	Color	Weight with mounting kit	Mounting Kit	
315 x 195 x 74 mm (12.40 x 7.68 x 2.91 inch)		ABS, UV Protected	White RAL9003	0.8 kg (1.76 lbs)	Wall mount (standard)	
Wireless Technology	No. of Port	Cable Length	Cable Type		Connector Type	
4G,5G FR1	2	1Ft (0.3m)	Ø 0.160" low loss SFF-50-3		NF	


ENVIRONMENTAL SPECIFICATIONS

PD698-3800M2NF				
Operating Temperature	Storage Temperature	RoHS Compliant	Ingress Protection	Warranty
-40 / +60° C	-40 / +60° C	Yes	IP50	2 years


Radiation Pattern –Vertical and Horizontal Plane

PD698-3800M2NF


Vertical



698-960MHz




1350-1550MHz




1710-3800MHz


Horizontal



698-960MHz




1350-1550MHz



1710-3800MHz


Mechanical Drawing

PD698-3800M2NF



Test Setup

General / Chamber Setup



Directional DAS Series

2xMiMo 4G/5G Antenna + 1350-1550MHz

PD698-3800M2NF


PACKAGING

PD698-3800M2NF

1. Inner box: 360*220*85mm;
2. Outer box size: 480*460*375mm;
3. 10Pcs/Carton;

Installation instructions

PD698-3800M2NF



Notes:

1. Please contact sales for availability, lead time, and/or any special requests. Samples available upon request.

For More Information:

Americas - antennas.us@pulseelectronics.com | Europe - antennas.eu@pulseelectronics.com | Asia - antennas.as@pulseelectronics.com | Questions? +1-800-ANTENNA
Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright , 2020. Pulse Electronics, Inc. All rights reserved.
Company address: Pulse Electronics, a YAGEO Company, 15255 Innovation Drive, Suite #100, San Diego, CA 92128.

'YAGEO Corporation and its affiliates do not recommend the use of commercial, automotive, and/or COTS grade products for high reliability applications or manned space flight.'

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pulse:

[PD698-3800M2NF](#)