

# vPolyTan™ Polymer Surface-Mount Chip Capacitors, Molded Case, High Performance Type



**RoHS**  
COMPLIANT  
HALOGEN  
**FREE**  
**GREEN**  
(5-2008)

## FEATURES

- Ultra low ESR
- 100 % surge current tested
- Accelerated voltage conditioning
- High ripple current capability
- Stable capacitance over operating temperature, voltage, and frequency range
- No wear out effect
- Molded case available in 9 case codes
- Terminations:  
cases C, J, P: 100 % tin  
case A, T, B, Z, V, D: Ni / Pd / Au
- Compatible with “high volume” automatic pick and place equipment
- Moisture sensitivity level 3
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)

## LINKS TO ADDITIONAL RESOURCES



3D Models

**SPICE**

Models



Calculators

## PERFORMANCE / ELECTRICAL CHARACTERISTICS

**Operating Temperature:** -55 °C to +105 °C / 125 °C

**Capacitance Range:** 3.3 µF to 1000 µF

**Capacitance Tolerance:** ± 20 %

**Voltage Rating:** 2.5 V<sub>DC</sub> to 63 V<sub>DC</sub>






## APPLICATIONS

- Decoupling, smoothing, filtering
- Bulk energy storage in wireless cards
- Infrastructure equipment
- Storage and networking
- Computer motherboards
- Smartphones and tablets

## ORDERING INFORMATION


| T55  | A                                | 156                                                                                                                            | M                     | 6R3                                                                                                                                                                    | C                                              | 0500                      |
|------|----------------------------------|--------------------------------------------------------------------------------------------------------------------------------|-----------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------|---------------------------|
| TYPE | CASE CODE                        | CAPACITANCE                                                                                                                    | CAPACITANCE TOLERANCE | DC VOLTAGE RATING                                                                                                                                                      | TERMINATION / PACKAGING                        | ESR                       |
|      | See Ratings and Case Codes table | This is expressed in picofarads. The first two digits are the significant figures. The third is the number of zeros to follow. | M = ± 20 %            | 2R5 = 2.5 V<br>004 = 4 V<br>6R3 = 6.3 V<br>007 = 7 V<br>010 = 10 V<br>12R = 12.5 V<br>016 = 16 V<br>020 = 20 V<br>025 = 25 V<br>035 = 35 V<br>050 = 50 V<br>063 = 63 V | C = lead (Pb)-free solderable coating, 7" reel | Maximum 100 kHz ESR in mΩ |

**DIMENSIONS** in inches [millimeters]


| <div> <div> <b>J case</b>  </div> <div> <b>P case</b>  </div> </div>       |          |                              |                               |                              |                               |                              |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------|------------------------------|-------------------------------|------------------------------|-------------------------------|------------------------------|
| <div> <div> <b>A, B case</b>  </div> <div> <b>C, T case</b>  </div> </div> |          |                              |                               |                              |                               |                              |
| <div> <b>D, V, Z case</b>  </div>                                                                                                                         |          |                              |                               |                              |                               |                              |
| CASE CODE                                                                                                                                                                                                                                     | EIA SIZE | L                            | W                             | H                            | l                             | a                            |
| J                                                                                                                                                                                                                                             | 1608-09  | 0.063 ± 0.004<br>[1.6 ± 0.1] | 0.031 ± 0.004<br>[0.8 ± 0.1]  | 0.031 ± 0.004<br>[0.8 ± 0.1] | 0.012 ± 0.006<br>[0.3 ± 0.15] | 0.024 ± 0.004<br>[0.6 ± 0.1] |
| P                                                                                                                                                                                                                                             | 2012-12  | 0.080 ± 0.008<br>[2.0 ± 0.2] | 0.049 ± 0.008<br>[1.25 ± 0.2] | 0.047 max.<br>[1.2 max.]     | 0.020 ± 0.008<br>[0.5 ± 0.2]  | 0.035 ± 0.004<br>[0.9 ± 0.1] |
| A                                                                                                                                                                                                                                             | 3216-18  | 0.126 ± 0.008<br>[3.2 ± 0.2] | 0.063 ± 0.008<br>[1.6 ± 0.2]  | 0.063 ± 0.008<br>[1.6 ± 0.2] | 0.028 ± 0.012<br>[0.7 ± 0.3]  | 0.047 ± 0.008<br>[1.2 ± 0.2] |
| T                                                                                                                                                                                                                                             | 3528-12  | 0.138 ± 0.008<br>[3.5 ± 0.2] | 0.110 ± 0.008<br>[2.8 ± 0.2]  | 0.047 max.<br>[1.2 max.]     | 0.030 ± 0.012<br>[0.8 ± 0.3]  | 0.087 ± 0.008<br>[2.2 ± 0.2] |
| B                                                                                                                                                                                                                                             | 3528-21  | 0.138 ± 0.008<br>[3.5 ± 0.2] | 0.110 ± 0.008<br>[2.8 ± 0.2]  | 0.075 ± 0.008<br>[1.9 ± 0.2] | 0.030 ± 0.012<br>[0.8 ± 0.3]  | 0.087 ± 0.008<br>[2.2 ± 0.2] |
| C                                                                                                                                                                                                                                             | 6032-28  | 0.228 ± 0.008<br>[5.8 ± 0.2] | 0.126 ± 0.008<br>[3.2 ± 0.2]  | 0.100 ± 0.008<br>[2.5 ± 0.2] | 0.051 ± 0.012<br>[1.3 ± 0.3]  | 0.087 ± 0.008<br>[2.2 ± 0.2] |
| Z                                                                                                                                                                                                                                             | 7343-19  | 0.287 ± 0.008<br>[7.3 ± 0.2] | 0.169 ± 0.012<br>[4.3 ± 0.3]  | 0.071 ± 0.004<br>[1.8 ± 0.1] | 0.051 ± 0.012<br>[1.3 ± 0.3]  | 0.094 ± 0.008<br>[2.4 ± 0.2] |
| V                                                                                                                                                                                                                                             | 7343-20  | 0.287 ± 0.008<br>[7.3 ± 0.2] | 0.169 ± 0.012<br>[4.3 ± 0.3]  | 0.075 ± 0.004<br>[1.9 ± 0.1] | 0.051 ± 0.012<br>[1.3 ± 0.3]  | 0.094 ± 0.008<br>[2.4 ± 0.2] |
| D                                                                                                                                                                                                                                             | 7343-31  | 0.287 ± 0.008<br>[7.3 ± 0.2] | 0.169 ± 0.012<br>[4.3 ± 0.3]  | 0.110 ± 0.012<br>[2.8 ± 0.3] | 0.051 ± 0.012<br>[1.3 ± 0.3]  | 0.094 ± 0.008<br>[2.4 ± 0.2] |

**RATINGS AND CASE CODES**

| μF   | 2.5 V         | 4.0 V         | 6.3 V                 | 7.0 V | 10 V      | 12.5 V | 16 V      | 20 V  | 25 V      | 35 V      | 50 V | 63 V  |
|------|---------------|---------------|-----------------------|-------|-----------|--------|-----------|-------|-----------|-----------|------|-------|
| 1.0  |               |               |                       |       |           |        |           |       |           |           |      | B     |
| 2.2  |               |               |                       |       |           |        |           |       |           | B         | B    |       |
| 3.3  |               |               | J / P                 |       | J / P     |        |           |       |           |           |      |       |
| 4.7  |               |               | J / P / A             |       | P / A     |        |           |       |           | B         |      | C / D |
| 6.8  |               |               | P / A                 |       | A         |        | B         |       | B         | B         |      |       |
| 10   |               | J / P / A     | P / A                 |       | A         |        | B         |       | B         | B / D     | D    | D     |
| 15   |               | P / A         | A                     |       | A         | T      | B         | B / V | B / V     | V         | D    |       |
| 22   | A             | A / B         | A / T / B             |       | A / T / B |        | B         | V     | V         | Z / V / D |      |       |
| 33   | A             | A / B         | A / T / B             |       | A / T / B |        | B / V / D | V     | Z / V / D | D         |      |       |
| 47   | A             | A / T / B     | A / T / B             |       | B         |        | Z / V / D | Z / V | D         | D         |      |       |
| 68   | A / B         | A / T / B     | T / B                 |       | V         |        | V         |       | D         |           |      |       |
| 100  | A / T / B     | A / T / B     | A / T / B / Z / V / D | A     | Z / V / D |        | Z / V / D | D     | D         |           |      |       |
| 150  | B             | B / Z / V     | B / Z / V / D         |       | Z / V / D |        | D         |       |           |           |      |       |
| 220  | B / V         | B / Z / V / D | B / Z / V / D         |       | Z / V / D |        |           |       |           |           |      |       |
| 330  | B / Z / V / D | Z / V / D     | V / D                 |       | D         |        |           |       |           |           |      |       |
| 470  | B / Z / V / D | Z / D         | V / D                 | D     |           |        |           |       |           |           |      |       |
| 680  | D             | D             | D                     |       |           |        |           |       |           |           |      |       |
| 1000 | D             |               |                       |       |           |        |           |       |           |           |      |       |

**MARKING**


| VOLTAGE CODE |      | CAPACITANCE CODE |      |
|--------------|------|------------------|------|
| V            | CODE | CAP, μF          | CODE |
| 2.5          | e    | 1.0              | A6   |
| 4            | G    | 1.5              | E6   |
| 6.3 (7)      | J    | 2.2              | J6   |
| 10           | A    | 3.3              | N6   |
| 12.5         | B    | 4.7              | S6   |
| 16           | C    | 6.8              | W6   |
| 20           | D    | 10               | A7   |
| 25           | E    | 15               | E7   |
| 35           | V    | 22               | J7   |
| 50           | H    | 33               | N7   |
| 63           | J    | 47               | S7   |
|              |      | 68               | W7   |
|              |      | 100              | A8   |
|              |      | 150              | E8   |
|              |      | 220              | J8   |
|              |      | 330              | N8   |
|              |      | 470              | S8   |
|              |      | 680              | W8   |
|              |      | 1000             | A9   |

**MARKING**


| RATED VOLTAGE | CAPACITANCE | MARKING |
|---------------|-------------|---------|
| 4             | 10          | AG      |
| 4             | 15          | EG      |
| 6.3           | 3.3         | NJ      |
| 6.3           | 4.7         | SJ      |
| 6.3           | 6.8         | WJ      |
| 6.3           | 10          | AJ      |
| 10            | 3.3         | NA      |
| 10            | 4.7         | SA      |

**DATE CODE**

| YEAR | MONTH |   |   |   |   |   |   |   |   |    |    |    |
|------|-------|---|---|---|---|---|---|---|---|----|----|----|
|      | 1     | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 |
| 2017 | A     | B | C | D | E | F | G | H | J | K  | L  | M  |
| 2018 | N     | P | Q | R | S | T | U | V | W | X  | Y  | Z  |
| 2019 | a     | b | c | d | e | f | g | h | j | k  | l  | m  |
| 2020 | n     | p | q | r | s | t | u | v | w | x  | y  | z  |
| 2021 | A     | B | C | D | E | F | G | H | J | K  | L  | M  |
| 2022 | N     | P | Q | R | S | T | U | V | W | X  | Y  | Z  |
| 2023 | a     | b | c | d | e | f | g | h | j | k  | l  | m  |
| 2024 | n     | p | q | r | s | t | u | v | w | x  | y  | z  |

**Note**

- Marking code repeats every four years in alphabetical order (letter of l, i, O, and o are excluded)



## STANDARD RATINGS

| CAPACITANCE<br>( $\mu$ F)                                      | CASE<br>CODE | PART NUMBER      | MAX. DCL<br>AT 25 °C<br>( $\mu$ A) | MAX. DF<br>AT 25 °C<br>120 Hz<br>(%) | MAX. ESR<br>AT + 25 °C<br>100 kHz<br>(m $\Omega$ ) | MAX. RIPPLE<br>AT 45 °C<br>100 kHz I <sub>RMS</sub><br>(A) | HIGH<br>TEMPERATURE<br>LOAD, TIME<br>(h) | MAX.<br>OPERATING<br>TEMPERATURE<br>(°C) |
|----------------------------------------------------------------|--------------|------------------|------------------------------------|--------------------------------------|----------------------------------------------------|------------------------------------------------------------|------------------------------------------|------------------------------------------|
| 2.5 V <sub>DC</sub> AT +105 °C, 1.7 V <sub>DC</sub> AT +125 °C |              |                  |                                    |                                      |                                                    |                                                            |                                          |                                          |
| 22                                                             | A            | T55A226M2R5C0200 | 5.5                                | 10                                   | 200                                                | 0.75                                                       | 1000                                     | 105                                      |
| 22                                                             | A            | T55A226M2R5C0180 | 5.5                                | 10                                   | 180                                                | 0.79                                                       | 1000                                     | 105                                      |
| 33                                                             | A            | T55A336M2R5C0200 | 8.2                                | 10                                   | 200                                                | 0.75                                                       | 1000                                     | 105                                      |
| 33                                                             | A            | T55A336M2R5C0180 | 8.2                                | 10                                   | 180                                                | 0.79                                                       | 1000                                     | 105                                      |
| 47                                                             | A            | T55A476M2R5C0200 | 11.7                               | 10                                   | 200                                                | 0.75                                                       | 1000                                     | 105                                      |
| 47                                                             | A            | T55A476M2R5C0180 | 11.7                               | 10                                   | 180                                                | 0.79                                                       | 1000                                     | 105                                      |
| 68                                                             | A            | T55A686M2R5C0250 | 17.0                               | 10                                   | 250                                                | 0.67                                                       | 1000                                     | 105                                      |
| 68                                                             | A            | T55A686M2R5C0200 | 17.0                               | 10                                   | 200                                                | 0.75                                                       | 1000                                     | 105                                      |
| 68                                                             | B            | T55B686M2R5C0070 | 17.0                               | 8                                    | 70                                                 | 1.36                                                       | 2000                                     | 125                                      |
| 100                                                            | A            | T55A107M2R5C0200 | 25.0                               | 10                                   | 200                                                | 0.75                                                       | 1000                                     | 105                                      |
| 100                                                            | A            | T55A107M2R5C0100 | 25.0                               | 10                                   | 100                                                | 1.07                                                       | 1000                                     | 105                                      |
| 100                                                            | T            | T55T107M2R5C0070 | 25.0                               | 10                                   | 70                                                 | 1.22                                                       | 1000                                     | 105                                      |
| 100                                                            | B            | T55B107M2R5C0070 | 25.0                               | 8                                    | 70                                                 | 1.36                                                       | 2000                                     | 125                                      |
| 100                                                            | B            | T55B107M2R5C0055 | 25.0                               | 8                                    | 55                                                 | 1.53                                                       | 2000                                     | 125                                      |
| 150                                                            | B            | T55B157M2R5C0070 | 37.5                               | 8                                    | 70                                                 | 1.36                                                       | 2000                                     | 105                                      |
| 150                                                            | B            | T55B157M2R5C0055 | 37.5                               | 8                                    | 55                                                 | 1.53                                                       | 2000                                     | 105                                      |
| 220                                                            | B            | T55B227M2R5C0070 | 55.0                               | 8                                    | 70                                                 | 1.36                                                       | 2000                                     | 105                                      |
| 220                                                            | B            | T55B227M2R5C0055 | 55.0                               | 8                                    | 55                                                 | 1.53                                                       | 2000                                     | 105                                      |
| 220                                                            | B            | T55B227M2R5C0045 | 55.0                               | 8                                    | 45                                                 | 1.69                                                       | 2000                                     | 105                                      |
| 220                                                            | B            | T55B227M2R5C0035 | 55.0                               | 8                                    | 35                                                 | 1.93                                                       | 2000                                     | 105                                      |
| 220                                                            | B            | T55B227M2R5C0030 | 55.0                               | 8                                    | 30                                                 | 2.08                                                       | 2000                                     | 105                                      |
| 220                                                            | B            | T55B227M2R5C0025 | 55.0                               | 8                                    | 25                                                 | 2.28                                                       | 2000                                     | 105                                      |
| 220                                                            | V            | T55V227M2R5C0025 | 55.0                               | 10                                   | 25                                                 | 2.73                                                       | 2000                                     | 125                                      |
| 220                                                            | V            | T55V227M2R5C0018 | 55.0                               | 10                                   | 18                                                 | 3.22                                                       | 2000                                     | 125                                      |
| 220                                                            | V            | T55V227M2R5C0015 | 55.0                               | 10                                   | 15                                                 | 3.53                                                       | 2000                                     | 125                                      |
| 330                                                            | B            | T55B337M2R5C0070 | 82.5                               | 8                                    | 70                                                 | 1.36                                                       | 2000                                     | 105                                      |
| 330                                                            | B            | T55B337M2R5C0045 | 82.5                               | 8                                    | 45                                                 | 1.70                                                       | 2000                                     | 105                                      |
| 330                                                            | B            | T55B337M2R5C0035 | 82.5                               | 8                                    | 35                                                 | 1.93                                                       | 2000                                     | 105                                      |
| 330                                                            | B            | T55B337M2R5C0025 | 82.5                               | 8                                    | 25                                                 | 2.28                                                       | 2000                                     | 105                                      |
| 330                                                            | Z            | T55Z337M2R5C0025 | 82.5                               | 10                                   | 25                                                 | 2.73                                                       | 2000                                     | 105                                      |
| 330                                                            | Z            | T55Z337M2R5C0018 | 82.5                               | 10                                   | 18                                                 | 3.22                                                       | 2000                                     | 105                                      |
| 330                                                            | V            | T55V337M2R5C0040 | 82.5                               | 10                                   | 40                                                 | 2.16                                                       | 2000                                     | 125                                      |
| 330                                                            | V            | T55V337M2R5C0025 | 82.5                               | 10                                   | 25                                                 | 2.73                                                       | 2000                                     | 125                                      |
| 330                                                            | V            | T55V337M2R5C0018 | 82.5                               | 10                                   | 18                                                 | 3.22                                                       | 2000                                     | 125                                      |
| 330                                                            | V            | T55V337M2R5C0015 | 82.5                               | 10                                   | 15                                                 | 3.53                                                       | 2000                                     | 125                                      |
| 330                                                            | D            | T55D337M2R5C0009 | 82.5                               | 10                                   | 9                                                  | 5.00                                                       | 2000                                     | 125                                      |
| 330                                                            | D            | T55D337M2R5C0008 | 82.5                               | 10                                   | 8                                                  | 5.30                                                       | 2000                                     | 125                                      |
| 330                                                            | D            | T55D337M2R5C0007 | 82.5                               | 10                                   | 7                                                  | 5.66                                                       | 2000                                     | 125                                      |
| 470                                                            | B            | T55B477M2R5C0025 | 117.5                              | 8                                    | 25                                                 | 2.28                                                       | 2000                                     | 105                                      |
| 470                                                            | Z            | T55Z477M2R5C0025 | 117.5                              | 10                                   | 25                                                 | 2.73                                                       | 2000                                     | 105                                      |
| 470                                                            | V            | T55V477M2R5C0025 | 117.5                              | 10                                   | 25                                                 | 2.73                                                       | 2000                                     | 105                                      |
| 470                                                            | V            | T55V477M2R5C0012 | 117.5                              | 10                                   | 12                                                 | 3.94                                                       | 2000                                     | 105                                      |
| 470                                                            | D            | T55D477M2R5C0050 | 117.5                              | 10                                   | 50                                                 | 2.12                                                       | 2000                                     | 125                                      |
| 470                                                            | D            | T55D477M2R5C0040 | 117.5                              | 10                                   | 40                                                 | 2.37                                                       | 2000                                     | 125                                      |
| 470                                                            | D            | T55D477M2R5C0025 | 117.5                              | 10                                   | 25                                                 | 3.00                                                       | 2000                                     | 125                                      |
| 470                                                            | D            | T55D477M2R5C0015 | 117.5                              | 10                                   | 15                                                 | 3.87                                                       | 2000                                     | 125                                      |
| 470                                                            | D            | T55D477M2R5C0012 | 117.5                              | 10                                   | 12                                                 | 4.33                                                       | 2000                                     | 125                                      |
| 470                                                            | D            | T55D477M2R5C0009 | 117.5                              | 10                                   | 9                                                  | 5.00                                                       | 2000                                     | 125                                      |
| 470                                                            | D            | T55D477M2R5C0008 | 117.5                              | 10                                   | 8                                                  | 5.30                                                       | 2000                                     | 125                                      |
| 470                                                            | D            | T55D477M2R5C0007 | 117.5                              | 10                                   | 7                                                  | 5.66                                                       | 2000                                     | 125                                      |
| 680                                                            | D            | T55D687M2R5C0009 | 170.0                              | 10                                   | 9                                                  | 5.00                                                       | 2000                                     | 125                                      |
| 680                                                            | D            | T55D687M2R5C0008 | 170.0                              | 10                                   | 8                                                  | 5.30                                                       | 2000                                     | 125                                      |
| 680                                                            | D            | T55D687M2R5C0007 | 170.0                              | 10                                   | 7                                                  | 5.66                                                       | 2000                                     | 125                                      |
| 1000                                                           | D            | T55D108M2R5C0009 | 250.0                              | 10                                   | 9                                                  | 5.00                                                       | 2000                                     | 105                                      |
| 1000                                                           | D            | T55D108M2R5C0008 | 250.0                              | 10                                   | 8                                                  | 5.30                                                       | 2000                                     | 105                                      |
| 1000                                                           | D            | T55D108M2R5C0007 | 250.0                              | 10                                   | 7                                                  | 5.67                                                       | 2000                                     | 105                                      |
| 1000                                                           | D            | T55D108M2R5C0006 | 250.0                              | 10                                   | 6                                                  | 6.12                                                       | 1000                                     | 105                                      |

## Note

- Termination code "C": cases C, J, P: 100 % tin, case A, T, B, Z, V, D: Ni / Pd / Au



## STANDARD RATINGS

| CAPACITANCE<br>( $\mu$ F)                                    | CASE<br>CODE | PART NUMBER      | MAX. DCL<br>AT 25 °C<br>( $\mu$ A) | MAX. DF<br>AT 25 °C<br>120 Hz<br>(%) | MAX. ESR<br>AT + 25 °C<br>100 kHz<br>(m $\Omega$ ) | MAX. RIPPLE<br>AT 45 °C<br>100 kHz I <sub>RMS</sub><br>(A) | HIGH<br>TEMPERATURE<br>LOAD, TIME<br>(h) | MAX.<br>OPERATING<br>TEMPERATURE<br>(°C) |
|--------------------------------------------------------------|--------------|------------------|------------------------------------|--------------------------------------|----------------------------------------------------|------------------------------------------------------------|------------------------------------------|------------------------------------------|
| 4 V <sub>DC</sub> AT +105 °C, 2.7 V <sub>DC</sub> AT +125 °C |              |                  |                                    |                                      |                                                    |                                                            |                                          |                                          |
| 10                                                           | J            | T55J106M004C0500 | 10.0                               | 10                                   | 500                                                | 0.32                                                       | 1000                                     | 105                                      |
| 10                                                           | P            | T55P106M004C0500 | 5.0                                | 10                                   | 500                                                | 0.36                                                       | 1000                                     | 105                                      |
| 10                                                           | P            | T55P106M004C0300 | 5.0                                | 10                                   | 300                                                | 0.46                                                       | 1000                                     | 105                                      |
| 10                                                           | P            | T55P106M004C0200 | 5.0                                | 10                                   | 200                                                | 0.56                                                       | 1000                                     | 105                                      |
| 10                                                           | A            | T55A106M004C0500 | 4.0                                | 10                                   | 500                                                | 0.48                                                       | 1000                                     | 105                                      |
| 10                                                           | A            | T55A106M004C0200 | 4.0                                | 10                                   | 200                                                | 0.76                                                       | 1000                                     | 105                                      |
| 15                                                           | P            | T55P156M004C0500 | 10.0                               | 10                                   | 500                                                | 0.36                                                       | 1000                                     | 105                                      |
| 15                                                           | P            | T55P156M004C0200 | 10.0                               | 10                                   | 200                                                | 0.56                                                       | 1000                                     | 105                                      |
| 15                                                           | A            | T55A156M004C0500 | 6.0                                | 10                                   | 500                                                | 0.48                                                       | 1000                                     | 105                                      |
| 15                                                           | A            | T55A156M004C0300 | 6.0                                | 10                                   | 300                                                | 0.61                                                       | 1000                                     | 105                                      |
| 15                                                           | A            | T55A156M004C0200 | 6.0                                | 10                                   | 200                                                | 0.76                                                       | 1000                                     | 105                                      |
| 22                                                           | A            | T55A226M004C0500 | 8.8                                | 10                                   | 500                                                | 0.48                                                       | 1000                                     | 105                                      |
| 22                                                           | A            | T55A226M004C0300 | 8.8                                | 10                                   | 300                                                | 0.61                                                       | 1000                                     | 105                                      |
| 22                                                           | A            | T55A226M004C0200 | 8.8                                | 10                                   | 200                                                | 0.76                                                       | 1000                                     | 105                                      |
| 22                                                           | B            | T55B226M004C0200 | 8.8                                | 8                                    | 200                                                | 0.81                                                       | 2000                                     | 125                                      |
| 22                                                           | B            | T55B226M004C0150 | 8.8                                | 8                                    | 150                                                | 0.93                                                       | 2000                                     | 125                                      |
| 33                                                           | A            | T55A336M004C0500 | 13.2                               | 10                                   | 500                                                | 0.48                                                       | 1000                                     | 105                                      |
| 33                                                           | A            | T55A336M004C0300 | 13.2                               | 10                                   | 300                                                | 0.61                                                       | 1000                                     | 105                                      |
| 33                                                           | A            | T55A336M004C0200 | 13.2                               | 10                                   | 200                                                | 0.76                                                       | 1000                                     | 105                                      |
| 33                                                           | B            | T55B336M004C0200 | 13.2                               | 8                                    | 200                                                | 0.81                                                       | 2000                                     | 125                                      |
| 47                                                           | A            | T55A476M004C0500 | 18.8                               | 10                                   | 500                                                | 0.48                                                       | 1000                                     | 105                                      |
| 47                                                           | A            | T55A476M004C0200 | 18.8                               | 10                                   | 200                                                | 0.76                                                       | 1000                                     | 105                                      |
| 47                                                           | A            | T55A476M004C0180 | 18.8                               | 10                                   | 180                                                | 0.79                                                       | 1000                                     | 105                                      |
| 47                                                           | T            | T55T476M004C0200 | 18.8                               | 10                                   | 200                                                | 0.72                                                       | 1000                                     | 105                                      |
| 47                                                           | T            | T55T476M004C0080 | 18.8                               | 10                                   | 80                                                 | 1.15                                                       | 1000                                     | 105                                      |
| 47                                                           | T            | T55T476M004C0070 | 18.8                               | 10                                   | 70                                                 | 1.22                                                       | 1000                                     | 105                                      |
| 47                                                           | B            | T55B476M004C0150 | 18.8                               | 8                                    | 150                                                | 0.93                                                       | 2000                                     | 125                                      |
| 47                                                           | B            | T55B476M004C0070 | 18.8                               | 8                                    | 70                                                 | 1.36                                                       | 2000                                     | 125                                      |
| 68                                                           | A            | T55A686M004C0500 | 27.2                               | 10                                   | 500                                                | 0.48                                                       | 1000                                     | 105                                      |
| 68                                                           | A            | T55A686M004C0250 | 27.2                               | 10                                   | 250                                                | 0.67                                                       | 1000                                     | 105                                      |
| 68                                                           | A            | T55A686M004C0200 | 27.2                               | 10                                   | 200                                                | 0.76                                                       | 1000                                     | 105                                      |
| 68                                                           | T            | T55T686M004C0200 | 27.2                               | 10                                   | 200                                                | 0.72                                                       | 1000                                     | 105                                      |
| 68                                                           | T            | T55T686M004C0180 | 27.2                               | 10                                   | 180                                                | 0.76                                                       | 1000                                     | 105                                      |
| 68                                                           | T            | T55T686M004C0080 | 27.2                               | 10                                   | 80                                                 | 1.15                                                       | 1000                                     | 105                                      |
| 68                                                           | T            | T55T686M004C0070 | 27.2                               | 10                                   | 70                                                 | 1.22                                                       | 1000                                     | 105                                      |
| 68                                                           | B            | T55B686M004C0150 | 27.2                               | 8                                    | 150                                                | 0.93                                                       | 2000                                     | 125                                      |
| 68                                                           | B            | T55B686M004C0070 | 27.2                               | 8                                    | 70                                                 | 1.36                                                       | 2000                                     | 125                                      |
| 100                                                          | A            | T55A107M004C0200 | 40.0                               | 10                                   | 200                                                | 0.75                                                       | 1000                                     | 105                                      |
| 100                                                          | A            | T55A107M004C0100 | 40.0                               | 10                                   | 100                                                | 1.07                                                       | 1000                                     | 105                                      |
| 100                                                          | T            | T55T107M004C0150 | 40.0                               | 10                                   | 150                                                | 0.84                                                       | 1000                                     | 105                                      |
| 100                                                          | T            | T55T107M004C0070 | 40.0                               | 10                                   | 70                                                 | 1.22                                                       | 1000                                     | 105                                      |
| 100                                                          | B            | T55B107M004C0070 | 40.0                               | 8                                    | 70                                                 | 1.36                                                       | 2000                                     | 125                                      |
| 100                                                          | B            | T55B107M004C0055 | 40.0                               | 8                                    | 55                                                 | 1.53                                                       | 2000                                     | 125                                      |
| 100                                                          | B            | T55B107M004C0045 | 40.0                               | 8                                    | 45                                                 | 1.70                                                       | 2000                                     | 125                                      |
| 100                                                          | B            | T55B107M004C0040 | 40.0                               | 8                                    | 40                                                 | 1.80                                                       | 2000                                     | 125                                      |
| 100                                                          | B            | T55B107M004C0035 | 40.0                               | 8                                    | 35                                                 | 1.92                                                       | 2000                                     | 125                                      |
| 150                                                          | B            | T55B157M004C0070 | 60.0                               | 8                                    | 70                                                 | 1.36                                                       | 2000                                     | 105                                      |
| 150                                                          | B            | T55B157M004C0055 | 60.0                               | 8                                    | 55                                                 | 1.53                                                       | 2000                                     | 105                                      |
| 150                                                          | B            | T55B157M004C0045 | 60.0                               | 8                                    | 45                                                 | 1.69                                                       | 2000                                     | 105                                      |
| 150                                                          | B            | T55B157M004C0040 | 60.0                               | 8                                    | 40                                                 | 1.80                                                       | 2000                                     | 105                                      |
| 150                                                          | B            | T55B157M004C0035 | 60.0                               | 8                                    | 35                                                 | 1.93                                                       | 2000                                     | 105                                      |
| 150                                                          | Z            | T55Z157M004C0025 | 60.0                               | 10                                   | 25                                                 | 2.73                                                       | 2000                                     | 105                                      |
| 150                                                          | V            | T55V157M004C0045 | 60.0                               | 10                                   | 45                                                 | 2.03                                                       | 2000                                     | 125                                      |
| 150                                                          | V            | T55V157M004C0025 | 60.0                               | 10                                   | 25                                                 | 2.73                                                       | 2000                                     | 125                                      |
| 150                                                          | V            | T55V157M004C0015 | 60.0                               | 10                                   | 15                                                 | 3.53                                                       | 2000                                     | 125                                      |

## Note

- Termination code "C": cases C, J, P: 100 % tin, case A, T, B, Z, V, D: Ni / Pd / Au



## STANDARD RATINGS

| CAPACITANCE<br>( $\mu$ F)                                    | CASE<br>CODE | PART NUMBER      | MAX. DCL<br>AT 25 °C<br>( $\mu$ A) | MAX. DF<br>AT 25 °C<br>120 Hz<br>(%) | MAX. ESR<br>AT + 25 °C<br>100 kHz<br>(m $\Omega$ ) | MAX. RIPPLE<br>AT 45 °C<br>100 kHz I <sub>RMS</sub><br>(A) | HIGH<br>TEMPERATURE<br>LOAD, TIME<br>(h) | MAX.<br>OPERATING<br>TEMPERATURE<br>(°C) |
|--------------------------------------------------------------|--------------|------------------|------------------------------------|--------------------------------------|----------------------------------------------------|------------------------------------------------------------|------------------------------------------|------------------------------------------|
| 4 V <sub>DC</sub> AT +105 °C, 2.7 V <sub>DC</sub> AT +125 °C |              |                  |                                    |                                      |                                                    |                                                            |                                          |                                          |
| 220                                                          | B            | T55B227M004C0070 | 88.0                               | 8                                    | 70                                                 | 1.36                                                       | 2000                                     | 105                                      |
| 220                                                          | B            | T55B227M004C0060 | 88.0                               | 8                                    | 60                                                 | 1.47                                                       | 2000                                     | 105                                      |
| 220                                                          | B            | T55B227M004C0055 | 88.0                               | 8                                    | 55                                                 | 1.53                                                       | 2000                                     | 105                                      |
| 220                                                          | B            | T55B227M004C0045 | 88.0                               | 8                                    | 45                                                 | 1.70                                                       | 2000                                     | 105                                      |
| 220                                                          | B            | T55B227M004C0035 | 88.0                               | 8                                    | 35                                                 | 1.93                                                       | 2000                                     | 105                                      |
| 220                                                          | Z            | T55Z227M004C0025 | 88.0                               | 10                                   | 25                                                 | 2.73                                                       | 2000                                     | 105                                      |
| 220                                                          | Z            | T55Z227M004C0018 | 88.0                               | 10                                   | 18                                                 | 3.22                                                       | 2000                                     | 105                                      |
| 220                                                          | V            | T55V227M004C0055 | 88.0                               | 10                                   | 55                                                 | 1.84                                                       | 2000                                     | 125                                      |
| 220                                                          | V            | T55V227M004C0045 | 88.0                               | 10                                   | 45                                                 | 2.03                                                       | 2000                                     | 125                                      |
| 220                                                          | V            | T55V227M004C0040 | 88.0                               | 10                                   | 40                                                 | 2.16                                                       | 2000                                     | 125                                      |
| 220                                                          | V            | T55V227M004C0035 | 88.0                               | 10                                   | 35                                                 | 2.31                                                       | 2000                                     | 125                                      |
| 220                                                          | V            | T55V227M004C0025 | 88.0                               | 10                                   | 25                                                 | 2.73                                                       | 2000                                     | 125                                      |
| 220                                                          | V            | T55V227M004C0018 | 88.0                               | 10                                   | 18                                                 | 3.22                                                       | 2000                                     | 125                                      |
| 220                                                          | V            | T55V227M004C0015 | 88.0                               | 10                                   | 15                                                 | 3.53                                                       | 2000                                     | 125                                      |
| 220                                                          | D            | T55D227M004C0055 | 88.0                               | 10                                   | 55                                                 | 2.02                                                       | 2000                                     | 125                                      |
| 220                                                          | D            | T55D227M004C0040 | 88.0                               | 10                                   | 40                                                 | 2.37                                                       | 2000                                     | 125                                      |
| 220                                                          | D            | T55D227M004C0025 | 88.0                               | 10                                   | 25                                                 | 3.00                                                       | 2000                                     | 125                                      |
| 330                                                          | Z            | T55Z337M004C0025 | 132.0                              | 10                                   | 25                                                 | 2.73                                                       | 2000                                     | 105                                      |
| 330                                                          | Z            | T55Z337M004C0018 | 132.0                              | 10                                   | 18                                                 | 3.22                                                       | 2000                                     | 105                                      |
| 330                                                          | V            | T55V337M004C0050 | 132.0                              | 10                                   | 50                                                 | 1.93                                                       | 2000                                     | 105                                      |
| 330                                                          | V            | T55V337M004C0045 | 132.0                              | 10                                   | 45                                                 | 2.03                                                       | 2000                                     | 105                                      |
| 330                                                          | V            | T55V337M004C0040 | 132.0                              | 10                                   | 40                                                 | 2.16                                                       | 2000                                     | 105                                      |
| 330                                                          | V            | T55V337M004C0025 | 132.0                              | 10                                   | 25                                                 | 2.73                                                       | 2000                                     | 105                                      |
| 330                                                          | V            | T55V337M004C0018 | 132.0                              | 10                                   | 18                                                 | 3.22                                                       | 2000                                     | 105                                      |
| 330                                                          | V            | T55V337M004C0015 | 132.0                              | 10                                   | 15                                                 | 3.53                                                       | 2000                                     | 105                                      |
| 330                                                          | D            | T55D337M004C0050 | 132.0                              | 10                                   | 50                                                 | 2.12                                                       | 2000                                     | 125                                      |
| 330                                                          | D            | T55D337M004C0040 | 132.0                              | 10                                   | 40                                                 | 2.37                                                       | 2000                                     | 125                                      |
| 330                                                          | D            | T55D337M004C0025 | 132.0                              | 10                                   | 25                                                 | 3.00                                                       | 2000                                     | 125                                      |
| 330                                                          | D            | T55D337M004C0015 | 132.0                              | 10                                   | 15                                                 | 3.87                                                       | 2000                                     | 125                                      |
| 330                                                          | D            | T55D337M004C0009 | 132.0                              | 10                                   | 9                                                  | 5.00                                                       | 2000                                     | 125                                      |
| 330                                                          | D            | T55D337M004C0008 | 132.0                              | 10                                   | 8                                                  | 5.30                                                       | 2000                                     | 125                                      |
| 330                                                          | D            | T55D337M004C0007 | 132.0                              | 10                                   | 7                                                  | 5.66                                                       | 2000                                     | 125                                      |
| 470                                                          | Z            | T55Z477M004C0025 | 188.0                              | 10                                   | 25                                                 | 2.74                                                       | 2000                                     | 105                                      |
| 470                                                          | Z            | T55Z477M004C0018 | 188.0                              | 10                                   | 18                                                 | 3.22                                                       | 2000                                     | 105                                      |
| 470                                                          | D            | T55D477M004C0055 | 188.0                              | 10                                   | 55                                                 | 2.02                                                       | 2000                                     | 125                                      |
| 470                                                          | D            | T55D477M004C0050 | 188.0                              | 10                                   | 50                                                 | 2.12                                                       | 2000                                     | 125                                      |
| 470                                                          | D            | T55D477M004C0040 | 188.0                              | 10                                   | 40                                                 | 2.37                                                       | 2000                                     | 125                                      |
| 470                                                          | D            | T55D477M004C0025 | 188.0                              | 10                                   | 25                                                 | 3.00                                                       | 2000                                     | 125                                      |
| 470                                                          | D            | T55D477M004C0018 | 188.0                              | 10                                   | 18                                                 | 3.53                                                       | 2000                                     | 125                                      |
| 470                                                          | D            | T55D477M004C0015 | 188.0                              | 10                                   | 15                                                 | 3.87                                                       | 2000                                     | 125                                      |
| 470                                                          | D            | T55D477M004C0012 | 188.0                              | 10                                   | 12                                                 | 4.33                                                       | 2000                                     | 125                                      |
| 470                                                          | D            | T55D477M004C0009 | 188.0                              | 10                                   | 9                                                  | 5.00                                                       | 2000                                     | 125                                      |
| 470                                                          | D            | T55D477M004C0008 | 188.0                              | 10                                   | 8                                                  | 5.30                                                       | 2000                                     | 125                                      |
| 470                                                          | D            | T55D477M004C0007 | 188.0                              | 10                                   | 7                                                  | 5.66                                                       | 2000                                     | 125                                      |
| 680                                                          | D            | T55D687M004C0025 | 272.0                              | 10                                   | 25                                                 | 3.00                                                       | 2000                                     | 105                                      |
| 680                                                          | D            | T55D687M004C0018 | 272.0                              | 10                                   | 18                                                 | 3.53                                                       | 2000                                     | 105                                      |
| 680                                                          | D            | T55D687M004C0015 | 272.0                              | 10                                   | 15                                                 | 3.87                                                       | 2000                                     | 105                                      |
| 680                                                          | D            | T55D687M004C0009 | 272.0                              | 10                                   | 9                                                  | 5.00                                                       | 2000                                     | 105                                      |
| 680                                                          | D            | T55D687M004C0008 | 272.0                              | 10                                   | 8                                                  | 5.30                                                       | 2000                                     | 105                                      |
| 680                                                          | D            | T55D687M004C0007 | 272.0                              | 10                                   | 7                                                  | 5.66                                                       | 2000                                     | 105                                      |
| 680                                                          | D            | T55D687M004C0006 | 272.0                              | 10                                   | 6                                                  | 6.12                                                       | 1000                                     | 105                                      |

## Note

- Termination code "C": cases C, J, P: 100 % tin, case A, T, B, Z, V, D: Ni / Pd / Au



## STANDARD RATINGS

| CAPACITANCE<br>( $\mu$ F)                                      | CASE<br>CODE | PART NUMBER      | MAX. DCL<br>AT 25 °C<br>( $\mu$ A) | MAX. DF<br>AT 25 °C<br>120 Hz<br>(%) | MAX. ESR<br>AT + 25 °C<br>100 kHz<br>(m $\Omega$ ) | MAX. RIPPLE<br>AT 45 °C<br>100 kHz I <sub>RMS</sub><br>(A) | HIGH<br>TEMPERATURE<br>LOAD, TIME<br>(h) | MAX.<br>OPERATING<br>TEMPERATURE<br>(°C) |
|----------------------------------------------------------------|--------------|------------------|------------------------------------|--------------------------------------|----------------------------------------------------|------------------------------------------------------------|------------------------------------------|------------------------------------------|
| 6.3 V <sub>DC</sub> AT +105 °C, 4.2 V <sub>DC</sub> AT +125 °C |              |                  |                                    |                                      |                                                    |                                                            |                                          |                                          |
| 3.3                                                            | J            | T55J335M6R3C0500 | 10.0                               | 10                                   | 500                                                | 0.32                                                       | 1000                                     | 105                                      |
| 3.3                                                            | P            | T55P335M6R3C0500 | 5.0                                | 10                                   | 500                                                | 0.36                                                       | 1000                                     | 105                                      |
| 4.7                                                            | J            | T55J475M6R3C0500 | 10.0                               | 10                                   | 500                                                | 0.32                                                       | 1000                                     | 105                                      |
| 4.7                                                            | P            | T55P475M6R3C0500 | 5.0                                | 10                                   | 500                                                | 0.36                                                       | 1000                                     | 105                                      |
| 4.7                                                            | A            | T55A475M6R3C0500 | 3.0                                | 10                                   | 500                                                | 0.48                                                       | 1000                                     | 105                                      |
| 6.8                                                            | P            | T55P685M6R3C0500 | 5.0                                | 10                                   | 500                                                | 0.36                                                       | 1000                                     | 105                                      |
| 6.8                                                            | A            | T55A685M6R3C0500 | 4.2                                | 10                                   | 500                                                | 0.48                                                       | 1000                                     | 105                                      |
| 10                                                             | P            | T55P106M6R3C0500 | 10.0                               | 10                                   | 500                                                | 0.36                                                       | 1000                                     | 105                                      |
| 10                                                             | P            | T55P106M6R3C0200 | 10.0                               | 10                                   | 200                                                | 0.56                                                       | 1000                                     | 105                                      |
| 10                                                             | A            | T55A106M6R3C0500 | 6.3                                | 10                                   | 500                                                | 0.48                                                       | 1000                                     | 105                                      |
| 10                                                             | A            | T55A106M6R3C0300 | 6.3                                | 10                                   | 300                                                | 0.61                                                       | 1000                                     | 105                                      |
| 10                                                             | A            | T55A106M6R3C0200 | 6.3                                | 10                                   | 200                                                | 0.76                                                       | 1000                                     | 105                                      |
| 15                                                             | A            | T55A156M6R3C0500 | 9.4                                | 10                                   | 500                                                | 0.48                                                       | 1000                                     | 105                                      |
| 15                                                             | A            | T55A156M6R3C0300 | 9.4                                | 10                                   | 300                                                | 0.61                                                       | 1000                                     | 105                                      |
| 15                                                             | A            | T55A156M6R3C0200 | 9.4                                | 10                                   | 200                                                | 0.76                                                       | 1000                                     | 105                                      |
| 22                                                             | A            | T55A226M6R3C0500 | 13.8                               | 10                                   | 500                                                | 0.48                                                       | 1000                                     | 105                                      |
| 22                                                             | A            | T55A226M6R3C0300 | 13.8                               | 10                                   | 300                                                | 0.61                                                       | 1000                                     | 105                                      |
| 22                                                             | A            | T55A226M6R3C0200 | 13.8                               | 10                                   | 200                                                | 0.76                                                       | 2000                                     | 105                                      |
| 22                                                             | T            | T55T226M6R3C0150 | 13.8                               | 10                                   | 150                                                | 0.84                                                       | 1000                                     | 105                                      |
| 22                                                             | T            | T55T226M6R3C0070 | 13.8                               | 10                                   | 70                                                 | 1.22                                                       | 1000                                     | 105                                      |
| 22                                                             | B            | T55B226M6R3C0150 | 13.8                               | 8                                    | 150                                                | 0.93                                                       | 2000                                     | 125                                      |
| 33                                                             | A            | T55A336M6R3C0500 | 20.7                               | 10                                   | 500                                                | 0.48                                                       | 1000                                     | 105                                      |
| 33                                                             | A            | T55A336M6R3C0200 | 20.7                               | 10                                   | 200                                                | 0.76                                                       | 1000                                     | 105                                      |
| 33                                                             | A            | T55A336M6R3C0180 | 20.7                               | 10                                   | 180                                                | 0.79                                                       | 1000                                     | 105                                      |
| 33                                                             | T            | T55T336M6R3C0200 | 20.7                               | 10                                   | 200                                                | 0.72                                                       | 1000                                     | 105                                      |
| 33                                                             | T            | T55T336M6R3C0150 | 20.7                               | 10                                   | 150                                                | 0.84                                                       | 1000                                     | 105                                      |
| 33                                                             | T            | T55T336M6R3C0070 | 20.7                               | 10                                   | 70                                                 | 1.22                                                       | 1000                                     | 105                                      |
| 33                                                             | B            | T55B336M6R3C0200 | 20.7                               | 8                                    | 200                                                | 0.81                                                       | 2000                                     | 125                                      |
| 33                                                             | B            | T55B336M6R3C0150 | 20.7                               | 8                                    | 150                                                | 0.93                                                       | 2000                                     | 125                                      |
| 33                                                             | B            | T55B336M6R3C0080 | 20.7                               | 8                                    | 80                                                 | 1.27                                                       | 2000                                     | 125                                      |
| 33                                                             | B            | T55B336M6R3C0070 | 20.7                               | 8                                    | 70                                                 | 1.36                                                       | 2000                                     | 125                                      |
| 33                                                             | B            | T55B336M6R3C0040 | 20.7                               | 8                                    | 40                                                 | 1.80                                                       | 2000                                     | 125                                      |
| 47                                                             | A            | T55A476M6R3C0500 | 29.6                               | 10                                   | 500                                                | 0.48                                                       | 1000                                     | 105                                      |
| 47                                                             | A            | T55A476M6R3C0200 | 29.6                               | 10                                   | 200                                                | 0.76                                                       | 1000                                     | 105                                      |
| 47                                                             | A            | T55A476M6R3C0180 | 29.6                               | 10                                   | 180                                                | 0.79                                                       | 1000                                     | 105                                      |
| 47                                                             | A            | T55A476M6R3C0150 | 29.6                               | 10                                   | 150                                                | 0.88                                                       | 1000                                     | 105                                      |
| 47                                                             | A            | T55A476M6R3C0100 | 29.6                               | 10                                   | 100                                                | 1.07                                                       | 1000                                     | 105                                      |
| 47                                                             | A            | T55A476M6R3C0070 | 29.6                               | 10                                   | 70                                                 | 1.28                                                       | 1000                                     | 105                                      |
| 47                                                             | T            | T55T476M6R3C0200 | 29.6                               | 10                                   | 200                                                | 0.72                                                       | 1000                                     | 105                                      |
| 47                                                             | T            | T55T476M6R3C0120 | 29.6                               | 10                                   | 120                                                | 0.93                                                       | 1000                                     | 105                                      |
| 47                                                             | T            | T55T476M6R3C0080 | 29.6                               | 10                                   | 80                                                 | 1.15                                                       | 1000                                     | 105                                      |
| 47                                                             | T            | T55T476M6R3C0070 | 29.6                               | 10                                   | 70                                                 | 1.22                                                       | 1000                                     | 105                                      |
| 47                                                             | B            | T55B476M6R3C0150 | 29.6                               | 8                                    | 150                                                | 0.93                                                       | 2000                                     | 125                                      |
| 47                                                             | B            | T55B476M6R3C0070 | 29.6                               | 8                                    | 70                                                 | 1.36                                                       | 2000                                     | 125                                      |
| 47                                                             | B            | T55B476M6R3C0060 | 29.6                               | 8                                    | 60                                                 | 1.47                                                       | 2000                                     | 125                                      |
| 47                                                             | B            | T55B476M6R3C0040 | 29.6                               | 8                                    | 40                                                 | 1.80                                                       | 2000                                     | 125                                      |
| 68                                                             | T            | T55T686M6R3C0200 | 42.8                               | 10                                   | 200                                                | 0.72                                                       | 1000                                     | 105                                      |
| 68                                                             | T            | T55T686M6R3C0150 | 42.8                               | 10                                   | 150                                                | 0.83                                                       | 1000                                     | 105                                      |
| 68                                                             | T            | T55T686M6R3C0070 | 42.8                               | 10                                   | 70                                                 | 1.22                                                       | 1000                                     | 105                                      |
| 68                                                             | B            | T55B686M6R3C0150 | 42.8                               | 8                                    | 150                                                | 0.93                                                       | 2000                                     | 105                                      |
| 68                                                             | B            | T55B686M6R3C0070 | 42.8                               | 8                                    | 70                                                 | 1.36                                                       | 2000                                     | 105                                      |
| 100                                                            | A            | T55A107M6R3C0200 | 63.0                               | 10                                   | 200                                                | 0.76                                                       | 1000                                     | 105                                      |
| 100                                                            | A            | T55A107M6R3C0150 | 63.0                               | 10                                   | 150                                                | 0.88                                                       | 1000                                     | 105                                      |
| 100                                                            | A            | T55A107M6R3C0100 | 63.0                               | 10                                   | 100                                                | 1.07                                                       | 1000                                     | 105                                      |
| 100                                                            | A            | T55A107M6R3C0070 | 63.0                               | 10                                   | 70                                                 | 1.28                                                       | 1000                                     | 105                                      |
| 100                                                            | A            | T55A107M6R3C0045 | 63.0                               | 10                                   | 45                                                 | 1.59                                                       | 1000                                     | 105                                      |

## Note

- Termination code "C": cases C, J, P: 100 % tin, case A, T, B, Z, V, D: Ni / Pd / Au



**STANDARD RATINGS**

| CAPACITANCE<br>( $\mu$ F)                                      | CASE<br>CODE | PART NUMBER      | MAX. DCL<br>AT 25 °C<br>( $\mu$ A) | MAX. DF<br>AT 25 °C<br>120 Hz<br>(%) | MAX. ESR<br>AT + 25 °C<br>100 kHz<br>(m $\Omega$ ) | MAX. RIPPLE<br>AT 45 °C<br>100 kHz I <sub>RMS</sub><br>(A) | HIGH<br>TEMPERATURE<br>LOAD, TIME<br>(h) | MAX.<br>OPERATING<br>TEMPERATURE<br>(°C) |
|----------------------------------------------------------------|--------------|------------------|------------------------------------|--------------------------------------|----------------------------------------------------|------------------------------------------------------------|------------------------------------------|------------------------------------------|
| 6.3 V <sub>DC</sub> AT +105 °C, 4.2 V <sub>DC</sub> AT +125 °C |              |                  |                                    |                                      |                                                    |                                                            |                                          |                                          |
| 100                                                            | T            | T55T107M6R3C0200 | 63.0                               | 10                                   | 200                                                | 0.72                                                       | 1000                                     | 105                                      |
| 100                                                            | T            | T55T107M6R3C0070 | 63.0                               | 10                                   | 70                                                 | 1.22                                                       | 2000                                     | 105                                      |
| 100                                                            | B            | T55B107M6R3C0100 | 63.0                               | 8                                    | 100                                                | 1.14                                                       | 2000                                     | 105                                      |
| 100                                                            | B            | T55B107M6R3C0070 | 63.0                               | 8                                    | 70                                                 | 1.36                                                       | 2000                                     | 105                                      |
| 100                                                            | B            | T55B107M6R3C0055 | 63.0                               | 8                                    | 55                                                 | 1.53                                                       | 2000                                     | 105                                      |
| 100                                                            | B            | T55B107M6R3C0045 | 63.0                               | 8                                    | 45                                                 | 1.70                                                       | 2000                                     | 105                                      |
| 100                                                            | B            | T55B107M6R3C0040 | 63.0                               | 8                                    | 40                                                 | 1.80                                                       | 2000                                     | 105                                      |
| 100                                                            | B            | T55B107M6R3C0035 | 63.0                               | 8                                    | 35                                                 | 1.93                                                       | 2000                                     | 105                                      |
| 100                                                            | Z            | T55Z107M6R3C0045 | 63.0                               | 10                                   | 45                                                 | 2.03                                                       | 2000                                     | 105                                      |
| 100                                                            | V            | T55V107M6R3C0045 | 63.0                               | 10                                   | 45                                                 | 2.03                                                       | 2000                                     | 125                                      |
| 100                                                            | D            | T55D107M6R3C0015 | 63.0                               | 10                                   | 15                                                 | 3.87                                                       | 2000                                     | 125                                      |
| 150                                                            | B            | T55B157M6R3C0100 | 94.5                               | 8                                    | 100                                                | 1.14                                                       | 2000                                     | 105                                      |
| 150                                                            | B            | T55B157M6R3C0070 | 94.5                               | 8                                    | 70                                                 | 1.36                                                       | 2000                                     | 105                                      |
| 150                                                            | B            | T55B157M6R3C0055 | 94.5                               | 8                                    | 55                                                 | 1.53                                                       | 2000                                     | 105                                      |
| 150                                                            | B            | T55B157M6R3C0045 | 94.5                               | 8                                    | 45                                                 | 1.70                                                       | 2000                                     | 105                                      |
| 150                                                            | B            | T55B157M6R3C0040 | 94.5                               | 8                                    | 40                                                 | 1.80                                                       | 2000                                     | 105                                      |
| 150                                                            | B            | T55B157M6R3C0035 | 94.5                               | 8                                    | 35                                                 | 1.93                                                       | 2000                                     | 105                                      |
| 150                                                            | B            | T55B157M6R3C0025 | 94.5                               | 8                                    | 25                                                 | 2.28                                                       | 2000                                     | 105                                      |
| 150                                                            | Z            | T55Z157M6R3C0035 | 94.5                               | 10                                   | 35                                                 | 2.31                                                       | 2000                                     | 105                                      |
| 150                                                            | Z            | T55Z157M6R3C0025 | 94.5                               | 10                                   | 25                                                 | 2.73                                                       | 2000                                     | 105                                      |
| 150                                                            | Z            | T55Z157M6R3C0018 | 94.5                               | 10                                   | 18                                                 | 3.22                                                       | 2000                                     | 105                                      |
| 150                                                            | V            | T55V157M6R3C0055 | 94.5                               | 10                                   | 55                                                 | 1.84                                                       | 2000                                     | 125                                      |
| 150                                                            | V            | T55V157M6R3C0045 | 94.5                               | 10                                   | 45                                                 | 2.03                                                       | 2000                                     | 125                                      |
| 150                                                            | V            | T55V157M6R3C0040 | 94.5                               | 10                                   | 40                                                 | 2.16                                                       | 2000                                     | 125                                      |
| 150                                                            | V            | T55V157M6R3C0035 | 94.5                               | 10                                   | 35                                                 | 2.31                                                       | 2000                                     | 125                                      |
| 150                                                            | V            | T55V157M6R3C0025 | 94.5                               | 10                                   | 25                                                 | 2.73                                                       | 2000                                     | 125                                      |
| 150                                                            | V            | T55V157M6R3C0018 | 94.5                               | 10                                   | 18                                                 | 3.22                                                       | 2000                                     | 125                                      |
| 150                                                            | D            | T55D157M6R3C0025 | 94.5                               | 10                                   | 25                                                 | 3.00                                                       | 2000                                     | 125                                      |
| 220                                                            | B            | T55B227M6R3C0200 | 138.6                              | 8                                    | 200                                                | 0.80                                                       | 2000                                     | 105                                      |
| 220                                                            | B            | T55B227M6R3C0070 | 138.6                              | 8                                    | 70                                                 | 1.36                                                       | 2000                                     | 105                                      |
| 220                                                            | B            | T55B227M6R3C0045 | 138.6                              | 8                                    | 45                                                 | 1.69                                                       | 2000                                     | 105                                      |
| 220                                                            | B            | T55B227M6R3C0035 | 138.6                              | 8                                    | 35                                                 | 1.93                                                       | 2000                                     | 105                                      |
| 220                                                            | B            | T55B227M6R3C0025 | 138.6                              | 8                                    | 25                                                 | 2.28                                                       | 2000                                     | 105                                      |
| 220                                                            | Z            | T55Z227M6R3C0025 | 138.6                              | 10                                   | 25                                                 | 2.73                                                       | 2000                                     | 105                                      |
| 220                                                            | Z            | T55Z227M6R3C0018 | 138.6                              | 10                                   | 18                                                 | 3.22                                                       | 2000                                     | 105                                      |
| 220                                                            | V            | T55V227M6R3C0050 | 138.6                              | 10                                   | 50                                                 | 1.93                                                       | 2000                                     | 125                                      |
| 220                                                            | V            | T55V227M6R3C0045 | 138.6                              | 10                                   | 45                                                 | 2.03                                                       | 2000                                     | 125                                      |
| 220                                                            | V            | T55V227M6R3C0040 | 138.6                              | 10                                   | 40                                                 | 2.16                                                       | 2000                                     | 125                                      |
| 220                                                            | V            | T55V227M6R3C0035 | 138.6                              | 10                                   | 35                                                 | 2.31                                                       | 2000                                     | 125                                      |
| 220                                                            | V            | T55V227M6R3C0025 | 138.6                              | 10                                   | 25                                                 | 2.73                                                       | 2000                                     | 125                                      |
| 220                                                            | V            | T55V227M6R3C0018 | 138.6                              | 10                                   | 18                                                 | 3.22                                                       | 2000                                     | 125                                      |
| 220                                                            | V            | T55V227M6R3C0015 | 138.6                              | 10                                   | 15                                                 | 3.53                                                       | 2000                                     | 125                                      |
| 220                                                            | D            | T55D227M6R3C0055 | 138.6                              | 10                                   | 55                                                 | 2.02                                                       | 2000                                     | 125                                      |
| 220                                                            | D            | T55D227M6R3C0050 | 138.6                              | 10                                   | 50                                                 | 2.12                                                       | 2000                                     | 125                                      |
| 220                                                            | D            | T55D227M6R3C0040 | 138.6                              | 10                                   | 40                                                 | 2.37                                                       | 2000                                     | 125                                      |
| 220                                                            | D            | T55D227M6R3C0035 | 138.6                              | 10                                   | 35                                                 | 2.53                                                       | 2000                                     | 125                                      |
| 220                                                            | D            | T55D227M6R3C0025 | 138.6                              | 10                                   | 25                                                 | 3.00                                                       | 2000                                     | 125                                      |
| 220                                                            | D            | T55D227M6R3C0009 | 138.6                              | 10                                   | 9                                                  | 5.00                                                       | 2000                                     | 125                                      |
| 220                                                            | D            | T55D227M6R3C0008 | 138.6                              | 10                                   | 8                                                  | 5.30                                                       | 2000                                     | 125                                      |
| 220                                                            | D            | T55D227M6R3C0007 | 138.6                              | 10                                   | 7                                                  | 5.66                                                       | 2000                                     | 125                                      |
| 330                                                            | V            | T55V337M6R3C0050 | 207.9                              | 10                                   | 50                                                 | 1.93                                                       | 2000                                     | 105                                      |
| 330                                                            | V            | T55V337M6R3C0045 | 207.9                              | 10                                   | 45                                                 | 2.03                                                       | 2000                                     | 105                                      |
| 330                                                            | V            | T55V337M6R3C0040 | 207.9                              | 10                                   | 40                                                 | 2.16                                                       | 2000                                     | 105                                      |
| 330                                                            | V            | T55V337M6R3C0025 | 207.9                              | 10                                   | 25                                                 | 2.73                                                       | 2000                                     | 105                                      |
| 330                                                            | V            | T55V337M6R3C0018 | 207.9                              | 10                                   | 18                                                 | 3.22                                                       | 2000                                     | 105                                      |
| 330                                                            | V            | T55V337M6R3C0015 | 207.9                              | 10                                   | 15                                                 | 3.53                                                       | 2000                                     | 105                                      |

**Note**

- Termination code "C": cases C, J, P: 100 % tin, case A, T, B, Z, V, D: Ni / Pd / Au



## STANDARD RATINGS

| CAPACITANCE<br>( $\mu$ F)                                      | CASE<br>CODE | PART NUMBER      | MAX. DCL<br>AT 25 °C<br>( $\mu$ A) | MAX. DF<br>AT 25 °C<br>120 Hz<br>(%) | MAX. ESR<br>AT + 25 °C<br>100 kHz<br>(m $\Omega$ ) | MAX. RIPPLE<br>AT 45 °C<br>100 kHz I <sub>RMS</sub><br>(A) | HIGH<br>TEMPERATURE<br>LOAD, TIME<br>(h) | MAX.<br>OPERATING<br>TEMPERATURE<br>(°C) |
|----------------------------------------------------------------|--------------|------------------|------------------------------------|--------------------------------------|----------------------------------------------------|------------------------------------------------------------|------------------------------------------|------------------------------------------|
| 6.3 V <sub>DC</sub> AT +105 °C, 4.2 V <sub>DC</sub> AT +125 °C |              |                  |                                    |                                      |                                                    |                                                            |                                          |                                          |
| 330                                                            | D            | T55D337M6R3C0055 | 207.9                              | 10                                   | 55                                                 | 2.02                                                       | 2000                                     | 125                                      |
| 330                                                            | D            | T55D337M6R3C0050 | 207.9                              | 10                                   | 50                                                 | 2.12                                                       | 2000                                     | 125                                      |
| 330                                                            | D            | T55D337M6R3C0045 | 207.9                              | 10                                   | 45                                                 | 2.23                                                       | 2000                                     | 125                                      |
| 330                                                            | D            | T55D337M6R3C0040 | 207.9                              | 10                                   | 40                                                 | 2.37                                                       | 2000                                     | 125                                      |
| 330                                                            | D            | T55D337M6R3C0025 | 207.9                              | 10                                   | 25                                                 | 3.00                                                       | 2000                                     | 125                                      |
| 330                                                            | D            | T55D337M6R3C0018 | 207.9                              | 10                                   | 18                                                 | 3.53                                                       | 2000                                     | 125                                      |
| 330                                                            | D            | T55D337M6R3C0015 | 207.9                              | 10                                   | 15                                                 | 3.87                                                       | 2000                                     | 125                                      |
| 330                                                            | D            | T55D337M6R3C0012 | 207.9                              | 10                                   | 12                                                 | 4.33                                                       | 2000                                     | 125                                      |
| 330                                                            | D            | T55D337M6R3C0009 | 207.9                              | 10                                   | 9                                                  | 5.00                                                       | 2000                                     | 125                                      |
| 330                                                            | D            | T55D337M6R3C0008 | 207.9                              | 10                                   | 8                                                  | 5.30                                                       | 2000                                     | 125                                      |
| 330                                                            | D            | T55D337M6R3C0007 | 207.9                              | 10                                   | 7                                                  | 5.66                                                       | 2000                                     | 125                                      |
| 470                                                            | V            | T55V477M6R3C0055 | 296.1                              | 10                                   | 55                                                 | 1.84                                                       | 2000                                     | 105                                      |
| 470                                                            | V            | T55V477M6R3C0050 | 296.1                              | 10                                   | 50                                                 | 1.93                                                       | 2000                                     | 105                                      |
| 470                                                            | D            | T55D477M6R3C0030 | 296.1                              | 10                                   | 30                                                 | 2.73                                                       | 2000                                     | 105                                      |
| 470                                                            | D            | T55D477M6R3C0025 | 296.1                              | 10                                   | 25                                                 | 3.00                                                       | 2000                                     | 105                                      |
| 470                                                            | D            | T55D477M6R3C0018 | 296.1                              | 10                                   | 18                                                 | 3.53                                                       | 2000                                     | 105                                      |
| 470                                                            | D            | T55D477M6R3C0015 | 296.1                              | 10                                   | 15                                                 | 3.87                                                       | 2000                                     | 105                                      |
| 470                                                            | D            | T55D477M6R3C0009 | 296.1                              | 10                                   | 9                                                  | 5.00                                                       | 2000                                     | 105                                      |
| 470                                                            | D            | T55D477M6R3C0008 | 296.1                              | 10                                   | 8                                                  | 5.30                                                       | 2000                                     | 105                                      |
| 470                                                            | D            | T55D477M6R3C0007 | 296.1                              | 10                                   | 7                                                  | 5.66                                                       | 2000                                     | 105                                      |
| 680                                                            | D            | T55D687M6R3C0025 | 428.4                              | 10                                   | 25                                                 | 3.00                                                       | 2000                                     | 105                                      |
| 7 V <sub>DC</sub> AT +105 °C, 4.7 V <sub>DC</sub> AT +125 °C   |              |                  |                                    |                                      |                                                    |                                                            |                                          |                                          |
| 100                                                            | A            | T55A107M007C0070 | 70.0                               | 10                                   | 70                                                 | 1.28                                                       | 1000                                     | 105                                      |
| 470                                                            | D            | T55D477M007C0025 | 329.0                              | 10                                   | 25                                                 | 3.00                                                       | 2000                                     | 105                                      |
| 10 V <sub>DC</sub> AT +105 °C, 6.7 V <sub>DC</sub> AT +125 °C  |              |                  |                                    |                                      |                                                    |                                                            |                                          |                                          |
| 3.3                                                            | J            | T55J335M010C0500 | 10.0                               | 10                                   | 500                                                | 0.32                                                       | 1000                                     | 105                                      |
| 3.3                                                            | P            | T55P335M010C0500 | 5.0                                | 10                                   | 500                                                | 0.36                                                       | 1000                                     | 105                                      |
| 4.7                                                            | P            | T55P475M010C0500 | 10.0                               | 10                                   | 500                                                | 0.36                                                       | 1000                                     | 105                                      |
| 4.7                                                            | P            | T55P475M010C0200 | 10.0                               | 10                                   | 200                                                | 0.56                                                       | 1000                                     | 105                                      |
| 4.7                                                            | A            | T55A475M010C0500 | 4.7                                | 10                                   | 500                                                | 0.48                                                       | 1000                                     | 105                                      |
| 4.7                                                            | A            | T55A475M010C0300 | 4.7                                | 10                                   | 300                                                | 0.61                                                       | 1000                                     | 105                                      |
| 4.7                                                            | A            | T55A475M010C0200 | 4.7                                | 10                                   | 200                                                | 0.76                                                       | 1000                                     | 105                                      |
| 6.8                                                            | A            | T55A685M010C0500 | 6.8                                | 10                                   | 500                                                | 0.48                                                       | 1000                                     | 105                                      |
| 6.8                                                            | A            | T55A685M010C0300 | 6.8                                | 10                                   | 300                                                | 0.61                                                       | 1000                                     | 105                                      |
| 6.8                                                            | A            | T55A685M010C0200 | 6.8                                | 10                                   | 200                                                | 0.76                                                       | 1000                                     | 105                                      |
| 10                                                             | A            | T55A106M010C0500 | 10.0                               | 10                                   | 500                                                | 0.48                                                       | 1000                                     | 105                                      |
| 10                                                             | A            | T55A106M010C0300 | 10.0                               | 10                                   | 300                                                | 0.61                                                       | 1000                                     | 105                                      |
| 10                                                             | A            | T55A106M010C0200 | 10.0                               | 10                                   | 200                                                | 0.76                                                       | 1000                                     | 105                                      |
| 15                                                             | A            | T55A156M010C0500 | 15.0                               | 10                                   | 500                                                | 0.48                                                       | 1000                                     | 105                                      |
| 15                                                             | A            | T55A156M010C0200 | 15.0                               | 10                                   | 200                                                | 0.76                                                       | 1000                                     | 105                                      |
| 22                                                             | A            | T55A226M010C0500 | 22.0                               | 10                                   | 500                                                | 0.48                                                       | 1000                                     | 105                                      |
| 22                                                             | A            | T55A226M010C0200 | 22.0                               | 10                                   | 200                                                | 0.76                                                       | 1000                                     | 105                                      |
| 22                                                             | A            | T55A226M010C0080 | 22.0                               | 10                                   | 80                                                 | 1.19                                                       | 1000                                     | 105                                      |
| 22                                                             | T            | T55T226M010C0200 | 22.0                               | 10                                   | 200                                                | 0.72                                                       | 1000                                     | 105                                      |
| 22                                                             | T            | T55T226M010C0150 | 22.0                               | 10                                   | 150                                                | 0.84                                                       | 1000                                     | 105                                      |
| 22                                                             | T            | T55T226M010C0070 | 22.0                               | 10                                   | 70                                                 | 1.22                                                       | 1000                                     | 105                                      |
| 22                                                             | B            | T55B226M010C0300 | 22.0                               | 8                                    | 300                                                | 0.66                                                       | 1000                                     | 125                                      |
| 22                                                             | B            | T55B226M010C0200 | 22.0                               | 8                                    | 200                                                | 0.81                                                       | 1000                                     | 125                                      |
| 22                                                             | B            | T55B226M010C0150 | 22.0                               | 8                                    | 150                                                | 0.93                                                       | 1000                                     | 125                                      |
| 22                                                             | B            | T55B226M010C0070 | 22.0                               | 8                                    | 70                                                 | 1.36                                                       | 1000                                     | 125                                      |
| 33                                                             | A            | T55A336M010C0500 | 33.0                               | 10                                   | 500                                                | 0.48                                                       | 1000                                     | 105                                      |
| 33                                                             | A            | T55A336M010C0200 | 33.0                               | 10                                   | 200                                                | 0.76                                                       | 1000                                     | 105                                      |
| 33                                                             | A            | T55A336M010C0150 | 33.0                               | 10                                   | 150                                                | 0.88                                                       | 1000                                     | 105                                      |
| 33                                                             | A            | T55A336M010C0070 | 33.0                               | 10                                   | 70                                                 | 1.28                                                       | 1000                                     | 105                                      |

## Note

- Termination code "C": cases C, J, P: 100 % tin, case A, T, B, Z, V, D: Ni / Pd / Au



| STANDARD RATINGS                                                |              |                  |                                    |                                      |                                                    |                                                            |                                          |                                          |
|-----------------------------------------------------------------|--------------|------------------|------------------------------------|--------------------------------------|----------------------------------------------------|------------------------------------------------------------|------------------------------------------|------------------------------------------|
| CAPACITANCE<br>( $\mu$ F)                                       | CASE<br>CODE | PART NUMBER      | MAX. DCL<br>AT 25 °C<br>( $\mu$ A) | MAX. DF<br>AT 25 °C<br>120 Hz<br>(%) | MAX. ESR<br>AT + 25 °C<br>100 kHz<br>(m $\Omega$ ) | MAX. RIPPLE<br>AT 45 °C<br>100 kHz I <sub>RMS</sub><br>(A) | HIGH<br>TEMPERATURE<br>LOAD, TIME<br>(h) | MAX.<br>OPERATING<br>TEMPERATURE<br>(°C) |
| 10 V <sub>DC</sub> AT +105 °C, 6.7 V <sub>DC</sub> AT +125 °C   |              |                  |                                    |                                      |                                                    |                                                            |                                          |                                          |
| 33                                                              | T            | T55T336M010C0200 | 33.0                               | 10                                   | 200                                                | 0.72                                                       | 1000                                     | 105                                      |
| 33                                                              | T            | T55T336M010C0150 | 33.0                               | 10                                   | 150                                                | 0.84                                                       | 1000                                     | 105                                      |
| 33                                                              | T            | T55T336M010C0080 | 33.0                               | 10                                   | 80                                                 | 1.14                                                       | 1000                                     | 105                                      |
| 33                                                              | T            | T55T336M010C0070 | 33.0                               | 10                                   | 70                                                 | 1.22                                                       | 1000                                     | 105                                      |
| 33                                                              | T            | T55T336M010C0040 | 33.0                               | 8                                    | 40                                                 | 1.62                                                       | 2000                                     | 105                                      |
| 33                                                              | B            | T55B336M010C0200 | 33.0                               | 8                                    | 200                                                | 0.81                                                       | 1000                                     | 125                                      |
| 33                                                              | B            | T55B336M010C0150 | 33.0                               | 8                                    | 150                                                | 0.93                                                       | 1000                                     | 125                                      |
| 33                                                              | B            | T55B336M010C0080 | 33.0                               | 8                                    | 80                                                 | 1.27                                                       | 1000                                     | 125                                      |
| 33                                                              | B            | T55B336M010C0070 | 33.0                               | 8                                    | 70                                                 | 1.36                                                       | 1000                                     | 125                                      |
| 47                                                              | B            | T55B476M010C0150 | 47.0                               | 8                                    | 150                                                | 0.93                                                       | 1000                                     | 105                                      |
| 47                                                              | B            | T55B476M010C0070 | 47.0                               | 8                                    | 70                                                 | 1.36                                                       | 1000                                     | 105                                      |
| 68                                                              | V            | T55V686M010C0100 | 68.0                               | 10                                   | 100                                                | 1.36                                                       | 2000                                     | 125                                      |
| 68                                                              | V            | T55V686M010C0060 | 68.0                               | 10                                   | 60                                                 | 1.76                                                       | 2000                                     | 125                                      |
| 100                                                             | Z            | T55Z107M010C0045 | 100.0                              | 10                                   | 45                                                 | 2.03                                                       | 2000                                     | 105                                      |
| 100                                                             | Z            | T55Z107M010C0025 | 100.0                              | 10                                   | 25                                                 | 2.73                                                       | 2000                                     | 105                                      |
| 100                                                             | V            | T55V107M010C0045 | 100.0                              | 10                                   | 45                                                 | 2.03                                                       | 2000                                     | 125                                      |
| 100                                                             | D            | T55D107M010C0080 | 100.0                              | 10                                   | 80                                                 | 1.67                                                       | 2000                                     | 125                                      |
| 100                                                             | D            | T55D107M010C0055 | 100.0                              | 10                                   | 55                                                 | 2.02                                                       | 2000                                     | 125                                      |
| 100                                                             | D            | T55D107M010C0045 | 100.0                              | 10                                   | 45                                                 | 2.23                                                       | 2000                                     | 125                                      |
| 100                                                             | D            | T55D107M010C0040 | 100.0                              | 10                                   | 40                                                 | 2.37                                                       | 2000                                     | 125                                      |
| 100                                                             | D            | T55D107M010C0025 | 100.0                              | 10                                   | 25                                                 | 3.00                                                       | 2000                                     | 125                                      |
| 100                                                             | D            | T55D107M010C0018 | 100.0                              | 10                                   | 18                                                 | 3.53                                                       | 2000                                     | 125                                      |
| 150                                                             | Z            | T55Z157M010C0040 | 150.0                              | 10                                   | 40                                                 | 2.16                                                       | 2000                                     | 105                                      |
| 150                                                             | Z            | T55Z157M010C0025 | 150.0                              | 10                                   | 25                                                 | 2.73                                                       | 2000                                     | 105                                      |
| 150                                                             | V            | T55V157M010C0055 | 150.0                              | 10                                   | 55                                                 | 1.84                                                       | 2000                                     | 125                                      |
| 150                                                             | V            | T55V157M010C0045 | 150.0                              | 10                                   | 45                                                 | 2.03                                                       | 2000                                     | 125                                      |
| 150                                                             | V            | T55V157M010C0040 | 150.0                              | 10                                   | 40                                                 | 2.16                                                       | 2000                                     | 125                                      |
| 150                                                             | V            | T55V157M010C0025 | 150.0                              | 10                                   | 25                                                 | 2.73                                                       | 2000                                     | 125                                      |
| 150                                                             | V            | T55V157M010C0015 | 150.0                              | 10                                   | 15                                                 | 3.53                                                       | 2000                                     | 125                                      |
| 150                                                             | D            | T55D157M010C0040 | 150.0                              | 10                                   | 40                                                 | 2.37                                                       | 2000                                     | 125                                      |
| 150                                                             | D            | T55D157M010C0025 | 150.0                              | 10                                   | 25                                                 | 3.00                                                       | 2000                                     | 125                                      |
| 220                                                             | Z            | T55Z227M010C0040 | 220.0                              | 10                                   | 40                                                 | 2.16                                                       | 2000                                     | 105                                      |
| 220                                                             | Z            | T55Z227M010C0025 | 220.0                              | 10                                   | 25                                                 | 2.73                                                       | 2000                                     | 105                                      |
| 220                                                             | V            | T55V227M010C0050 | 220.0                              | 10                                   | 50                                                 | 1.93                                                       | 2000                                     | 105                                      |
| 220                                                             | V            | T55V227M010C0045 | 220.0                              | 10                                   | 45                                                 | 2.03                                                       | 2000                                     | 105                                      |
| 220                                                             | V            | T55V227M010C0040 | 220.0                              | 10                                   | 40                                                 | 2.16                                                       | 2000                                     | 105                                      |
| 220                                                             | V            | T55V227M010C0025 | 220.0                              | 10                                   | 25                                                 | 2.73                                                       | 2000                                     | 105                                      |
| 220                                                             | V            | T55V227M010C0018 | 220.0                              | 10                                   | 18                                                 | 3.22                                                       | 2000                                     | 105                                      |
| 220                                                             | D            | T55D227M010C0055 | 220.0                              | 10                                   | 55                                                 | 2.02                                                       | 2000                                     | 125                                      |
| 220                                                             | D            | T55D227M010C0050 | 220.0                              | 10                                   | 50                                                 | 2.12                                                       | 2000                                     | 125                                      |
| 220                                                             | D            | T55D227M010C0040 | 220.0                              | 10                                   | 40                                                 | 2.37                                                       | 2000                                     | 125                                      |
| 220                                                             | D            | T55D227M010C0025 | 220.0                              | 10                                   | 25                                                 | 3.00                                                       | 2000                                     | 125                                      |
| 220                                                             | D            | T55D227M010C0018 | 220.0                              | 10                                   | 18                                                 | 3.53                                                       | 2000                                     | 125                                      |
| 220                                                             | D            | T55D227M010C0009 | 220.0                              | 10                                   | 9                                                  | 5.00                                                       | 2000                                     | 125                                      |
| 220                                                             | D            | T55D227M010C0008 | 220.0                              | 10                                   | 8                                                  | 5.30                                                       | 2000                                     | 125                                      |
| 220                                                             | D            | T55D227M010C0007 | 220.0                              | 10                                   | 7                                                  | 5.66                                                       | 2000                                     | 125                                      |
| 330                                                             | D            | T55D337M010C0040 | 330.0                              | 10                                   | 40                                                 | 2.37                                                       | 2000                                     | 105                                      |
| 330                                                             | D            | T55D337M010C0035 | 330.0                              | 10                                   | 35                                                 | 2.53                                                       | 2000                                     | 105                                      |
| 330                                                             | D            | T55D337M010C0025 | 330.0                              | 10                                   | 25                                                 | 3.00                                                       | 2000                                     | 105                                      |
| 330                                                             | D            | T55D337M010C0018 | 330.0                              | 10                                   | 18                                                 | 3.53                                                       | 2000                                     | 105                                      |
| 330                                                             | D            | T55D337M010C0009 | 330.0                              | 10                                   | 9                                                  | 5.00                                                       | 2000                                     | 125                                      |
| 330                                                             | D            | T55D337M010C0008 | 330.0                              | 10                                   | 8                                                  | 5.30                                                       | 2000                                     | 125                                      |
| 330                                                             | D            | T55D337M010C0007 | 330.0                              | 10                                   | 7                                                  | 5.66                                                       | 2000                                     | 125                                      |
| 12.5 V <sub>DC</sub> AT +105 °C, 8.4 V <sub>DC</sub> AT +125 °C |              |                  |                                    |                                      |                                                    |                                                            |                                          |                                          |
| 15                                                              | T            | T55T156M12RC0080 | 18.7                               | 8                                    | 80                                                 | 1.14                                                       | 1000                                     | 105                                      |

**Note**

- Termination code "C": cases C, J, P: 100 % tin, case A, T, B, Z, V, D: Ni / Pd / Au



| STANDARD RATINGS                                               |              |                  |                                    |                                      |                                                    |                                                            |                                          |                                          |
|----------------------------------------------------------------|--------------|------------------|------------------------------------|--------------------------------------|----------------------------------------------------|------------------------------------------------------------|------------------------------------------|------------------------------------------|
| CAPACITANCE<br>( $\mu$ F)                                      | CASE<br>CODE | PART NUMBER      | MAX. DCL<br>AT 25 °C<br>( $\mu$ A) | MAX. DF<br>AT 25 °C<br>120 Hz<br>(%) | MAX. ESR<br>AT + 25 °C<br>100 kHz<br>(m $\Omega$ ) | MAX. RIPPLE<br>AT 45 °C<br>100 kHz I <sub>RMS</sub><br>(A) | HIGH<br>TEMPERATURE<br>LOAD, TIME<br>(h) | MAX.<br>OPERATING<br>TEMPERATURE<br>(°C) |
| 16 V <sub>DC</sub> AT +105 °C, 10.7 V <sub>DC</sub> AT +125 °C |              |                  |                                    |                                      |                                                    |                                                            |                                          |                                          |
| 6.8                                                            | B            | T55B685M016C0200 | 10.8                               | 8                                    | 200                                                | 0.80                                                       | 2000                                     | 125                                      |
| 10                                                             | B            | T55B106M016C0200 | 16.0                               | 8                                    | 200                                                | 0.80                                                       | 2000                                     | 125                                      |
| 10                                                             | B            | T55B106M016C0100 | 16.0                               | 8                                    | 100                                                | 1.14                                                       | 2000                                     | 125                                      |
| 15                                                             | B            | T55B156M016C0150 | 24.0                               | 8                                    | 150                                                | 0.93                                                       | 2000                                     | 125                                      |
| 15                                                             | B            | T55B156M016C0090 | 24.0                               | 8                                    | 90                                                 | 1.20                                                       | 2000                                     | 125                                      |
| 22                                                             | B            | T55B226M016C0150 | 35.2                               | 8                                    | 150                                                | 0.93                                                       | 2000                                     | 125                                      |
| 22                                                             | B            | T55B226M016C0070 | 35.2                               | 8                                    | 70                                                 | 1.36                                                       | 2000                                     | 125                                      |
| 33                                                             | B            | T55B336M016C0070 | 52.8                               | 8                                    | 70                                                 | 1.36                                                       | 2000                                     | 105                                      |
| 33                                                             | V            | T55V336M016C0070 | 52.8                               | 10                                   | 70                                                 | 1.63                                                       | 2000                                     | 125                                      |
| 33                                                             | D            | T55D336M016C0070 | 52.8                               | 10                                   | 70                                                 | 1.79                                                       | 2000                                     | 125                                      |
| 47                                                             | Z            | T55Z476M016C0045 | 75.2                               | 10                                   | 45                                                 | 2.03                                                       | 2000                                     | 105                                      |
| 47                                                             | V            | T55V476M016C0070 | 75.2                               | 10                                   | 70                                                 | 1.63                                                       | 2000                                     | 125                                      |
| 47                                                             | V            | T55V476M016C0045 | 75.2                               | 10                                   | 45                                                 | 2.03                                                       | 2000                                     | 125                                      |
| 47                                                             | D            | T55D476M016C0070 | 75.2                               | 10                                   | 70                                                 | 1.79                                                       | 2000                                     | 125                                      |
| 47                                                             | D            | T55D476M016C0065 | 75.2                               | 10                                   | 65                                                 | 1.86                                                       | 2000                                     | 125                                      |
| 68                                                             | V            | T55V686M016C0070 | 108.8                              | 10                                   | 70                                                 | 1.63                                                       | 2000                                     | 125                                      |
| 68                                                             | V            | T55V686M016C0050 | 108.8                              | 10                                   | 50                                                 | 1.934                                                      | 2000                                     | 125                                      |
| 100                                                            | Z            | T55Z107M016C0050 | 160.0                              | 10                                   | 50                                                 | 1.93                                                       | 2000                                     | 105                                      |
| 100                                                            | V            | T55V107M016C0050 | 160.0                              | 10                                   | 50                                                 | 1.93                                                       | 2000                                     | 125                                      |
| 100                                                            | D            | T55D107M016C0050 | 160.0                              | 10                                   | 50                                                 | 2.12                                                       | 2000                                     | 125                                      |
| 150                                                            | D            | T55D157M016C0050 | 240.0                              | 10                                   | 50                                                 | 2.12                                                       | 2000                                     | 105                                      |
| 150                                                            | D            | T55D157M016C0040 | 240.0                              | 10                                   | 40                                                 | 2.37                                                       | 2000                                     | 105                                      |
| 150                                                            | D            | T55D157M016C0015 | 240.0                              | 10                                   | 15                                                 | 3.87                                                       | 2000                                     | 125                                      |
| 20 V <sub>DC</sub> AT +105 °C, 13.4 V <sub>DC</sub> AT +125 °C |              |                  |                                    |                                      |                                                    |                                                            |                                          |                                          |
| 15                                                             | B            | T55B156M020C0090 | 30.0                               | 8                                    | 90                                                 | 1.20                                                       | 2000                                     | 125                                      |
| 15                                                             | B            | T55B156M020C0070 | 30.0                               | 8                                    | 70                                                 | 1.36                                                       | 2000                                     | 125                                      |
| 15                                                             | V            | T55V156M020C0125 | 30.0                               | 10                                   | 125                                                | 1.22                                                       | 2000                                     | 125                                      |
| 22                                                             | V            | T55V226M020C0040 | 44.0                               | 10                                   | 40                                                 | 2.16                                                       | 2000                                     | 125                                      |
| 33                                                             | V            | T55V336M020C0040 | 66.0                               | 10                                   | 40                                                 | 2.16                                                       | 2000                                     | 125                                      |
| 47                                                             | Z            | T55Z476M020C0070 | 94.0                               | 10                                   | 70                                                 | 1.63                                                       | 2000                                     | 105                                      |
| 47                                                             | V            | T55V476M020C0045 | 94.0                               | 10                                   | 45                                                 | 2.03                                                       | 2000                                     | 125                                      |
| 100                                                            | D            | T55D107M020C0055 | 200.0                              | 10                                   | 55                                                 | 2.02                                                       | 2000                                     | 125                                      |
| 25 V <sub>DC</sub> AT +105 °C, 16.8 V <sub>DC</sub> AT +125 °C |              |                  |                                    |                                      |                                                    |                                                            |                                          |                                          |
| 6.8                                                            | B            | T55B685M025C0100 | 17.0                               | 8                                    | 100                                                | 1.14                                                       | 2000                                     | 125                                      |
| 10                                                             | B            | T55B106M025C0150 | 25.0                               | 8                                    | 150                                                | 0.93                                                       | 2000                                     | 125                                      |
| 10                                                             | B            | T55B106M025C0100 | 25.0                               | 8                                    | 100                                                | 1.14                                                       | 2000                                     | 125                                      |
| 15                                                             | B            | T55B156M025C0100 | 37.5                               | 8                                    | 100                                                | 1.14                                                       | 2000                                     | 105                                      |
| 15                                                             | V            | T55V156M025C0125 | 37.5                               | 10                                   | 125                                                | 1.22                                                       | 2000                                     | 125                                      |
| 22                                                             | V            | T55V226M025C0040 | 55.0                               | 10                                   | 40                                                 | 2.16                                                       | 2000                                     | 125                                      |
| 33                                                             | Z            | T55Z336M025C0050 | 82.5                               | 10                                   | 50                                                 | 1.93                                                       | 2000                                     | 105                                      |
| 33                                                             | V            | T55V336M025C0050 | 82.5                               | 10                                   | 50                                                 | 1.93                                                       | 2000                                     | 125                                      |
| 33                                                             | V            | T55V336M025C0040 | 82.5                               | 10                                   | 40                                                 | 2.16                                                       | 2000                                     | 125                                      |
| 33                                                             | D            | T55D336M025C0060 | 82.5                               | 10                                   | 60                                                 | 1.93                                                       | 2000                                     | 125                                      |
| 47                                                             | D            | T55D476M025C0065 | 117.5                              | 10                                   | 65                                                 | 1.86                                                       | 2000                                     | 125                                      |
| 68                                                             | D            | T55D686M025C0070 | 170.0                              | 10                                   | 70                                                 | 1.793                                                      | 2000                                     | 125                                      |
| 100                                                            | D            | T55D107M025C0060 | 250.0                              | 10                                   | 60                                                 | 1.93                                                       | 2000                                     | 125                                      |
| 100                                                            | D            | T55D107M025C0040 | 250.0                              | 10                                   | 40                                                 | 2.37                                                       | 2000                                     | 125                                      |
| 35 V <sub>DC</sub> AT +105 °C, 23.5 V <sub>DC</sub> AT +125 °C |              |                  |                                    |                                      |                                                    |                                                            |                                          |                                          |
| 2.2                                                            | B            | T55B225M035C0200 | 7.7                                | 8                                    | 200                                                | 0.80                                                       | 2000                                     | 105                                      |
| 4.7                                                            | B            | T55B475M035C0200 | 16.4                               | 8                                    | 200                                                | 0.80                                                       | 2000                                     | 105                                      |
| 6.8                                                            | B            | T55B685M035C0200 | 23.8                               | 8                                    | 200                                                | 0.81                                                       | 2000                                     | 105                                      |
| 10                                                             | B            | T55B106M035C0200 | 35.0                               | 8                                    | 200                                                | 0.80                                                       | 2000                                     | 105                                      |
| 10                                                             | D            | T55D106M035C0120 | 35.0                               | 10                                   | 120                                                | 1.36                                                       | 2000                                     | 125                                      |
| 15                                                             | V            | T55V156M035C0125 | 52.5                               | 10                                   | 125                                                | 1.22                                                       | 2000                                     | 125                                      |
| 22                                                             | Z            | T55Z226M035C0070 | 77.0                               | 10                                   | 70                                                 | 1.63                                                       | 2000                                     | 105                                      |

**Note**


- Termination code "C": cases C, J, P: 100 % tin, case A, T, B, Z, V, D: Ni / Pd / Au

**STANDARD RATINGS**

| CAPACITANCE<br>( $\mu$ F)                                           | CASE<br>CODE | PART NUMBER      | MAX. DCL<br>AT 25 °C<br>( $\mu$ A) | MAX. DF<br>AT 25 °C<br>120 Hz<br>(%) | MAX. ESR<br>AT + 25 °C<br>100 kHz<br>(m $\Omega$ ) | MAX. RIPPLE<br>AT 45 °C<br>100 kHz I <sub>RMS</sub><br>(A) | HIGH<br>TEMPERATURE<br>LOAD, TIME<br>(h) | MAX.<br>OPERATING<br>TEMPERATURE<br>(°C) |
|---------------------------------------------------------------------|--------------|------------------|------------------------------------|--------------------------------------|----------------------------------------------------|------------------------------------------------------------|------------------------------------------|------------------------------------------|
| <b>35 V<sub>DC</sub> AT +105 °C, 23.5 V<sub>DC</sub> AT +125 °C</b> |              |                  |                                    |                                      |                                                    |                                                            |                                          |                                          |
| 22                                                                  | V            | T55V226M035C0070 | 77.0                               | 10                                   | 70                                                 | 1.63                                                       | 2000                                     | 125                                      |
| 22                                                                  | D            | T55D226M035C0120 | 77.0                               | 10                                   | 120                                                | 1.36                                                       | 2000                                     | 125                                      |
| 33                                                                  | D            | T55D336M035C0100 | 115.5                              | 10                                   | 100                                                | 1.50                                                       | 2000                                     | 125                                      |
| 33                                                                  | D            | T55D336M035C0065 | 115.5                              | 10                                   | 65                                                 | 1.86                                                       | 2000                                     | 125                                      |
| 47                                                                  | D            | T55D476M035C0070 | 164.5                              | 10                                   | 70                                                 | 1.79                                                       | 2000                                     | 105                                      |
| 47                                                                  | D            | T55D476M035C0055 | 164.5                              | 10                                   | 55                                                 | 2.02                                                       | 2000                                     | 105                                      |
| <b>50 V<sub>DC</sub> AT +105 °C, 33.5 V<sub>DC</sub> AT +125 °C</b> |              |                  |                                    |                                      |                                                    |                                                            |                                          |                                          |
| 2.2                                                                 | B            | T55B225M050C0200 | 11.0                               | 8                                    | 200                                                | 0.80                                                       | 2000                                     | 105                                      |
| 10                                                                  | D            | T55D106M050C0120 | 50.0                               | 10                                   | 120                                                | 1.36                                                       | 2000                                     | 125                                      |
| 10                                                                  | D            | T55D106M050C0090 | 50.0                               | 10                                   | 90                                                 | 1.58                                                       | 2000                                     | 125                                      |
| 15                                                                  | D            | T55D156M050C0090 | 75.0                               | 10                                   | 90                                                 | 1.58                                                       | 2000                                     | 105                                      |
| <b>63 V<sub>DC</sub> AT +105 °C, 42.2 V<sub>DC</sub> AT +125 °C</b> |              |                  |                                    |                                      |                                                    |                                                            |                                          |                                          |
| 1.0                                                                 | B            | T55B105M063C0200 | 6.3                                | 8                                    | 200                                                | 0.80                                                       | 2000                                     | 105                                      |
| 4.7                                                                 | C            | T55C475M063C0200 | 29.6                               | 10                                   | 200                                                | 0.90                                                       | 1000                                     | 105                                      |
| 4.7                                                                 | D            | T55D475M063C0100 | 29.6                               | 10                                   | 100                                                | 1.50                                                       | 2000                                     | 125                                      |
| 10                                                                  | D            | T55D106M063C0150 | 63.0                               | 10                                   | 150                                                | 1.22                                                       | 2000                                     | 105                                      |
| 10                                                                  | D            | T55D106M063C0060 | 63.0                               | 10                                   | 60                                                 | 1.93                                                       | 2000                                     | 105                                      |

**Note**

- Termination code "C": cases C, J, P: 100 % tin, case A, T, B, Z, V, D: Ni / Pd / Au

**RECOMMENDED TEMPERATURE DERATING****RECOMMENDED VOLTAGE DERATING GUIDELINES**

| CAPACITOR<br>VOLTAGE RATING<br>AT -55 °C TO +105 °C | CAPACITOR<br>CATEGORY VOLTAGE<br>AT +105 °C TO +125 °C | RECOMMENDED<br>VOLTAGE DERATING<br>AT -55 °C TO +105 °C | RECOMMENDED<br>VOLTAGE DERATING<br>AT +105 °C TO +125 °C |
|-----------------------------------------------------|--------------------------------------------------------|---------------------------------------------------------|----------------------------------------------------------|
| 2.5                                                 | 1.7                                                    | 2.3                                                     | 1.5                                                      |
| 4                                                   | 2.7                                                    | 3.6                                                     | 2.4                                                      |
| 6.3                                                 | 4.2                                                    | 5.7                                                     | 3.8                                                      |
| 7                                                   | 4.7                                                    | 6.3                                                     | 4.2                                                      |
| 10                                                  | 6.7                                                    | 9                                                       | 6.0                                                      |
| 12.5                                                | 8.4                                                    | 10                                                      | 6.8                                                      |
| 16                                                  | 10.7                                                   | 12.8                                                    | 8.6                                                      |
| 20                                                  | 13.4                                                   | 16                                                      | 10.8                                                     |
| 25                                                  | 16.8                                                   | 20                                                      | 13.5                                                     |
| 35                                                  | 23.5                                                   | 28                                                      | 18.9                                                     |
| 50                                                  | 33.5                                                   | 40                                                      | 27.0                                                     |
| 63                                                  | 42.2                                                   | 50                                                      | 34                                                       |

| POWER DISSIPATION |                                                                                     |
|-------------------|-------------------------------------------------------------------------------------|
| CASE CODE         | MAXIMUM PERMISSIBLE POWER DISSIPATION (W) AT $\leq +45^{\circ}\text{C}$ IN FREE AIR |
| J                 | 0.050                                                                               |
| P                 | 0.064                                                                               |
| A                 | 0.115                                                                               |
| T                 | 0.105                                                                               |
| B                 | 0.130                                                                               |
| C                 | 0.165                                                                               |
| Z                 | 0.187                                                                               |
| V                 | 0.187                                                                               |
| D                 | 0.225                                                                               |

| STANDARD PACKAGING QUANTITY |                   |
|-----------------------------|-------------------|
| CASE CODE                   | UNITS PER 7" REEL |
| J                           | 4000              |
| P                           | 3000              |
| A                           | 2000              |
| T                           | 3000              |
| B                           | 2000              |
| C                           | 500               |
| Z                           | 800               |
| V                           | 800               |
| D                           | 500               |

| PERFORMANCE CHARACTERISTICS |                                                                                                                                                                                                                                |     |     |     |     |    |      |    |    |    |    |    |    |                                                            |                         |                                                   |                   |                                                  |  |
|-----------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----|-----|-----|-----|----|------|----|----|----|----|----|----|------------------------------------------------------------|-------------------------|---------------------------------------------------|-------------------|--------------------------------------------------|--|
| ITEM                        | CONDITION                                                                                                                                                                                                                      |     |     |     |     |    |      |    |    |    |    |    |    | POST TEST PERFORMANCE                                      |                         |                                                   |                   |                                                  |  |
| Temperature characteristics | Measure the specified characteristics in each stage                                                                                                                                                                            |     |     |     |     |    |      |    |    |    |    |    |    |                                                            | Specified initial value | -55 °C                                            | +105 °C / +125 °C |                                                  |  |
|                             |                                                                                                                                                                                                                                |     |     |     |     |    |      |    |    |    |    |    |    | Capacitance change                                         |                         | -                                                 | -30 % to 0 %      | 0 % to +50 %                                     |  |
|                             |                                                                                                                                                                                                                                |     |     |     |     |    |      |    |    |    |    |    |    | Dissipation factor shown in Standard Ratings table or less |                         | 8 to 10                                           | 14                | -                                                |  |
|                             |                                                                                                                                                                                                                                |     |     |     |     |    |      |    |    |    |    |    |    | Leakage current                                            |                         | Refer to Standard Ratings table                   | -                 | Not more than 1 CV or 30 μA which is greater     |  |
| Surge voltage               | 105 °C, 1000 successive test cycles in series with a 1 kΩ resistor at the rate of 30 s ON, 30 s OFF; test voltage per table below:                                                                                             |     |     |     |     |    |      |    |    |    |    |    |    | Capacitance change                                         |                         | Within ± 20 % of initial value                    |                   |                                                  |  |
|                             | Rated voltage                                                                                                                                                                                                                  | 2.5 | 4.0 | 6.3 | 7.0 | 10 | 12.5 | 16 | 20 | 25 | 35 | 50 | 63 | Dissipation factor                                         |                         | Within initial limit                              |                   |                                                  |  |
|                             | Surge voltage                                                                                                                                                                                                                  | 3.2 | 5.2 | 8.2 | 9.0 | 13 | 16.2 | 20 | 23 | 29 | 40 | 57 | 72 | Leakage current                                            |                         | Shall not exceed 300 % of initial limit           |                   |                                                  |  |
| Solder heat resistance      | Reflow board surface peak temperature: less than 260 °C<br>Time: 5 s max.                                                                                                                                                      |     |     |     |     |    |      |    |    |    |    |    |    | Capacitance change                                         |                         | Within ± 20 % of initial value                    |                   |                                                  |  |
|                             |                                                                                                                                                                                                                                |     |     |     |     |    |      |    |    |    |    |    |    | Dissipation factor                                         |                         | Initial specified value or less                   |                   |                                                  |  |
|                             |                                                                                                                                                                                                                                |     |     |     |     |    |      |    |    |    |    |    |    | Leakage current                                            |                         | Shall not exceed 300 % of initial specified value |                   |                                                  |  |
| Moisture resistance no load | Leave at 60 °C and 90 % RH for 500 h                                                                                                                                                                                           |     |     |     |     |    |      |    |    |    |    |    |    | Capacitance change                                         |                         | V <sub>R</sub> ≤ 4 V                              |                   | Relative to the value before test +50 % to -20 % |  |
|                             |                                                                                                                                                                                                                                |     |     |     |     |    |      |    |    |    |    |    |    |                                                            |                         | V <sub>R</sub> ≥ 6.3 V                            |                   | Relative to the value before test +40 % to -20 % |  |
|                             |                                                                                                                                                                                                                                |     |     |     |     |    |      |    |    |    |    |    |    | Dissipation factor                                         |                         | Initial specified value or less                   |                   |                                                  |  |
|                             |                                                                                                                                                                                                                                |     |     |     |     |    |      |    |    |    |    |    |    | Leakage current                                            |                         | Shall not exceed 300 % of initial specified value |                   |                                                  |  |
| High temperature load       | 105 °C. The rated voltage is applied through a protective resistor of 3 Ω for 1000 h or 2000 h <sup>(1)</sup><br>125 °C. 2/3 rated voltage is applied through a protective resistor of 3 Ω for 1000 h or 2000 h <sup>(1)</sup> |     |     |     |     |    |      |    |    |    |    |    |    | Capacitance change                                         |                         | Within ± 20 % of initial value                    |                   |                                                  |  |
|                             |                                                                                                                                                                                                                                |     |     |     |     |    |      |    |    |    |    |    |    | Dissipation factor                                         |                         | Initial specified value or less                   |                   |                                                  |  |
|                             |                                                                                                                                                                                                                                |     |     |     |     |    |      |    |    |    |    |    |    | Leakage current                                            |                         | Shall not exceed 300 % of initial specified value |                   |                                                  |  |
| Thermal shock               | Leave at -55 °C, normal temperature, 105 °C, and normal temperature for 30 min., 15 min. 30 min., and 15 min.<br>Repeat this operation 5 times running.                                                                        |     |     |     |     |    |      |    |    |    |    |    |    | Capacitance change                                         |                         | Within ± 20 % of initial value or less            |                   |                                                  |  |
|                             |                                                                                                                                                                                                                                |     |     |     |     |    |      |    |    |    |    |    |    | Dissipation factor                                         |                         | Initial specified value or less                   |                   |                                                  |  |
|                             |                                                                                                                                                                                                                                |     |     |     |     |    |      |    |    |    |    |    |    | Leakage current                                            |                         | Shall not exceed 300 % of initial specified value |                   |                                                  |  |
| Failure rate                | 105 °C. The rated voltage is applied through a protective resistor of 1 Ω/V.                                                                                                                                                   |     |     |     |     |    |      |    |    |    |    |    |    | 1 % / 1000 h                                               |                         |                                                   |                   |                                                  |  |

**Notes**

- Test conditions per JIS C5101-1

<sup>(1)</sup> Test time and test temperature, please refer to table "Standard Ratings"





## Guide for Tantalum Solid Electrolyte Chip Capacitors With Polymer Cathode

### INTRODUCTION

Tantalum electrolytic capacitors are the preferred choice in applications where volumetric efficiency, stable electrical parameters, high reliability, and long service life are primary considerations. The stability and resistance to elevated temperatures of the tantalum/tantalum oxide/manganese dioxide system make solid tantalum capacitors an appropriate choice for today's surface mount assembly technology.

Vishay Sprague has been a pioneer and leader in this field, producing a large variety of tantalum capacitor types for consumer, industrial, automotive, military, and aerospace electronic applications.

Tantalum is not found in its pure state. Rather, it is commonly found in a number of oxide minerals, often in combination with Columbium ore. This combination is known as "tantalite" when its contents are more than one-half tantalum. Important sources of tantalite include Australia, Brazil, Canada, China, and several African countries. Synthetic tantalite concentrates produced from tin slags in Thailand, Malaysia, and Brazil are also a significant raw material for tantalum production.

Electronic applications, and particularly capacitors, consume the largest share of world tantalum production. Other important applications for tantalum include cutting tools (tantalum carbide), high temperature super alloys, chemical processing equipment, medical implants, and military ordnance.

Vishay Sprague is a major user of tantalum materials in the form of powder and wire for capacitor elements and rod and sheet for high temperature vacuum processing.

### THE BASICS OF TANTALUM CAPACITORS

Most metals form crystalline oxides which are non-protecting, such as rust on iron or black oxide on copper. A few metals form dense, stable, tightly adhering, electrically insulating oxides. These are the so-called "valve" metals and include titanium, zirconium, niobium, tantalum, hafnium, and aluminum. Only a few of these permit the accurate control of oxide thickness by electrochemical means. Of these, the most valuable for the electronics industry are aluminum and tantalum.

Capacitors are basic to all kinds of electrical equipment, from radios and television sets to missile controls and automobile ignitions. Their function is to store an electrical charge for later use.

Capacitors consist of two conducting surfaces, usually metal plates, whose function is to conduct electricity. They are separated by an insulating material or dielectric. The dielectric used in all tantalum electrolytic capacitors is tantalum pentoxide.

Tantalum pentoxide compound possesses high-dielectric strength and a high-dielectric constant. As capacitors are being manufactured, a film of tantalum pentoxide is applied to their electrodes by means of an electrolytic process. The film is applied in various thicknesses and at various voltages and although transparent to begin with, it takes on different colors as light refracts through it. This coloring occurs on the tantalum electrodes of all types of tantalum capacitors.

Rating for rating, tantalum capacitors tend to have as much as three times better capacitance/volume efficiency than aluminum electrolytic capacitors. An approximation of the capacitance/volume efficiency of other types of capacitors may be inferred from the following table, which shows the dielectric constant ranges of the various materials used in each type. Note that tantalum pentoxide has a dielectric constant of 26, some three times greater than that of aluminum oxide. This, in addition to the fact that extremely thin films can be deposited during the electrolytic process mentioned earlier, makes the tantalum capacitor extremely efficient with respect to the number of microfarads available per unit volume. The capacitance of any capacitor is determined by the surface area of the two conducting plates, the distance between the plates, and the dielectric constant of the insulating material between the plates.

#### COMPARISON OF CAPACITOR DIELECTRIC CONSTANTS

| DIELECTRIC                | $\epsilon$<br>DIELECTRIC CONSTANT |
|---------------------------|-----------------------------------|
| Air or vacuum             | 1.0                               |
| Paper                     | 2.0 to 6.0                        |
| Plastic                   | 2.1 to 6.0                        |
| Mineral oil               | 2.2 to 2.3                        |
| Silicone oil              | 2.7 to 2.8                        |
| Quartz                    | 3.8 to 4.4                        |
| Glass                     | 4.8 to 8.0                        |
| Porcelain                 | 5.1 to 5.9                        |
| Mica                      | 5.4 to 8.7                        |
| Aluminum oxide            | 8.4                               |
| <b>Tantalum pentoxide</b> | <b>26</b>                         |
| Ceramic                   | 12 to 400K                        |

In the tantalum electrolytic capacitor, the distance between the plates is very small since it is only the thickness of the tantalum pentoxide film. As the dielectric constant of the tantalum pentoxide is high, the capacitance of a tantalum capacitor is high if the area of the plates is large:

$$C = \frac{\epsilon A}{t}$$

where

C = capacitance

$\epsilon$  = dielectric constant

A = surface area of the dielectric

t = thickness of the dielectric

Tantalum capacitors contain either liquid or solid electrolytes. In solid electrolyte capacitors, a dry material (manganese dioxide) forms the cathode plate. A tantalum lead is embedded in or welded to the pellet, which is in turn connected to a termination or lead wire. The drawings show the construction details of the surface mount types of tantalum capacitors shown in this catalog.


## SOLID ELECTROLYTE POLYMER TANTALUM CAPACITORS

Solid electrolyte polymer capacitors utilize sintered tantalum pellets as anodes. Tantalum pentoxide dielectric layer is formed on the entire surface of anode, which is further impregnated with highly conductive polymer as cathode system.


The conductive polymer layer is then coated with graphite, followed by a layer of metallic silver, which provides a conductive surface between the capacitor element and the outer termination (lead frame or other).

Molded chip polymer tantalum capacitor encases the element in plastic resins, such as epoxy materials. The molding compound has been selected to meet the requirements of UL 94 V-0 and outgassing requirements of ASTM E-595. After assembly, the capacitors are tested and inspected to assure long life and reliability. It offers excellent reliability and high stability for variety of applications in electronic devices. Usage of conductive polymer cathode system provides very low equivalent series resistance (ESR), which makes the capacitors particularly suitable for high frequency applications.

### TANTALUM CAPACITOR WITH POLYMER CATHODE TYPE T50 / T55 / T56





### TANTALUM CAPACITOR WITH POLYMER CATHODE TYPE T58







## TANTALUM CAPACITOR WITH POLYMER CATHODE TYPE T52



## TANTALUM CAPACITOR WITH POLYMER CATHODE TYPE T54 / T59 / 20021






## HERMETICALLY SEALED TANTALUM CAPACITOR WITH POLYMER CATHODE TYPE T27



## POLYMER CAPACITORS - METAL CASE, HERMETICALLY SEALED


| SERIES                | T27                                                                                   |
|-----------------------|---------------------------------------------------------------------------------------|
| PRODUCT IMAGE         |  |
| TYPE                  | VPolyTan™ hermetically sealed polymer surface-mount chip capacitors, low ESR          |
| FEATURES              | Hermetically sealed in metal case, low ESR / low DCL, hi-rel. processing              |
| TEMPERATURE RANGE     | -55 °C to +125 °C                                                                     |
| CAPACITANCE RANGE     | 15 µF to 470 µF                                                                       |
| VOLTAGE RANGE         | 16 V to 75 V                                                                          |
| CAPACITANCE TOLERANCE | ± 20 %                                                                                |
| LEAKAGE CURRENT       | 0.05 CV                                                                               |
| DISSIPATION FACTOR    | 12 %                                                                                  |
| ESR                   | 25 mΩ to 100 mΩ                                                                       |
| CASE SIZES            | D                                                                                     |
| TERMINATION FINISH    | 100 % tin; tin / lead                                                                 |

| POLYMER CAPACITORS - MOLDED CASE |                                                                                    |
|----------------------------------|------------------------------------------------------------------------------------|
| SERIES                           | T50, T55, T56                                                                      |
| PRODUCT IMAGE                    |  |
| TYPE                             | VPolyTan™, molded case, high performance polymer                                   |
| FEATURES                         | High performance                                                                   |
| TEMPERATURE RANGE                | -55 °C to +105 °C / +125 °C                                                        |
| CAPACITANCE RANGE                | 3.3 µF to 1000 µF                                                                  |
| VOLTAGE RANGE                    | 2.5 V to 63 V                                                                      |
| CAPACITANCE TOLERANCE            | ± 20 %                                                                             |
| LEAKAGE CURRENT                  | 0.1 CV                                                                             |
| DISSIPATION FACTOR               | 8 % to 10 %                                                                        |
| ESR                              | 6 mΩ to 500 mΩ                                                                     |
| CASE SIZES                       | J, P, A, T, B, Z, V, D, C                                                          |
| TERMINATION FINISH               | Cases J, P, C: 100 % tin<br>Case A, T, B, Z, V, D: Ni / Pd / Au                    |

| POLYMER CAPACITORS - LEADFRAMELESS MOLDED CASE |                                                                                         |                                                                                     |                                                                                      |                                                                                                                             |                                                                                                   |
|------------------------------------------------|-----------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------|
| SERIES                                         | T52                                                                                     | T58                                                                                 | T59                                                                                  | T54                                                                                                                         | 20021                                                                                             |
| PRODUCT IMAGE                                  |      |  |  |                                        |              |
| TYPE                                           | vPolyTan™ polymer surface mount chip capacitors, low profile, leadframeless molded type | vPolyTan™ polymer surface mount chip capacitors, compact, leadframeless molded type | vPolyTan™ polymer surface mount chip capacitors, low ESR, leadframeless molded type  | vPolyTan™ polymer surface mount chip capacitors, low ESR, leadframeless molded type, hi-rel commercial off-the-shelf (COTS) | vPolyTan™ polymer surface mount chip capacitors, low ESR, leadframeless molded type, DLA approved |
| FEATURES                                       | Low profile                                                                             | Small case size                                                                     | Multinode                                                                            | Hi-rel COTS, multinode                                                                                                      | Multinode                                                                                         |
| TEMPERATURE RANGE                              | -55 °C to +105 °C                                                                       | -55 °C to +105 °C                                                                   | -55 °C to +105 °C                                                                    | -55 °C to +125 °C                                                                                                           | -55 °C to +125 °C                                                                                 |
| CAPACITANCE RANGE                              | 47 µF to 1500 µF                                                                        | 1 µF to 330 µF                                                                      | 15 µF to 470 µF                                                                      | 15 µF to 470 µF (discrete capacitors)<br>30 µF to 2800 µF (stacked capacitors)                                              | 15 µF to 470 µF                                                                                   |
| VOLTAGE RANGE                                  | 10 V to 35 V                                                                            | 6.3 V to 35 V                                                                       | 16 V to 75 V                                                                         | 16 V to 75 V                                                                                                                | 16 V to 63 V                                                                                      |
| CAPACITANCE TOLERANCE                          | ± 20 %                                                                                  | ± 20 %                                                                              | ± 10 %, ± 20 %                                                                       | ± 20 %                                                                                                                      | ± 20 %                                                                                            |
| LEAKAGE CURRENT                                | 0.1 CV                                                                                  |                                                                                     |                                                                                      |                                                                                                                             |                                                                                                   |
| DISSIPATION FACTOR                             | 10 %                                                                                    | 8 % to 14 %                                                                         | 12 %                                                                                 | 12 %                                                                                                                        | 10 %                                                                                              |
| ESR                                            | 25 mΩ to 55 mΩ                                                                          | 50 mΩ to 500 mΩ                                                                     | 25 mΩ to 150 mΩ                                                                      | 5 mΩ to 150 mΩ                                                                                                              | 25 mΩ to 150 mΩ                                                                                   |
| CASE SIZES                                     | E5, M1, M9, B2                                                                          | MM, W0, W9, A0, BB                                                                  | EE                                                                                   | EE, E2, E3, E4, E6                                                                                                          | EE                                                                                                |
| TERMINATION                                    | 100 % tin                                                                               |                                                                                     | 100 % tin; tin / lead                                                                |                                                                                                                             | Tin / lead                                                                                        |

## MOLDED CAPACITORS, T50 / T55 / T56 TYPES

### PLASTIC TAPE AND REEL PACKAGING DIMENSIONS in millimeters




| TAPE WIDTH    | 8   | 12                |
|---------------|-----|-------------------|
| $A + 0 / - 3$ |     | $\varnothing 180$ |
| $B + 1 / 0$   |     | $\varnothing 60$  |
| $C \pm 0.2$   |     | $\varnothing 13$  |
| $D \pm 0.5$   |     | $\varnothing 21$  |
| $E \pm 0.5$   |     | 2.0               |
| $W \pm 0.3$   | 9.0 | 13.0              |

#### Note

- A reel diameter of 330 mm is also applicable

### PLASTIC TAPE SIZE DIMENSIONS in millimeters




| CASE CODE | $A \pm 0.2$ | $B \pm 0.2$ | $W \pm 0.3$ | $F \pm 0.1$ | $E \pm 0.1$ | $P_1 \pm 0.1$ | $t_{max.}$ |
|-----------|-------------|-------------|-------------|-------------|-------------|---------------|------------|
| J         | 1.0         | 1.8         | 8.0         | 3.5         | 1.75        | 4.0           | 1.3        |
| P         | 1.4         | 2.2         | 8.0         | 3.5         | 1.75        | 4.0           | 1.6        |
| A         | 1.9         | 3.5         | 8.0         | 3.5         | 1.75        | 4.0           | 2.5        |
| T         | 3.1         | 3.8         | 8.0         | 3.5         | 1.75        | 4.0           | 1.7        |
| B         | 3.1         | 3.8         | 8.0         | 3.5         | 1.75        | 4.0           | 2.5        |
| C         | 3.7         | 6.3         | 12.0        | 5.5         | 1.75        | 8.0           | 3.1        |
| Z         | 4.8         | 7.7         | 12.0        | 5.5         | 1.75        | 8.0           | 2.6        |
| V         | 4.8         | 7.7         | 12.0        | 5.5         | 1.75        | 8.0           | 2.6        |
| D         | 4.8         | 7.7         | 12.0        | 5.5         | 1.75        | 8.0           | 3.4        |

#### Note

- A reel diameter of 330 mm is also applicable

## LEADFRAMELESS MOLDED CAPACITORS, ALL TYPES

### PLASTIC TAPE AND REEL PACKAGING in inches [millimeters]




#### Notes

- Metric dimensions will govern. Dimensions in inches are rounded and for reference only
- (1)  $A_0$ ,  $B_0$ ,  $K_0$ , are determined by the maximum dimensions to the ends of the terminals extending from the component body and / or the body dimensions of the component. The clearance between the ends of the terminals or body of the component to the sides and depth of the cavity ( $A_0$ ,  $B_0$ ,  $K_0$ ) must be within 0.002" (0.05 mm) minimum and 0.020" (0.50 mm) maximum. The clearance allowed must also prevent rotation of the component within the cavity of not more than 20°
- (2) Tape with components shall pass around radius "R" without damage. The minimum trailer length may require additional length to provide "R" minimum for 12 mm embossed tape for reels with hub diameters approaching N minimum
- (3) This dimension is the flat area from the edge of the sprocket hole to either outward deformation of the carrier tape between the embossed cavities or to the edge of the cavity whichever is less
- (4) This dimension is the flat area from the edge of the carrier tape opposite the sprocket holes to either the outward deformation of the carrier tape between the embossed cavity or to the edge of the cavity whichever is less
- (5) The embossed hole location shall be measured from the sprocket hole controlling the location of the embossment. Dimensions of embossment location shall be applied independent of each other
- (6)  $B_1$  dimension is a reference dimension tape feeder clearance only

| CARRIER TAPE DIMENSIONS in inches [millimeters] |           |                                      |                       |                                |                       |                                |                                |                                                  |
|-------------------------------------------------|-----------|--------------------------------------|-----------------------|--------------------------------|-----------------------|--------------------------------|--------------------------------|--------------------------------------------------|
| CASE CODE                                       | TAPE SIZE | B <sub>1</sub> (MAX.) <sup>(1)</sup> | D <sub>1</sub> (MIN.) | F                              | K <sub>0</sub> (MAX.) | P <sub>1</sub>                 | P <sub>2</sub>                 | W                                                |
| E5                                              | 12 mm     | 0.329 [8.35]                         | 0.059 [1.5]           | 0.217 ± 0.002<br>[5.50 ± 0.05] | 0.071 [1.8]           | 0.315 ± 0.004<br>[8.0 ± 0.10]  | 0.079 ± 0.002<br>[2.00 ± 0.05] | 0.476 ± 0.008<br>[12.1 ± 0.20]                   |
| MM <sup>(2)</sup>                               | 8 mm      | 0.075 [1.91]                         | 0.02 [0.5]            | 0.138 [3.5]                    | 0.043 [1.10]          | 0.157 [4.0]                    | 0.079 ± 0.002<br>[2.00 ± 0.05] | 0.315 [8.0]                                      |
| M1, M9                                          | 12 mm     | 0.32 [8.2]                           | 0.059 [1.5]           | 0.217 ± 0.002<br>[5.5 ± 0.05]  | 0.094 [2.39]          | 0.315 ± 0.04<br>[8.0 ± 1.0]    | 0.079 ± 0.002<br>[2.00 ± 0.05] | 0.472 + 0.012 / - 0.004<br>[12.0 + 0.3 / - 0.10] |
| W9                                              | 8 mm      | 0.126 [3.20]                         | 0.030 [0.75]          | 0.138 [3.5]                    | 0.045 [1.15]          | 0.157 [4.0]                    | 0.079 ± 0.002<br>[2.00 ± 0.05] | 0.315 [8.0]                                      |
| W0                                              | 8 mm      | 0.126 [3.20]                         | 0.030 [0.75]          | 0.138 [3.5]                    | 0.045 [1.15]          | 0.157 [4.0]                    | 0.079 ± 0.002<br>[2.00 ± 0.05] | 0.315 [8.0]                                      |
| A0                                              | 8 mm      | -                                    | 0.02 [0.5]            | 0.138 [3.5]                    | 0.049 [1.25]          | 0.157 [4.0]                    | 0.079 ± 0.002<br>[2.00 ± 0.05] | 0.315 [8.0]                                      |
| BB                                              | 8 mm      | 0.157 [4.0]                          | 0.039 [1.0]           | 0.138 [3.5]                    | 0.087 [2.22]          | 0.157 [4.0]                    | 0.079 ± 0.002<br>[2.00 ± 0.05] | 0.315 [8.0]                                      |
| EE                                              | 12 mm     | 0.32 [8.2]                           | 0.059 [1.5]           | 0.217 ± 0.002<br>[5.5 ± 0.05]  | 0.175 [4.44]          | 0.315 ± 0.04<br>[8.0 ± 1.0]    | 0.079 ± 0.002<br>[2.00 ± 0.05] | 0.472 + 0.012 / - 0.004<br>[12.0 + 0.3 / - 0.10] |
| B2                                              | 8 mm      | 0.157 [4.0]                          | 0.039 [1.0]           | 0.138 [3.5]                    | 0.057 [1.45]          | 0.157 [4.0]                    | 0.079 ± 0.002<br>[2.00 ± 0.05] | 0.315 [8.0]                                      |
| D <sup>(3)</sup>                                | 16 mm     | 0.321 [8.16]                         | 0.059 [1.5]           | 0.295 ± 0.004<br>[7.50 ± 0.1]  | 0.308 [7.83]          | 0.472 ± 0.004<br>[12.00 ± 0.1] | 0.079 ± 0.004<br>[2.00 ± 0.1]  | 0.630 ± 0.012<br>[16.00 ± 0.3]                   |

## Notes

- (1) For reference only  
(2) Standard packaging of MM case is with paper tape. Plastic tape is available per request  
(3) Tape thickness 0.018 [0.45] max.

| PAPER TAPE AND REEL PACKAGING DIMENSIONS in inches [millimeters]                     |           |                                |                                |                             |                              |                              |                               |                               |                                |                              |                                |
|--------------------------------------------------------------------------------------|-----------|--------------------------------|--------------------------------|-----------------------------|------------------------------|------------------------------|-------------------------------|-------------------------------|--------------------------------|------------------------------|--------------------------------|
|  |           |                                |                                |                             |                              |                              |                               |                               |                                |                              |                                |
| CASE SIZE                                                                            | TAPE SIZE | A <sub>0</sub>                 | B <sub>0</sub>                 | D <sub>0</sub>              | P <sub>0</sub>               | P <sub>1</sub>               | P <sub>2</sub>                | E                             | F                              | W                            | T                              |
| MM                                                                                   | 8 mm      | 0.041 ± 0.002<br>[1.05 ± 0.05] | 0.071 ± 0.002<br>[1.8 ± 0.05]  | 0.06 ± 0.004<br>[1.5 ± 0.1] | 0.157 ± 0.004<br>[4.0 ± 0.1] | 0.157 ± 0.004<br>[4.0 ± 0.1] | 0.079 ± 0.002<br>[2.0 ± 0.05] | 0.069 ± 0.004<br>[1.75 ± 0.1] | 0.0138 ± 0.002<br>[3.5 ± 0.05] | 0.315 ± 0.008<br>[8.0 ± 0.2] | 0.037 ± 0.002<br>[0.95 ± 0.05] |
| M0                                                                                   | 8 mm      | 0.049 ± 0.002<br>[1.25 ± 0.05] | 0.081 ± 0.002<br>[2.05 ± 0.05] | 0.06 ± 0.004<br>[1.5 ± 0.1] | 0.157 ± 0.004<br>[4.0 ± 0.1] | 0.157 ± 0.004<br>[4.0 ± 0.1] | 0.079 ± 0.002<br>[2.0 ± 0.05] | 0.069 ± 0.004<br>[1.75 ± 0.1] | 0.0138 ± 0.002<br>[3.5 ± 0.05] | 0.315 ± 0.008<br>[8.0 ± 0.2] | 0.041 ± 0.002<br>[1.05 ± 0.05] |

## Note

- (1) A<sub>0</sub>, B<sub>0</sub> are determined by the maximum dimensions to the ends of the terminals extending from the component body and / or the body dimensions of the component. The clearance between the ends of the terminals or body of the component to the sides and depth of the cavity (A<sub>0</sub>, B<sub>0</sub>) must be within 0.002" (0.05 mm) minimum and 0.020" (0.50 mm) maximum. The clearance allowed must also prevent rotation of the component within the cavity of not more than 20°


**PACKING AND STORAGE**

Polymer capacitors meet moisture sensitivity level rating (MSL) of 3 or 4 as specified in IPC/JEDEC® J-STD-020 and are dry packaged in moisture barrier bags (MBB) per J-STD-033. MSL for each particular family is defined in the datasheet - either in "Features" section or "Standard Ratings" table. Level 3 specifies a floor life (out of bag) of 168 hours and level 4 specifies a floor life of 72 hours at 30 °C maximum and 60 % relative humidity (RH). Unused capacitors should be re-sealed in the MBB with fresh desiccant. A moisture strip (humidity indicator card) is included in the bag to assure dryness. To remove excess moisture, capacitors can be dried at 40 °C (standard "dry box" conditions).

For detailed recommendations please refer to J-STD-033.

**RECOMMENDED REFLOW PROFILES**

Vishay recommends no more than 3 cycles of reflow in accordance with J-STD-020.



| PROFILE FEATURE                                         | SnPb EUTECTIC ASSEMBLY                     | LEAD (Pb)-FREE ASSEMBLY |
|---------------------------------------------------------|--------------------------------------------|-------------------------|
| <b>PREHEAT AND SOAK</b>                                 |                                            |                         |
| Temperature min. ( $T_{Smin.}$ )                        | 100 °C                                     | 150 °C                  |
| Temperature max. ( $T_{Smax.}$ )                        | 150 °C                                     | 200 °C                  |
| Time ( $t_s$ ) from ( $T_{Smin.}$ to $T_{Smax.}$ )      | 60 s to 120 s                              | 60 s to 120 s           |
| <b>RAMP UP</b>                                          |                                            |                         |
| Ramp-up rate ( $T_L$ to $T_p$ )                         | 3 °C/s maximum                             |                         |
| Liquidus temperature ( $T_L$ )                          | 183 °C                                     | 217 °C                  |
| Time ( $t_L$ ) maintained above $T_L$                   | 60 s to 150 s                              |                         |
| Peak package body temperature ( $T_p$ ) max.            | Depends on type and case - see table below |                         |
| Time ( $t_p$ ) within 5 °C of the peak max. temperature | 20 s                                       | 5 s <sup>(1)</sup>      |
| <b>RAMP DOWN</b>                                        |                                            |                         |
| Ramp-down rate ( $T_p$ to $T_L$ )                       | 6 °C/s maximum                             |                         |
| Time from 25 °C to peak temperature                     | 6 min maximum                              | 8 min maximum           |

**Note**

<sup>(1)</sup> For T27, lead (Pb)-free capacitors  $t_p = 30$  s

**PEAK PACKAGE BODY TEMPERATURE ( $T_p$ ) MAXIMUM**

| TYPE  | CASE CODE                 | PEAK PACKAGE BODY TEMPERATURE ( $T_p$ ) MAX. |                         |
|-------|---------------------------|----------------------------------------------|-------------------------|
|       |                           | SnPb EUTECTIC ASSEMBLY                       | LEAD (Pb)-FREE ASSEMBLY |
| T27   | D                         | 220 °C                                       | 245 °C                  |
| T55   | J, P, A, T, B, C, Z, V, D | n/a                                          | 260 °C                  |
| T52   | E5, M1, M9, B2            |                                              | 260 °C                  |
| T58   | MM, M0, W9, W0, A0, BB    |                                              | 260 °C                  |
| T50   | D                         |                                              | 260 °C                  |
| T56   | D                         |                                              | 250 °C                  |
| T59   | EE                        | 220 °C                                       | 250 °C                  |
| T54   | EE, E2, E3, E4, E6        | 220 °C                                       | 250 °C                  |
| 20021 | EE                        | 220 °C                                       | n/a                     |


**Notes**

- T50, T52, T55, T56, and T58 capacitors are process sensitive. PSL classification to JEDEC J-STD-075: R4G
- T54 and T59 capacitors with 100 % tin termination are process sensitive. PSL classification to JEDEC J-STD-075: R6G



## MOLDED CAPACITORS, T50 / T55 / T56 TYPES


### PAD DIMENSIONS in millimeters



| CASE /<br>DIMENSIONS | CAPACITOR SIZE |      | PAD DIMENSIONS |          |          |          |
|----------------------|----------------|------|----------------|----------|----------|----------|
|                      | L              | W    | G (max.)       | Z (min.) | X (min.) | Y (Ref.) |
| J                    | 1.6            | 0.8  | 0.7            | 2.5      | 1.0      | 0.9      |
| P                    | 2.0            | 1.25 | 0.5            | 2.6      | 1.2      | 1.05     |
| A                    | 3.2            | 1.6  | 1.1            | 3.8      | 1.5      | 1.35     |
| T / B                | 3.5            | 2.8  | 1.4            | 4.1      | 2.7      | 1.35     |
| C                    | 5.8            | 3.2  | 2.9            | 6.9      | 2.7      | 2.0      |
| Z / V / D            | 7.3            | 4.3  | 4.1            | 8.2      | 2.9      | 2.05     |

## LEADFRAMELESS MOLDED CAPACITORS T52 / T58


### PAD DIMENSIONS in inches [millimeters]



| FAMILY | CASE CODE | A (NOM.)     | B (MIN.)     | C (NOM.)     | D (MIN.)     |
|--------|-----------|--------------|--------------|--------------|--------------|
| T52    | E5        | 0.094 [2.40] | 0.077 [1.95] | 0.180 [4.57] | 0.333 [8.46] |
|        | M1, M9    | 0.178 [4.52] | 0.098 [2.48] | 0.138 [3.50] | 0.333 [8.46] |
|        | B2        | 0.081 [2.06] | 0.057 [1.44] | 0.070 [1.77] | 0.183 [4.64] |
| T58    | MM        | 0.024 [0.61] | 0.027 [0.70] | 0.025 [0.64] | 0.080 [2.03] |
|        | W0, W9    | 0.035 [0.89] | 0.029 [0.74] | 0.041 [1.05] | 0.099 [2.52] |
|        | A0        | 0.047 [1.19] | 0.042 [1.06] | 0.065 [1.65] | 0.148 [3.76] |
|        | BB        | 0.094 [2.39] | 0.044 [1.11] | 0.072 [1.82] | 0.159 [4.03] |

## LEADFRAMELESS MOLDED CAPACITORS T59 / T54 / 20021


### PAD DIMENSIONS in inches [millimeters]



| FAMILY    | CASE CODE | A (NOM.)     | B (MIN.)     | C (NOM.)     | D (MIN.)     |
|-----------|-----------|--------------|--------------|--------------|--------------|
| T59 / T54 | EE        | 0.209 [5.30] | 0.098 [2.50] | 0.169 [4.30] | 0.366 [9.30] |
| T54       | E2 / E3   | 0.128 [3.24] | 0.120 [3.04] | 0.154 [3.92] | 0.394 [10.0] |
| T54       | E4 / E6   | 0.301 [7.64] | 0.120 [3.04] | 0.154 [3.92] | 0.394 [10.0] |
| 20021     | EE        | 0.209 [5.30] | 0.098 [2.50] | 0.169 [4.30] | 0.366 [9.30] |

## HERMETICALLY SEALED CAPACITOR T27 TYPE

### PAD DIMENSIONS in inches [millimeters]



| CASE CODE | A (MIN.)     | B (NOM.)     | C (NOM.)     | D (NOM.)     |
|-----------|--------------|--------------|--------------|--------------|
| D         | 0.295 [7.50] | 0.138 [3.50] | 0.100 [2.50] | 0.374 [9.50] |

### GUIDE TO APPLICATION

- AC Ripple Current:** the maximum allowable ripple current shall be determined from the formula:

$$I_{RMS} = \sqrt{\frac{P}{R_{ESR}}}$$

where,

P = power dissipation in W at +45 °C as given in the tables in the product datasheets.

R<sub>ESR</sub> = the capacitor equivalent series resistance at the specified frequency.

- AC Ripple Voltage:** the maximum allowable ripple voltage shall be determined from the formula:

$$V_{RMS} = Z \sqrt{\frac{P}{R_{ESR}}}$$

or, from the formula:

$$V_{RMS} = I_{RMS} \times Z$$


where,

P = power dissipation in W at +45 °C as given in the tables in the product datasheets.

R<sub>ESR</sub> = The capacitor equivalent series resistance at the specified frequency.

Z = The capacitor impedance at the specified frequency.

- 2.1 The tantalum capacitors must be used in such a condition that the sum of the working voltage and ripple voltage peak values does not exceed the rated voltage as shown in figure below.



- Temperature Derating:** power dissipation is affected by the heat sinking capability of the mounting surface. If these capacitors are to be operated at temperatures above +45 °C, the permissible ripple current (or voltage) shall be calculated using the derating coefficient as shown in the table below:

| MAXIMUM RIPPLE CURRENT TEMPERATURE DERATING FACTOR |      |
|----------------------------------------------------|------|
| ≤ 45 °C                                            | 1.0  |
| 55 °C                                              | 0.8  |
| 85 °C                                              | 0.6  |
| 105 °C                                             | 0.4  |
| 125 °C                                             | 0.25 |

- Reverse Voltage:** the capacitors are not intended for use with reverse voltage applied. However, they are capable of withstanding momentary reverse voltage peaks, which must not exceed the following values:  
At 25 °C: 10 % of the rated voltage or 1 V, whichever is smaller.  
At 85 °C: 5 % of the rated voltage or 0.5 V, whichever is smaller.  
At 105 °C: 3 % of the rated voltage or 0.3 V, whichever is smaller.

- Mounting Precautions:**

- 5.1 **Soldering:** capacitors can be attached by conventional soldering techniques; vapor phase, convection reflow, infrared reflow, wave soldering, and hot plate methods. The soldering profile charts show recommended time / temperature conditions for soldering. Preheating is recommended. The recommended maximum ramp rate is 3 °C per second. Attachment with a soldering iron is not recommended due to the difficulty of controlling temperature and time at temperature. The soldering iron must never come in contact with the capacitor. For details see [www.vishay.com/doc?40214](http://www.vishay.com/doc?40214).

5.2 **Limit Pressure on Capacitor Installation with Mounter:** pressure must not exceed 4.9 N with a tool end diameter of 1.5 mm when applied to the capacitors using an absorber, centering tweezers, or similar (maximum permitted pressurization time: 5 s). An excessively low absorber setting position would result in not only the application of undue force to the capacitors but capacitor and other component scattering, circuit board wiring breakage, and / or cracking as well, particularly when the capacitors are mounted together with other chips having a height of 1 mm or less.

### 5.3 Flux Selection

5.3.1 Select a flux that contains a minimum of chlorine and amine.

5.3.2 After flux use, the chlorine and amine in the flux remain must be removed.

5.4 **Cleaning After Mounting:** the following solvents are usable when cleaning the capacitors after mounting. Never use a highly active solvent.

- Halogen organic solvent (HCFC225, etc.)
- Alcoholic solvent (IPA, ethanol, etc.)
- Petroleum solvent, alkali saponifying agent, water, etc.

Circuit board cleaning must be conducted at a temperature of not higher than 50 °C and for an immersion time of not longer than 30 minutes. When an ultrasonic cleaning method is used, cleaning must be conducted at a frequency of 48 kHz or lower, at an vibrator output of 0.02 W/cm<sup>3</sup>, at a temperature of not higher than 40 °C, and for a time of 5 minutes or shorter.

#### Notes

- Care must be exercised in cleaning process so that the mounted capacitor will not come into contact with any cleaned object or the like or will not get rubbed by a stiff brush or similar. If such precautions are not taken particularly when the ultrasonic cleaning method is employed, terminal breakage may occur
- When performing ultrasonic cleaning under conditions other than stated above, conduct adequate advance checkout



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

|                                  |                                  |                                  |                                  |                                  |
|----------------------------------|----------------------------------|----------------------------------|----------------------------------|----------------------------------|
| <a href="#">T55A106M004C0200</a> | <a href="#">T55A106M004C0500</a> | <a href="#">T55A106M010C0200</a> | <a href="#">T55A106M010C0500</a> | <a href="#">T55A106M6R3C0200</a> |
| <a href="#">T55A106M6R3C0500</a> | <a href="#">T55A107M6R3C0070</a> | <a href="#">T55A107M6R3C0150</a> | <a href="#">T55A156M004C0200</a> | <a href="#">T55A156M004C0500</a> |
| <a href="#">T55A156M010C0200</a> | <a href="#">T55A156M010C0500</a> | <a href="#">T55A156M6R3C0200</a> | <a href="#">T55A156M6R3C0500</a> | <a href="#">T55A226M004C0200</a> |
| <a href="#">T55A226M004C0500</a> | <a href="#">T55A226M010C0200</a> | <a href="#">T55A226M010C0500</a> | <a href="#">T55A226M6R3C0200</a> | <a href="#">T55A226M6R3C0500</a> |
| <a href="#">T55A336M004C0200</a> | <a href="#">T55A336M004C0500</a> | <a href="#">T55A336M010C0200</a> | <a href="#">T55A336M010C0500</a> | <a href="#">T55A336M6R3C0200</a> |
| <a href="#">T55A336M6R3C0500</a> | <a href="#">T55A475M010C0200</a> | <a href="#">T55A475M010C0500</a> | <a href="#">T55A475M6R3C0500</a> | <a href="#">T55A476M004C0200</a> |
| <a href="#">T55A476M004C0500</a> | <a href="#">T55A476M6R3C0200</a> | <a href="#">T55A476M6R3C0500</a> | <a href="#">T55A685M010C0200</a> | <a href="#">T55A685M010C0500</a> |
| <a href="#">T55A685M6R3C0500</a> | <a href="#">T55A686M004C0200</a> | <a href="#">T55A686M004C0500</a> | <a href="#">T55B107M004C0045</a> | <a href="#">T55B107M004C0070</a> |
| <a href="#">T55B107M6R3C0035</a> | <a href="#">T55B107M6R3C0040</a> | <a href="#">T55B107M6R3C0045</a> | <a href="#">T55B107M6R3C0070</a> | <a href="#">T55B107M6R3C0100</a> |
| <a href="#">T55B157M004C0035</a> | <a href="#">T55B157M004C0070</a> | <a href="#">T55B157M6R3C0035</a> | <a href="#">T55B157M6R3C0040</a> | <a href="#">T55B157M6R3C0070</a> |
| <a href="#">T55B157M6R3C0100</a> | <a href="#">T55B226M004C0200</a> | <a href="#">T55B226M010C0070</a> | <a href="#">T55B226M010C0200</a> | <a href="#">T55B227M004C0035</a> |
| <a href="#">T55B227M004C0070</a> | <a href="#">T55B227M2R5C0030</a> | <a href="#">T55B227M2R5C0035</a> | <a href="#">T55B227M2R5C0070</a> | <a href="#">T55B227M6R3C0070</a> |
| <a href="#">T55B336M004C0200</a> | <a href="#">T55B336M010C0070</a> | <a href="#">T55B336M010C0200</a> | <a href="#">T55B336M6R3C0070</a> | <a href="#">T55B336M6R3C0200</a> |
| <a href="#">T55B337M2R5C0035</a> | <a href="#">T55B337M2R5C0070</a> | <a href="#">T55B476M004C0070</a> | <a href="#">T55B476M004C0150</a> | <a href="#">T55B476M010C0070</a> |
| <a href="#">T55B476M010C0150</a> | <a href="#">T55B476M6R3C0070</a> | <a href="#">T55B476M6R3C0150</a> | <a href="#">T55B686M004C0070</a> | <a href="#">T55B686M004C0150</a> |
| <a href="#">T55B686M6R3C0070</a> | <a href="#">T55B686M6R3C0150</a> | <a href="#">T55J106M004C0500</a> | <a href="#">T55J335M010C0500</a> | <a href="#">T55J335M6R3C0500</a> |
| <a href="#">T55J475M6R3C0500</a> | <a href="#">T55P106M004C0200</a> | <a href="#">T55P106M004C0500</a> | <a href="#">T55P106M6R3C0200</a> | <a href="#">T55P106M6R3C0500</a> |
| <a href="#">T55P156M004C0200</a> | <a href="#">T55P156M004C0500</a> | <a href="#">T55P335M010C0500</a> | <a href="#">T55P335M6R3C0500</a> | <a href="#">T55P475M010C0200</a> |
| <a href="#">T55P475M010C0500</a> | <a href="#">T55P475M6R3C0500</a> | <a href="#">T55P685M6R3C0500</a> | <a href="#">T55T107M004C0070</a> | <a href="#">T55T226M010C0070</a> |
| <a href="#">T55T226M010C0200</a> | <a href="#">T55T336M010C0070</a> | <a href="#">T55T336M010C0200</a> | <a href="#">T55T336M6R3C0070</a> | <a href="#">T55T336M6R3C0200</a> |